

文件名称：锂离子聚合物电芯规格表 Specification for Lithium-ion Polymer Rechargeable Cell						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
1	V2847105P	1950	3.80	2.80	46.80	105.00	7.41	≤60	36.8
2	U284854P	1010	3.85	2.80	48.00	54.00	3.89	≤60	16.0
3	V289791P	3180	3.80	2.80	97.00	91.00	12.08	≤60	53.0
4	V294393P	1500	3.80	2.90	42.80	93.00	5.70	≤60	26.0
5	V296078P	2000	3.80	2.90	60.30	78.00	7.60	≤60	33.0
6	V296473P	1900	3.80	2.90	63.50	73.00	7.22	≤60	32.2
7	V2965108P	2800	3.80	2.90	65.00	108.00	10.64	≤60	45.0
8	V296585P	2400	3.80	2.90	65.30	85.00	9.12	≤60	44.0
9	S297099P	2400	3.70	2.90	70.50	99.50	8.88	≤60	41.4
10	304362P	960	3.70	2.95	43.50	61.30	3.55	≤60	18.0
11	S303540P	370	3.70	3.00	35.00	40.00	1.37	≤150	7.0
12	V304556P	950	3.80	3.00	45.00	56.00	3.61	≤60	16.4
13	LP304556	500	3.20	3.00	45.00	56.00	1.60	≤90	11.0
14	G305762P	1500	3.70	3.00	57.00	61.50	5.55	≤60	25.0
15	V306780P	2370	3.80	3.00	67.00	80.00	9.01	≤60	39.0
16	G306987P	2250	3.70	3.00	69.50	87.00	8.33	≤60	39.0
17	V307886P	3020	3.80	3.00	77.50	85.70	11.48	≤50	45.0
18	V315572P	1800	3.80	3.05	54.80	71.80	6.84	≤60	34.0
19	V306173P	2000	3.80	3.05	60.30	73.00	7.60	≤60	33.0
20	V3078116P	4000	3.80	3.05	78.80	116.50	15.20	≤60	75.5
21	V313996PN	1715	3.80	3.10	38.50	95.50	6.52	≤35	28.6
22	V3149119PN	2750	3.80	3.10	48.50	119.00	10.45	≤35	45.8
23	V315975P	2000	3.80	3.10	59.00	75.00	7.60	≤60	37.7
24	G3161107P	2200	3.70	3.10	61.00	107.00	8.14	≤60	41.5
25	V316586P	2600	3.80	3.10	65.00	85.80	9.88	≤60	43.3
26	G324038P	600	3.70	3.15	39.90	38.00	2.22	≤100	10.5
27	V315970PF	1800	3.80	3.15	59.00	70.00	6.84	≤60	32.0
28	U326688P	3050	3.85	3.15	66.00	88.00	11.74	≤50	44.0
29	V3149109P	2740	3.80	3.17	48.70	109.00	10.41	≤35	52.0
30	V3149109PN	2691	3.82	3.17	48.70	109.00	10.28	≤35	41.0
31	323450P	500	3.70	3.20	34.00	50.00	1.85	≤100	11.0
32	V323893P	1860	3.80	3.20	38.60	93.00	7.07	≤35	28.0
33	V323893PN	1821	3.82	3.20	38.60	93.00	6.96	≤35	28.0
34	V325362P	1600	3.80	3.20	53.00	62.00	6.08	≤60	25.0
35	V326075P	2000	3.80	3.20	59.80	75.20	7.60	≤60	37.7

文件名称: 锂离子聚合物电池规格表 Specification for Lithium-ion Polymer Rechargeable Battery						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
36	V326076P	2200	3.80	3.20	60.00	76.00	8.36	≤60	36.0
37	V326480P	2480	3.80	3.20	63.50	80.00	9.42	≤60	37.0
38	U326688PF	3000	3.85	3.20	66.00	88.00	11.55	≤60	44.0
39	V335876P	2000	3.80	3.25	58.00	75.50	7.60	≤60	33.3
40	V333996P	1920	3.80	3.28	38.50	96.00	7.30	≤35	29.0
41	V3349B9P	2990	3.80	3.28	48.00	118.20	11.36	≤35	44.0
42	V323993P	1960	3.80	3.29	39.00	93.00	7.45	≤50	32.0
43	V3249A9P	2900	3.80	3.29	49.00	109.00	11.02	≤50	44.0
44	V3349119P1	3380	3.80	3.30	49.00	119.00	12.84	≤35	50.0
45	V3252112P	2750	3.80	3.30	51.20	112.00	10.45	≤60	47.4
46	V335465P	1750	3.80	3.30	54.00	65.00	6.65	≤60	33.0
47	V335465P1	1800	3.80	3.30	54.00	65.00	6.84	≤60	34.0
48	U336076P	2750	3.85	3.30	60.00	76.00	10.59	≤60	45.8
49	U336190P	3000	3.85	3.30	61.00	90.00	11.55	≤45	44.0
50	V336576PF	2300	3.80	3.30	65.00	75.50	8.74	≤60	38.3
51	V336584P	2900	3.80	3.30	65.00	84.00	11.02	≤60	48.3
52	V3366128P	4000	3.80	3.30	65.50	128.00	15.20	≤60	64.0
53	V3385103P	4600	3.80	3.30	85.00	103.00	17.48	≤60	76.7
54	V333993P	1975	3.80	3.33	39.00	93.00	7.51	≤35	32.0
55	V3349A9P	3020	3.80	3.35	49.00	109.00	11.48	≤35	44.0
56	V343996PN	1810	3.80	3.40	38.50	95.50	6.88	≤35	30.2
57	V343993P	1960	3.80	3.40	38.60	93.00	7.45	≤35	32.0
58	V343993PN	1960	3.82	3.40	39.00	93.00	7.49	≤35	29.0
59	V3449119PN	2915	3.80	3.40	48.50	119.00	11.08	≤35	48.6
60	V3449109P	2910	3.80	3.40	49.00	108.80	11.06	≤35	45.0
61	V3449109PN	2900	3.82	3.40	49.00	109.00	11.08	≤35	44.0
62	V345881P	2500	3.80	3.40	58.00	80.50	9.50	≤60	41.7
63	V346088P	2700	3.80	3.40	59.30	87.40	10.26	≤60	45.8
64	V346084P	2500	3.80	3.40	60.00	84.00	9.50	≤60	41.6
65	V346579P	2600	3.80	3.40	65.00	79.00	9.88	≤60	43.3
66	V346886P	3000	3.80	3.40	67.80	86.00	11.40	≤60	56.6
67	U356481P	3020	3.85	3.43	63.50	80.30	11.63	≤60	43.0
68	U356283P	3000	3.85	3.45	62.00	83.00	11.55	≤60	44.0
69	V356679P	2860	3.80	3.45	65.50	78.50	10.87	≤60	47.7
70	U356479P	3020	3.85	3.49	63.60	78.60	11.63	≤60	50.3

文件名称: 锂离子聚合物电池规格表 Specification for Lithium-ion Polymer Rechargeable Battery						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
71	V355662P	1750	3.80	3.50	55.50	62.00	6.65	≤60	29.0
72	V355875P	2250	3.80	3.50	58.00	75.00	8.55	≤60	37.0
73	G356070P	2000	3.70	3.50	60.00	69.70	7.40	≤60	37.7
74	V356073P	2250	3.80	3.50	60.00	72.80	8.55	≤60	37.5
75	U356379P	2920	3.85	3.50	62.80	78.30	11.24	≤50	48.7
76	U356581P	3000	3.85	3.50	65.00	81.00	11.55	≤60	44.0
77	U356583P	3220	3.85	3.50	65.00	83.00	12.40	≤60	45.0
78	U356585P	3300	3.85	3.50	65.00	85.00	12.71	≤60	47.0
79	U356588P	3400	3.85	3.50	65.00	88.00	13.09	≤60	50.0
80	V356771P	2500	3.80	3.50	67.00	71.00	9.50	≤60	41.0
81	V355272P	2000	3.80	3.55	52.00	71.80	7.60	≤60	33.0
82	U366474P	2850	3.85	3.55	63.92	73.88	10.97	≤60	41.0
83	V366583P	3000	3.80	3.55	64.80	82.60	11.40	≤60	50.0
84	V366586P	3000	3.80	3.55	65.00	85.80	11.40	≤60	50.0
85	G368092P	3800	3.70	3.55	80.00	91.50	14.06	≤60	71.7
86	363031P	270	3.70	3.60	30.50	31.00	1.00	≤150	5.1
87	V3640107PF	2200	3.80	3.60	40.00	107.00	8.36	≤60	36.0
88	V355274P	2000	3.80	3.60	52.00	73.10	7.60	≤60	34.5
89	V365467P	1900	3.80	3.60	53.50	67.30	7.22	≤60	35.8
90	U365576P	2500	3.85	3.60	55.00	76.00	9.63	≤60	36.5
91	V365799P	3000	3.80	3.60	56.30	98.70	11.40	≤60	56.6
92	V365866P	2200	3.80	3.60	58.00	66.00	8.36	≤60	36.7
93	U366074P	2480	3.85	3.60	60.00	74.00	9.55	≤60	41.0
94	V366174P	2600	3.80	3.60	61.00	74.00	9.88	≤60	43.3
95	U366478P	3050	3.85	3.60	63.50	77.40	11.74	≤45	44.0
96	V366580P	2800	3.80	3.60	65.00	80.00	10.64	≤60	46.5
97	V366678P	2800	3.80	3.60	66.20	78.00	10.64	≤60	45.2
98	V366782P	2950	3.80	3.60	67.00	82.00	11.21	≤60	46.0
99	V365276P	2260	3.80	3.63	52.00	75.50	8.59	≤60	34.0
100	U356479PF	2950	3.85	3.63	64.00	79.00	11.36	≤60	44.0
101	G365063P	1500	3.70	3.65	50.00	63.00	5.55	≤60	24.0
102	U356585PF	3300	3.85	3.65	65.00	85.00	12.71	≤60	48.0
103	V363390P	1700	3.80	3.68	32.50	90.30	6.46	≤35	25.0
104	V365493P	3000	3.80	3.70	54.00	93.00	11.40	≤50	50.0
105	V375585P	2500	3.80	3.70	55.00	85.00	9.50	≤60	38.0

文件名称: 锂离子聚合物电池规格表 Specification for Lithium-ion Polymer Rechargeable Battery						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
106	V375990P	3200	3.80	3.70	59.00	90.00	12.16	≤60	47.0
107	V376073P	2500	3.80	3.70	60.00	72.55	9.50	≤60	41.7
108	U376077P	3000	3.85	3.70	60.00	77.00	11.55	≤60	43.0
109	U376180P	3020	3.85	3.70	60.30	80.00	11.63	≤45	45.0
110	V376173P	2500	3.80	3.70	61.00	73.10	9.50	≤60	42.0
111	V376383PF	3000	3.80	3.70	62.80	83.00	11.40	≤60	56.5
112	V376383P1	3000	3.80	3.70	63.00	83.00	11.40	≤60	51.5
113	U376480P	3270	3.85	3.70	63.60	80.00	12.59	≤50	47.0
114	U376479P	3100	3.85	3.70	64.00	79.00	11.94	≤60	46.0
115	U376585P	3240	3.85	3.70	65.00	84.50	12.47	≤40	50.0
116	V376586P	3400	3.80	3.70	65.00	86.00	12.92	≤60	50.0
117	U376880P	3320	3.85	3.70	67.10	79.50	12.78	≤50	55.4
118	V385664P	2000	3.80	3.75	56.00	63.80	7.60	≤60	37.7
119	V385799P	3000	3.80	3.75	56.30	98.70	11.40	≤60	56.6
120	U386159P	2150	3.85	3.75	61.00	58.10	8.28	≤60	35.8
121	V386183P	3000	3.80	3.75	61.00	82.80	11.40	≤60	45.0
122	V386376P1	2800	3.80	3.75	62.50	76.00	10.64	≤60	42.0
123	V386495P	3700	3.80	3.75	64.00	95.00	14.06	≤60	61.6
124	V3867102P	4000	3.80	3.75	67.00	101.80	15.20	≤60	65.6
125	S3944102P	2270	3.70	3.78	44.00	102.00	8.40	≤60	44.5
126	V376478P	3020	3.80	3.78	63.90	76.80	11.48	≤60	50.3
127	G383181P	1080	3.70	3.80	31.00	80.50	4.00	≤60	19.0
128	383562PN	830	3.70	3.80	35.00	60.50	3.07	≤60	16.0
129	V3842105P	2470	3.80	3.80	41.30	105.00	9.39	≤60	41.1
130	V385468P	2100	3.80	3.80	54.00	68.00	7.98	≤60	35.0
131	V385669P	2320	3.80	3.80	56.00	68.50	8.82	≤60	35.0
132	U385763P	2250	3.85	3.80	56.80	62.20	8.66	≤60	37.5
133	U385769P	2500	3.85	3.80	56.80	68.20	9.63	≤60	41.7
134	V386075P	2600	3.80	3.80	59.80	75.20	9.88	≤60	45.0
135	U386278P	2920	3.85	3.80	62.00	77.40	11.24	≤60	48.7
136	U386283P	3200	3.85	3.80	62.00	83.00	12.32	≤60	46.0
137	U386283PF	3200	3.85	3.80	62.00	83.00	12.32	≤60	46.0
138	U386587P	3650	3.85	3.80	64.80	86.50	14.05	≤40	55.0
139	V386584P	3200	3.80	3.80	65.00	83.50	12.16	≤60	53.3
140	U386587PF	3400	3.85	3.80	65.00	87.00	13.09	≤60	50.0

文件名称: 锂离子聚合物电池规格表 Specification for Lithium-ion Polymer Rechargeable Battery						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
141	U386784P	3420	3.85	3.80	66.20	84.00	13.17	≤50	57.0
142	U396067P	2500	3.85	3.85	59.50	66.20	9.63	≤60	41.7
143	U386278PF	2800	3.85	3.85	62.00	77.40	10.78	≤60	41.0
144	U396380P	3470	3.85	3.85	62.80	80.20	13.36	≤60	50.0
145	U396587P	3730	3.85	3.86	64.95	86.80	14.36	≤45	58.0
146	S393547P	700	3.70	3.88	34.80	46.40	2.59	≤60	13.2
147	V395066P	1970	3.80	3.90	49.20	65.80	7.49	≤60	29.0
148	V395585P	3000	3.80	3.90	55.00	85.00	11.40	≤60	45.0
149	V395689P	3000	3.80	3.90	56.00	88.30	11.40	≤60	50.0
150	U395776P	2800	3.85	3.90	57.00	76.00	10.78	≤45	41.0
151	U395872P	2800	3.85	3.90	58.00	72.00	10.78	≤60	40.0
152	U395977P	2950	3.85	3.90	59.00	77.00	11.36	≤60	42.5
153	V396070P	2500	3.80	3.90	60.00	70.00	9.50	≤60	41.0
154	U396180P	2950	3.85	3.90	60.50	80.00	11.36	≤50	49.2
155	U396178P	3100	3.85	3.90	61.00	77.80	11.94	≤40	46.0
156	U396278P	3120	3.85	3.90	61.20	77.70	12.01	≤60	48.0
157	U396587PN	3700	3.85	3.90	65.00	87.00	14.25	≤60	53.0
158	V396588P	3400	3.80	3.90	65.00	88.00	12.92	≤60	56.0
159	V396588P1	3500	3.80	3.90	65.00	88.00	13.30	≤60	55.0
160	V397091P	4150	3.80	3.90	70.00	91.00	15.77	≤50	61.0
161	V397091PL	4050	3.80	3.90	70.00	91.00	15.39	≤50	59.0
162	U396272P	3030	3.85	3.93	61.90	72.00	11.67	≤45	41.0
163	V405980P	3050	3.80	3.95	59.00	80.00	11.59	≤60	50.8
164	U406072P	2820	3.85	3.95	60.00	71.50	10.86	≤60	47.0
165	U396377PF	3300	3.85	3.95	63.00	77.00	12.71	≤60	47.0
166	U376480PF	3300	3.85	3.95	64.00	80.00	12.71	≤60	48.0
167	U396587PF	3700	3.85	3.95	65.00	87.00	14.25	≤60	54.0
168	U396587PL	3650	3.85	3.95	65.00	87.00	14.05	≤60	54.0
169	V406588P	3450	3.80	3.95	65.00	88.00	13.11	≤60	52.3
170	G402025P	165	3.70	4.00	20.00	25.50	0.61	≤185	4.0
171	V403264P	1130	3.80	4.00	31.50	64.00	4.29	≤60	17.5
172	V403862P	1450	3.80	4.00	37.50	61.50	5.51	≤35	21.5
173	G404047P	900	3.70	4.00	39.30	46.20	3.33	≤60	15.0
174	G404272P	1450	3.70	4.00	42.00	71.50	5.37	≤60	26.0
175	V4045100P	2942	3.80	4.00	44.50	100.00	11.18	≤35	43.0

文件名称: 锂离子聚合物电池规格表 Specification for Lithium-ion Polymer Rechargeable Battery						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
176	V405472P	2500	3.80	4.00	54.00	72.00	9.50	≤60	41.7
177	V405480P	2500	3.80	4.00	54.00	79.50	9.50	≤60	41.0
178	V405782P	3000	3.80	4.00	57.00	82.00	11.40	≤60	45.0
179	V405869P	2600	3.80	4.00	57.50	69.00	9.88	≤60	44.8
180	U395976PF	2900	3.85	4.00	59.00	76.00	11.17	≤60	42.0
181	U405980P	3000	3.85	4.00	59.00	80.00	11.55	≤60	44.0
182	V406078P	2950	3.80	4.00	60.00	78.00	11.21	≤60	48.0
183	V406175P	2800	3.80	4.00	60.20	74.50	10.64	≤60	46.0
184	U396178PF	3100	3.85	4.00	61.00	78.00	11.94	≤60	45.0
185	U406272P	3050	3.85	4.00	61.40	71.20	11.74	≤45	44.0
186	U406367P	2950	3.85	4.00	62.80	66.70	11.36	≤60	41.5
187	V406373P	3000	3.80	4.00	63.00	73.00	11.40	≤60	44.0
188	U406696P	4000	3.85	4.00	66.00	96.00	15.40	≤60	67.4
189	V4066125P	5000	3.80	4.00	66.00	125.00	19.00	≤60	84.2
190	U406781P	3900	3.85	4.00	67.00	81.00	15.02	≤60	54.0
191	U395981PF	3200	3.85	4.03	59.00	81.00	12.32	≤60	46.0
192	G4148104P	3000	3.70	4.05	48.00	104.00	11.10	≤60	48.0
193	V405777P	2900	3.80	4.05	57.00	77.00	11.02	≤60	48.3
194	G413655P	1100	3.70	4.10	36.00	55.00	4.07	≤60	18.0
195	V415383P	3000	3.80	4.10	53.00	83.00	11.40	≤60	45.0
196	V416089P	3500	3.80	4.10	60.00	88.65	13.30	≤60	58.3
197	V416283P	3200	3.80	4.10	62.00	83.00	12.16	≤60	53.0
198	V416398P	4000	3.80	4.10	62.40	98.00	15.20	≤60	66.7
199	U416381P	3550	3.85	4.10	62.90	80.20	13.67	≤45	52.0
200	U416484P	3600	3.85	4.10	63.50	84.50	13.86	≤60	52.0
201	V416589P	3770	3.80	4.10	65.00	89.00	14.33	≤50	58.0
202	V416671P	2920	3.80	4.10	65.50	72.00	11.10	≤60	55.1
203	V416663P	2750	3.80	4.10	66.00	63.00	10.45	≤60	42.0
204	U416686P	3900	3.85	4.10	66.00	86.00	15.02	≤40	58.0
205	V416867P	3000	3.80	4.10	67.80	67.00	11.40	≤60	44.0
206	U406578PF	3400	3.85	4.12	65.00	78.00	13.09	≤60	50.0
207	U406578PL	3350	3.85	4.12	65.00	78.00	12.90	≤60	49.0
208	V4267102P	4300	3.80	4.15	67.00	101.80	16.34	≤60	71.7
209	G423540P	600	3.70	4.20	34.70	40.00	2.22	≤90	11.0
210	U425596P	3520	3.85	4.20	55.00	96.00	13.55	≤60	58.7

文件名称: 锂离子聚合物电池规格表 Specification for Lithium-ion Polymer Rechargeable Battery						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
211	V425774P	2800	3.80	4.20	57.00	74.00	10.64	≤60	46.0
212	U425776PF	3000	3.85	4.20	57.00	76.00	11.55	≤60	44.0
213	U425777PF	3050	3.85	4.20	57.00	77.00	11.74	≤60	44.0
214	U425868P	2800	3.85	4.20	58.00	68.00	10.78	≤60	39.0
215	U425869P	2930	3.85	4.20	58.00	68.80	11.28	≤40	40.5
216	V426077P	3050	3.80	4.20	59.50	77.00	11.59	≤60	51.0
217	U406178PF	3300	3.85	4.20	61.00	78.00	12.71	≤60	49.0
218	U426484P	3550	3.85	4.20	63.50	84.50	13.67	≤60	52.0
219	U436268P	3000	3.85	4.22	61.50	67.50	11.55	≤60	42.0
220	433049PH	500	3.70	4.25	29.50	48.50	1.85	≤120	10.0
221	V436075P	3000	3.80	4.25	60.00	74.80	11.40	≤60	56.6
222	U4364103P	4900	3.85	4.25	64.00	103.00	18.87	≤40	71.0
223	V433457P	1315	3.80	4.30	34.30	57.50	5.00	≤48	20.0
224	V433857P	1485	3.80	4.30	38.30	57.50	5.64	≤48	22.0
225	V434985P	2800	3.80	4.30	49.00	85.00	10.64	≤60	46.7
226	V435675P	2800	3.80	4.30	56.00	75.00	10.64	≤60	46.7
227	U436089P	4000	3.85	4.30	60.00	89.00	15.40	≤60	56.0
228	V426175P	3060	3.80	4.30	61.00	75.00	11.63	≤40	51.0
229	U436191P	4000	3.85	4.30	61.00	90.50	15.40	≤60	57.0
230	V436472P	3050	3.80	4.30	63.30	71.80	11.59	≤60	48.0
231	U436483PN	3820	3.85	4.30	63.50	83.00	14.71	≤40	58.0
232	V436486P	3700	3.80	4.30	64.00	86.00	14.06	≤60	60.0
233	V436780P	3700	3.80	4.30	67.00	80.00	14.06	≤60	57.0
234	V437091P	4000	3.80	4.30	69.50	91.00	15.20	≤50	61.0
235	V437089P	4000	3.80	4.30	70.00	88.50	15.20	≤50	61.0
236	V435964P	2470	3.80	4.35	58.30	63.15	9.39	≤45	41.0
237	U446579P	3900	3.85	4.35	65.00	79.00	15.02	≤60	57.0
238	V443588PN	2120	3.80	4.40	35.00	87.50	8.06	≤60	36.2
239	V443588P1	2120	3.80	4.40	35.10	87.50	8.06	≤60	36.2
240	G445457P	1900	3.70	4.40	54.00	57.50	7.03	≤60	30.0
241	V445457P	2020	3.80	4.40	54.00	57.50	7.68	≤60	33.0
242	U445868P	2900	3.85	4.40	57.80	68.00	11.17	≤40	44.0
243	U4563102P	5000	3.85	4.45	63.00	101.50	19.25	≤50	72.0
244	G452533P	320	3.70	4.50	25.00	33.00	1.18	≤80	7.0
245	S453336P	500	3.70	4.50	32.60	36.00	1.85	≤150	10.0

文件名称: 锂离子聚合物电池规格表 Specification for Lithium-ion Polymer Rechargeable Battery						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
246	C443441PV	630	3.70	4.50	34.50	41.50	2.33	≤70	11.9
247	453450P	800	3.70	4.50	34.50	50.50	2.96	≤80	15.1
248	S463662P	1100	3.70	4.50	35.00	58.50	4.07	≤80	22.0
249	S454061P	1520	3.70	4.50	39.80	60.50	5.62	≤60	24.0
250	U454661P	1850	3.85	4.50	45.50	60.50	7.12	≤60	28.0
251	V455166P	2000	3.80	4.50	51.00	66.00	7.60	≤60	32.5
252	U455369P	2820	3.85	4.50	52.90	69.00	10.86	≤60	53.2
253	V455466P	2500	3.80	4.50	54.00	65.50	9.50	≤60	47.2
254	V455870P	3000	3.80	4.50	58.00	70.00	11.40	≤60	50.0
255	U455872P	3200	3.85	4.50	58.00	72.00	12.32	≤60	47.0
256	V455993P	4000	3.80	4.50	58.50	92.50	15.20	≤60	62.0
257	V466071P	3020	3.80	4.55	60.00	71.00	11.48	≤40	50.0
258	U466379P	3900	3.85	4.55	62.93	79.28	15.02	30±8	57.0
259	HU466379P	4020	3.86	4.55	62.93	79.28	15.52	30±8	57.0
260	V466781P	4000	3.80	4.57	67.00	81.00	15.20	≤60	66.7
261	V465565P	2400	3.80	4.58	55.00	64.50	9.12	≤60	40.0
262	G464085P	2020	3.70	4.60	39.50	84.50	7.47	≤60	33.0
263	U464854P	1950	3.85	4.60	48.00	54.00	7.51	≤60	32.5
264	V465476P	3020	3.80	4.60	53.50	76.00	11.48	≤45	44.0
265	G465580P	2200	3.70	4.60	54.70	80.00	8.14	≤45	39.0
266	U465560P	2510	3.85	4.60	55.00	60.00	9.66	≤60	36.0
267	U465871P	3130	3.85	4.60	58.00	71.00	12.05	≤40	47.0
268	U466584P	4030	3.85	4.60	64.20	83.50	15.52	≤60	59.0
269	S473661P	1100	3.70	4.62	35.15	61.00	4.07	≤80	20.7
270	V476380P	3920	3.80	4.67	63.00	80.00	14.90	≤60	65.3
271	G474957P	1900	3.70	4.70	49.00	57.00	7.03	≤60	30.0
272	V474957P	2000	3.80	4.70	49.00	57.00	7.60	≤60	35.0
273	V475474P	3000	3.80	4.70	53.50	73.50	11.40	≤45	50.0
274	G475580P	2700	3.70	4.70	54.70	80.00	9.99	≤60	44.0
275	V475683P	3600	3.80	4.70	56.00	83.00	13.68	≤60	60.0
276	U476079P	3600	3.85	4.70	60.00	79.00	13.86	≤60	53.0
277	V466086P	4000	3.80	4.70	60.00	86.00	15.20	≤50	66.7
278	U476280P	4000	3.85	4.70	62.00	80.00	15.40	≤60	62.0
279	V476393P	4500	3.80	4.70	63.00	93.00	17.10	≤60	67.0
280	U476899P	5530	3.85	4.70	67.50	99.00	21.29	≤60	79.0

文件名称: 锂离子聚合物电池规格表 Specification for Lithium-ion Polymer Rechargeable Battery						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
281	U486279P	4020	3.85	4.73	61.80	79.00	15.48	≤45	56.0
282	V485886P	4000	3.80	4.75	58.00	85.70	15.20	≤50	60.0
283	V484969P	2500	3.80	4.80	49.00	68.10	9.50	≤60	41.6
284	U4858102P	5000	3.85	4.80	58.00	102.00	19.25	≤60	72.0
285	V486471P	3420	3.80	4.80	63.50	71.00	13.00	≤60	57.0
286	V495472P	3000	3.80	4.85	54.00	72.00	11.40	≤60	50.0
287	U4959103P	5000	3.85	4.85	58.50	102.50	19.25	≤60	83.3
288	V496180P	3900	3.80	4.85	60.40	79.10	14.82	≤60	65.0
289	U493177P	1800	3.85	4.90	30.50	77.00	6.93	≤40	26.5
290	G496083P	3500	3.70	4.90	59.90	82.50	12.95	≤60	57.0
291	V496594P	5000	3.80	4.90	65.00	94.00	19.00	≤60	76.0
292	V505075P	3000	3.80	4.95	50.00	74.50	11.40	≤60	50.0
293	G502648P	600	3.70	5.00	26.00	48.00	2.22	≤80	11.0
294	U503988P	3000	3.85	5.00	39.00	87.30	11.55	≤50	43.0
295	V505895P	4000	3.80	5.00	57.40	94.50	15.20	≤60	66.7
296	U506586P	4920	3.85	5.00	64.90	85.29	18.94	≤35	68.0
297	G5067102P	5000	3.70	5.00	67.00	102.00	18.50	≤60	81.0
298	U514397P	3600	3.85	5.10	42.30	96.10	13.86	≤40	53.0
299	U515280P	3700	3.85	5.10	52.00	80.00	14.25	≤60	53.0
300	V515865P	2950	3.80	5.10	57.40	64.85	11.21	≤60	49.2
301	V516083P	4000	3.80	5.10	59.90	82.50	15.20	≤60	60.0
302	V516280PN	4000	3.80	5.10	61.90	79.50	15.20	≤60	66.7
303	V516280P	4000	3.80	5.10	62.00	80.00	15.20	≤60	66.0
304	U5198116P	10000	3.85	5.10	97.50	115.50	38.50	≤60	144.0
305	V525885P	4000	3.80	5.15	58.00	84.50	15.20	≤60	65.0
306	523450PV	950	3.70	5.20	34.50	50.50	3.52	≤60	16.5
307	503562PV	1250	3.70	5.20	35.50	62.50	4.63	≤60	23.5
308	503759PV	1240	3.70	5.20	37.50	59.50	4.59	≤60	25.2
309	524047PH	900	3.70	5.20	39.50	46.20	3.33	≤90	15.8
310	U5247102P	4000	3.85	5.20	46.40	101.20	15.40	≤60	66.0
311	G5251135P	4600	3.70	5.20	50.50	135.00	17.02	≤50	76.5
312	V525979P	4000	3.80	5.20	59.00	78.50	15.20	≤60	66.0
313	U5398116P	10000	3.85	5.25	97.50	116.00	38.50	≤10	144.0
314	G533975P	2000	3.70	5.30	39.00	75.00	7.40	≤60	33.0
315	U536174P	4000	3.85	5.30	61.00	73.50	15.40	≤60	57.0

文件名称: 锂离子聚合物电池规格表 Specification for Lithium-ion Polymer Rechargeable Battery						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
316	V536278P	4000	3.80	5.30	62.00	78.00	15.20	≤60	60.0
317	V536596P	5500	3.80	5.30	64.50	95.30	20.90	≤60	91.7
318	V545166P	2500	3.80	5.37	50.50	66.00	9.50	≤60	42.0
319	G543149P	960	3.70	5.40	31.00	49.00	3.55	≤150	18.1
320	V544380P	3030	3.80	5.40	43.00	80.00	11.51	≤60	46.0
321	V546089P	4700	3.80	5.40	60.00	89.00	17.86	≤60	78.3
322	H546381P	4900	3.86	5.40	63.00	81.00	18.91	≤60	68.0
323	G551843P	450	3.70	5.50	18.00	43.00	1.67	≤100	8.0
324	S553136P	625	3.70	5.50	31.00	36.00	2.31	≤60	10.5
325	V553964P	2180	3.80	5.50	38.70	63.40	8.28	≤60	32.0
326	U554966PF	2960	3.85	5.50	49.00	65.50	11.40	≤60	42.0
327	U555067PF	3060	3.85	5.50	49.50	67.00	11.78	≤60	43.0
328	U5564100P	6070	3.85	5.50	64.00	100.00	23.37	≤35	88.0
329	G563448P	1200	3.70	5.60	34.00	48.00	4.44	≤90	20.0
330	V565376P	3500	3.80	5.60	53.00	76.00	13.30	≤60	58.0
331	U566296P	6000	3.85	5.60	62.00	96.00	23.10	≤60	83.0
332	U566479P	5000	3.85	5.60	63.80	79.00	19.25	≤60	69.0
333	V566699P	5900	3.80	5.60	66.00	99.00	22.42	≤60	98.0
334	G5698116P	10000	3.70	5.60	97.50	115.50	37.00	≤60	156.0
335	LP5565134	3900	3.20	5.62	65.00	134.00	12.48	≤50	87.0
336	G573440P	800	3.70	5.70	33.50	40.00	2.96	≤90	14.0
337	G574152P	1500	3.70	5.70	40.50	51.50	5.55	≤60	25.0
338	V575868P	3500	3.80	5.70	58.00	68.00	13.30	≤60	58.3
339	V5758102P	5000	3.80	5.70	58.00	102.00	19.00	≤55	75.0
340	G583171P	1810	3.70	5.75	31.00	71.00	6.70	≤60	30.0
341	G582648PF	850	3.70	5.80	26.00	48.00	3.15	≤90	15.0
342	G583565P	1720	3.70	5.80	35.00	65.00	6.36	≤60	30.0
343	V585497P	5000	3.80	5.80	54.00	96.50	19.00	≤60	83.3
344	G5854105P	4500	3.70	5.80	54.00	105.00	16.65	≤60	74.0
345	U585973P	4400	3.85	5.80	59.15	73.00	16.94	≤60	61.0
346	V596089P	5020	3.80	5.85	60.00	89.00	19.08	≤60	75.0
347	V596080P	4200	3.80	5.90	60.00	80.00	15.96	≤60	70.0
348	V595885P	4000	3.80	5.95	58.00	85.00	15.20	≤40	60.0
349	G603448P	1300	3.70	6.00	34.00	48.00	4.81	≤60	22.0
350	G603863P	2040	3.70	6.00	38.00	62.50	7.55	≤60	33.0

文件名称: 锂离子聚合物电池规格表 Specification for Lithium-ion Polymer Rechargeable Battery						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
351	G603990P	2720	3.70	6.00	39.00	90.00	10.06	≤60	48.0
352	V604960P	2400	3.80	6.00	49.00	60.00	9.12	≤60	40.0
353	G6053119P	5500	3.70	6.00	53.00	119.00	20.35	≤60	91.0
354	G6060130P	7000	3.70	6.00	60.00	130.00	25.90	≤60	111.0
355	U607093P	5900	3.85	6.00	70.00	93.00	22.72	≤50	88.0
356	V614272P	3000	3.80	6.10	42.00	72.00	11.40	≤60	50.0
357	V615469P	3600	3.80	6.10	53.20	68.30	13.68	≤60	53.0
358	V616087P	5030	3.80	6.10	60.00	87.00	19.11	≤45	76.0
359	U616077P	5000	3.85	6.10	60.20	77.00	19.25	≤60	68.0
360	V625477P	4000	3.80	6.15	54.00	77.00	15.20	≤60	66.7
361	V622929P	560	3.80	6.20	29.00	29.00	2.13	≤90	9.0
362	643141PH	680	3.70	6.20	30.90	41.00	2.52	≤120	14.0
363	U6251107P	5000	3.85	6.20	50.20	106.20	19.25	≤60	84.6
364	V625783P	4700	3.80	6.20	57.00	83.00	17.86	≤60	71.0
365	V625885P	5000	3.80	6.20	58.00	85.00	19.00	≤40	72.0
366	V626090P	5000	3.80	6.20	60.00	90.00	19.00	≤60	75.0
367	G6060100P	5000	3.70	6.20	60.00	100.00	18.50	≤55	85.0
368	G633227P	500	3.70	6.30	32.40	27.50	1.85	≤80	9.5
369	U633440P	1140	3.85	6.30	33.50	40.00	4.39	≤80	17.0
370	V635061P	3000	3.80	6.30	50.00	61.00	11.40	≤60	43.0
371	V635979P	4700	3.80	6.30	59.00	79.00	17.86	≤60	68.5
372	V636468P	4000	3.80	6.30	63.50	68.00	15.20	≤60	66.7
373	644341PH	1000	3.70	6.40	43.00	41.00	3.70	≤90	20.0
374	V6458102P	6000	3.70	6.40	58.00	102.00	22.20	≤40	88.0
375	G655236P	1500	3.70	6.50	51.20	35.80	5.55	≤60	25.0
376	V666394P	6300	3.80	6.60	63.00	94.00	23.94	≤60	93.0
377	S673041P	1000	3.70	6.70	30.30	41.50	3.70	≤70	18.8
378	V676069P	4400	3.80	6.70	60.00	69.00	16.72	≤60	73.3
379	G683141P	800	3.70	6.80	30.40	41.00	2.96	≤90	15.0
380	G683440P	1200	3.70	6.80	34.00	39.50	4.44	≤70	19.0
381	V683840P	1500	3.80	6.80	37.50	40.00	5.70	≤60	23.0
382	G685498P	5000	3.70	6.80	54.00	98.00	18.50	≤60	89.0
383	V685498P	5000	3.80	6.80	54.00	98.00	19.00	≤60	89.0
384	V685780P	5000	3.80	6.80	57.00	80.00	19.00	≤60	73.0
385	G702628P	500	3.70	7.00	25.50	27.60	1.85	≤150	9.0

文件名称: 锂离子聚合物电池规格表 Specification for Lithium-ion Polymer Rechargeable Battery						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
386	G703590P	3000	3.70	7.00	34.60	90.00	11.10	≤60	48.0
387	G704762P	2750	3.70	7.00	47.00	62.00	10.18	≤45	46.0
388	G705085P	3800	3.70	7.00	50.00	85.00	14.06	≤45	64.0
389	V705566P	3950	3.80	7.00	55.00	66.00	15.01	≤60	65.0
390	V705693P	5000	3.80	7.00	56.00	93.00	19.00	≤60	77.0
391	V706098P	6000	3.80	7.00	60.00	98.00	22.80	≤60	91.0
392	G713860P	2000	3.70	7.10	37.50	59.50	7.40	≤60	34.0
393	V716077P	5000	3.80	7.10	60.00	77.00	19.00	≤60	78.0
394	U724270P	3100	3.85	7.20	42.00	70.00	11.94	≤60	45.0
395	G733234P	850	3.70	7.30	31.50	34.00	3.15	≤100	16.0
396	G733432P	700	3.70	7.30	34.10	32.30	2.59	≤100	13.5
397	V734674P	3600	3.80	7.30	46.00	74.00	13.68	≤60	56.0
398	H735590P	6710	3.88	7.30	55.00	90.00	26.03	≤60	88.0
399	V735874P	5000	3.80	7.30	57.50	73.50	19.00	≤60	73.0
400	V743759P	2500	3.80	7.35	36.50	58.50	9.50	≤60	37.0
401	V743862P	2400	3.80	7.40	37.50	62.00	9.12	≤50	37.0
402	G746072P	4750	3.70	7.40	59.80	72.00	17.58	≤45	75.0
403	7546100P	3700	3.70	7.50	46.50	100.50	13.69	≤40	69.8
404	H755590P	6880	3.88	7.50	55.00	90.00	26.69	≤60	93.0
405	V755872P	5000	3.80	7.50	58.00	72.00	19.00	≤60	74.0
406	V756161P	4200	3.80	7.50	60.50	60.50	15.96	≤60	63.0
407	G7647145P	8000	3.70	7.60	47.00	145.00	29.60	≤40	125.0
408	S804060P	2000	3.70	7.80	39.80	60.00	7.40	≤80	38.0
409	V793052P	1670	3.80	7.90	30.00	52.00	6.35	≤60	25.0
410	G795260P	3375	3.70	7.90	51.10	59.50	12.49	≤60	54.0
411	G7960130P	9000	3.70	7.90	60.00	130.00	33.30	≤40	141.0
412	V804770P	4000	3.80	8.00	47.00	70.00	15.20	≤60	61.0
413	V8050120P	7800	3.80	8.00	50.00	120.50	29.64	≤60	115.0
414	U812743P	1270	3.85	8.10	27.00	42.40	4.89	≤60	19.0
415	G813462P	2500	3.65	8.10	33.60	61.30	9.13	≤15	34.5
416	V823558P	2000	3.80	8.20	35.00	58.00	7.60	≤60	33.3
417	V8237130P	5510	3.70	8.20	37.00	129.50	20.39	≤60	82.0
418	G824670P	3600	3.70	8.20	46.00	70.50	13.32	≤8	54.5
419	G833655P	2100	3.70	8.30	36.00	55.00	7.77	≤60	34.0
420	G843450P	1800	3.70	8.40	34.20	48.00	6.66	≤60	29.5

文件名称: 锂离子聚合物电池规格表 Specification for Lithium-ion Polymer Rechargeable Battery						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
421	S844474P	3700	3.70	8.40	44.00	74.00	13.69	≤60	62.4
422	G8450132P	7200	3.70	8.40	50.00	132.00	26.64	≤60	115.0
423	V853332P	1000	3.80	8.50	33.00	32.00	3.80	≤80	17.0
424	G854676P	4000	3.70	8.50	46.00	76.00	14.80	≤60	65.0
425	V805165P	4000	3.80	8.50	51.00	64.30	15.20	≤60	74.5
426	G855560P	3600	3.70	8.50	55.00	60.00	13.32	≤45	60.0
427	G863764P	2760	3.70	8.60	36.90	63.90	10.21	≤50	45.0
428	G875870P	4520	3.70	8.65	57.40	69.50	16.72	≤50	76.0
429	G874575P	3600	3.70	8.70	44.80	75.00	13.32	≤8	55.0
430	G904159P	2500	3.70	9.00	41.00	58.20	9.25	≤40	43.0
431	U905052P	3620	3.85	9.00	50.00	52.00	13.94	≤50	51.0
432	V9058102P	8000	3.80	9.00	58.00	102.00	30.40	≤40	118.0
433	G913548P	2000	3.70	9.10	35.00	48.00	7.40	≤80	31.0
434	G913657P	2000	3.70	9.10	35.70	56.50	7.40	≤60	35.0
435	G922543P	1050	3.70	9.20	25.00	44.00	3.89	≤90	18.0
436	G952024P	420	3.70	9.50	20.00	24.00	1.55	≤100	8.0
437	U952270P	2050	3.85	9.50	22.00	70.00	7.89	≤50	30.0
438	V953046P	1670	3.70	9.50	30.30	46.00	6.18	≤70	25.0
439	U955165P	4650	3.85	9.50	50.90	65.00	17.90	≤45	67.5
440	G955165P	4500	3.70	9.50	50.90	65.00	16.65	≤50	70.0
441	G955565P	5000	3.70	9.50	55.00	65.00	18.50	≤60	75.0
442	G963771P	3500	3.70	9.60	37.00	71.00	12.95	≤60	54.0
443	U9858102P	10000	3.85	9.80	58.00	102.00	38.50	≤60	132.5
444	G986095P	8000	3.70	9.80	60.00	95.00	29.60	≤50	126.0
445	G994550P	2920	3.70	9.90	45.00	50.00	10.80	≤50	46.0
446	G994550PN	2920	3.70	9.90	45.00	50.00	10.80	≤50	46.0
447	G994550PL	2750	3.70	9.90	45.00	50.00	10.18	≤50	44.0
448	103450P	1800	3.70	10.00	33.60	50.00	6.66	≤60	32.0
449	103450P1	2000	3.70	10.00	33.60	50.00	7.40	≤60	32.0
450	V103557P	3000	3.80	10.00	35.00	57.00	11.40	≤60	43.0
451	G9960115P	10000	3.70	10.00	60.30	115.00	37.00	≤40	154.0
452	G104159P	2900	3.70	10.10	41.00	58.50	10.73	≤40	47.0
453	V114169P	4400	3.80	10.20	40.20	68.80	16.72	≤60	63.0
454	V105555P	4000	3.80	10.20	55.00	55.00	15.20	≤60	66.7
455	V114765P	5000	3.80	11.00	47.00	65.00	19.00	≤60	73.0

文件名称: 锂离子聚合物电池规格表 Specification for Lithium-ion Polymer Rechargeable Battery						文件编号			版次
						P3-PRD/PLB-001			B01
序号 NO.	型号 Model	额定容量 Rated Capacity Min (mAh)	额定电压 Rated Voltage (V)	厚度 Thickness Max (mm)	宽度 Width Max (mm)	高度 Height Max (mm)	瓦时 Watt hour (WH)	内阻 Internal resistance (mΩ)	重量 Weight (g)
456	G1165115P	10200	3.70	11.00	65.00	115.00	37.74	≤40	165.0
457	G1160100P	10000	3.70	11.20	60.00	100.00	37.00	≤60	157.0
458	G1160115P	10500	3.70	11.40	60.30	115.00	38.85	≤40	175.0
459	G125050P	4060	3.70	12.00	50.00	50.00	15.02	≤60	65.0
460	G1260100P	10000	3.70	12.00	60.00	100.00	37.00	≤40	165.0
461	G1260115P	10200	3.70	12.00	60.30	115.00	37.74	≤40	175.0
462	G1260110P	10500	3.70	12.00	60.50	110.50	38.85	≤40	175.0
463	G1265115P	13000	3.70	12.00	65.00	115.00	48.10	≤60	201.0