


NOTES:

- STRAIGHT ACTION PRINCIPLE;
- RATCHED RELEASE;
- SIMPLE PRESSURE ADJUSTMENT WITH LOCKING DEVICE;
- FEEDING AND CUTTING DEVICE
- PRECISELY GROUND PROFILES;
- ERGONOMIC SOFT GRIPS, COLOUR ORANGE;
- FULLY RECYCLABLE;
- APPLICATION RANGE: T1 INDUSTRIAL CONTACTS;
- CROSS SECTION RANGE: AWG 28-26

**PRELIMINARY PART
NOT RELEASED FOR PRODUCTION**

**THIS PRODUCT HAS NOT COMPLETED
VALIDATION TESTING**

PARTNUMBER:
2368260-1

DWN P. POORTER	21APR2020	MATERIAL TBD	HEAT TREAT -
CHK -	-	 TE Connectivity	
APVD -	-		
NAME T1 HAND CRIMPING TOOL AWG 28-26, 500PCS			
SCALE NTS	SIZE A3	DRAWING NO 2368260	SHEET 1 OF 1
			REV 1

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC	±0.0
1 PLC	±0.00
2 PLC	±0.000
3 PLC	±0.000
4 PLC	±0.0000
ANGLES	-
SURFACE TEXTURE	✓

LTR	REVISION RECORD	DATE	DWN	APVD
1	INITIATE	22APR2020	PP	JDB