

Material	EU-REACH (SVHC > 0,1% (w/w))				
	SVHC name	SVHC CAS num	SVHC weight	Location	SCIP number
300530	Lead	7439-92-1	3 mg	KIT;PL700SM-N;RECPT;FPM;3P;22GA;KY1;GY;S/CRMP	
300822	Lead	7439-92-1	5 mg	KIT;PL700SM-N;PLUG;IL;18P;26GA;KY1;BK/BK;S/CUP	
300850	Lead	7439-92-1	7 mg	KIT;PL700SM-N;PLUG;IL;24P;26GA;KY1;BK/BK;S/CUP	
320070	Lead	7439-92-1	3 mg	KIT;PL500SM-N;PLUG;IL;6P;22GA;KY1;BK/BK;S/CUP	
320427	Lead	7439-92-1	3 mg	KIT;PL500SM-N;RECPT;RPM;6P;22GA;KY1;BK;S/CUP	
320455	Lead	7439-92-1	3 mg	KIT;PL500SM-N;RECPT;RPM;10P;26GA;KY1;BK;S/CUP	
331322	Lead	7439-92-1	5 mg	KIT;PL700SM-N;RECPT;RPM;18P;26GA;KY1;BK;PCB	
331336	Lead	7439-92-1	5 mg	KIT;PL700SM-N;RECPT;RPM;24P;26GA;KY1;BK;PCB	
341238	Lead	7439-92-1	5 mg	KIT;PL900RG-N;PLUG;IL;41P;26GA;KY2;BK/BK;S/CUP	
342505	Lead	7439-92-1	3 mg	KIT;PL900RG-N;RECPT;RPM;41P;26GA;KY2;BK;PCB	