

CTCS SP SERIES



CTCS SP
2.8 21W Female



CTCS SP
2.8 21W Male

CTCS FAMILY BENEFITS

- Versatile connection system
- Unparalleled reliability and performance
- Designed for the transportation market

SP SERIES FEATURES

- Lever lock integrated into the back shell for easier plugging
- Locking features on slides prevent accidental release of connectors prior to full mating




AVAILABLE CONFIGURATIONS


Cavity Count (ways)	15, 21, 26, 39, 62
Cavity Configurations	1.5, 2.8, 6.3, Mixed
Materials	Non-V0 and V0
Genders	Female and Male
Lock Assist Type	Lever lock
Mounting Options	Panel and Bracket



TEMPERATURE



VIBRATION




APPLICATIONS

Chassis
Engine compartment



SEALING IP RATING (IEC/ISO)



See back page for representative part numbers and packaging dimensions.

About Aptiv

Aptiv is a global technology company that develops safer, greener and more connected solutions enabling the future of mobility. Headquartered in Dublin, Aptiv has approximately 150,000 employees and operates 14 technical centers, as well as manufacturing sites and customer support centers in 45 countries.

Visit aptiv.com




Cavity count	Blade size (mm)	Gender	Dimensions WxHxD (mm)	V0 part number	Non-V0 part number	Mounting type	Index	Color	Indexes offered
15	2.8	F	59.2x37.6x54.6	33276638	33188785	Universal	A	Black	A, B, C
21	2.8	F	69.2x37.6x56.95	33276630	33101162	Universal	A	Black	A, B, C, D
21	2.8	M	68.4x46.1x84	33276634	33237993	Panel	A	Black	A, B, C, D
26	1.5(12)/2.8(12)/6.3(2)	F	92.15x41.4x64.71	33283998	33207220	Universal	A	Black	A, B, C, D
26	1.5(12)/2.8(12)/6.3(2)	M	75.9x51x77.6	33284519	33207134	Panel	A	Black	A, B, C, D
39	2.8	F	120.1x44.15x64.13	33273782	33111401	Universal	A	Green	A, B
39	2.8	M	108x78x89.9	33276705	33198862	Panel	A	Green	A, B
62	1.5(56)/2.8(6)	F	120.55x44.1x64.55	33337581	33337577	Universal	A	Black	A, B, C, D
62	1.5(56)/2.8(6)	M	108x78x89.9	33276719	33213199	Panel	A	Black	A, B, C, D

Please, refer to the CTCS catalogue for the full part number list.

REQUIRED ACCESSORIES

Cavity count	Accessory	V0 part number	Non-V0 part number
15	Female back shell/Lever	33276642	33200044
21	Female back shell/Lever	33276641	33106893
26	Female back shell/Lever	33284004	33207232
39	Female back shell/Lever	33273779	33111591
62	Female back shell/Lever	33273779	33111591

DIMENSION MEASUREMENT SAMPLE



COMPATIBLE WITH



Part numbers, specifications, dimensions and performance data in this document are for general references only and are subject to change without notice. To verify product information, please contact a Aptiv representative.

CS-SP6-CTCS-En0218