USB Smart Charge Modules



Molex USB smart-charge modules lead the market by combining automotive-grade durability and off-the-shelf availability through distribution.

Features and Benefits

Modern Features

Easy to read lettering and display. Blue LED backlighting. Panel Thickness: 3.4 mm to 3.8 mm.



Single Port Charger

Electric Performance 1A output current. Battery Operating Voltage: 9V to 16V. Operating temperature: -40°C to 85°C.

> Quality Connector Styles Automotive-grade USB Type A on the front. 10K cycle life. MicroFit on the rear.



Easy to Design-In

Plastic housing designed to fit existing rocker panel switch cut out.

Charging Profiles Supported:

USB Battery Charging Specification BC1.2 compliant. YD/T 1591-2009 (China Telecom Specification). Apple MFI compliant. 1.2 V Mode.



Modern Features

Easy to read lettering and display. LED backlight. Painted and laser etched housing. Panel Thickness: 2.35- 2.65 mm.

Safety Protection Features

Over voltage, Reverse battery and over current protection. ESD and short circuit protection. Optional tethered dust caps.



Modern Features

Easy to read lettering and display. Halo Lighting (Light Pipe). Cosmetic Molding and Pad Printed Icon. Panel Thickness: 2.5- 3.5 mm

Single Port USB Smart Charger

Electric Performance

2.4A output current. Battery Operating Voltage: 9V to 16V. Operating temperature: -40°C to 85°C.

Quality Connector Styles

Automotive-grade USB Type A on the front.10K cycle life. Molex Mini50 on the rear



Safety Protection Features

Over voltage, Reverse battery and over current protection. ESD and short circuit protection

Dual Port USB Smart Charger

Electric Performance

2.4A output current. Battery Operating Voltage: 9V to 16V. Operating temperature: -40°C to 85°C.



Quality Connector Styles Automotive-grade USB

Automotive-grade USB Type A on the front. 10K cycle life. Molex Mini50 on the rear

Charging Profiles Supported:

USB Battery Charging Specification BC1.2 compliant. YD/T 1591-2009 (China Telecom Specification). Apple MFI compliant. 1.2 V Mode.

USB Smart Charge Modules

molex

Applications

Commercial Vehicle

Construction equipment Farm equipment Trains Airplanes

Automotive Cars

Pickup trucks SUVs



Automotive



Commercial Vehicle

Specifications

Single Port USB Charger Module

REFERENCE INFORMATION

Packaging: Individual Mates With: Micro-Fit 3.0[™] Receptacle (Series No. 43645) and Micro-Fit 3.0[™] Female Crimp (Series 43030, 45773) Use With: USB A Type Connector Designed In: Millimeters RoHS: Yes (with exemption) Halogen Free: No Glow Wire Compliant: No

Single Port USB Smart Charger Module

REFERENCE INFORMATION

Packaging: Per PK-68532-4510 Mates With: Mini50 and MicroFit Use With: Mini50 and MicroFit Designed In: Millimeters RoHS: Yes (with exemption) Halogen Free: No Glow Wire Compliant: No Supported charging schemes: D+ and D- Divider Mode 2.7V and 2.7V D+ and D- 1.2V Mode D+ and D- Shorted Mode per USB Battery Charging Specification 1.2 (BC1.2).

ELECTRICAL

Voltage (max.): 16V DC Input: 9 to 16V DC Output (max.): 5V DC +/-5% 1.0A Backlight: Blue LED, 12V DC

MECHANICAL

Mating cycles: 5,000

MATERIALS

PCB: FR4, UL 94V-0
Plastic Housings: PC, Color: black for rear housing white for front housing
Color finish: black over white material (on front housing)
USB Type A:
Housing material: high temp thermoplastic, UL-94v-0, color: black.
Terminal: phosphor bronze, plating: gold 0.75μm
Shield: stainless steel, NI 0.75μm min.
Mini50 connector:
Housing material: polyester alloy, color: black
Terminal: brass, plating: tin

PHYSICAL

Housing: Polycarbonate/Acrylonitrile Butadiene Styrene (PC+ABS), Black Dimensions (mm): 48.00 H x 26.00 W x 37.05 D Operating Temperature: -40 to +85°C (automotive grade)

PHYSICAL

Industrial Operating Range: -40°C to +85°C Non-operating: -55°C to +85°CUSB Module Envelope Dimensions: 49.0 X 22.8 X 40.58 mm Insertion: 35n max Extraction: 10n min Durability: 10,000 cycles Pull out force for docking module measured on metal plate cut out/fixture (with recommended opening): 100n min. Module weight: 0.028 kg

ELECTRICAL

Input voltage range: 9VDC – 16VDC Output voltage range: 5VDC +/- 10% USB output Maximum output charging current: 2.4 A DC, limited to 2.9 A Maximum input current at maximum load: 1.5A DC Maximum input current for illumination line: 12mA DC

USB Smart Charge Modules

molex

Specifications

Dual Port USB Smart Charger Module

REFERENCE INFORMATION

Packaging: Per PK-68532-4460 Packaging for module 685324466 according to: rpk_68532_001/2 Mates With: Mini50 and MicroFit Use With: Mini50 and MicroFit Designed In: Millimeters RoHS: Yes (with exemption) Halogen Free: No Glow Wire Compliant: No Supported charging schemes: D+ and D- Divider Mode 2.7V and 2.7V D+ and D- 1.2V Mode D+ and D- Shorted Mode per USB Battery Charging Specification 1.2 (BC1.2).

MATERIALS

Front housing: pc+abs, cycloloy lg9000, pg05 black Surface finish (faceplate): nissan#424 Light pipes: sc-28876 rtp 0300 2405 lt diff. Rear housing: pc+abs, cycloloy lg9000, pg05 black Rubber cover: empilon ha65s4 Printing circuit board: fr4, thickness 1.6 mm Input power conn.: 2usb ports type a Terminal: phosphor bronze, plating: gold 0.75µm Shield: stainless steel, NI 0.75µm min. Mini50 connector: Housing material: polyacter alloy, color: black

Housing material: polyester alloy, color: black Terminal: brass, plating: tin

PHYSICAL

Industrial Operating Range: -40°C to +85°C Non-operating: -55°C to +85°CUSB Module Color for illuminated usb halo is white candles per iluminated usb halo: ordinary switch 2cd/m2 Insertion: 49n max Extraction: 68.8n min Durability: 10,000 cycles

ELECTRICAL

Input voltage range: 9VDC – 16VDC Output voltage range: 5VDC +/- 0.25V @ 2.4A Maximum output charging current: 2.4 A DC, limited to 2.9 A Maximum input current at no load: 26mA

Ordering Information

Series No.	Ports	Output Current	Charging Profiles Supported
68532-4461	- Dual Single	2.4 Amps	USB Battery Charging Specification BC1.2 compliant. YD/T 1591-2009 (China Telecom Specification) Apple MFI Compatible.
68532-4462			
68532-4510			USB Battery Charging Specification BC1.2 compliant. YD/T 1591-2009 (China Telecom Specification) Apple MFI compliant. 1.2 V Mode
79540-5015		1 Amp	

www.molex.com/link/invehiclesmartcharging.html

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.