

ChipLED Selection Guide

Mono-color

0603 ChipLEDs - 0.37mm height

Dimensions (mm): 1.6 x 0.6 x 0.37			Test current: 20mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (typ.)	Iv @ 20mA (typ)
HSMW-C130	white	x 0.29/y 0.27	InGaN	145°	3.6V	150mcd
HSMR-C130	blue	473nm	InGaN	145°	3.4V	55mcd
HSMQ-C130	green	527nm	InGaN	120°	2.5V-3.5V	285mcd-715mcd
HSMC-C130	yell-green	573nm	AllnGaP	110°	1.94V	54mcd
HSMG-C130	yell-green	573nm	AllnGaP	110°	1.94V	54mcd
HSMH-C130	amber	589nm	AllnGaP	110°	2.05V	87mcd
HSMI-C130	orange	606nm	AllnGaP	110°	1.94V	139mcd
HSMJ-C130	orange	606nm	AllnGaP	110°	1.94V	139mcd
HSMK-C130	red	626nm	AllnGaP	110°	1.94V	131mcd

0603 ChipLEDs - 0.8mm height

Dimensions (mm): 1.6 x 0.8 x 0.8			Test current: 20mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 20mA (typ)
HSMR-C190	blue	473nm	InGaN	140°	3.4V-3.9V	55mcd
HSMQ-C190	green	527nm	InGaN	140°	3.4V-3.9V	145mcd
HSMG-C190	yell-green	572nm	AllnGaP	170°	1.6V-2.6V	15mcd
HSMC-C190	yell-green	572nm	AllnGaP	170°	1.6V-2.6V	50mcd
HSMH-C190	amber	592nm	AllnGaP	170°	1.9V-2.4V	90mcd
HSMI-C190	amber	592nm	AllnGaP	170°	1.6V-2.6V	8mcd
HSMJ-C190	orange	605nm	AllnGaP	170°	1.9V-2.4V	90mcd
HSMK-C190	orange	604nm	AllnGaP	170°	1.6V-2.6V	8mcd
HSML-C190	orange	604nm	AllnGaP	170°	1.6V-2.6V	8mcd
HSMO-C190	red	626nm	AllnGaP	170°	1.6V-2.4V	90mcd
HSMH-H190	red	639nm	AllnGaP	170°	1.6V-2.6V	7.2mcd (min)

0402 ChipLEDs - 0.25mm height

Dimensions (mm): 1.0 x 0.5 x 0.25			Test current: 20mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 20mA (typ)
HSMC-C290	yell-green	572nm	AllnGaP	135°	1.6V-2.4V	63mcd
HSMH-C290	amber	589nm	AllnGaP	135°	1.6V-2.4V	79mcd
HSMI-C290	orange	605nm	AllnGaP	135°	1.6V-2.4V	89mcd
HSMJ-C290	red	624nm	AllnGaP	135°	1.6V-2.4V	97mcd

0603 Lens ChipLEDs - 0.98mm height

Dimensions (mm): 1.6 x 0.6 x 0.37			Test current: 20mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (typ.)	Iv @ 20mA (min-max)
HSMR-C320	blue	473nm	InGaN	50°	2.5V-3.5V	200mcd-1125mcd
HSMQ-C320	green	527nm	InGaN	50°	2.5V-3.5V	1125mcd-4500mcd
HSMC-C320	yell-green	572nm	AllnGaP	60°	1.6V-2.4V	180mcd-450mcd
HSMH-C320	amber	592nm	AllnGaP	60°	1.6V-2.4V	285mcd-715mcd
HSMI-C320	orange	605nm	AllnGaP	60°	1.6V-2.4V	285mcd-715mcd
HSMJ-C320	red	626nm	AllnGaP	60°	1.6V-2.4V	450mcd-1125mcd

1206 Lens ChipLEDs - 1.85mm height

Dimensions (mm): 3.2 x 1.6 x 1.85			Test current: 20mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 20mA (min-max)
HSMQ-C380	green	528nm	InGaN	15°	2.9V-3.9V	1800mcd-7150mcd
HSMC-C380	yell-green	570nm	AllnGaP	15°	1.6V-2.4V	285mcd-4500mcd
HSMH-C380	amber	589nm	AllnGaP	15°	1.6V-2.4V	715mcd-4500mcd
HSMI-C380	orange	603nm	AllnGaP	15°	1.6V-2.4V	450mcd-4500mcd
HSMJ-C380	red	630nm	AllnGaP	15°	1.6V-2.4V	450mcd-4500mcd

1206 Lens ChipLEDs - 1.1mm height

Dimensions (mm): 3.2 x 1.6 x 1.1			Test current: 20mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 20mA (min-max)
HSMQ-C350	green	528nm	InGaN	70°	2.9V-3.9V	450mcd-2850mcd
HSMC-C350	yell-green	570nm	AllnGaP	70°	1.6V-2.4V	715mcd-1125mcd
HSMH-C350	amber	589nm	AllnGaP	70°	1.6V-2.4V	180mcd-1125mcd
HSMI-C350	orange	603nm	AllnGaP	70°	1.6V-2.4V	1125mcd-1125mcd
HSMJ-C350	red	630nm	AllnGaP	70°	1.6V-2.4V	1125mcd-1125mcd

Right angle ChipLEDs - 0.3mm height

Dimensions (mm): 1.0 x 0.55 x 0.3			Test current: 20mA, 5mA (W&B)		Type: Side Firing	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv (min)
HSMW-C230	white	x 0.29/y 0.28	InGaN	175°	2.55V-3.15V	45mcd @ 5mA
HSMR-C230	blue	468nm	InGaN	175°	2.55V-3.15V	18mcd @ 5mA
HSMQ-C230	green	525nm	InGaN	140°	2.9V-3.9V	112.5mcd @ 20mA
HSMC-C230	yell-green	572nm	AllnGaP	140°	1.6V-2.4V	28.5mcd @ 20mA
HSMH-C230	amber	589nm	AllnGaP	140°	1.6V-2.4V	28.5mcd @ 20mA
HSMI-C230	orange	605nm	AllnGaP	140°	1.6V-2.4V	28.5mcd @ 20mA
HSMJ-C230	red	622nm	AllnGaP	140°	1.6V-2.4V	28.5mcd @ 20mA

0603 ChipLEDs - 0.6mm height

Dimensions (mm): 1.6 x 0.8 x 0.6			Test current: 20mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 20mA (typ)
HSMW-C191	white	x 0.29/y 0.27	InGaN	140°	3.4V-3.9V	200mcd
HSMR-C191	blue	473nm	InGaN	140°	3.4V-3.9V	55mcd
HSMQ-C191	green	527nm	InGaN	140°	3.4V-3.9V	145mcd
HSMG-C191	yell-green	572nm	AllnGaP	170°	1.6V-2.6V	15mcd
HSMC-C191	yell-green	572nm	AllnGaP	170°	1.6V-2.6V	50mcd
HSMH-C191	amber	592nm	AllnGaP	170°	1.9V-2.4V	90mcd
HSMI-C191	amber	592nm	AllnGaP	170°	1.6V-2.6V	8mcd
HSMJ-C191	orange	605nm	AllnGaP	170°	1.9V-2.4V	90mcd
HSMK-C191	orange	604nm	AllnGaP	170°	1.6V-2.6V	8mcd
HSMO-C191	orange	604nm	AllnGaP	170°	1.6V-2.6V	8mcd
HSMC-C191	red	626nm	AllnGaP	170°	1.6V-2.4V	90mcd
HSMH-H191	red	639nm	AllnGaP	170°	1.6V-2.6V	7.2mcd (min)

Right angle ChipLEDs - 0.6mm height

Dimensions (mm): 2.1 x 1.0 x 0.6			Test current: 20mA		Type: Side Firing	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 20mA (min)
HSMW-C240	white	x 0.29/y 0.28	InGaN	175°	2.55V-3.15V	45mcd
HSMC-C240	yell-green	572nm	AllnGaP	120°	1.6V-2.4V	45mcd
HSMH-C240	amber	592nm	AllnGaP	120°	1.6V-2.4V	45mcd
HSMI-C240	orange	605nm	AllnGaP	120°	1.6V-2.4V	45mcd
HSMJ-C240	red	626nm	AllnGaP	120°	1.6V-2.4V	45mcd

0805 ChipLEDs - 0.8mm height

Dimensions (mm): 2.0 x 1.25 x 0.8			Test current: 20mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 20mA (typ)
HSMR-C170	blue	473nm	InGaN	140°	3.4V-3.9V	55mcd
HSMQ-C170	green	527nm	InGaN	140°	3.4V-3.9V	145mcd
HSMC-C170	yell-green	572nm	AllnGaP	170°	1.6V-2.6V	50mcd
HSMG-C170	yell-green	572nm	AllnGaP	170°	1.6V-2.6V	15mcd
HSMH-C170	amber	586nm	AllnGaP	170°	1.6V-2.6V	90mcd
HSMI-C170	amber	586nm	AllnGaP	170°	1.6V-2.6V	8mcd
HSMJ-C170	orange	604nm	AllnGaP	170°	1.6V-2.6V	90mcd
HSMK-C170	orange	604nm	AllnGaP	170°	1.6V-2.6V	8mcd
HSMO-C170	red	626nm	AllnGaP	170°	1.6V-2.4V	90mcd
HSMH-H170	red	639nm	AllnGaP	170°	1.6V-2.6V	7.2mcd (min)

1206 ChipLEDs - 1.10mm height

Dimensions (mm): 3.2 x 1.6 x 1.1			Test current: 20mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 20mA (typ)
HSMR-C150	blue	473nm	InGaN	140°	3.4V-3.9V	55mcd
HSMQ-C150	green	527nm	InGaN	140°	3.4V-3.9V	145mcd
HSMC-C150	yell-green	572nm	AllnGaP	170°	1.6V-2.6V	50mcd
HSMG-C150	yell-green	572nm	AllnGaP	170°	1.6V-2.6V	15mcd
HSMY-C150	amber	586nm	AllnGaP	170°	1.6V-2.6V	8mcd
HSMO-C150	orange	604nm	AllnGaP	170°	1.6V-2.6V	8mcd
HSMO-C170	orange	604nm	AllnGaP	170°	1.6V-2.6V	8mcd
HSMC-C150	red	626nm	AllnGaP	170°	1.6V-2.4V	90mcd
HSMH-H150	red	626nm	AllnGaP	170°	1.6V-2.6V	10mcd
HSMH-H150	red	639nm	AllnGaP	170°	1.6V-2.6V	7.2mcd (min)

ChipLED Selection Guide

Bi-color

0603 Bi-Color ChipLEDs - 0.5mm height

Dimensions (mm): 1.6 x 0.8 x 0.5			Type: Top Mount			
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (typ-max)	Iv (typ) or (min-max)
HSMF-C162	AllnGaP amber	592nm	AllnGaP	120°	1.8V-2.3V	90mcd @20mA
	AllnGaP red	626nm	AllnGaP	120°	1.8V-2.3V	90mcd @20mA
HSMF-C163	AllnGaP red	626nm	AllnGaP	120°	1.8V-2.3V	90mcd @20mA
	InGaN green	525nm	InGaN	120°	3.4V-3.8V	45mcd @10mA
HSMF-C164	AllnGaP red	626nm	AllnGaP	120°	1.8V-2.3V	90mcd @20mA
	InGaN blue	470nm	InGaN	120°	3.4V-3.8V	10mcd @10mA
HSMF-C165	GaP red	621nm	GaP	120°	1.95V-2.6V	10mcd @20mA
	GaP green	572nm	GaP	120°	2.2V-2.6V	15mcd @20mA
HSMF-C166	GaP yellow	586nm	GaP	120°	2.1V-2.6V	8mcd @20mA
	GaP green	572nm	GaP	120°	2.2V-2.6V	15mcd @20mA
HSMF-C167	GaP Orange	604nm	GaP	120°	2.2V-2.6V	8mcd @20mA
	GaP green	572nm	GaP	120°	2.2V-2.6V	15mcd @20mA
HSMF-C168	InGaN green	525nm	InGaN	120°	3.4V-3.8V	45mcd @10mA
	InGaN blue	470nm	InGaN	120°	3.4V-3.8V	10mcd @10mA
HSMF-C169	AllnGaP amber	592nm	AllnGaP	120°	1.8V-2.3V	90mcd @20mA
	InGaN blue	470nm	InGaN	120°	3.4V-3.8V	10mcd @10mA
HSMF-C168	AllnGaP orange	605nm	AllnGaP	120°	1.6V-2.24V	11.2mcd-45mcd @ 5mA
	InGaN green	525nm	InGaN	120°	2.55V-3.15V	45mcd-112.5mcd @ 5mA
HSMF-C16M	AllnGaP red	626nm	AllnGaP	120°	1.6V-2.4V	104.4mcd @20mA
	AllnGaP green	572nm	AllnGaP	120°	1.6V-2.4V	55.4mcd @20mA
HSMF-C16Z	AllnGaP orange	605nm	AllnGaP	125°	1.6V-2.4V	18mcd-45mcd @5mA
	white		InGaN	125°	2.55V-3.15V	71.5mcd-180mcd @ 5mA
HSMF-CZA1	AllnGaP orange	605nm	AllnGaP	120°	1.6V-2.4V	45mcd-285mcd @20mA
	InGaN blue	470nm	InGaN	120°	2.9V-3.8V	28.5mcd-180mcd @20mA

0605 Bi-Color ChipLEDs - 0.4mm height

Dimensions (mm): 1.6 x 1.25 x 1.1			Type: Top Mount			
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv (min)
HSMF-C171	AllnGaP Orange	605nm	AllnGaP	140°	1.6V-2.4V	28.5mcd @10mA
	InGaN blue	467nm	InGaN	150°	2.7V-3.9V	18mcd @10mA
HSMF-C172	AllnGaP Orange	605nm	AllnGaP	140°	1.6V-2.4V	28.5mcd @20mA
	AllnGaP green	570nm	AllnGaP	140°	1.6V-2.4V	28.5mcd @20mA
HSMF-C173	AllnGaP red	624nm	AllnGaP	140°	1.6V-2.4V	28.5mcd @20mA
	InGaN green	525nm	InGaN	150°	2.7V-3.9V	71.5mcd @20mA
HSMF-C174	AllnGaP red	624nm	AllnGaP	140°	1.6V-2.4V	28.5mcd @20mA
	AllnGaP green	570nm	AllnGaP	140°	1.6V-2.4V	28.5mcd @20mA
HSMF-C175	AllnGaP amber	589nm	AllnGaP	140°	1.6V-2.4V	28.5mcd @20mA
	AllnGaP green	570nm	AllnGaP	140°	1.6V-2.4V	28.5mcd @20mA
HSMF-C176	InGaN blue	467nm	InGaN	150°	2.7V-3.9V	18mcd @10mA
	InGaN green	525nm	InGaN	150°	2.7V-3.9V	71.5mcd @10mA
HSMF-C177	AllnGaP Orange	605nm	AllnGaP	140°	1.6V-2.4V	28.5mcd @10mA
	InGaN green	525nm	InGaN	150°	2.7V-3.9V	180mcd @10mA
HSMF-C178	AllnGaP amber	589nm	AllnGaP	150°	1.6V-2.4V	92mcd @20mA
	InGaN green	525nm	InGaN	140°	2.9V-3.9V	285mcd @20mA
HSMF-C179	AllnGaP red	626nm	AllnGaP	140°	1.6V-2.4V	45mcd @20mA
	InGaN blue	467nm	InGaN	140°	2.9V-3.9V	45mcd @20mA

0606 Bi-Color ChipLEDs - 0.55mm height

Dimensions (mm): 1.6 x 1.5 x 0.55			Test current: 20mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv (min-max)
HSMF-C1A4	AllnGaP red	626nm	AllnGaP	130°	1.6V-2.4V	45mcd-112.5mcd @20mA
	InGaN green	527nm	InGaN	130°	2.9V-3.9V	112.5mcd-285mcd @20mA

1210 Bi-Color ChipLEDs - 1.1mm height

Dimensions (mm): 3.2 x 2.7 x 1.1			Test current: 20mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (typ-max)	Iv (typ)
HSMF-C150	AllnGaP red	632nm	AllnGaP	170°	2.0V-2.4V	79mcd @20mA
	AllnGaP green	572nm	AllnGaP	170°	2.1V-2.4V	45mcd @20mA
HSMF-C153	GaP yellow	586nm	GaP	170°	2.1V-2.6V	8mcd @20mA
	GaP red	626nm	GaP	170°	2.1V-2.6V	10mcd @20mA
HSMF-C155	GaP red	626nm	GaP	170°	2.1V-2.6V	10mcd @20mA
	GaP green	572nm	GaP	170°	2.2V-2.6V	15mcd @20mA
HSMF-C156	GaP yellow	586nm	GaP	170°	2.1V-2.6V	8mcd @20mA
	GaP green	572nm	GaP	170°	2.2V-2.6V	15mcd @20mA
HSMF-C157	GaP Orange	604nm	GaP	170°	2.2V-2.6V	15mcd @20mA
	GaP green	572nm	GaP	170°	2.2V-2.6V	15mcd @20mA
HSMF-C158	AllnGaP green	572nm	AllnGaP	170°	2.1V-2.4V	45mcd @20mA
	AllnGaP amber	572nm	AllnGaP	170°	1.9V-2.4V	55mcd @20mA
HSMF-C15A	AllnGaP amber	592nm	AllnGaP	170°	1.9V-2.4V	55mcd @20mA
	AllnGaP red	632nm	AllnGaP	170°	2.0V-2.4V	79mcd @20mA

0606 Bi-Color ChipLEDs - 0.7mm height

Dimensions (mm): 1.6 x 1.5 x 0.7			Test current: 20mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv (min-max)
HSMF-C180	GaP green	572nm	GaP	160°	1.6V-2.6V	4.5mcd-28.5mcd @20mA
	GaP yellow	588nm	GaP	160°	1.6V-2.6V	2.8mcd-18mcd @20mA
HSMF-C181	GaP green	572nm	GaP	170°	1.6V-2.6V	4.5mcd-28.5mcd @20mA
	GaP red	629nm	GaP	170°	1.6V-2.6V	2.8mcd-18mcd @20mA
HSMF-C182	AllnGaP green	572nm	AllnGaP	150°	1.6V-2.4V	28.5mcd-58.25mcd @20mA
	AllnGaP amber	592nm	AllnGaP	150°	1.6V-2.4V	36.75mcd-112.5mcd @20mA
HSMF-C183	AllnGaP green	572nm	AllnGaP	130°	1.6V-2.4V	23.2mcd-112.5mcd @20mA
	AllnGaP red	626nm	AllnGaP	130°	1.6V-2.4V	36.7mcd-180mcd @20mA
HSMF-C185	GaP green	572nm	GaP	160°	1.6V-2.6V	4.5mcd-28.5mcd @20mA
	AllnGaP red	626nm	AllnGaP	130°	1.6V-2.4V	71.5mcd-285mcd @20mA
HSMF-C186	AllnGaP red	626nm	AllnGaP	170°	1.6V-2.4V	18mcd-112.5mcd @20mA
	InGaN blue	473nm	InGaN	170°	2.9V-3.9V	18mcd-112.5mcd @20mA
HSMF-C187	AllnGaP green	572nm	AllnGaP	150°	1.6V-2.4V	18mcd-112.5mcd @20mA
	InGaN blue	473nm	InGaN	140°	2.9V-3.9V	28.5mcd-180mcd @20mA
HSMF-C188	AllnGaP amber	592nm	AllnGaP	150°	1.6V-2.4V	28.5mcd-180mcd @20mA
	InGaN green	525nm	InGaN	150°	2.9V-3.9V	45mcd-285mcd @20mA
HSMF-C189	AllnGaP amber	592nm	AllnGaP	140°	1.6V-2.4V	28.5mcd-180mcd @20mA
	InGaN blue	473nm	InGaN	140°	2.9V-3.9V	28.5mcd-180mcd @20mA

Right angle Bicolor ChipLEDs - 1.0mm height

Dimensions (mm): 3.0 x 2.0 x 1.0			Test current: 20mA		Type: Side Firing	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv (min-max)
HSMF-C142	AllnGaP red	639nm	AllnGaP	120°	1.6V-2.4V	18mcd-66mcd @20mA
	AllnGaP green	570nm	AllnGaP	120°	1.6V-2.4V	18mcd-33mcd @20mA
HSMF-C143	AllnGaP amber	589nm	AllnGaP	120°	1.6V-2.4V	28.5mcd-103mcd @20mA
	AllnGaP green	570nm	AllnGaP	120°	1.6V-2.4V	18mcd-33mcd @20mA
HSMF-C144	AllnGaP red	632nm	AllnGaP	120°	1.6V-2.4V	18mcd-79mcd @20mA
	AllnGaP green	570nm	AllnGaP	120°	1.6V-2.4V	18mcd-33mcd @20mA
HSMF-C145	AllnGaP red	632nm	AllnGaP	120°	1.6V-2.4V	18mcd-79mcd @20mA
	InGaN green	525nm	InGaN	120°	2.9V-3.9V	45mcd-223mcd @20mA
HSMF-C146	AllnGaP red	632nm	AllnGaP	110°	1.6V-2.4V	18mcd-79mcd @20mA
	InGaN blue	464nm	InGaN	110°	2.9V-3.9V	28.5mcd-75mcd @20mA



ChipLED Selection Guide

Tri-color

0303 Tri-Color ChipLEDs - 0.5mm height

Dimensions (mm): 0.69 x 0.69 x 0.5			Test current: 10mA(R), 5mA (G&B)		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv (min-max)
HSMF-C112	red	622nm	AllnGaP	130°	1.6V-2.4V	36mcd-79mcd @10mA
	green	527nm	InGaN	150°	2.4V-3.4V	71mcd-155mcd @10mA
	blue	468nm	InGaN	150°	2.4V-3.4V	14mcd-31.5mcd @ 5mA

0404 Tri-Color ChipLEDs - 0.65mm height

Dimensions (mm): 1.05 x 1.05 x 0.65			Test current: 10mA(R), 5mA (G&B)		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv (min-max)
HSMF-C116	red	622nm	AllnGaP	137°	1.8V-2.2V	63mcd-140mcd @ 10mA
	green	528nm	InGaN	140°	2.5V-3.3V	135mcd-315mcd @ 5mA
	blue	471nm	InGaN	140°	2.7V-3.3V	24mcd-63mcd @ 5mA

0404 Tri-Color ChipLEDs - 0.25mm height

Dimensions (mm): 1.08 x 1.08 x 0.25			Test current: 5mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 5mA (min-max)
HSMF-C118	red	626nm	AllnGaP	140°	1.6V-2.4V	45mcd-285mcd
	green	527nm	InGaN	140°	2.55V-3.15V	112.5mcd-450mcd
	blue	473nm	AllnGaP	140°	2.55V-3.15V	18mcd-112.5mcd

0606 Tri-Color ChipLEDs - 0.7mm height

Dimensions (mm): 1.6 x 1.6 x 0.7			Test current: 20mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 20mA (min)
HSMF-C128	red	626nm	AllnGaP	135°	1.6V-2.4V	28.5mcd
	green	525nm	InGaN	145°	2.7V-3.5V	285mcd
	blue	470nm	AllnGaP	145°	2.7V-3.5V	45mcd

0606 Tri-Color ChipLEDs - 0.4mm height (6 pins)

Dimensions (mm): 1.6 x 1.6 x 0.4			Test current: 10mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 10mA (min-max)
HSMF-C125	red	625nm	AllnGaP	130°	1.9V-2.4V	45mcd-180mcd
	green	522nm	InGaN	150°	2.93V-3.9V	112.5mcd-360mcd
	blue	467nm	InGaN	150°	2.93V-3.9V	28.5mcd-112.5mcd

0805 Tri-Color ChipLEDs - 0.5mm height

Dimensions (mm): 2.0 x 1.3 x 0.5			Test current: 10mA		Type: Top Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 10mA (min)
HSMF-C129	red	625nm	AllnGaP	140°	1.6V-2.4V	18mcd
	green	529nm	InGaN	140°	2.9V-3.9V	71.5mcd
	blue	468nm	AllnGaP	140°	2.9V-3.9V	18mcd

Right Angle Tri-Color ChipLEDs - 1mm height

Dimensions (mm): 3.2 x 1.5 x 1.0			Test current: 20mA		Type: Side Firing	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 20mA (min)
HSMF-C127	red	626nm	InGaN	150°	1.6V-2.4V	285mcd
	green	527nm	InGaN	150°	2.9V-3.9V	450mcd
	blue	473nm	AllnGaP	150°	2.9V-3.9V	112.5mcd

Tri-Color Reverse Mount ChipLEDs

Dimensions (mm): 3.2 x 1.2 x 0.8			Test current: 10mA		Type: Reverse Mount	
Product Number	Color	Wavelength (typ.)	Dice Material	Viewing Angle	Vf (min-max)	Iv @ 10mA (min-max)
HSMF-C255	red	625nm	AllnGaP	150°	1.6V-2.4V	28.5mcd-180mcd
	green	521nm	InGaN	125°	2.5V-3.5V	180mcd-450mcd
	blue	466nm	AllnGaP	150°	2.5V-3.5V	28.5mcd-180mcd



Broadcom Inc. is a global infrastructure technology leader built on 50 years of innovation, collaboration and engineering excellence.

Broadcom Inc. (NASDAQ: AVGO) is a global technology leader that designs, develops and supplies a broad range of semiconductor and infrastructure software solutions.

Broadcom's category-leading product portfolio serves critical markets including data center, networking, enterprise software, broadband, wireless, storage and industrial. Our solutions include data center networking and storage, enterprise, mainframe and cyber security software focused on automation, monitoring and security, smartphone components, telecoms and factory automation. For more information, go to www.broadcom.com.

Learn more at:

broadcom.com/leds