

5.7kVDC 6W Quad Output Isolated Gate Drive SM DC-DC Converters



#### **FEATURES**

- No opto feedback
- Patent protected
- Four isolated output voltages suitable for powering IGBT/SiC & Mosfet gate drives simultaneously in a three phase bridge configuration
- Reinforced insulation to UL60950 with 8mm creepage & clearance recognition pending
- ANSI/AAMI ES60601-1 recognition pending
- Characterised dv/dt immunity 80kV/µs at 1.6kV
- Characterised partial discharge performance
- 5.7kVDC isolation test voltage 'Hi Pot Test'
- Ultra low coupling capacitance typically 15pF
- DC link voltage 3kVDC
- 5V, 12V & 24V input voltages
- 105°C operating temperature


#### **PRODUCT OVERVIEW**

Offering four isolated output voltages of 24V, the MGJ6 series of DC-DC converters is ideal for powering 'high side' and 'low side' gate drive circuits simultaneously for IGBTs, Silicon and Silicon Carbide Mosfets in three phase circuits.The MGJ6 series is characterised for high isolation and dv/dt requirements commonly seen in bridge circuits used in motor drives and inverters.

SELECTION GUIDE								
		Output 1 VH	A / Output 2 V VHC	HB Output 3	Output 4 VL			
Order Code <sup>1</sup>	Input Voltage Range	Rated Output Voltage	Rated Output Current	Output Power	Rated Output Voltage	Rated Output Current	Output Power	
	V	V	mA	W	V	mA	W	
MGJ6Q05P24MC	4.5 - 9	24	42	1	24	125	3	
MGJ6Q12P24MC	9 - 18	24	42	1	24	125	3	
MGJ6Q24P24MC	18 - 36	24	42	1	24	125	3	

								-	-
SELECTION GUIDE (Continued)									
		Output 1 VHA / Output 2 VHB Output 3 VHC				Output 4 VL			
Order Code <sup>1</sup> Input Voltage Range	Load Regulation (Typ)	Load Regulation (Max)	Ripple & Noise (Typ) <sup>2</sup>	Ripple & Noise (Max) <sup>2</sup>	Load Regulation (Typ)	Load Regulation (Max)	Ripple & Noise (Typ) <sup>2</sup>	Ripple & Noise (Max) <sup>2</sup>	
	V		%	mV	р-р	9	6	mV	р-р
MGJ6Q05P24MC	4.5 - 9	2	3	100	150	2	3	100	150
MGJ6Q12P24MC	9 - 18	2	3	70	120	2	3	70	120
MGJ6Q24P24MC	18 - 36	2	3	70	120	2	3	70	120

SELECTION GUIDE (Continued)							
	ag st t				MT	TF <sup>3</sup>	
Order Code <sup>1</sup>	Nominal Input Voltage Input Current at Rated Load (Min) Efficiency	Efficiency (Typ)	MIL 217	Telecordia			
	V mA		9	%	kH	lrs	
MGJ6Q05P24MC	5	1500	76	79.5			
MGJ6Q12P24MC	12	600	81	84			
MGJ6Q24P24MC	24	300	82	85			





<sup>3.</sup> Calculated using MIL-HDBK-217 FN2 and Telecordia SR-332 calculation model at TA=25°C with nominal input voltage at full load.

All specifications typical at TA=25°C, nominal input voltage and rated output current unless otherwise specified.







### MGJ6 Three Phase Bridge Series 5.714/DC CW Quad Output legisted Cate Prive SM DC DC Conventers

INPUT CHARACTERISTICS					
Parameter	Conditions	Min.	Typ.	Max.	Units
	5V input types	4.5	5	9	
Voltage range	12V input types	9	12	18	V
	24V input types	18	24	36	
	Turn on threshold MGJ6Q05		3.8		
	Turn off threshold MGJ6Q05		3.2		
	Turn on threshold MGJ6Q12		8.1		
Under voltage lock out	Turn off threshold MGJ6Q12		7.5		V
	Turn on threshold MGJ6Q24		16.7		
	Turn off threshold MGJ6Q24		16.3		
	5V input types		30		
land displacement					mA
Input ripple current	12V input types		45		р-р
	24V input types		25		
OUTPUT CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
Minimum load	Below 10% load, output may rise to 30V maximum voltage	10			%
Voltage set point accuracy	5V output types		+4 / -1		%
voltage set point accuracy	oliage set point accuracy  All other output types				70
Total regulation				10	%
Line regulation	Low line to high line		0.5	1	%
ISOLATION CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
	Flash tested for 1 second (input to output)	4000	,,		
In the Paris As a Assaultance	Flash tested for 1 second (output to output)	2500			VAC
Isolation test voltage	Qualification tested for 1 minute (input to output)	5700			VDO
	Qualification tested for 1 minute (output to output)	3000			VDC
Resistance	Viso = 1kVDC	100			GΩ
				3000	VDC
Continuous barrier withstand voltage	Non-safety barrier application			3000	
·	Non-safety barrier application Input to output			8	
Continuous barrier withstand voltage  Creepage & clearance					mm
·	Input to output		15	8	mm
Creepage & clearance	Input to output Output to output		15 15	8	
·	Input to output Output to output Primary to Output 1 VHA Primary to Output 2 VHB			8	mm pF
Creepage & clearance	Input to output Output to output Primary to Output 1 VHA		15	8	
Creepage & clearance Isolation capacitance	Input to output Output to output Primary to Output 1 VHA Primary to Output 2 VHB Primary to Output 3 VHC		15 15	8	
Creepage & clearance Isolation capacitance  GENERAL CHARACTERISTICS	Input to output Output to output Primary to Output 1 VHA Primary to Output 2 VHB Primary to Output 3 VHC Primary to Output 4 VL	Min	15 15 15	8 8	pF
Creepage & clearance  Isolation capacitance  GENERAL CHARACTERISTICS  Parameter	Input to output Output to output Primary to Output 1 VHA Primary to Output 2 VHB Primary to Output 3 VHC Primary to Output 4 VL  Conditions	Min.	15 15 15 Typ.	8	pF Units
Creepage & clearance Isolation capacitance  GENERAL CHARACTERISTICS	Input to output Output to output Primary to Output 1 VHA Primary to Output 2 VHB Primary to Output 3 VHC Primary to Output 4 VL	Min.	15 15 15	8 8	pF
Creepage & clearance  Isolation capacitance  GENERAL CHARACTERISTICS  Parameter  Power Consumption  Switching frequency	Input to output Output to output Primary to Output 1 VHA Primary to Output 2 VHB Primary to Output 3 VHC Primary to Output 4 VL  Conditions	Min.	15 15 15 Typ.	8 8	pF Units mW
Creepage & clearance  Isolation capacitance  GENERAL CHARACTERISTICS  Parameter  Power Consumption  Switching frequency  TEMPERATURE CHARACTERISTICS	Input to output Output to output Primary to Output 1 VHA Primary to Output 2 VHB Primary to Output 3 VHC Primary to Output 4 VL  Conditions Disable pin pulled low		15 15 15 15 Typ. 45 100	8 8 Max.	pF Units mW kHz
Creepage & clearance  Isolation capacitance  GENERAL CHARACTERISTICS  Parameter  Power Consumption  Switching frequency  TEMPERATURE CHARACTERISTICS  Parameter	Input to output Output to output Primary to Output 1 VHA Primary to Output 2 VHB Primary to Output 3 VHC Primary to Output 4 VL  Conditions Disable pin pulled low  Conditions	Min.	15 15 15 Typ.	8 8 Max.	pF Units mW
Creepage & clearance  Isolation capacitance  GENERAL CHARACTERISTICS  Parameter  Power Consumption  Switching frequency  TEMPERATURE CHARACTERISTICS  Parameter  Operation	Input to output Output to output Primary to Output 1 VHA Primary to Output 2 VHB Primary to Output 3 VHC Primary to Output 4 VL  Conditions Disable pin pulled low	Min. -40	15 15 15 Typ. 45 100	8 8 Max.	pF Units mW kHz Units
Creepage & clearance  Isolation capacitance  GENERAL CHARACTERISTICS  Parameter  Power Consumption  Switching frequency  TEMPERATURE CHARACTERISTICS  Parameter	Input to output Output to output Primary to Output 1 VHA Primary to Output 2 VHB Primary to Output 3 VHC Primary to Output 4 VL  Conditions Disable pin pulled low  Conditions	Min.	15 15 15 Typ. 45 100	8 8 Max.	pF Units mW kHz

ABSOLUTE MAXIMUM RATINGS	
Short-circuit protection	Continuous
Input voltage, MGJ6 5V input types	12V
Input voltage, MGJ6 12V input types	20V
Input voltage, MGJ6 24V input types	40V



5.7kVDC 6W Quad Output Isolated Gate Drive SM DC-DC Converters

#### **TECHNICAL NOTES**

#### **ISOLATION VOLTAGE**

'Hi Pot Test', 'Flash Tested', 'Withstand Voltage', 'Poof Voltage', 'Dielectric Withstand Voltage' & 'Isolation Test Voltage' are all terms that relate to the same thing, a test voltage, applied for a specified time, across a component designed to provide electrical isolation, to verify the integrity of that isolation.

Murata Power Solutions MGJ6 series of DC-DC converters are all 100% production tested at 4kVACrms for 1 second from input to output and 2.5kVACrms for 1 second from output to output. Also they are all qualification tested at 5.7kVDC for 1 minute from input to output and 3kVDC for 1 minute from output to output.

A question commonly asked is, "What is the continuous voltage that can be applied across the part in normal operation?"

When the insulation in the MGJ6 series is not used as a safety barrier, i.e. provides functional isolation only, continuous or switched voltages across the barrier up to 3kV are sustainable. Long term reliability testing at these voltages continues. Peak Inception voltages measured were in excess of 3.5kV when testing for partial discharge in accordance with IEC 60270. Please contact Murata for further information.

The MGJ6 series pending recognition by Underwriters Laboratory to 250 Vrms Reinforced Insulation, please see safety approval section below.

#### REPEATED HIGH-VOLTAGE ISOLATION TESTING

It is well known that repeated high-voltage isolation testing of a barrier component can actually degrade isolation capability, to a lesser or greater degree depending on materials, construction and environment. We therefore strongly advise against repeated high voltage isolation testing, but if it is absolutely required, that the voltage be reduced by 20% from specified test voltage.

#### **SAFETY APPROVAL**

#### **ANSI/AAMI ES60601-1**

The MGJ6 series is pending recognition ANSI/AAMI ES60601-1.

#### **UL 60950**

The MGJ6 series pending recognition by Underwriters Laboratory (UL) to UL 60950 for reinforced insulation to a working voltage of 250Vrms with a maximum measured product operating temperature of 105°C.

Creepage and clearance 8mm, input to output & across outputs.

#### **FUSING**

The MGJ6 Series of converters are not internally fused so to meet the requirements of UL an anti-surge input line fuse should always be used with ratings as defined below. Input Voltage, 5V 4A

Input Voltage, 12V 2A

Input Voltage, 24V 1A


All fuses should be UL recognized, 250Vac rated.

### CHARACTERISATION TEST METHODS Ripple & Noise Characterisation Method

Ripple and noise measurements are performed with the following test configuration.

C1	1µF X7R multilayer ceramic capacitor, voltage rating to be a minimum of 3 times the output voltage of the DC-DC converter
C2	$10\mu F$ tantalum capacitor, voltage rating to be a minimum of 1.5 times the output voltage of the DC-DC converter with an ESR of less than $100  \text{m}\Omega$ at $100  \text{kHz}$
C3	100nF multilayer ceramic capacitor, general purpose
R1	$450\Omega$ resistor, carbon film, $\pm 1\%$ tolerance
R2	$50\Omega$ BNC termination
T1	3T of the coax cable through a ferrite toroid
RLOAD	Resistive load to the maximum power rating of the DC-DC converter. Connections should be made via twisted wires
Measured va	lues are multiplied by 10 to obtain the specified values.

Differential Mode Noise Test Schematic



#### www.murata-ps.com/support


5.7kVDC 6W Quad Output Isolated Gate Drive SM DC-DC Converters


#### Rohs Compliance, MSL and PSL Information




This series is compatible with Pb-Free soldering systems and is also backward compatible with Sn/Pb soldering systems. The MGJ6 three phase series has a process, moisture, and reflow sensitivity classification of MSL2 PSL R7F as defined in J-STD-020 and J-STD-075. This translates to: MSL2 = 1 year floor life, PSL R7F = Peak reflow temperature 245°C with a limitation on the time above liquidus (217°C) which for this series is 90sec max. The pin termination finish on this product series is Gold with Nickel Pre-plate.

#### EFFICIENCY VS LOAD










5.7kVDC 6W Quad Output Isolated Gate Drive SM DC-DC Converters



Derating curves are based on IPC-9592. With no derating some components may be operating at the manufacturers maximum temperature ratings.








5.7kVDC 6W Quad Output Isolated Gate Drive SM DC-DC Converters

#### EMC FILTERING AND SPECTRA

#### FILTERING


The following filter circuit and filter table shows the input filters typically required to meet conducted emissions limits for EN 55022 curve B using Quasi-Peak (pink line) and average (green line) detectors according to CISPR22. The following plots show measurements of the positive (L1) and negative (L2) inputs for both Quasi-peak limit B adherence and Average limit B adherence. If a high dv/dt above 80kV/us is expected from output to input it is advised that a common mode filter is used on each output as this will reduce the common mode current circulating between outputs and input and causing interference.





C1, C2 & C3 Polyester or ceramic capacitor


C4 Electrolytic capacitor (note R1 could be omitted if C4 has ESR >= R1)


TO MEET CURVE B							
Part Number	C1	L1	Part Number	C2	C3	R1	C4
MGJ6Q05P24MC	10μF	1mH	51105C	1nF	1nF	1Ω	470µF
MGJ6Q12P24MC	10μF	1mH	51105C	1nF	1nF	1Ω	470µF
MGJ6Q24P24MC	10µF	1mH	51105C	1nF	1nF	1Ω	470µF













5.7kVDC 6W Quad Output Isolated Gate Drive SM DC-DC Converters

#### **APPLICATION NOTES**

#### Start-up times

Typical start up times for this series, with recommended maximum additional output capacitance are:

Part No.	Start-up times
rait No.	ms
MGJ6Q05P24MC	30
MGJ6Q12P24MC	30
MGJ6Q24P24MC	30

Output capacitance must not exceed:

Output Voltage	Maximum output capacitance
V	μF
24 VHA	18
24 VHB	18
24 VHC	18
24 VL	56

#### Disable/Frequency synchronisation

Please refer to application notes for further information.

		Min	Тур	Max	Units
Disable/Synch (Pin is active low)	Pull Down Current		0.5		mA
	Input High	2		5	V
	Input Low	0		8.0	V
Cunchronication	Frequency Range	90	100	110	kHz
Synchronisation	Duty Cycle	25		75	%

The Disable/Synchronization pin has three modes:

- 1. When a dc logic low voltage is applied to this pin the MGJ6 is disabled and enters a low guiescent current sleep mode.
- 2. When this pin is left floating or a dc logic high (CMOS/TTL compatible) voltage is applied the MGJ6 is enabled and operates at the programmed frequency of 100kHz.
- 3. When a square wave of between 90kHz and 110kHz is applied to this pin, the switcher operates at the same frequency as the square wave. The falling edge of the square wave corresponds to the start of the switching cycle. If the signal is slower than 25Hz, it will be interpreted as enabling and disabling the part. If the MGJ6 is disabled, it must be disabled for 7 clock cycles before being re-enabled.


The DIS/Sync pin is a high impedance TTL input and can be triggered by noise from external circuits if not treated carefully. It is advised that any pcb traces connected to the DIS/Sync pin are kept as short as possible and away from other noisy pcb traces. The track should follow a similar route to the return path to avoid differential noise pick up. If the pin is not used for synchronisation then a 22nF capacitor can be added from DIS/Sync pin to -Vin to suppress noise.


#### Output configurations for power switches

There are several zener based divider circuits that can be used to configure a bipolar output for gate drives as shown below. The table below shows suggested component values for various power switches using circuit A.

Component	IGBT	SIC	MOSFET
Zener diode <sup>1</sup>	9V1	5V1	9V1
Resistor	15K	18K	15K

1. Suggested zener diode is BZX84C.





5.7kVDC 6W Quad Output Isolated Gate Drive SM DC-DC Converters

#### **APPLICATION NOTES (Continued)**


For convenience the four isolated 24V outputs have been labelled VHA (Voltage A for high side), VHB (Voltage B for high side), VHC (Voltage C for high side) and VL (Voltage for low side) however they can be swapped if this helps to improve system layout. It is recommended however that if VHA, VHB or VHC are used in place of VL that an additional 4.7uF ceramic capacitor is added close to the output pins to reduce ripple voltage.

Any output can be connected in parallel with another and all three outputs can also be connected in series with one another. With the possibility of series and parallel output connections a number of output configurations are possible. Some are shown below:

A) 24V @ 0.25A

- B) 96V @ 0.063A output
- C) +24V/-48V @ 0.063A
- D) +/-48V @ 0.063A
- E) Non-isolated +12V to +108V boost converter @0.063A

Note: Any single 24V output can deliver up to 3W however the






5.7kVDC 6W Quad Output Isolated Gate Drive SM DC-DC Converters

### **APPLICATION NOTES (Continued)**


#### **SLIC Circuits**

Power source is preferred to the telephone system power due to either the power quality of the telecommunications system power supply or to avoid potential power line disturbances, such as lightning strikes and access switching, which will affect the target circuit function.


Another application area is in fibre-in-the-loop (FITL) or radio-in-the-loop (RITL) interfacing via a standard telecommunication SLIC, where the usual telecommunication battery voltage is not available due to the transmission media in use (fibre or radio). In particular, FITL/RITL interfaces directly on PC cards, in local monitor and boost circuits and at exchanges between the fibre/radio and wire media. The supply rails can be used for ringing generators as well as SLIC circuits or where both are combined, such as in the AMD AM79R79 Ringing SLIC device (see figure 2). The -72V rail is used primarily for the generation of the ringing signal (VBAT1), the -48V rail is used to supply in line access circuitry (VBAT2) and the -24V supply for the on-chip regulator for the logic interface (VNEG). Alternative devices from other manufacturers could use the  $\pm$ -24V outputs for their internal circuit supply and  $\pm$ 72V for ringing.




















## Murata Power Solutions MGJ6 Three Phase Bridge Series

5.7kVDC 6W Quad Output Isolated Gate Drive SM DC-DC Converters





This product is subject to the following operating requirements and the Life and Safety Critical Application Sales Policy: Refer to: http://www.murata-ps.com/requirements/

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not infly the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.