

Medical Power Supply

From The World's No.1 Power Supply Company



www.DeltaPSU.com



Medical Power Supply

Product Introduction

Enclosed Power Supply

MDS



AR

- Safety approvals for medical and IT applications
- Compliant with IEC 60601-1-2 4th Ed. requirements
- Suitable for type BF medical product
- Remote on/off control
- Power Good signal

Open Frame Power Supply

MDS



AR

- Safety approvals for medical and IT applications
- 2 × MOPP isolation
- Low touch current (< 0.1mA Normal & < 0.3mA Single Fault)
- Compliant with IEC 60601-1-2 4th Ed. Requirements
- Power Good Signal, Remote Sense, Remote inhibit


MEB



AR

- Safety approvals for medical and IT applications
- 2 × MOPP isolation, Suitable for type BF medical products
- IEC 60601-1-2 4th Edition Immunity Compliance
- PMBus Ver 1.3 supported
- Intelligent fan speed control



MEU



AR

- Safety approvals for medical and IT applications
- 2 × MOPP isolation
- 5V/1A standby output and 12V/0.6A fan output
- Compliant with IEC 60601-1-2 4th Ed. Requirements

MEP



AR

- Safety approvals for medical and IT applications
- 2 × MOPP
- Compliant with IEC 60601-1-2 4th Ed. Requirements
- Low leakage current (<70uA Normal & 210uA single fault)

Adapter

MDS



- Safety approvals for medical and IT applications
- Over-Voltage/Load/Temperature & Short Circuit Protections
- Low touch current (< 0.1mA Normal & < 0.3mA Single Fault)
- Compliant with IEC 60601-1-2 4th Ed. Requirements
- 2 × MOPP isolation

ATX Power Supply

MDS



- Safety approvals for medical and IT applications
- Compliant with IEC 60601-1-2 4th Ed. Requirements
- Suitable for type BF patient access applications
- ATX 12V standard function & form factor
- Maximum output power of 350 watts
- Built-in active PFC

MEA



- Safety approvals for medical and IT applications
- Compact Size and High Power Density
- High Efficiency meet DoE VI
- High MTBF
- 2 × MOPP isolation

Configurable Power Supply

MEF



- Safety Approvals for medical and IT applications
- 2 × MOPP isolation
- Compliant with IEC 60601-1-2 4th Ed. Requirements
- Meets Limited Power Source (LPS) requirements
- IP22 ingress protection rating

MEG



- Safety Approvals for medical and IT applications
- 2 × MOPP isolation
- Output selectable from 2Vdc to 60Vdc
- Normal and Reversed Option for Global Remote On/Off
- Analog and Digital Voltage Trimming
- PMBus Ver 1.3 Supported

Medical Power Supply

Product Introduction

Product Type	Series	Model Name	CC Code	Input Terminal	Output Voltage	Convection		Forced Air		Dimensions (L x W x H)	
						Current	Power	Current	Power		
Enclosed Power Supply	MDS	MDS-200ADB12	AA	Molex 2-pin	12V	9.17A	110W	16.67A	200W	64.7 × 113.9 × 44.7 mm (2.5" × 4.5" × 1.8")	
		MDS-250ADB12	AA	Molex 2-pin		12.5A	150W	20.84A	250W	64.7 × 113.9 × 44.7 mm (3.5" × 5.5" × 1.75")	
		MDS-300ADB12	AA	Molex 2-pin		15.83A	190W	25.0A	300W	64.7 × 113.9 × 44.7 mm (3.5" × 5.5" × 1.75")	
		MDS-400ADB12	AA	Molex 2-pin		-	-	33.33A	400W	64.7 × 113.9 × 44.7 mm (3.5" × 5.5" × 1.75")	
		MDS-300ADB18	AA	Molex 2-pin	18V	10.55A	190W	16.66A	300W	(64.7 × 113.9 × 44.7 mm (3.5" × 5.5" × 1.75"))	
		MDS-200ADB24	A	Molex 2-pin	24V	5.0A	120W	8.33A	200W	64.7 × 113.9 × 44.7 mm (2.5" × 4.5" × 1.8")	
		MDS-250ADB24	AA	Molex 2-pin		5.62A	150W	10.41A	250W	64.7 × 113.9 × 44.7 mm (3.5" × 5.5" × 1.75")	
		MDS-300ADB24	AA	Molex 2-pin		8.75A	210W	12.5A	300W	64.7 × 113.9 × 44.7 mm (3.5" × 5.5" × 1.75")	
		MDS-400ADB24	AA	Molex 2-pin		-	-	16.67A	400W	64.7 × 113.9 × 44.7 mm (3.5" × 5.5" × 1.75")	
		MDS-300ADB48	AA	Molex 2-pin	48V	4.375A	210W	6.25A	300W	64.7 × 113.9 × 44.7 mm (3.5" × 5.5" × 1.75")	
	MEB • Intelligent Fan Speed Control • PMBus Ver 1.3 Supported	MEB-500A24F	AA	DECA 3-pin	24V	-	-	21.0A	500W	85.2 × 165.3 × 41 mm (3.35" × 6.5" × 1.61")	
		MEB-1K2A24T	AAA	Terminal Block 3-pin		-	-	50.0A	1200W	127 × 204 × 40.5 mm (5.0" × 8.03" × 1.59")	
		MEB-1K2A42T	AAA	Terminal Block 3-pin		42V	-	-	28.5A	1200W	127 × 204 × 40.5 mm (5.0" × 8.03" × 1.59")
		MEB-1K2A48T	AAA			48V	-	-	25.0A	1200W	127 × 204 × 40.5 mm (5.0" × 8.03" × 1.59")
Open Frame Power Supply	MDS	MDS-040APS12 B	A	JST 2-pin	12V	3.33A	40W	-	-	50.8 × 76.2 × 23 mm (2.0" × 3.0" × 0.9")	
		MDS-065APS12 B	A	JST 2-pin		5.42A	65W	-	-	50.8 × 101.6 × 30 mm (2.0" × 4.0" × 1.2")	
		MDS-100APS12 B	A	JST 2-pin		8.33A	100W	-	-	76.2 × 127 × 31 mm (3.0" × 5.0" × 1.2")	
		MDS-100BPS12 B	A	JST 2-pin		6.67A	80W	8.33A	100W	50.8 × 101.6 × 31.8 mm (2.0" × 4.0" × 1.25")	
		MDS-200APB12*	AA	Molex 2-pin		10.83A	130W	16.67A	200W	50.8 × 101.6 × 35.6 mm (2.0" × 4.0" × 1.4")	
		MDS-250APB12*	AA	Molex 2-pin		12.5A	150W	20.84A	250W	76.2 × 127 × 36.1 mm (3.0" × 5.0" × 1.4")	
		MDS-300APB12*	AA	Molex 2-pin		18.33A	220W	25.0A	300W	76.2 × 127 × 35.6 mm (3.0" × 5.0" × 1.4")	
		MDS-400APB12*	AA	Molex 2-pin		-	-	33.33A	400W	76.2 × 127 × 35.6 mm (3.0" × 5.0" × 1.4")	
		MDS-040APS15 B	A	JST 2-pin	15V	2.67A	40W	-	-	50.8 × 76.2 × 23 mm (2.0" × 3.0" × 0.9")	
		MDS-065APS15 B	A	JST 2-pin		4.2A	65W	-	-	50.8 × 101.6 × 30 mm (2.0" × 4.0" × 1.2")	
		MDS-100APS15 B	A	JST 2-pin		6.67A	100W	-	-	76.2 × 127 × 31 mm (3.0" × 5.0" × 1.2")	
		MDS-100BPS15 B	A	JST 2-pin		5.3A	80W	6.7A	100W	50.8 × 101.6 × 31.8 mm (2.0" × 4.0" × 1.25")	
		MDS-040APS18 B	A	JST 2-pin		18V	2.22A	40W	-	-	50.8 × 76.2 × 23 mm (2.0" × 3.0" × 0.9")
		MDS-065APS18 B	A	JST 2-pin			3.61A	65W	-	-	50.8 × 101.6 × 30 mm (2.0" × 4.0" × 1.2")
		MDS-100APS18 B	A	JST 2-pin			5.55A	100W	-	-	76.2 × 127 × 31 mm (3.0" × 5.0" × 1.2")
		MDS-100BPS18 B	A	JST 2-pin			4.4A	80W	5.5A	100W	50.8 × 101.6 × 31.8 mm (2.0" × 4.0" × 1.25")
		MDS-300APB18*	AA	Molex 2-pin	12.22A		220W	16.66A	300W	76.2 × 127 × 35.6 mm (3.0" × 5.0" × 1.4")	
		MDS-400AUS19 B	A	DECA 3-pin	19V		15.8A	300W	21.1A	400W	97 × 198 × 41.50 mm (3.8" × 7.8" × 1.6")
		MDS-400AUS24 B	A	DECA 3-pin	24V		12.5A	300W	16.67A	400W	
		MDS-400AUS30 B	A	DECA 3-pin	30V		13.3A	300W	11.67A	400W	
		MDS-040APS24 B	A	JST 2-pin	24V	1.67A	40W	-	-	50.8 × 76.2 × 23 mm (2.0" × 3.0" × 0.9")	
		MDS-065APS24 B	A	JST 2-pin		2.71A	65W	-	-	50.8 × 101.6 × 30 mm (2.0" × 4.0" × 1.2")	

*Product with options for enclosed or Open Frame

Product Type	Series	Model Name	CC Code	Input Terminal	Output Voltage	Convection		Forced Air		Dimensions (L x W x H)
						Current	Power	Current	Power	
Open Frame Power Supply	MDS	MDS-100APS24 B	A	JST 2-pin	24V	4.17A	100W	-	-	76.2 x 127 x 31 mm (3.0" x 5.0" x 1.2")
		MDS-100BPS24 B	A	JST 2-pin		3.3A	80W	4.2A	100W	50.8 x 101.6 x 31.8 mm (2.0" x 4.0" x 1.25")
		MDS-200APB24*	AA	Molex 2-pin		5.83A	140W	8.33A	200W	50.8 x 101.6 x 35.6 mm (2.0" x 4.0" x 1.4")
		MDS-250APB24*	AA	Molex 2-pin		6.25A	150W	10.41A	250W	76.2 x 127 x 35.6 mm (3.0" x 5.0" x 1.4")
		MDS-300APB24*	AA	Molex 2-pin		10.0A	240W	12.5A	300W	76.2 x 127 x 35.6 mm (3.0" x 5.0" x 1.4")
		MDS-400APB24*	AA	Molex 2-pin		8.33A	200W	16.66A	400W	76.2 x 127 x 35.6 mm (3.0" x 5.0" x 1.4")
		MDS-300APB48*	AA	Molex 2-pin		48V	5.0A	240W	6.25A	300W
		MDS-100AP401 B	A	Molex 2-pin	5.1V/12V/-15V/15V	4A/2A/0.6A/0.8A	65W	8A/3A/0.8A/0.8A	100W	76.2 x 127 x 31 mm (3.0" x 5.0" x 1.2")
	MEP	MEP-25A15J	BNA	JWT 2-pin	15V	1.67A	25W	-	-	50.8 x 76.2 x 23 mm (2.0" x 3.0" x 0.9")
	MEU	MEU-600C24T	AAA	DINKLE 3-pin	24V	25.0A	600W	-	-	127 x 203.2 x 40 mm (5.0" x 8.0" x 1.57")
	MEU-600C48T	AAA	DINKLE 3-pin	48V	12.5A	600W	-	-	127 x 203.2 x 40 mm (5.0" x 8.0" x 1.57")	

*Product with options for enclosed or U-Frame

Product Type	Series	Model Name	CC Code	AC Inlet	Output Voltage	Output Current	Output Power	Dimensions (L x W x H)
Adapter	MDS	MDS-005AAS05 A	R	Wall mount-China type	5V	1.00A	5W	39.5 x 56.5 x 28 mm (1.6" x 2.2" x 1.1")
		MDS-005AAS05 B	R	Wall mount-Japan, USA type		1.00A	5W	39.5 x 56.5 x 28 mm (1.6" x 2.2" x 1.1")
		MDS-005AAS05 C	R	Wall mount-EU type		1.00A	5W	39.5 x 56.5 x 28 mm (1.6" x 2.2" x 1.1")
		MDS-030AAC05*		Duck Head	3.00A	15W	53.5 x 88 x 27.5 mm (2.1" x 3.5" x 1.1")	
		MDS-005AAS06 A	R	Wall mount-China type	6V	0.83A	5W	39.5 x 55.8 x 28 mm (1.6" x 2.2" x 1.1")
		MDS-005AAS06 B	R	Wall mount-Japan, USA type		0.83A	5W	39.5 x 55.8 x 28 mm (1.6" x 2.2" x 1.1")
		MDS-005AAS06 C	R	Wall mount-EU type		0.83A	5W	39.5 x 55.8 x 28 mm (1.6" x 2.2" x 1.1")
		MDS-030AAC07*		Duck Head	3.00A	21W	53.5 x 88 x 27.5 mm (2.1" x 3.5" x 1.1")	
		MDS-030AAC12*		Duck Head	2.00A	24W	53.5 x 88 x 27.5 mm (2.1" x 3.5" x 1.1")	
		MDS-060AAS12 B	A	C14	5.00A	60W	62 x 135 x 34.1 mm (2.4" x 5.3" x 1.3")	
		MDS-060BAS12 A	B	C8	5.00A	60W	62 x 135 x 34.1 mm (2.4" x 5.3" x 1.3")	
		MDS-080AAS12 A		C8	6.66A	80W	75 x 150 x 40 mm (3.0" x 5.9" x 1.6")	
		MDS-150AAS12 B	A	C14	10.00A	120W	85 x 170 x 40 mm (3.4" x 6.7" x 1.6")	
		MDS-030AAC15*		Duck Head	15V	2.00A	30W	39.5 x 56.5 x 28 mm (2.1" x 3.5" x 1.1")
		MDS-060AAS15 B	A	C14		4.00A	60W	62 x 135 x 34.1 mm (2.4" x 5.3" x 1.3")
		MDS-090AAS15 B	A	C14		6.00A	90W	60 x 150 x 35 mm (2.4" x 5.9" x 1.4")
		MDS-060AAS19 B	A	C14	19V	3.20A	60W	62 x 135 x 34.1 mm (2.4" x 5.3" x 1.3")
		MDS-060BAS19 A	A	C8		3.15A	60W	62 x 135 x 34.1 mm (2.4" x 5.3" x 1.3")
		MDS-090AAS19 B	A	C14		4.74A	90W	60 x 150 x 35 mm (2.4" x 5.9" x 1.4")
		MDS-150AAS19 B	A	C14	7.89A	150W	86.3 x 170.1 x 40.6 mm (3.4" x 6.7" x 1.6")	
		MDS-150CAB19	AA	C6	7.90A	150W	60 x 150 x 35 mm (2.6" x 5.9" x 1.3")	
		MDS-030AAC24*		Duck Head	24V	1.25A	30W	39.5 x 56.5 x 28 mm (2.1" x 3.5" x 1.1")
		MDS-060AAS24 B	A	C14		2.50A	60W	62 x 135 x 34.1 mm (2.4" x 5.3" x 1.3")
		MDS-060BAS24 A	A	C8		2.50A	60W	62 x 135 x 34.1 mm (2.4" x 5.3" x 1.3")
	MDS-090AAS24 B	A	C14	3.75A		90W	60 x 150 x 35 mm (2.4" x 5.9" x 1.4")	
	MDS-090BAS24 A	B	C8	3.75A		90W	75 x 150 x 40 mm (3.0" x 5.9" x 1.6")	
	MDS-150AAS24 B	A	C14	6.25A		150W	86.3 x 170.1 x 40.6 mm (3.4" x 6.7" x 1.6")	
	MEA	MEA-065A12C	A-A	C14		12V	5.0A	60W
		MEA-120A15B	G-A	C8	15V	8.0A	120W	167.6 x 83.8 x 38.1 mm (6.6" x 3.3" x 1.5")
		MEA-065A24C	A-A	C14	24V	2.71A	65W	50.0 x 115 x 29 mm (1.9" x 4.5" x 1.1")
		MEA-250A24C	H-A	C14		10.42A	250W	200 x 100 x 43 mm (7.8" x 3.9" x 1.7")
	MEF	MEF-010A05B	J-A	Wall mount-US type	5V	2.0A	5W	43 x 70 x 27.5 mm (1.7" x 2.8" x 1.1")

*Please refer to technical datasheet to get detailed information

Product Type	Series	Model Name	CC Code	AC Inlet	Output Voltage	Output Current	Output Power	Dimensions (L x W x H)
ATX Power Supply	MDS	MDS-350AD701	AA	C14	+3.3V, +5V, +5V _{SB} , +12V ₁ , +12V ₂ , -12V, -5V	8A, 9A, 1.25A, 8A, 8A, 0.25A, 0.1A	350W	100 × 194 × 40.5 mm (3.9" × 7.6" × 1.6")

Product Type	Series	Model Name	Output Slots	Output Voltage	Output Power	Dimensions (L x W x H)
Configurable Power Supply	MEG • PMBus Ver 1.3 Supported • IT & Medical safety approvals	MEG-1K2A4	4 Slots	Single Output: 2V-60V	1,200W	254 × 88.9 × 40.5 mm (10" × 3.5" × 1.59")
		MEG-2K1A6	6 Slots		2,100W	254 × 127 × 40.5 mm (10" × 5" × 1.59")

Model Numbering

Enclosed Power Supply

MDS –	XXX	□	□	□	□	□□
Delta Medical Power Supply MDS-200A series MDS-250A series MDS-300A series MDS-400A series	Max power wattage in the product series. May be lower at some conditions. 200 - 200W 250 - 250W	Family Code A	Product Type D - Enclosed P - Open Frame	Input Type Class II 2-pin connector: A, C, E, G... Class I 3-pin connector: B, D, F, H...	Output Voltage 12 - 12V 24 - 24V	CC Code For DC connector, label, etc. A - DC connector type ¹⁾
ME	B –	XXX	□	□□	□	□□□
Delta Medical Power Supply	B - Enclosed	Max power wattage in the product series. May be lower at some conditions. 500 - 500W 1K2 - 1,200W	Family Code A	Output Voltage 24 - 24V	Inlet Type T - Terminal F - Front Face	CC Code

1) Refer to technical datasheet or product catalog

Open Frame Power Supply

MDS –	XXX	□	□	□	□	□	□
Delta Medical Power Supply MDS-040APS series MDS-065APS series MDS-100APS series MDS-100BPS series MDS-400AUS series	Max power wattage in the product series. May be lower at some conditions. 040 - 40W 065 - 65W	Family Code A - Family A B - Family B	Product Type P - Open Frame U - U Frame	# of output S - Single Output	Output Voltage 12 - 12V 24 - 24V	Input Configuration B - Class I 3-pin connector A - Class II 2-pin connector	CC Code For DC connector, label, etc. A - DC connector ¹⁾
MDS –	XXX	□	□	□	□	□	□
Delta Medical Power Supply MDS-100AP401	Max power wattage in the product series. May be lower at some conditions. 100 - 100W	Family Code A	Product Type P - Open Frame	Output Voltage 401 - 5.1V, 12V, -15V, 15V	Input Configuration B - Class I with PE connection	CC Code For DC connector, label, etc. A - DC connector ¹⁾	
ME	P –	XX	□	□	□	□	□□□
Delta Medical Power Supply	P - Open Frame	Max power wattage in the product series. May be lower at some conditions. 25 - 25W	Family Code A	Output Voltage 15 - 15V	Input Connector J - Harness	CC Code	
ME	U –	XXX	□	□	□	□□□	
Delta Medical Power Supply	U - U Frame	Max power wattage in the product series. May be lower at some conditions. 600 - 600W	Family Code A - Family A C - Family C D - Family D	Output Voltage 24 - 24V 48 - 48V	Inlet Type T - Terminal	CC Code	

1) Refer to technical datasheet or product catalog

Model Numbering

Adapter

MDS –	XXX	□	□	□	□	□	□□
Delta Medical Power Supply MDS-005AAS series MDS-060AAS series MDS-060BAS series MDS-080AAS series MDS-090AAS series MDS-090BAS series MDS-150AAS series	Max power wattage in the product series. May be lower at some conditions. 005 - 5W 060 - 60W	Family Code A - Family A B - Family B	Product Type A - Adapter	# of Output S - Single Output	Output Voltage 12 - 12V 24 - 24V	Input Configuration A - C8 B - C14 C - NA For 005AAS A - CN B - US C - EU	CC Code For DC plug, cable length, label, etc.

MDS –	XXX	AAC	□	□	□
Delta Medical Power Supply MDS-030 series	Max power wattage in the product series. May be lower at some conditions. 030 - 30W	Family Code C	Output Voltage (Single Output) 05 - 5V 07 - 7V 12 - 12V 15 - 15V ¹⁾ 24 - 24V	CC Code DC plug type and output cable length A - 2.1 × 5.5 × 10 mm DC plug, and 1200 mm cable length B - 2.1 × 5.5 × 12 mm DC plug, and 1200 mm cable length ²⁾	CC Code Country Duck Head Type A - China B - United States ²⁾ C - European ²⁾ D - United Kingdom ²⁾ E - Australia ²⁾ G - Korea ²⁾ H - India ²⁾ J - Argentina ²⁾ K - Brazil ²⁾ M - South Africa ²⁾

MDS –	XXX	□	□	□	□□	□□
Delta Medical Power Supply MDS-150CAB19A	Max power wattage in the product series. May be lower at some conditions. 150 - 150W	Family Code C	Product Type A - Adapter	Input Connector Type A, C, E, G - Class II C8/C18 B, D, F, H - Class I C6/C14	Output Voltage 19 - 19V	CC Code AA - ZX Power cord length, plug, label, etc.

ME	A –	XXX	□	□□	□	□□
Delta Medical Power Supply	A - Desktop Adapter	Max power wattage in the product series. May be lower at some conditions. 065 - 65W 120 - 120W 250 - 250W	Family Code A	Output Voltage 12 - 12V 15 - 15V 24 - 24V	Input Connector Type B - Class II C8 C - Class I C14	CC Code For DC plug, cable length, label, etc.

ME	F –	XXX	□	□□	B	□□
Delta Medical Power Supply	F - Fixed	Max power wattage in the product series. May be lower at some conditions. 010 - 10W	Family Code A	Output Voltage 05 - 5V	Country Duck Head Type B - United States (2-pin)	CC Code For DC plug, cable length, label, etc.

1) MDS-030AAC15 BB is not available
2) Options

ATX Power Supply

MDS –	XXX	□	□	□	□□
Delta Medical Power Supply MDS-350AD701	Max power wattage in the product series. May be lower at some conditions. 350 - 350W	Family Code A	Product Type D - Enclosed	Output Voltage 701 - +3.3V, +5V, +5V _{SB} , +12V ₁ , 12V ₂ , -12V, -5V	CC Code

Configurable Power Supply

ME	G –	XXX	A	□
Delta Medical Power Supply	G - Configurable	Max power wattage in the product series. May be lower at some conditions. 1K2 - 1,200W 2K1 - 2,100W	Family Code A	Slot Number 4 - 4 Slots 6 - 6 Slots



To learn more about Medical power supply
Please visit our website.

GLOBAL OPERATION AND SERVICE



ASIA

Delta Electronics, Inc.

3 Tungyuan Road, Chungli Industrial Zone,
Taoyuan County 32063, Taiwan, R.O.C

TEL: +886 3 452 6107
FAX: +886 3 434 3617

Delta Electronics (Shanghai) Co., Ltd. China Headquarters

No. 182 Minyu Road, Pudong,
Shanghai, P.R.C. 201209

TEL: +86 21 6872 3988
FAX: +86 21 6872 3996

Delta Electronics (Shanghai) Co., Ltd. Beijing Branch

No. 7 Building, 6th Courtyard, Beichen East Rd.,
Chaoyang Dist., Beijing, P.R.C. 100105

TEL: +86 10 8225 3225
FAX: +86 10 8225 1360

Delta Electronics (Thailand) PCL.

909 Soi 9, Moo 4, Bangpoo Industrial Estate
(E.P.Z.), Pattana 1 Rd., T. Phrakasa, A. Muang,
Samutprakarn 10280, Thailand

TEL: +662 709 2800
FAX: +662 709 2827

Delta Electronics India Pvt. Ltd.

Plot No. 43, Sector - 35, HSIIDC,
Gurgaon, Haryana 122001

TEL: +91 124 4874 900
+91 124 4169 040
FAX: +91 124 4874 945

Delta Electronics (Japan), Inc.

2-1-14 Minato-ku Shibadaimon,
Tokyo 105-0012, Japan

TEL: +81 3 5733 1111
FAX: +81 3 5733 1211

Delta Electronics (Korea), Inc.

1504, Byucksan Digital Valley 6-Cha,
Gasan-dong, Geumcheon-gu, Seoul,
153-704, Korea

TEL: +82 2 515 5303
+82 2 515 5305
FAX: +82 2 515 5302

Delta Electronics (Australia) Pty. Ltd

20-21, 45 Normanby Rd.
Nothing Hill, VIC 3168, Australia

TEL: +61 9543 3720
FAX: +61 9544 0606

Delta Energy Systems (Singapore) Pte. Ltd

4 Kaki Bukit Avenue 1
#05-04, Singapore 417939

TEL: +65 6747 5155
FAX: +65 6744 9228

NORTH AMERICA

Delta Electronics (Americas) Ltd. North American Headquarters

46101 Fremont Blvd.
Fremont, CA 94538, U.S.A.

TEL: +1 510 668 5100
FAX: +1 510 668 0680

CENTRAL & SOUTH AMERICA

Delta Electronics International Mexico S.A. de C.V.

Centrum Park, Av. Gustavo Baz Prada 309
Edificio E Planta Baja, Col. La Loma, C.P. 54030
Tlalnepanitla, Estado de México

TEL: +52 55 3603 9200

Delta Greentech (Brasil) S.A.

Rua Itapeva, 26 - 3º, andar - Bela Vista
01332-000 - São Paulo - SP - Brasil

TEL: +55 11 3568 3850
FAX: +55 11 3568 3865

EUROPE

Delta Electronics (Netherlands) B.V. EMEA Headquarters

Zandsteen 15, 2132 MZ Hoofddorp,
The Netherlands

TEL: +31 20 800 3900
FAX: +31 20 800 3999

De Witbogt 20
5652 AG Eindhoven, The Netherlands

TEL: +31 40 800 3800
FAX: +31 40 800 3898

www.DeltaPSU.com | info@deltapsu.com

October 2019 - All information and specifications are subjected to change without prior notice.