

0.50mm pitch FFC/FPC – F308/F332 Series

RIGHT ANGLE NON-ZIF FLEX AUTOLOCK CONNECTORS

F308/F332 series is a 0.50mm pitch right angle Non-ZIF flex connector with an auto lock mechanism and surface mount termination. It features a height of 2.45mm and comes in 6 to 68 contacts. This series features a cable thickness of 0.33mm and provide durability of 20 mating cycles. Its robust connector design makes it suitable for robotic operations, supporting Industry 4.0. These are also ideal for automotive, data, industrial, communication, consumer and medical applications.

- Allows one-handed operation and ease of assembly
- Strong FFC/FPC retention makes it vibration-proof
- GND terminals to prevent noise
- Ensures high durability



FEATURES

- Non-ZIF (Zero Insertion Force) mechanism requires some force for insertion
- Autolock mechanism
- Provision for GND terminal
- High temperature thermoplastic housing
- 6 to 68 positions available
- Lead and halogen-free

BENEFITS

- Strong FFC/FPC retention makes it vibration-proof
- Allows one-handed operation and ease of assembly
- Prevents noise
- Wide operating temperature range of -55°C to $+105^{\circ}\text{C}$
- Comprehensive range to satisfy different customer requirements
- Meets environmental, health and safety requirements

▶ 0.50mm pitch FFC/FPC – F308/F332 Series

TECHNICAL INFORMATION

MATERIAL

- Housing: LCP, black color (UL94V-0)
- Actuator: PPS, black color (UL94V-0)
- Contact : Copper alloy, T=0.15mm
- GND Terminal: Copper alloy, T=0.20mm
- Lock Terminal: T=0.12mm, thermostable

MECHANICAL PERFORMANCE

- FFC/FPC Retention Force: 25gf/terminal min.
- Insertion force: 0.5N x n + 4N max.
- Un-mating force: 0.1N x n min.
- Durability: 20 mating cycles

ELECTRICAL PERFORMANCE

- Voltage Rating: 50V AC/DC
- Current Rating: 0.5A
- Contact Resistance: (Initial) 60MΩ max., (final) 40MΩ max.
- Insulation Resistance: 100MΩ min.
- Dielectric Withstanding Voltage: No short or breakdown after 500V AC, 2mA, 1min.

PACKAGING

- Tape & Reel

APPROVALS AND CERTIFICATIONS

- UL file number E106764
- RoHS compliant

SPECIFICATION

- Aorora Product Specification: IS.EQC.155

ENVIRONMENTAL

- Operating Temperature Range: -55°C to +105°C

TARGET MARKETS/APPLICATIONS



Car Multimedia
Car Navigation
Dashboard
PND



Base Station
Power
Switches



Notebook
Tablets
Wearables
Gaming
DSC
LCD & PDP TV




Router
Server
ODD
HDD



Sensing element
Monitoring camera
Human Machine Interface
Industrial PC
Robotics

Ultrasonic
Patient Monitor
MRI
CT
Infusion Pump

PART NUMBER SELECTOR



AORORAF308F332052IEA4