

# Product Overview



# Rechargeable Batteries

## Rechargeable Lithium Battery Range

### Rechargeable Button Cells (Li-Ion) CoinPower

TYPE DESIGNATION	TYPE NO.	VOLTAGE (V)	CAPACITY (mAh)	DIAMETER (mm)	HEIGHT (mm)	LENGTH (mm)	WIDTH (mm)	WEIGHT (g)
<b>Main types</b>								
CP 1654 A4	63165	3.7	155	16.1	5.4			3.2
CP 1454 A4	63145	3.7	114	14.1	5.4			2.4
CP 1254 A4	63125	3.7	77	12.1	5.4			1.6
CP 1250 A4	63121	3.7	62	12.1	5.0			1.6
CP 1240 A4	63124	3.7	55	12.1	4.0			1.2
<b>Special types</b>								
CP 9454 A4	63095	3.7	41	9.4	5.4			1.0
CP 9440 A4	63094	3.7	29	9.4	4.0			0.8

Further types on request

## Rechargeable NiMH Battery Range

### Rechargeable Button Cells (NiMH)

TYPE DESIGNATION	TYPE NO.	VOLTAGE (V)	CAPACITY (mAh)	DIAMETER (mm)	HEIGHT (mm)	LENGTH (mm)	WIDTH (mm)	WEIGHT (g)
<b>V...H robust</b>								
V 15 H	55602	1.2	16	11.5	3.10			1.30
V 40 H	55604	1.2	43	11.5	5.35			1.70
V 80 H	55608	1.2	80	15.5	6.00			4.00
V 150 H	55615	1.2	150		5.85	14.1	25.6	6.00
V 200 H	55620	1.2	210		7.40	14.1	25.6	7.00
V 250 H	55625	1.2	250	25.1	6.70			10.00
CP 300 H	55630	1.2	300	25.1	7.55			11.00
<b>V...HT robust85C</b>								
V 65 HT	55707	1.2	70	15.5	6.00			4.00
V 150 HT	55716	1.2	150		5.85	14.1	25.6	6.00
<b>V...HR powerfut</b>								
V 6 HR	55996	1.2	6.2	6.8	2.15			0.28
V 450 HR	55945	1.2	450		5.60	24.1	34.1	12.50
V 600 HR	55960	1.2	600		6.80	24.1	34.1	14.50
<b>V...HRT powerful85C</b>								
V 18 HRT	55802	1.2	19	11.5	2.30			0.90
V 150 PT	55815	1.2	150		3.60	24.1	34.1	7.50
V 500 HT	55750	1.2	510		6.60	24.2	34.1	14.00
V 550 HRA	55855	1.2	550		6.80	24.1	34.1	14.50
V 600 HRT	55860	1.2	600		6.80	24.1	34.1	14.50

Not all product types are available at the time of printing.  
Voltage and Capacity indicated refer to nominal and typical values respectively.

## Rechargeable Cylindrical Cells (NiMH)

VH 700 AAA	55171	1.2	730	10.5	43.7			13.0
VH 1800 AA	55123	1.2	1850	14.5	49.2			27.0
VH 2200 AA	55022	1.2	2250	14.5	49.5			30.5
VH 2100 4/5A	55021	1.2	2160	17.0	43.0			33.0
VH 2700 A	55027	1.2	2700	17.0	50.0			39.5
VH 4000 4/3 A	55038	1.2	3820	17.5	67.0			53.5
VH 4500 4/3 FA	55044	1.2	4500	18.3	67.0			63.0

## 9V Battery (NiMH)

V 7/8 H ECO	05522	8.4	150		15.7	48.5	26.6	47.0
V 7/8 H ULTRA	05622	8.4	150		15.7	48.5	26.6	47.0

## CellPac LITE

### Rechargeable Lithium-Polymer and Lithium-Ion / Standard Battery Packs

DESCRIPTION	ORDER CODE (VKB)	CAPACITY (mAh)	HEIGHT (mm)	LENGTH (mm)	WIDTH (mm)	VOLTAGE (V)
<b>Li-Cylindrical Types</b>						
1/LIC 18650-26 SKE PCM S WC	56653 201 012	2600	19.70	71.2		3.65
2S/LIC 18650-26 SKE PCM S WC	56653 502 012	2600	18.90	70.4	38.0	7.30
2P/LIC 18650-26 SKE PCM S WC	56653 502 013	5200	21.00	70.0	37.7	3.65
1/LIC 21700-40 SAE PCM S WC – SOC 30%	56658 201 099	4000	23.20	78.5		3.65
2S/LIC 21700-40 SAE PCM S WC – SOC 30%	56658 502 099	4000	44.50	78.5	22.3	7.30
2P/LIC 21700-40 SAE PCM S WC – SOC 30%	56658 502 098	8000	44.50	76.5	22.3	3.65
<b>Li-Polymer / Li-Ion Pouch Types</b>						
1/LPP 523450 S PCM W	56457 201 012	1000	5.30	52.0	34.5	3.70
2P/LPP 503562 S PCM WC	56456 302 012	2400	10.60	64.5	35.5	3.70
1/LPP 503759 8HH PCM W	56427 201 020	1400	5.40	60.5	37.5	3.70
1/LPP 443441 S PCM W	56455 201 012	660	4.35	41.5	34.0	3.70
1/LPP 423566 BE PCM W	56437 201 012	1160	4.60	67.0	35.5	3.70
1/LPP 503562 S PCM W	5645 6201 012	1200	5.60	63.5	35.5	3.70

### EasyPack Range

EasyPack S	56455 701 099	660	5.80	43.5	35.4	3.70
EasyPack L	56456 701 099	1200	6.40	64.5	36.6	3.70
EasyPack XL	56456 702 099	2400	11.40	64.5	36.6	3.70
EasyPack PLUS	56653 702 099	5200	21.00	74.9	40.4	3.70

### Application Specific Batteries

Easy Block 24 V	56650 764 099	22.80	171	256	197	25.6
Easy Block 48 V	56650 764 098	11.40	171	256	197	51.2
Easy Blade 24 V	56654 799 098	64.00	230	330	80	25.9
Easy Blade 48 V	56654 799 097	32.00	230	330	80	51.8

## CellPac PLUS

CellPac PLUS is a custom battery design service by VARTA Storage. It combines the company's cell and electronics knowledge and experience of designing batteries for electronic applications for industrial, medical, robotics and communications markets. CellPac PLUS offers a total project management, end to end battery design solution from the initial specification to product manufacture.

The design and development process includes

- Mechanical design
- Chemical architecture
- Electrical and electronic design
- Embedded vs. removable battery
- Certification and testing



For further information please visit [www.varta-storage.com](http://www.varta-storage.com)

## CellPac BLOX

CellPac BLOX from VARTA Storage suits customers in need of semi-customization and where design-cycles, engineering costs and time to market must be minimized for success. Battery designs are limited in their complexity, but available for minimal NRE cost in many cases and minimal development effort. It is designed as a portfolio of cells and PCMs which can be ordered under the CellPac BLOX program. All possible combinations have been reviewed and safety-tested by VARTA in advance to ensure a good fit and function between the cell and electronics.

# Primary Batteries

## Silver Oxide Button Cells (Ag<sub>2</sub>O)

TYPE DESIGNATION	TYPE NO.	VOLTAGE (V)	CAPACITY (mAh)	DIAMETER (mm)	HEIGHT (mm)	LENGTH (mm)	WIDTH (mm)	WEIGHT (g)
<b>Mercury-free</b>								
V 301 MF	20301	1.55	82	11.6	4.20			1.78
V 303 MF	20303	1.55	160	11.6	5.40			2.33
V 309 MF	20309	1.55	73	7.9	5.40			1.08
V 315 MF	20315	1.55	20	7.9	1.65			0.33
V 317 MF	20317	1.55	10.5	5.8	1.60			0.18
V 319 MF	20319	1.55	21	5.8	2.66			0.29
V 321 MF	20321	1.55	14.5	6.8	1.65			0.25
V 329 MF	20329	1.55	37	7.9	3.10			0.60
V 335 MF	20335	1.55	6	5.8	1.25			0.15
V 337 MF	20337	1.55	9	4.8	1.65			0.13
V 339 MF	20339	1.55	12	6.8	1.40			0.21
V 341 MF	20341	1.55	15	7.9	1.45			0.28
V 344 MF	20344	1.55	105	11.6	3.60			1.49
V 346 MF	20346	1.55	10	7.9	1.29			0.30
V 350 MF	20350	1.55	105	11.6	3.60			1.49
V 357 MF	20357	1.55	145	11.6	5.40			2.33
V 361 MF	20361	1.55	22	7.9	2.10			0.40
V 362 MF	20362	1.55	21	7.9	2.10			0.40
V 364 MF	20364	1.55	17	6.8	2.15			0.31
V 370 MF	20370	1.55	30	9.5	2.10			0.57
V 371 MF	20371	1.55	30	9.5	2.10			0.61
V 373 MF	20373	1.55	28	9.5	1.60			0.50
V 377 MF	20377	1.55	21	6.8	2.60			0.34
V 379 MF	20379	1.55	15	5.8	2.15			0.23
V 381 MF	20381	1.55	49	11.6	2.10			0.90
V 384 MF	20384	1.55	37	7.9	3.60			0.69
V 386 MF	20386	1.55	115	11.6	4.20			1.78
V 389 MF	20389	1.55	81	11.6	3.05			1.31
V 390 MF	20390	1.55	59	11.6	3.05			1.32
V 391 MF	20391	1.55	42	11.6	2.10			0.90
V 392 MF	20392	1.55	40	7.9	3.60			0.69
V 393 MF	20393	1.55	77	7.9	5.40			1.08
V 394 MF	20394	1.55	58	9.5	3.60			1.04
V 395 MF	20395	1.55	38	9.5	2.70			0.68
V 396 MF	20396	1.55	32	7.9	2.60			0.55
V 397 MF	20397	1.55	23	7.9	2.60			0.50
V 399 MF	20399	1.55	42	9.5	2.70			0.75

## Lithium Cylindrical Cells (Li-MnO<sub>2</sub>)

TYPE DESIGNATION	TYPE NO.	VOLTAGE (V)	CAPACITY (mAh)	DIAMETER (mm)	HEIGHT (mm)	WEIGHT (g)
<b>CR mass / bobbin series</b>						
CR 1/2 AA	6127	3.0	950	14.75	25.1	11.5
CR 2/3 AA	6237	3.0	1350	14.75	33.5	15.0
CR AA	6117	3.0	2000	14.75	50.5	21.5
<b>CR coiled series</b>						
CR 2	6206	3.0	850	15.60	27.0	11.0
CR 123 A	6205	3.0	1550	17.00	34.5	17.0
CR 2/3 AH	6215	3.0	1500	17.00	33.5	17.0
CR 1/2 AAH-R	6213	3.0	850	14.22	25.0	9.0
CR 2/3 AH-R	6214	3.0	1600	17.00	33.5	17.0
CR AH-R	6217	3.0	2400	17.00	45.0	23.0

## Lithium Button Cells (Li-MnO<sub>2</sub>)

<b>CR coin series</b>						
CR 1216	6216	3.0	27	12.5	1.6	0.7
CR 1220	6220	3.0	35	12.5	2.0	0.8
CR 1616	6616	3.0	55	16.0	1.6	1.2
CR 1620	6620	3.0	70	16.0	2.0	1.2
CR 2016	6016	3.0	90	20.0	1.6	1.8
CR 2025	6025	3.0	165	20.0	2.5	2.5
CR 2032	6032	3.0	230	20.0	3.2	3.0
CR 2430	6430	3.0	300	24.5	3.0	4.0
CR 2450	6450	3.0	620	24.5	5.0	6.2
CR 1/3 N	6131	3.0	170	11.6	10.8	3.0

## Alkaline Manganese Button Cells (Zn-MnO<sub>2</sub>)

<b>Mercury-free</b>						
V 13 GA	24276	1.5	155	11.6	5.40	2.0
V 23 GA	24223	12.0	50	10.3	28.50	7.9

## Hydrogen Gas Generating Cells (H<sub>2</sub> Cells)\*

<b>Mercury-free</b>						
V 150 H <sub>2</sub> MF	24690	150 ml		11.6	5.5	1.65
V 40 H <sub>2</sub> MF**	24696	40 ml		7.8	5.5	0.85

\* Portable energy independent H<sub>2</sub> gas generating cells

\*\* R&D Samples

For more details see: [www.varta-microbattery.com/top/h2](http://www.varta-microbattery.com/top/h2)

## VARTA Industrial Pro Alkaline Cylindrical Cells

TYPE DESIGNATION	TYPE NO.	VOLTAGE (V)	CAPACITY (mAh)	DIAMETER (mm)	HEIGHT (mm)	LENGTH (mm)	WIDTH (mm)	WEIGHT (g)
<b>LR 3</b>								
Micro/AAA/AM 4	04003	1.5	1270	10.5	44.5			11
<b>LR 6</b>								
Mignon/AA/AM 3	04006	1.5	2970	14.5	50.5			23
<b>LR 14</b>								
Baby/C/AM 2	04014	1.5	7800	26.0	50.0			69
<b>LR 20</b>								
Mono/D/AM 1	04020	1.5	17000	34.0	61.0			141
<b>6 LR 61</b>								
E-Block/6 AM 6	04022	9.0	640		17.5	48.5	26.5	46

## Hearing Aid Batteries

### power one

#### Mercury-free

TYPE DESIGNATION	TYPE NO.	VOLTAGE (V)	CAPACITY (mAh)	DIAMETER (mm)	HEIGHT (mm)	WEIGHT (g)
p675	24600	1.45	650	11.6	5.4	1.85
p312	24607	1.45	170	7.9	3.6	0.58
p13	24606	1.45	300	7.9	5.4	0.83
p10	24610	1.45	100	5.8	3.6	0.30
IMPLANT plus 675	24602	1.45	540	11.6	5.4	1.85

#### Rechargeable

p675 ACCU plus	54600	1.20	68	11.6	5.4	2.00
p312 ACCU plus	54607	1.20	21	7.9	3.6	0.60
p13 ACCU plus	54606	1.20	28	7.9	5.4	0.90
p10 ACCU plus	54610	1.20	11	5.8	3.6	0.30

### ecopack

#### Mercury-free

675	24600	1.45	620	11.6	5.4	1.85
312	24607	1.45	161	7.9	3.6	0.58
13	24606	1.45	285	7.9	5.4	0.83
10	24610	1.45	95	5.8	3.6	0.30

# PRODUCT PORTFOLIO

## Rechargeable Batteries



Li-Ion Button Cells  
CoinPower



NiMH Button Cells



NiMH Cylindrical Cells



CellPac PLUS



CellPac BLOX



CellPac LITE

## Primary Batteries



Zinc Air Hearing Aid batteries  
power one



Lithium Button Cells



Lithium Cylindrical Cells



Alkaline Batteries



Silver Oxide Button Cells



Hydrogen Gas  
Generating Cells

# Contact

## Headquarters

VARTA Microbattery GmbH  
VARTA-Platz 1,  
73479 Ellwangen, Germany  
Tel +49 7961 921-0  
Fax +49 7961 921-2553

VARTA Storage GmbH  
Nürnberger Strasse 65  
86720 Nördlingen, Germany  
Tel +49 9081 240 86 60

## France

VARTA Microbattery GmbH  
12 - 14, Rue Raymond RIDEL  
92250 La Garenne Colombes, France  
Tel +33 1 47 84 84 54  
Fax +33 1 47 84 28 32

## USA

VARTA Microbattery Inc.  
555 Theodore Fremd Avenue,  
Suite C 304 Rye, NY 10580, USA  
Tel +1 914 592 25 00  
Fax +1 914 345 04 88

## Taiwan

VARTA Microbattery Pte. Ltd.  
3F No.85, Xinhua 1st Road,  
Neihu District Taipei City 114, Taiwan  
Tel +886 2 27 90 29 92

## Romania

VARTA Microbattery SRL  
Str. Horia, Closca si Crisan, Nr. 61-63  
075100 Otopeni, Jud. Ilfov, Romania  
Factory:  
VARTA Microbattery SRL  
Boulevard Grivita 1  
500177 Brasov, Romania  
Tel +40 2 12 03 00 77

## Indonesia

PT VARTA Microbattery Indonesia  
Jalan Gaharu Lot 23, Jalan  
Angsana Lot 307-310  
Batamindo Industrial Park,  
Mukakuning,  
Batam, KEPRI 29433, Indonesia  
Tel +62 770 611 099  
Fax +62 770 611 966

## Asia Pacific

VARTA Microbattery Pte. Ltd.  
300 Tampines Avenue 5,  
#05-01 Income  
@ Tampines Junction,  
529653 Singapore  
Tel +65 6 260 58 01  
Fax +65 6 260 59 60

## Japan

VARTA Microbattery Japan K.K.  
Kyobashi Y'SUS Bldg,  
3F.1-6-12, Kyobashi, Chuo-Ku  
Tokyo 104-0031, Japan  
Tel +81 3 35 67 81 71  
Fax +81 3 35 67 81 75

## Hong Kong

VARTA Microbattery Pte. Ltd.  
Room 1702-3, 17/F Fullerton Centre  
19 Hung to Road, Kwun Tong  
Kowloon, Hongkong  
Tel +852 28 98 83 73  
Fax +852 28 97 76 09

## China

VARTA Competence Center Shenzhen  
EMEA Consumer Batteries (Shenzhen) Co. Ltd.  
No. 1003 Forsafe Technology Building B,  
13 GaoXinSouth 1st Rd. Hi-tech Industrial Park,  
Nanshan District, Shenzhen City, China  
Tel: +86 755 3397 4791

Representations and distributors in all major countries worldwide.  
Please see webpage.



Subscribe to our YouTube channel.  
[www.youtube.com/VARTAMicrobatteryGmbH](http://www.youtube.com/VARTAMicrobatteryGmbH)



[www.linkedin.com/showcase/varta-microbatteries](http://www.linkedin.com/showcase/varta-microbatteries)



[www.youtube.com/VARTAMicrobatteryGmbH](http://www.youtube.com/VARTAMicrobatteryGmbH)

VARTA Microbattery GmbH and VARTA Storage GmbH is a company of VARTA AG.

[www.varta-ag.com](http://www.varta-ag.com)