

## PRODUCT CATEGORIES

- Integrated Receive RF Front-ends
- Transmit Chains
- mmWave Beamformers
- Digital step attenuators (DSA)
- Variable voltage attenuators (VVA)
- RF switches
- Broadband mixers
- Variable gain amplifiers (VGA)
- Amplifiers
- Broadband modulators
- DPD Demodulators with integrated DSA, RF switch and LO switch

## FEATURES

- Highly differentiated RF products
- Smart Silicon enables unique technical innovations
  - Low noise
  - High linearity
  - Low power
  - Small form factors
- Scalable RF Solutions for increased integration

## APPLICATIONS

### Wireless Infrastructure

- 4G / 5G macro base stations
- Active antenna systems (AAS)
- 5G mmWave
- Distributed antenna systems (DAS)
- Repeaters
- Microwave (RF/IF) point to point

### SATCOM

- Phased Array Antenna


### Industrial

- Military/tactical communication systems
- FMCW Radar
- Public Safety
- Test and Measurement

### Broadband CATV

- Headend (CMTS)
- Distribution nodes
- Fiber repeaters
- Cable modem, set-top box
- Satellite receivers and modems

# RF Products Family



IDT's RF products are best-in-class in dealing with unwanted interference from an increasingly crowded radio spectrum. Today's higher data rates drive the need for better radio signal-to-noise ratios, which translates to the need for IDT's higher linearity RF components. IDT's unique patented RF solutions enable green networks with minimal power consumption, and will serve as a company growth driver for years to come.


RF solutions from IDT address the evolving needs of a wide range of applications, including cellular 4G and 5G base stations, Active Antenna Systems for both sub-6 GHz and mmWave frequencies, and SATCOM phased array antennas.

IDT's innovative silicon-based products utilize CMOS, SOI and SiGe processes. To continue advancing our portfolio, IDT adds in III-V technologies to enable further improvements in device performance as needed for next-generation designs.

With a combination of technologies and advanced IP, IDT delivers unique solutions to the design challenges faced by designers.

RF Products Family


### GLITCH-FREE™




**IDT RF Digital Step Attenuators and RF Variable Gain Amplifiers**

IDT devices virtually eliminate transient overshoot that can occur during MSB attenuation state transitions of standard DSAs. Thus, amplifier damage and loss of information at the ADC are avoided.


**F1950 Glitch-Free™ DSA vs Competitor Standard DSA**




### FLATNOISE™



Noise Figure is kept virtually flat in the critical region while gain is reduced. Greatly eases design constraints for Radio Engineers by enhancing SNR.




### ZERO-DISTORTION™




**IDT RF Mixers and IF Variable Gain Amplifiers**

IDT devices improve SNR by reducing the noise floor and IM3 intermodulation distortion, as shown below in yellow. This is key for crowded spectrum environments, as it enhances Quality of Service and frees up under-utilized spectrum.


**Zero-Distortion IDT Rx**




**Standard Rx**




### K<sub>LIN</sub> CONSTANT LINEARITY



K<sub>LIN</sub> maintains constant high linearity as gain is adjusted. As the gain is reduced, the linearity (OIP3) remains constant in the critical region (see graph). This prevents intermodulation distortion from degrading as the gain is reduced.



### K<sub>|z|</sub> CONSTANT IMPEDANCE



K<sub>|z|</sub> maintains a near constant impedance when switching between RF ports preserving a higher RF port return loss. Standard switches without K<sub>|z|</sub> create a large Voltage Standing Wave Ratio, VSWR, transient when switching RF paths because the impedance of the switch is not well controlled during the switching event. By controlling the impedance during the switching process VSWR transients are minimized, improving switch reliability, reducing voltage stresses on downstream components and improving overall system performance.

To learn more about IDT's RF products, patented technologies, or request samples, visit: [idt.com/rf](http://idt.com/rf)