


Overview

PHOTOMOS RELAYS



What makes PhotoMOS® relays so successful?

Modern semiconductor technology enables fast, quiet, bounce-free switching, even in miniature sizes. PhotoMOS relays nevertheless enjoy an almost unlimited lifetime if used according to the specifications. Moreover, they are extremely reliable, unaffected by vibrations, and their ON-resistance remains stable throughout their entire lifetime.




Package size change


PhotoMOS® technology

The basic construction of the PhotoMOS relay can be seen in the illustration. Light emitted from an LED on the input side passes through an isolator permeable to light and is detected by a solar cell. Via a trigger circuit, the solar cell's output voltage controls the gates of two

source-coupled MOSFETs at the output. This arrangement allows PhotoMOS relays to switch both AC and DC loads. The integration of MOSFET technology in PhotoMOS relays differentiates them significantly from semiconductor relays with triacs or transistors at the output.



PACKAGE VARIATIONS



NEW

The right PhotoMOS relay for all APPLICATIONS.

Three different search functions help you find the right PhotoMOS relay within seconds!

Get an overview of the wide range of products with this APP.

Scan QR code directly with a QR code reader on your smartphone

GET IT ON Google Play

Download on the App Store


The most important advantages at a glance

- › Linear output characteristics
- › No threshold voltage
- › Low operate current (sensitive type $\leq 0.31\text{mA}$)
- › Low output capacitance (RF type $\leq 1\text{pF}$)
- › Absolute minimum leakage current (pA)
- › Extremely long lifetime
- › Stable ON-resistance over the entire lifetime
- › Extremely compact design (TSON, VSSOP, SON, SSOP)
- › No contact bounce
- › Highly resistant to shock and vibration
- › Flexible mounting orientation

A FEW DISTINGUISHING FEATURES


1. Linear output characteristics

(e.g. AQY225R2V)




2. Low off-state leakage current

in the pA range (e.g. AQY21*S)




3. Fast switching times

with little variation (e.g. AQY221N3V)



4. Low output capacitance






(e.g. AQY221*V)



Typical applications

- › Measuring devices and technology
- › IC and PC board testers
- › Multiplexers
- › Medical technology
- › Industrial control systems
- › Battery management
- › Signal/alarm contacts
- › Outputs for programmable controllers
- › Pulse and counter outputs
- › Isolation monitoring

POPULAR TYPE SELECTION TABLE

| | Type ¹⁾ | Package | Contact | Voltage (V) ²⁾ | Current (A) ²⁾ | R _{on} ³⁾ (Ω) | C _{out} ³⁾ (pF) | Info | |
|---|---|---------|---------|---------------------------|---------------------------|-----------------------------------|-------------------------------------|------------------------------|---------------------|
|  | AQY212EH(A) | DIP4 | 1a | 60 | 0.55 | 0.85 | 80 | General use | |
| | AQY212GH(A) | | | | 1.1 | 0.34 | 220 | | |
| | AQY210EH(A) | | | 350 | 0.13 | 18 | 45 | | |
| | AQY214EH(A) | | | | 0.12 | 26 | 45 | | |
| | AQY216EH(A) | | | | 0.05 | 52 | 35 | | |
|  | AQY212S | SOP4 | 1a | 60 | 0.5 | 0.83 | 80 | | |
| | AQY212GS | | | | 1.0 | 0.34 | 220 | | |
| | AQY210S | | | 350 | 0.12 | 17 | 45 | | |
| | AQY214S | | | | 0.1 | 25 | 45 | | |
| | AQY412S | 1b | 1a | 60 | 0.5 | 1 | 450 | | |
| | AQY410S | | | 350 | 0.12 | 18 | 110 | | |
| | AQY414S | | | 400 | 0.1 | 26 | 100 | | |
| |  | AQY232S | SOP4 | 1a | 60 | 0.5 | 0.85 | 80 | Low operate current |
| | | AQY230S | | | 350 | 0.12 | 19 | 45 | |
| AQY234S | | 400 | | | 0.1 | 27 | 45 | | |
|  | AQV112KL(A) | DIP6 | 1a | 60 | 0.5 | 0.55 | 300 | Short circuit protected | |
| | AQY210KS | SOP4 | | 350 | 0.12 | 23 | 42 | | |
|  | AQV251G | DIP6 | 1a | 30 | 3.5 | 0.035 | 350 | High power | |
| | AQV252G2S | SOP6 | | 50 | 3 | 0.04 | 360 | | |
| | AQV252G | DIP6 | | 60 | 2.5 | 0.08 | 240 | | |
| | AQV255GS | SOP6 | | 80 | 1.25 | 0.09 | 300 | | |
| | AQV259H(A) | DIP6 | | 1.000 | 0.03 | 85 | 80 | | |
| | AQV258H(A) | DIP6 | | 1.500 | 0.02 | 345 | 80 | | |
|  | AQY2C1R6P | TSOP | 1a | 30 | 0.75 | 0.22 | 40 | Low CxR for high frequencies | |
| | AQY2C1R2P | | | 40 | 0.3 | 0.9 | 14.5 | | |
| | AQY2C2R2P | | | 60 | 0.3 | 1.0 | 27 | | |
|  | AQY221N3T | VSSOP | 1a | 25 | 0.15 | 5.5 | 1.1 | | |
| | AQY221N2T | | | 40 | 0.12 | 9.5 | 1.1 | | |
| | AQY222R2T | | | 60 | 0.4 | 0.8 | 27 | | |
| | AQY225R3T | | | 100 | 0.12 | 8.8 | 5.8 | | |
|  | AQY221N3M | SON | 1a | 25 | 0.15 | 5.5 | 1.1 | | |
| | AQY221N2M | | | 40 | 0.12 | 9.5 | 1.1 | | |
| | AQY221R2M | | | 40 | 0.25 | 0.8 | 14 | | |
|  | AQY221N2V | SSOP | 1a | 40 | 0.12 | 9.5 | 1 | | |
| | AQY221R2V | | | 40 | 0.25 | 0.75 | 12.5 | | |
| | AQY221R4V | | | 40 | 0.5 | 0.55 | 24 | | |
| | AQY225R2V | | | 80 | 0.12 | 10.5 | 4.5 | | |
| | AQY225R3V | | | 100 | 0.12 | 8.8 | 5.8 | | |
|  | AQZ202 | SIL | 1a | 60 | 3.0 | 0.11 | 1400 | AC and DC | |
| | AQZ205 | | | 100 | 2.0 | 0.23 | 1400 | | |
| | AQZ204 | | | 400 | 0.5 | 2 | 600 | | |
| | AQZ404 | | 1b | 400 | 0.5 | 2.8 | 2000 | | |

1) A = SMD type, 2) Maximum values (DC or peak AC), 3) Typical value

AUSTRIA
Schönbrunner Str. 297-307
A-1120 Vienna
Phone: +31 86642 0
Fax: +43 1 86642 250
wien@avnet-abacus.eu

BELARUS
c/o Avnet Abacus Russia
Office 24, Building 2
10 Korovinskoye Shosse,
127486 Moscow
Phone: +7 (495) 737 3688
Fax: +7 (495) 737 3686
belarus@avnet-abacus.eu

BELGIUM
De Kleetlaan 3
1831 Diegem
Phone: +32 2 227 2000
diegem@avnet-abacus.eu

BULGARIA
c/o Avnet Abacus Romania
4 Gara Herastrau,
Building B, 2nd Floor RO-020334
Bucharest
Phone: +4021 528 16 90
bulgaria@avnet-abacus.eu

CROATIA
c/o Avnet Abacus Slovenia
Dunajska Cesta 167
1000 Ljubljana
Phone: +386 (0) 1560 97 54
Fax: +386 (0) 1560 98 78
croatia@avnet-abacus.eu

CZECH REPUBLIC
Amazon Court Karolinska 661/4
CZ-18600 Prague Czech Republic
Phone: +420 234 091 011
Fax: +420 234 091 010
praha@avnet-abacus.eu

DENMARK
Knudlundvej 24 DK-8653 Them
Phone: +45 86 84 84 84
Fax: +45 86 84 82 44
them@avnet-abacus.eu

Lyskaer 9, DK-2730 Herlev
Phone: +45 86 84 84 84
Fax: +45 43 29 37 00
herlev@avnet-abacus.eu

EGYPT
c/o Avnet Abacus Turkey
Tatilsu Mahallesi Pakdil
Sokak No: 7 Kat: 2 34774
Umraniye Istanbul Türkiye
Phone: +90 216 52 88 370
Fax: +90 216 52 88 377
egypt@avnet-abacus.eu

ESTONIA
Suur-Jõe 63, Pärnu,
80042 Pärnu Maakond,
Estonia
Phone: +372 56637737
paernu@avnet-abacus.eu

FINLAND
Pihatörmä 1 B
FI-02240 Espoo
Phone: +358 (0) 207 499 220
Fax: +358 (0) 207 499 240
espoo@avnet-abacus.eu

FRANCE
Immeuble Carnot Plaza
14 Avenue Carnot
91349 Massy Cedex, Paris
Phone: +33 (0) 1 6447 2929
Fax: +33 (0) 1 6447 9150
paris@avnet-abacus.eu

8 chemin de la Terrasse
Bat D 1er étage
31500 Toulouse
Phone: +33 (0) 5 6247 4787
Fax: +33 (0) 5 6247 4761
toulouse@avnet-abacus.eu

35 avenue des Peupliers
Les Peupliers2
35510 Cesson
Phone: +33 (0) 2 9983 7720
Fax: +33 (0) 2 9983 4829
rennes@avnet-abacus.eu

Parc Club du Moulin à Vent
Bât 10, 33 rue du Dr. G Lévy
F-69693 Vénissieux Cedex, Lyon
Phone: +33 (0) 4 7877 1370
Fax: +33 (0) 4 7877 1391
lyon@avnet-abacus.eu

GERMANY
Englische Str. 27
D - 10587 Berlin
Phone: +49 (0) 30 790 997 0
Fax: +49 (0) 30 790997 51
berlin@avnet-abacus.eu

Industriestr. 26
D-76297 Stutensee
Phone: +49 (0)7249 910 149
Fax: +49 (0)7249 910 177
stutensee@avnet-abacus.eu

Wilhelmstr. 1,
D-59439 Holzwickede / Dortmund
Phone: +49 (0) 2301 2959 27
Fax: +49 (0) 2301 2959 29
dortmund@avnet-abacus.eu

Oehleckerweg 9a - 13 22419
Hamburg
Phone: +49 (0) 40 608 23 59 0
Fax: +49 (0) 40 608 23 59 20
hamburg@avnet-abacus.eu

Gruber Str. 60c-60d
D-85586 Poing / Munich
Phone: +49 (0) 8121 777 03
Fax: +49 (0) 8121 777 531
muencheng@avnet-abacus.eu

Lina-Ammon-Str. 19 b
D-90471 Nürnberg
Phone: +49 (0) 911 244 250
Fax: +49 (0) 911 244 25 25
nuernberg@avnet-abacus.eu

Gutenbergr. 15
D-70771 Leinfelden - Echterdingen
/ Stuttgart
Phone: +49 (0) 711 78260 02
Fax: +49 (0) 711 78260 333
stuttgart@avnet-abacus.eu

Gaußstraße 10 D-31275 Lehrte
Phone: +49(0) 5132 5099 0
Fax: +49(0) 5132 5099 76
lehrte@avnet-abacus.eu

GREECE
c/o Abacus Avnet Serbia
Milentija Popovicka 5B,
Floors 6-8 Belgrade RS11070
Phone: +381 11 4023230
Fax: +381 11 4049900
belgrade@avnet-abacus.eu

HUNGARY
c/o Avnet Abacus Czech Republic
GreenPoint Offices,
Blok F Turcianska 2 SK-82109,
Bratislava
Phone: +421 232 242 608
Fax: +421 2 32 111 40
budapest@avnet-abacus.eu

IRELAND
c/o Avnet Abacus Bolton
Oceanic Building
Waters Meeting Road
Bolton BL1 8SW
Phone: +44 (0)1204 547170
Fax: +44 (0)1204 547171
bolton@avnet.eu

ISRAEL
Avnet Components Israel Ltd.
P.O. Box 48
Tel-Mond, 4065001
Phone: 972-9-7780280
Fax: 972-3-760-1115
avnet.israel@avnet.com

ITALY
Via Manzoni 44
I-20095 Cusano Milanino (Milano)
Phone: +39 02 660 921
Fax: +39 02 66092 332
milano@avnet-abacus.eu

Viale dell'industria 23
I-35129 Padova
Phone: +39 049 7800 381
Fax: +39 049 7730 36
padova@avnet-abacus.eu

Via di Settebagni, 390
I-00138 Roma
Phone: +396-41231951
roma@avnet-abacus.eu

Via Scaglia Est, 31/33
41126 Modena
Phone: +39 059 344991
Fax: +39 059 344993
modena@avnet-abacus.eu

Via Panticaffi 40/11
I-50127 Firenze
Phone: +39 055 436 1928
Fax: +39 055 428 8810
firenze@avnet-abacus.eu

LATVIA
c/o Avnet Abacus Poland
Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
latvia@avnet-abacus.eu

LITHUANIA
c/o Avnet Abacus Poland
Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
lithuania@avnet-abacus.eu

NETHERLANDS
Stadionstraat 2, 6th fl.
NL-4815 NG Breda
Phone: +31 (0) 76 57 22 300
Fax: +31 (0) 76 57 22 303
breda@avnet-abacus.eu

NORWAY
Olaf Helsetves vei 6,
0694 Oslo Norway
Phone: +47 (0) 94 89 53 73
oslo@avnet-abacus.eu

POLAND
Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
wroclaw@avnet-abacus.eu

PORTUGAL
Tower Plaza, Rot. Eng.
Edgar Cardoso,
23, Pl. 14, Sala E
PT-4400-676 Vila Nova de Gaia
Phone: +351 223 779502
Fax: +351 223 779503
portugal@avnet-abacus.eu

ROMANIA
4 Gara Herastrau, Building B,
2nd Floor
RO-020334 Bucharest
Phone: +4021 528 16 90
romania@avnet-abacus.eu

RUSSIA
49A Tatischeva Street,
Ekaterinburg
RUS-620028
Phone: +7 (912) 650 1944
Ekaterinburg@avnet-abacus.eu

Office 24, Building 2
10 Korovinskoye Shosse
127486 Moscow
Phone: +7 (495) 737 3688
Fax: +7 (495) 737 3686
Moscow@avnet-abacus.eu

SERBIA
Milentija Popovicka 5B, Floors 6-8
Belgrade RS11070
Phone: +381 11 4023230
Fax: +381 11 4049900
belgrade@avnet-abacus.eu

SLOVAKIA
GreenPoint Offices, Blok F
Turcianska 2
SK-82109, Bratislava
Phone: +421 232 242 608
Fax: +421 2 32 111 40
slovakia@avnet-abacus.eu

SLOVENIA
Dunajska Cesta 167
1000 Ljubljana
Phone: +386 (0) 1560 97 54
Fax: +386 (0) 1560 98 78
ljubljana@avnet-abacus.eu

SOUTH AFRICA
First Floor, Forrest House
Belmont Office Park
Belmont Road,
Rondebosch 7700, Cape Town
Phone: +27 (0) 21 689 4141
Fax: +27 (0) 21 686 4709
sales@avnet.co.za

11 Forest Square, Suite 4,
Bauhnia Building, Derby Place,
Westville, 3629, Durban
Phone: +27 (0) 31 266 8104
Fax: +27 (0) 31 266 1891
sales@avnet.co.za

Block 13, Pinewood Office Park
33 Rileys Road Woodmead,
2191 Sandton, Johannesburg
Phone: +27 (0) 11 319 8600
Fax: +27 (0) 11 319 8650
sales@avnet.co.za

SPAIN
NyN Tower, C/ Tarragona,
149-157, Floor 19
ES-08014 Barcelona
Phone: +34 (0) 93 327 85 50
Fax: +34 (0) 93 425 05 44
barcelona@avnet-abacus.eu

Plaza Zabalgane 12 Bajo Izda,
Galdakao / Vizcaya
ES -48960 Bilbao
Phone: +34 (0) 94 457 0044
Fax: +34 (0) 94 456 8855
bilbao@avnet-abacus.eu

C/Chile, 10 2º Pta. Oficina 229
ES -28290 Las Matas / Madrid
Phone: +34 (0) 913 72 7200
Fax: +34 (0) 916 36 9788
madrid@avnet-abacus.eu

SWEDEN
Löstfröms Allé 5,
Sundbyberg, Box 1830,
SE-171 27 Solna
Phone: +46 (0) 858 746200
Fax: +46 (0) 858 746 001
stockholm@avnet-abacus.eu

Smörhålevägen 3
SE-43442 Kungälv
Phone: +46 (0)18 58746 200
Fax: +46 (0)300 140 15
gothenburg@avnet-abacus.eu

SWITZERLAND
Bernstrasse 392
CH-8953 Dietikon
Phone: +41 (0) 43 322 49 90
Fax: +41 (0) 43 322 49 99
zurich@avnet-abacus.eu

TURKEY
Tatilsu Mahallesi Pakdil
Sokak No: 7 Kat: 2 34774
Umraniye Istanbul Türkiye
Phone: +90 216 52 88 370
Fax: +90 216 52 88 377
istanbul@avnet-abacus.eu

UK
First Floor, The Gatehouse
Gateway Office Park Aylesbury,
Bucks HP19 8DB
Phone: +44 (0) 1296 678920
Fax: +44 (0) 1296 678959
aylesbury@avnet.eu

Building 5 Waltham Park
White Waltham, Maidenhead
Berkshire SL6 3TN
Phone: +44 (0)1628 512900
Fax: +44 (0)1628 512999
maidenhead@avnet.eu

Avnet House
Rutherford Close
Meadway, Stevenage
Hertfordshire SG1 2EF
Phone: +44 (0)1438 788 500
Fax: +44 (0)1438 788 250
stevenage@avnet.eu

Oceanic Building
Waters Meeting Road
Bolton BL1 8SW
Phone: +44 (0)1204 547170
Fax: +44 (0)1204 547171
bolton@avnet.eu

UKRAINE
c/o Avnet Abacus Poland
Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
ukraine@avnet-abacus.eu

All trademarks and logos are the property of their respective owners. This document provides a brief overview only, no binding offers are intended. No guarantee as to the accuracy or completeness of any information. All information is subject to change, modifications and amendments without notice. Printed on FSC certified paper.