

# Murata Products for Automotive




# Cars and the Future

An indispensable element in an “omnipresent network society” – Murata technology links people and the ever-evolving automobile.



Ever-evolving automotive technology is no longer confined to the basic vehicle functions of propulsion, steering, and braking. It is now expanding into a variety of disciplines. Remarkable advances in automotive technology, most notably in areas such as telematics, advanced safety features, and environmental compatibility, have led to tremendous evolution in our vehicles and our automotive society since the days when vehicles were merely a means of getting around.

This evolution has been facilitated by electronic components that monitor the vehicle inside and out and exchange information among the components. Murata produces components that are so small and light you wouldn't even notice them on your fingertip and sensors and modules made of materials we have engineered at the molecular level. We are staking our future potential and the boundless development of automobiles on these small electronic components. With our technology and know-how, Murata will contribute to developing a “ubiquitous network society” preserving the global environment, and creating a future with safer and more comfortable automobiles.



## Index

Cars and the Future	01-02
Work in Automotive	03-04
Circuit Applications	05-06
Specific Use Products Lineup	07-09
Products Lineup	10-20
Corporate Activities	21-22

<http://www.murata.com/en-global/apps/auto>


## For Safety

Murata's sensing technology – protecting both people and cars.

Sensing technology provides precision control by electronics, which is essential for the safety systems of vehicles. Murata's electronic components, including various sensors, support a pleasant driving experience with excellent performance by the latest technology and high reliability that can only be provided by ceramics, which can endure severe operating conditions.

### 3D Autonomous Nervous Structure

This is a sensing technology that promotes improvements in the safety functions and intelligence of vehicles. Only Murata's 3D MEMS technology can provide a reduction of the cross axis, improving reliability of linearity.



MEMS Acceleration Sensor

- For ESC Acceleration Detection
- Excellent temperature drift characteristic. Compliant to Quality Standard AEC-Q100 for automobiles.


## For the Environment

The next generation performance – providing cars for the earth's environment.

Consideration of the global environment is important for the automobile industry. Murata helps reduce CO<sub>2</sub> and conserve energy by developing and supplying electronic components that take advantage of such characteristics of ceramics as compactness and thermal resistance. We are helping to expand the market share of environmentally friendly vehicles such as electric vehicles (EVs) and hybrid electric vehicles (HEVs).

### Intelligent Power Solution

Murata's unique "smart" power supply provides amazing value by combining intelligent energy saving features and high power output in an ultra-small package.




DC-DC Converter for E-Bike

- For E-bike auxiliary drive
- Highly efficient
- Non-isolated type
- Small (palm sized) module & lightweight
- Conforms to IP56 for dust and water ingress

Murata contributes to the development of mobile communication systems with the technology and know-how we developed for the information communication equipment market and with the high reliability that comes with the outstanding heat and vibration resistance typical of our ceramic components. Automotive telematics achieves the combining of a radio transmission system with the car navigation and security system. Murata's information communication technology is also playing an active role in making such new systems prevalent.

### Network on Wheels

Various wireless communication standards are used for information and communications in vehicles. Murata offers a highly reliable connectivity module, making full use of the excellent high frequency portion and high frequency circuit technology.



Connectivity Module

- On-board Communication Module for Automobiles
- Murata has achieved the wireless communication functions required for on-board communications with compact modules, such as Bluetooth®, Wi-Fi®, GPS, FM and others.

Bluetooth is a registered trademark of Bluetooth SIG, Inc. of the United States. Wi-Fi is a registered trademark or trademark of Wi-Fi Alliance.

# Work in Automotive

**1**  
SAW Filters  
SF Series



**2**  
Ceramic ESD  
Protection Devices  
LXES Series




**3**  
Ionizer  
MHM Series



**4**  
AMR Sensors



**5**  
Isolated DC-DC Converters  
MP Series



**6**  
Ultrasonic Sensors  
MA Series



**7**  
Wi-Fi® · Bluetooth®  
Connectivity  
Modules



**8**  
Shock Sensors  
PKGS Series



**9**  
Antenna Coils  
MSA Series



**10**  
Wi-Fi® Modules



**11**  
Safety Standard  
Certified Ceramic  
Capacitors DE6 Series



**12**  
Ultrasonic Sensors  
Open Structure Type  
MA Series



PTC Thermistors PRF Series



Ferrite Cores



Piezoelectric Sounders PK Series



Trimmer Capacitors TZY2 Series



EMI Suppression Filters BLM Series



Rotary Position Sensors SV01 Series



Chip Monolithic Capacitors



EMI Suppression Filters NFM Series



## Infotainment



Multilayer LC Filters  
LF\_V Series



DC-DC Converters  
MP Series



RF Inductors  
LQW/LQG Series



Polymer Aluminum  
Electrolytic Capacitors  
ECAS Series



## Comfort/In Vehicle LAN



Ceramic Filters  
SFEFC Series



Common Mode  
Choke Coils  
DLW Series



Crystal Units  
XRCHA\_F\_A Series



Ceramic Resonators  
CERALOCK®  
CSTCE/CSTCR Series




DC-DC Converters  
H8 Series



Electrical Double Layer  
Capacitors  
DMT Series



## Powertrain



Metal Terminal  
Capacitors  
KCM/KC3 Series



Lead Type Ceramic  
Capacitors RHE Series  
150°C Compatible Type




Ceramic Functional  
Substrates  
LFC®



Common Mode  
Choke Coils  
PLT10H Series



## Safety



Acceleration Sensors  
SCA Series



Combo Sensors  
SCC Series




Ceramic Functional  
Substrates  
LFC®




# Circuit Applications


## PIM (Power Inverter Module)




## IVI (In Vehicle Infotainment)




## BMS (Battery Management System)



## Airbag Combined Stability Controller



## OBC (On Board Charger)




C1	Metal Terminal Monolithic Ceramic Capacitors (for 250V or more)	KC3 Series/X7T
C2	Chip Monolithic Ceramic Capacitors (for 250V or more)	GCM Series/U2J
C3	Chip Monolithic Ceramic Capacitors (Soft Termination Type)	GCJ Series/X7R
C4	Metal Terminal Monolithic Ceramic Capacitors	KCM Series/X7R
C5	Chip Monolithic Ceramic Capacitors (High Allowable Ripple Current Type)	GC3 Series/X7T
C6	Safety Standard Certified Ceramic Capacitors	DE6 Series
C7	Chip Monolithic Ceramic Capacitors	GCM Series
C8	Low ESL Ceramic Capacitors	LL Series
C9	3-Terminal Capacitors	NFM Series
F1	SAW Filters	SF Series
L1	Chip Common Mode Choke Coils	DLW Series
L2	RF Inductors	LQP/LQG/LQW Series
L3	Inductors for Power Lines	LQM/LQH Series
Q1	Connectivity Modules	LBW Series
Q2	DC-DC Converters	MP Series
S1	Combined Gyroscopes and Accelerometers	SCC Series
S2	Accelerometers	SCA Series
S3	Rotary Position Sensors	SV01 Series
X1	Crystal Units	XRCHA-F-A Series
X2	Ceramic Resonators (CERALOCK®)	CSTCR/CSTCE Series



# Products Lineup

## Connectivity Modules


This product can be used for communication in Bluetooth®, Wi-Fi®, GPS, FM and others. One stop solution of multimedia environment in the automotive.




## Chip Multilayer LC Filters (Available for consumer grade use only.)

Ultra-small and low-profile filters based on ceramic multilayer technology.

### Band Pass Filters




LFB18\_V Series



LFB21\_V Series

(in mm)

### Low Pass Filters



LFL18\_V Series



LFL21\_V Series

(in mm)

## Chip Multilayer Baluns (Available for consumer grade use only.)

SMD baluns constructed with a copper conductor and ceramic material. Ideal for high-frequency applications. Small-size and low-loss baluns can be customized for balance impedance of 50Ω to 200Ω.



LDB21\_V Series



LDM18\_V Series


(in mm)

## Chip Multilayer Hybrid Dividers (Available for consumer grade use only.)

Power divider with a multilayer low pass filter in an ultra-compact package.



LDD18\_V Series



LDD21\_V Series

(in mm)

## Chip Multilayer Couplers (Available for consumer grade use only.)

An ultra-small, low-profile directional coupler based on ceramic multilayer technology. This coupler achieves ultra-small size, low insertion loss and high isolation.



LDC18\_V Series



LDC21\_V Series

(in mm)

## DC-DC Converters

Murata provides custom DC-DC Converters designed for power supply of Navigation System, Audio System, DVD and HDD.



Cars and the Future



## Capacitors

### Application Matrix

Product Name		Series	Powertrain	Safety	Comfort	Infotainment
MLCC	General Purpose Products for Automotive	GCM	●	●	●	●
	For General Purpose (Infotainment/Comfort)	GRM			●	●
	Products Based on the Electrical Appliance and Material Safety Law of Japan	GA2			●	●
	Safety Standard Certified Type	GA3			●	●
	High Effective Capacitance & High Allowable Ripple Current	GC3	●	●	●	●
	Specially Designed Product to Reduce Shorts	GCD	●	●	●	●
	Specially Designed Product to Reduce Shorts & Resin Electrode Products	GCE	●	●	●	●
	Conductivity Adhesive Compatible Type	GCG	●	●	●	●
	Resin External Electrode Products	GCJ	●	●	●	●
	High Frequency High Q Type 1005(in mm)/0402(in inch) Size Max.	GJM			●	●
	Top & Bottom Electrode Type for Bonding	GMA			●	●
	Compatible to Bonding/AuSn Soldering	GMD			●	●
	High Frequency High Q Type 1608(in mm)/0603(in inch) Size Min.	GQM			●	●
	High Effective Capacitance & High Allowable Ripple Current	GR3			●	●
	For Ethernet LAN & Primary-secondary Coupling of DC-DC Converters	GR4			●	●
	Resin External Electrode Type	GRJ			●	●
	Metal Terminal Type/High Effective Capacitance & High Allowable Ripple Current for Automotive	KC3	●	●	●	●
	Metal Terminal Type for Automotive	KCM	●	●	●	●
	Metal Terminal Type High Effective Capacitance & High Allowable Ripple Current for General Purpose	KR3			●	●
	Metal Terminal Type for General Purpose (Infotainment/Comfort)	KRM			●	●
Lead Type	8-Terminal Low ESL Type	LLA			●	●
	LW Reversed Low ESL Type	LLL			●	●
	10-Terminal Low ESL Type	LLM			●	●
	ESR Controlled Low ESL Type	LLR			●	●
	Safety Standard Certified (IEC60384-14 Class X1/Y1)	DE1			●	●
	Safety Standard Certified (IEC60384-14 Class X1/Y2)	DE2			●	●
	Safety Standard Certified (IEC60384-14 Class X1/Y2 for Automotive)	DE6	●	●	●	●
	High Voltage (Class 1 (Char. SL) DC1-3.15kV Rated)	DEA			●	●
	High Voltage (Class 2 DC1-3.15kV Rated)	DEB			●	●
	High Voltage (Class 1, 2 DC6.3kV Rated)	DEC			●	●
	High Voltage (LCD Backlight Inverter Circuit)	DEF			●	●
	High Voltage (High Temperature Guaranteed, Low-dissipation Factor (Char. R, C)	DEH			●	●
	Based on the Electrical Appliance and Material Safety Law of Japan	DEJ			●	●
High Voltage (High Temperature Guaranteed, Low-dissipation Factor (Char. D)	DES			●	●	
Ultrahigh Voltage	DHR			●	●	
125°C Compatible Type for Automotive	RCE	●	●	●	●	
Monolithic Lead Type for Consumer Market	RDE			●	●	
150°C Compatible Type for Automotive	RHE	●	●	●	●	
Polymer Aluminum Electrolytic Capacitors	ECAS			●	●	
Electrical Double Layer Capacitors	DMT			●	●	
Trimmer Capacitors	TZ			●	●	

Continued on the following page.

## Chip Monolithic Ceramic Capacitors/Lead Type Ceramic Capacitors

### Powertrain/Safety

Series	Series Name	Characteristics	Rated Voltage		Capacitance							
			V	kV	pF		μF					
			1	10	100	1	10	0.1	1	10	100	1000
GCM	General Purpose Products for Automotive	AEC-Q200	6.3Vdc	1000Vdc	1.0pF	47μF						
GCD	Specially Designed Product to Reduce Shorts	AEC-Q200, Fail safe, Deflecting crack	25Vdc	100Vdc	1000pF	0.10μF						
GCE	Specially Designed Product to Reduce Shorts & Resin Electrode Products	AEC-Q200, Fail safe, Deflecting crack	25Vdc	100Vdc	1000pF	0.10μF						
GCG	Conductivity Adhesive Compatible Type	AEC-Q200, Deflecting crack, Soldering crack	16Vdc	100Vdc	10pF	10μF						
GCJ	Resin External Electrode Products	AEC-Q200, Fail safe, Deflecting crack	6.3Vdc	1000Vdc	220pF	47μF						
GC3	High Effective Capacitance & High Allowable Ripple Current	AEC-Q200, Anti-noise	250Vdc	630Vdc	10000pF	1.0μF						
KCM	Metal Terminal Type for Automotive	AEC-Q200, Anti-noise, Deflecting crack, Soldering crack	25Vdc	100Vdc	4.7μF	68μF						
KC3	Metal Terminal Type/High Effective Capacitance & High Allowable Ripple Current for Automotive	AEC-Q200, Anti-noise, Deflecting crack, Soldering crack	250Vdc	630Vdc	0.10μF	2.2μF						
DE6	Safety Standard Certified (IEC60384-14 Class X1/Y2 for Automotive)	AEC-Q200, Safety standard	300Vac	(r.m.s.)	100pF	4700pF						
RCE	125°C Compatible Type for Automotive	AEC-Q200	25Vdc	1000Vdc	1.0pF	22μF						
RHE	150°C Compatible Type for Automotive	AEC-Q200	50Vdc	100Vdc	100pF	10μF						

### Infotainment/Comfort

Series	Series Name	Characteristics	Rated Voltage		Capacitance							
			V	kV	pF		μF					
			1	10	100	1	10	0.1	1	10	100	1000
GRM	For General Purpose (Infotainment/Comfort)		2.5Vdc	3150Vdc	0.10pF	100μF						
GA2	Products Based on the Electrical Appliance and Material Safety Law of Japan		250Vac		470pF	0.10μF						
GA3	Safety Standard Certified Type		250Vac		10pF	56000pF						
GJM	High Frequency High Q Type 1005(in mm)/0402(in inch) Size Max.	High Q	25Vdc	50Vdc	0.10pF	47pF						
GMA	Top & Bottom Electrode Type for Bonding		6.3Vdc	100Vdc	100pF	0.47μF						
GMD	Compatible to Bonding/AuSn Soldering		6.3Vdc	50Vdc	100pF	0.47μF						
GQM	High Frequency High Q Type 1608(in mm)/0603(in inch) Size Min.	High Q	50Vdc	500Vdc	0.10pF	100pF						
GR3	High Effective Capacitance & High Allowable Ripple Current	Anti-noise	250Vdc	630Vdc	10000pF	1.0μF						
GR4	For Ethernet LAN & Primary-secondary Coupling of DC-DC Converters		2000Vdc		100pF	10000pF						
GRJ	Resin External Electrode Type	Deflecting crack	6.3Vdc	1000Vdc	470pF	47μF						
KR3	Metal Terminal Type High Effective Capacitance & High Allowable Ripple Current for General Purpose	Anti-noise, Deflecting crack, Soldering crack	250Vdc	630Vdc	0.10μF	2.2μF						
KRM	Metal Terminal Type for General Purpose (Infotainment/Comfort)	Anti-noise, Deflecting crack, Soldering crack	25Vdc	1000Vdc	68000pF	68μF						

Continued on the following page.

Series	Series Name	Characteristics	Rated Voltage		Capacitance							
			V	kV	pF		μF					
			1	10	100	1	10	0.1	1	10	100	1000
LLA	8-Terminal Low ESL Type	Low ESL	4Vdc	25Vdc			10000pF	4.7μF				
LLL	LW Reversed Low ESL Type	Low ESL	4Vdc	50Vdc			2200pF	10μF				
LLM	10-Terminal Low ESL Type	Low ESL	4Vdc	16Vdc			0.10μF	2.2μF				
LLR	ESR Controlled Low ESL Type	Low ESL	4Vdc					1.0μF				
DE1	Safety Standard Certified (IEC60384-14 Class X1/Y1)		250Vac	(r.m.s.)	300Vac	(r.m.s.)	10pF	4700pF				
DE2	Safety Standard Certified (IEC60384-14 Class X1/Y2)		250Vac	(r.m.s.)	300Vac	(r.m.s.)	10pF	10000pF				
DEA	High Voltage (Class 1 (Char. SL) DC1-3.15kV Rated)		1000Vdc	3150Vdc			10pF	560pF				
DEB	High Voltage (Class 2 DC1-3.15kV Rated)		1000Vdc	3150Vdc			100pF	10000pF				
DEC	High Voltage (Class 1, 2 DC6.3kV Rated)		6300Vdc				10pF	2200pF				
DEF	High Voltage (LCD Backlight Inverter Circuit)		6300Vdc	(p-p)			2.0pF	47pF				
DEH	High Voltage (High Temperature Guaranteed, Low-dissipation Factor (Char. R, C))		500Vdc	3150Vdc			150pF	4700pF				
DEJ	Based on the Electrical Appliance and Material Safety Law of Japan		250Vac	(r.m.s.)			1000pF	10000pF				
DES	High Voltage (High Temperature Guaranteed, Low-dissipation Factor (Char. D))		500Vdc	1000Vdc			100pF	4700pF				
DHR	Ultrahigh Voltage	Ultrahigh voltage, Deflecting crack, Soldering crack	10kVdc	15kVdc			100pF	1000pF				
RDE	Monolithic Lead Type for Consumer Market	Anti-noise, Deflecting crack, Soldering crack	25Vdc	1000Vdc			1.0pF	47μF				

### Explanation of Symbols

	AEC-Q200 compliant product		Low dissipation for high frequency		Product with solder cracking suppression
	Product suitable for acoustic noise reduction and low distortion		Low inductance		Withstands voltage of 10-40kV
	Fail safe product		Product resistant to deflection cracking		Certified by safety standard

## Polymer Aluminum Electrolytic Capacitors

### Infotainment/Comfort

Series	L×W	Characteristics	Rated Voltage		Capacitance							
			V	kV	pF		μF					
			1	10	100	1	10	0.1	1	10	100	1000
ECAS	7.3×4.3mm	Large Cap, Effective Cap	2Vdc	16Vdc					6.8μF	560μF		

### Explanation of Symbols

	Over 220μF		No DC bias characteristics
--	------------	--	----------------------------

Continued on the following page.

## Electrical Double Layer Capacitors

### Comfort

Series	Rated Voltage (V)	Nominal Capacitance (mF) ( ): Tolerance	ESR@1kHz (mΩ)	Size (mm)	Operating Temperature (°C)
DMT 	4.2	470 (±20%)	130	21.0×14.0×3.5	-40 to +85

Optimal for peak power assist during wireless communication for RKE.

## Trimmer Capacitors

### Infotainment/Comfort

Series	Type	Size (mm)	The Number of Product	Rated Voltage (Vdc)	Variable Range (pF)			
					0.1	1	10	100
TZY2_AC01 	SMD	2.5×3.2×1.25	8	25		0.6pF-45pF		
TZB4 	SMD	4.0×4.5×3.0	8	100		1.4pF-50pF		

## Noise Suppression Products

### Application Matrix

Product Name	Series	Powertrain	Safety	Comfort	Infotainment
Chip Ferrite Beads	BLM	●	●	●	●
Chip EMIFIL®	NFM	●	●	●	●
	NFL			●	●
	NFE	●	●	●	●
	NFZ			●	●
Block Type EMIFIL®	BNX	●	●	●	●
Chip Common Mode Choke Coils	DLW	●	●	●	●
	DLM			●	●
Common Mode Choke Coils	PLT	●	●	●	●
EMIGARD® (EMIFIL® with Varistor Function)	VFC	●	●	●	●
Disc Type EMIFIL®	DSS			●	●
Ferrite Cores	FS			●	●

## EMI Suppression Filters

### Powertrain/Safety

BL□ Inductor Type	Series	Size Code in inch (in mm)	Impedance (Ω) at 100MHz	Effective Frequency Range (Applicable Frequency Ranges are only for reference.)							
				10kHz	100kHz	1MHz	10MHz	100MHz	1GHz	10GHz	
For General Band Noise	For General Signal Lines	BLM_AG	0402-0805 (1005-2012)	10-1000							
	For High Speed Signal Lines	BLM_B	0402-0805 (1005-2012)	5-2700							
	Power Lines Type	BLM_PG*	0603-1806 (1608-4516)	22(6A)-1000(1.5A)							
For GHz Band Noise	Universal Type [Power Lines/Signal Lines]	BLM18EG*	0603 (1608)	100(2A)-600(0.5A)							
	Signal Lines Type	BLM_HG·HD	0402-0603 (1005-1608)	470-1800							

\* The derating of rated current is required for some items according to the operating temperature.

Continued on the following page. 

NF□ Capacitor Type	Series	Size Code in inch (in mm)	Capacitance (F)	Effective Frequency Range (Applicable Frequency Ranges are only for reference.)						
Universal Type [Power Lines/Signal Lines]	NFM21HC	0805 (2012)	22p-1μ							
	NFM31HK*	1206 (3216)	10000p-0.1μ							

NF□ LC Combined Type	Series	Size Code in inch (in mm)	Capacitance (F)	Effective Frequency Range (Applicable Frequency Ranges are only for reference.)						
Universal Type [Power Lines/Signal Lines]	NFE61HT	2706 (6816)	33p-3300p							

DL□ Common Mode Choke Coils	Series	Size Code in inch (in mm)	Common Mode Impedance (Ω) at 100MHz	Effective Frequency Range (Applicable Frequency Ranges are only for reference.)						
Signal Lines Type	For Differential Signal Lines	DLW31S	2200							

DL□ Common Mode Choke Coils	Series	Size Code in inch (in mm)	Common Mode Inductance (μH) at 100MHz	Effective Frequency Range (Applicable Frequency Ranges are only for reference.)						
Signal Lines Type	For Differential Signal Lines	DLW43S	11-100							

PL□ Large Current Common Mode Choke Coils for Automotive Available	Series	Size Code in inch (in mm)	Common Mode Impedance (Ω) at 100MHz	Effective Frequency Range (Applicable Frequency Ranges are only for reference.)						
Power Lines Type	PLT10H*	-	45-1000							

BNX□ Block EMIFIL®	Series	Height (mm)	Rated Voltage (Vdc)	Rated Current (A)	Effective Frequency Range (Applicable Frequency Ranges are only for reference.)						
					10kHz	100kHz	1MHz	10MHz	100MHz	1GHz	10GHz
Power Lines Type	SMD Type	BNX024H01*	3.5	50	15						
		BNX025H01*	3.5	25	15						
		BNX026H01*	3.5	50	15						
		BNX027H01*	3.5	16	15						
	Lead Type	BNX012H01*	8.5 max.	50	15						

VF□ Lead Type Capacitors with Varistor Function	Series	Height (mm)	Capacitance (F)	Varistor Voltage (V)
Power Lines Type	VFC2	6.0 max.	1.0μ	27

### Infotainment/Comfort

BL□ Inductor Type	Series	Size Code in inch (in mm)	Impedance (Ω) at 100MHz	Effective Frequency Range (Applicable Frequency Ranges are only for reference.)						
				10kHz	100kHz	1MHz	10MHz	100MHz	1GHz	10GHz
For General Band Noise	Universal Type [Power Lines/Signal Lines]	BLM_AX	0201-0402 (0603-1005)	10-1000						
	For General Signal Lines	BLM_AG	0201-0805 (0603-2012)	10-1000						
	For High Speed Signal Lines	BLM_B	0201-0805 (0603-2012)	5-2700						
	Power Lines Type	BLM_PX*·PG*·P*·KG*·SG*	0201-1806 (0603-4516)	10(1A)-1000(1.5A)						
		BLE32PN	1210 (3225)	30						

\* The derating of rated current is required for some items according to the operating temperature.

Continued on the following page. 

BL Inductor Type		Series	Size Code in inch (in mm)	Impedance (Ω) at 100MHz	Effective Frequency Range (Applicable Frequency Ranges are only for reference.) 10kHz 100kHz 1MHz 10MHz 100MHz 1GHz 10GHz
For GHz Band Noise	Universal Type [Power Lines/Signal Lines]	BLM_EB*·EG*·HE*	0201-0603 (0603-1608)	25(0.6A)-1500(0.5A)	
	Signal Lines Type	BLM_HG·HD·HB·HG	0201-0603 (0603-1608)	120-1800	
For High-GHz Band Noise	Signal Lines Type	BLM_GG·GA	0402-0603 (1005-1608)	75-470	

NF LC Combined Type		Series	Size Code in inch (in mm)	Cut-off Frequency (MHz)	Effective Frequency Range (Applicable Frequency Ranges are only for reference.) 10kHz 100kHz 1MHz 10MHz 100MHz 1GHz 10GHz
Signal Lines Type		NFL18ZT	0603 (1608)	50-500	

NF LC Combined Type		Series	Size Code in inch (in mm)	Capacitance (F)	Effective Frequency Range (Applicable Frequency Ranges are only for reference.) 10kHz 100kHz 1MHz 10MHz 100MHz 1GHz 10GHz
Universal Type [Power Lines/Signal Lines]		NFE31ZT	1206 (3216)	22p-2200p	

NF Inductor Type		Series	Size Code in inch (in mm)	Impedance (Ω) at 1MHz	Effective Frequency Range (Applicable Frequency Ranges are only for reference.) 10kHz 100kHz 1MHz 10MHz 100MHz 1GHz 10GHz
Universal Type [Power Lines/Signal Lines]		NFZ32BW	1210 (3225)	3.3-880	

DL Common Mode Choke Coils		Series	Size Code in inch (in mm)	Common Mode Impedance (Ω) at 100MHz	Effective Frequency Range (Applicable Frequency Ranges are only for reference.) 100kHz 1MHz 10MHz 100MHz 1GHz 10GHz
Signal Lines Type	For Differential Signal Lines	DLM11S	0504 (1210)	45-90	
		DLW21S	0805 (2012)	67-490	
Universal Type [Power Lines/Signal Lines]		DLW5BS*	2020 (5050)	500-800	
		DLW5AT*/DLW5BT*	2014 /2020 (5036)/(5050)	45-1400	

DS 3-Terminal Capacitors Lead Type		Series	Height (mm)	Capacitance (F)	Effective Frequency Range (Applicable Frequency Ranges are only for reference.) 10kHz 100kHz 1MHz 10MHz 100MHz 1GHz 10GHz
Universal Type [Power Lines/Signal Lines]		DSS1	7.5 max.	22p-0.1μ	

\* The derating of rated current is required for some items according to the operating temperature.


## Ferrite Cores

### Infotainment/Comfort

Type	Line-up	Frequency (MHz)
Coating Cores	Workable with all line-ups	Several 10 to Several 100
Thin Type Sandwich Cores	Length of Core 10, 15, 20, 22, 29mm	

Coated type with a 50μm thin film coating that prevents scattering.  
Thin type sandwich core (split type) provides prevention effectiveness if cracking should occur.

## Inductors



### Application Matrix

Product Name	Series	Powertrain	Safety	Comfort	Infotainment
RF Inductors Film Type	LQP			●	●
RF Inductors Multilayer Type	LQG	●	●	●	●
RF Inductors/Power Lines Wire Wound Type	LQW			●	●
Power Lines/General Circuit Multilayer Type	LQM	●	●	●	●
Power Lines/General Circuit Wire Wound Type	LQH	●	●	●	●

### Powertrain/Safety

Series	Type	Size Code in inch (in mm)	Thickness (mm/max.)	Inductance Range (H)							Rated Current	
				1n	10n	100n	1μ	10μ	100μ	1m		10m
LQG	RF Inductors Multilayer Type	0402 (1005)	—				1.0nH-270nH					110mA-300mA
		0603 (1608)	—				1.2nH-270nH					200mA-500mA
LQM	Power Lines/General Circuit Multilayer Type	0805 (2012)	1.2 ≥ Size T ≥ 1						2.2μH			800mA
LQH	Power Lines/General Circuit Wire Wound Type	1210 (3225)	Size T > 1.2						0.15μH-22μH			250mA-1.45A

### Infotainment/Comfort

Series	Type	Size Code in inch (in mm)	Thickness (mm/max.)	Inductance Range (H)							Rated Current		
				1n	10n	100n	1μ	10μ	100μ	1m		10m	
LQP	RF Inductors Film Type	0201 (0603)	—				0.6nH-120nH					80mA-850mA	
LQG	RF Inductors Multilayer Type	0402 (1005)	—				1.0nH-270nH					110mA-300mA	
LQW	RF Inductors/Power Lines Wire Wound Type	0402 (1005)	—				1.3nH-120nH					110mA-1.2A	
		0603 (1608)	—				2.2nH-470nH					75mA-1.4A	
LQM	Power Lines/General Circuit Multilayer Type	0805 (2012)	1 > Size T						0.47μH-2.2μH			600mA-1.1A	
			1.2 ≥ Size T ≥ 1						0.47μH-4.7μH			800mA-1.3A	
		0806 (2016)	1.2 ≥ Size T ≥ 1							0.47μH-4.7μH			1.1A-1.6A
		1008 (2520)	1 > Size T							0.56μH			1.5A
			1.2 ≥ Size T ≥ 1						0.24μH-4.7μH			800mA-1.8A	
LQH	Power Lines/General Circuit Wire Wound Type	1008 (2520)	1.2 ≥ Size T ≥ 1						0.47μH-22μH			430mA-2.75A	
		1206 (3216)	Size T > 1.2						0.054μH-0.88μH			180mA-920mA	
		1210 (3225)	Size T > 1.2							0.47μH-330μH			60mA-2.9A
		1212 (3030)	1.2 ≥ Size T ≥ 1							0.47μH-47μH			460mA-2.86A
		1515 (4040)	1.2 ≥ Size T ≥ 1							0.68μH-47μH			410mA-2.5A
		1812 (4532)	Size T > 1.2							1.0μH-2200μH			30mA-3.3A
		2020 (5050)	Size T > 1.2						0.47μH-22μH			1.05A-4.0A	




## Products for Radio Communication

Safety Comfort Infotainment

### CERAFIL® 10.7MHz Chip Type

Compact and lightweight filter for IF circuits adapting the piezoelectric function of ceramic.



Series	Type	3dB Bandwidth (kHz)						
		D 350	E 330	F 280	G 230	H 180	J 150	K 110
SFECF10M7□	Standard Type	●	●	●	●	●	—	—
SFECK10M7□	High-reliability Type	—	—	—	—	—	●	●
SFECV10M7□	Standard Type	—	—	—	—	—	●	●
SFECV15M0□	Standard Type	—	●	—	—	—	—	—


□ is filled in with a letter denoting 3dB bandwidth.

### Ceramic Discriminators

In combination with ICs, this type obtains stable demodulation characteristics in a wide bandwidth.

Series	Center Frequency
CDCSB	10.700MHz±30kHz

Recommended part number depends on IC specifications. Please contact us with the IC part number to be applied.



## Sensors

Comfort Infotainment

### Rotary Position Sensors

Angle detection: feedback sensor for motor actuators, etc. Position detection: replaces limit switches  
Switching: replaces rotary switches Variable resistance: works as a low-profile, long-life variable resistor

Series	Total Resistance (kΩ)	Linearity (%)	Effective Electric Rotational Angle (°)	Operating Temperature Range (°C)	Rotational Life (Cycle)
SV01 Series	10	2	333.3	-40 to +85	1M
SV03 Series	10	2	333.3	-40 to +125	300k



Care and the Future

## Sound Components

Comfort Infotainment

### Piezoelectric Sounders

Sound components to generate acknowledgment tone in instrumental panel, power slide door alarm, ultrasonic sonar operation alert and other alarm sounds.




Series	Type	Features
PKLCS	SMD Type	Super-compact and low-profiled, workable with automatic mounting and reflow soldering
PKM_EPP(H)	Pin Type	General-purpose products, low frequency (2kHz) products and high sound pressure products are in the line-up
PKM13EPYH	Pin Type	Small and low-profiled, workable with automatic insertion

## Products for Power Supply

Comfort

### Ionizer Modules Ionissimo® (High-concentration ion, compact design, ozone control)

Ionissimo® is an ionizer module with unprecedented compactness and high efficiency, capable of generating the largest amount of ions in the industry owing to Murata's own high-voltage technology and structural design. The ion generator is connected to the driving power supply for modularization and ease of incorporating into equipment.



#### MHM Series

- A large amount of ion will be created by original structure.
- Compact equipment may be designed due to small ionizer element and driving power supply.
- Ozone amounts may be optimized for specific applications by controlling the generation of ozone without changing the number of ions.

## For Automotive/Variety Product Catalogs

<http://www.murata.com/en-global/support/library/catalog/>



Chip Monolithic Ceramic Capacitors for Automotive

Cat.No.C03E



Radial Lead Type Monolithic Ceramic Capacitors

Cat.No.C49E



EMI Suppression Filters (for DC)/Chip Inductors for Automotive

Cat.No.C51E



Ceramic Resonators (CERALOCK®)

Cat.No.P16E



Low Temperature Co-fired Ceramics (LTCC) Multi-layer Module Boards

Cat.No.N20E

# Corporate Activities


## Value for Market

Providing a network to link the world, and solutions without borders.

Murata's electronic components are used throughout the world in fields ranging from home intelligent appliances to industrial electronics and car electronics. The production and supply of these components is supported by a global network consisting of production and sales offices in over a dozen countries. By this worldwide network, Murata is actively involved in a borderless and far-reaching effort to turn even more ideas into reality.

### Murata's globally accepted electronic components


For all of its leading products, Murata maintains a market share that is one of the highest in the world. Murata's electronic components play an important role inside many types of devices around the world.



## Quality Management System

Continuous Improvement of the Quality Management System.

Murata continuously improves the effectiveness and efficiency of the quality management system, with all functions at all levels improving continuously in synch with each other. All personnel ensure that the quality of their work improves in an upward spiral, and in this way we provide quality that satisfies our customers.



ISO9001 and ISO/TS16949

For a company with global business operations, it is important to meet a single global standard of product quality.

All Murata Group plants inside and outside Japan have received certification under the international quality management standard ISO9001. Of these plants, 14 supplying the automotive industry have also been certified as meeting the ISO/TS16949 quality management standard, a stricter international standard specific to the automotive industry.

### Certified According to International Quality Management Standards

Plants/Subsidiaries	Registration Standard	Plants/Subsidiaries	Registration Standard
Murata Manufacturing Co., Ltd., Yokaiichi Plant	ISO9001 ISO/TS16949	Wakura Murata Manufacturing Co., Ltd.	ISO9001
Murata Manufacturing Co., Ltd., Yasu Plant	ISO9001	Asuwa Murata Manufacturing Co., Ltd.	ISO9001
Fukui Murata Manufacturing Co., Ltd.	ISO9001 ISO/TS16949	Anamizu Murata Manufacturing Co., Ltd.	ISO9001
Toyama Murata Manufacturing Co., Ltd.	ISO9001 ISO/TS16949	Tokyo Denpa Co., Ltd.	ISO9001
Kanazawa Murata Manufacturing Co., Ltd.	ISO9001	Murata Electronics (Thailand), Ltd.	ISO9001 ISO/TS16949
Himi Murata Manufacturing Co., Ltd.	ISO9001 ISO/TS16949	Murata Electronics Singapore (Pte.) Ltd.	ISO9001 ISO/TS16949
Hakui Murata Manufacturing Co., Ltd.	ISO9001 ISO/TS16949	Wuxi Murata Electronics Co., Ltd.	ISO9001 ISO/TS16949
Sabae Murata Manufacturing Co., Ltd.	ISO9001	Shenzhen Murata Technology Co., Ltd.	ISO9001
Ogaki Murata Manufacturing Co., Ltd.	ISO9001 ISO/TS16949	Taiwan Murata Electronics Co., Ltd.	ISO9001
Izumo Murata Manufacturing Co., Ltd.	ISO9001 ISO/TS16949	Murata Electronics (Malaysia) Sdn. Bhd.	ISO9001
Iwami Murata Manufacturing Co., Ltd.	ISO9001 ISO/TS16949	Murata Electronics Europe B.V.	ISO9001
Okayama Murata Manufacturing Co., Ltd.	ISO9001	Murata Electronics North America Inc.	ISO9001
Azumi Murata Manufacturing Co., Ltd.	ISO9001 ISO/TS16949	Murata Electronics Oy	ISO9001 ISO/TS16949
Tome Murata Manufacturing Co., Ltd.	ISO9001 ISO/TS16949	Philippine Manufacturing Company of Murata INC.	ISO9001
Komoro Murata Manufacturing Co., Ltd.	ISO9001	Murata Power Solutions Inc.	ISO9001
Komatsu Murata Manufacturing Co., Ltd.	ISO9001		
Kanazu Murata Manufacturing Co., Ltd.	ISO9001		

For further details, please visit the following website: <http://www.murata.com/corporate/csr/social/customer/status.html>

## Environment

Continuing Our Quest for Harmony with the Environment

- In All Our Corporate Activities, Including Development, Design and Production -

We assess the impact of our products on the environment from the development and design stages, to ensure that every product we offer our customers takes the environment into consideration. We classify products that go even further towards contributing to reduced environmental impact as "Eco-friendly Products" and we are working to create a wider range of these products.

### Eco-products



### Global Multi-site

### ISO14001 Certification

Murata had acquired ISO14001 certification for all its production plants in Japan and overseas, and all non-manufacturing sites in Japan (Murata Head Office, Tokyo branch and sales offices) by the end of fiscal 2006. We had concentrated on integrating systems, and in March 2007, we completed switching individual certification of the 34 domestic Group business sites to ISO14001 multi-site certification. Since then, we have implemented an integrated environmental management system from design and development to production and sales, and also applied improvements that proved successful in one plant or office to other plants or offices, so as to improve the environmental performance of the entire Murata Group. In March 2010, we integrated the environmental management systems of all our domestic business sites and overseas production plants. By building a global environmental management system, we have further enhanced our governance as a Group, and enabled the implementation of more efficient and highly effective environmental activities.


In addition, while we previously conducted the PDCA cycle on an individual business site basis, since 2012 we have been conducting the cycle on the basis of management units consisting of multiple business sites. In fiscal 2013, we included Komoro Murata Manufacturing Co., Ltd., and PHILIPPINE MANUFACTURING CO. OF MURATA, INC., in the scope of our multi-site certification. As a result, the scope of the certification now includes all of our domestic business sites as well as our sites in China and the Philippines.

ISO 14001 Certification Status: <http://www.murata.com/en-eu/about/csr/certification/iso14001>

The materials that make up Murata products contain many chemical substances, and Murata is therefore working to reduce the volume of these substances used through strict and proper management.

Although the electronic components manufactured by Murata are small, the types of chemical substances used during production are numerous and their volume, as well as that of energy used, is not small. We therefore prioritize the reduction of emissions of CO<sub>2</sub> and chemical substances used in production into the atmosphere or water.

### Management of Substances with Environmental Impact



\* Beginning this fiscal year, GHG Protocol (2005) coefficients for each country are used for CO<sub>2</sub> emissions from electricity purchased at overseas plants.

The shown data in this chart is the data gained from April, 2013 in March, 2014.

# Offices

## AUSTRIA

Schönbrunner Str. 297-307  
A-1120 Vienna  
Phone: +43 1 86642 0  
Fax: +43 1 86642 250  
wien@avnet-abacus.eu

## BELARUS

c/o Avnet Abacus Russia  
Office 26, Building 2  
10 Korovinskoye Shosse,  
127486 Moscow  
Phone: +7 (495) 737 3689  
Fax: +7 (495) 737 3686  
belarus@avnet-abacus.eu

## BELGIUM

De Kleetlaan 3  
1831 Diegem  
Phone: +32 2 227 2000  
diegem@avnet-abacus.eu

## BULGARIA

c/o Avnet Abacus Austria  
Schönbrunner Str. 297-307  
A-1120 Vienna  
Phone: +43 1 86642 0  
Fax: +43 1 86642 250  
bulgaria@avnet-abacus.eu

## CROATIA

c/o Avnet Abacus Slovenia  
Dunajska Cesta 167  
1000 Ljubljana  
Phone: +386 (0)1 560 97 54  
Fax: +386 (0)1 560 98 78  
croatia@avnet-abacus.eu

## CZECH REPUBLIC

c/o Avnet Abacus Austria  
Schönbrunner Str. 297-307  
A-1120 Vienna  
Phone: +43 1 86642-0  
Fax: +43 1 86642 250  
praha@avnet-abacus.eu

## DENMARK

Knudlundvej 24  
DK-8653 Them  
Phone: +45 86 84 84 84  
Fax: +45 86 84 82 44  
them@avnet-abacus.eu

Lyskær 9, DK-2730 Herlev  
Phone: +45 86 84 84 84  
Fax: +45 43 29 37 00  
herlev@avnet-abacus.eu

## EGYPT

Canan Residence  
Hendem Cad.  
No:54 Ofis A2  
Serifali Umraniye Istanbul  
TR - 34775 Turkiye  
Phone: +90 216 52 88 370  
Fax: +90 216 52 88 377  
egypt@avnet-abacus.eu

## ESTONIA

Aida 5,  
EE-80011 Pärnu  
Phone: +372 56637737  
paernu@avnet-abacus.eu

## FINLAND

Pihatörmä 1 B  
FI-02240 Espoo  
Phone: +358 (0) 207 499 220  
Fax: +358 (0) 207 499 240  
espo@avnet-abacus.eu

## FRANCE

Immeuble Carnot Plaza  
14 Avenue Carnot  
91349 Massy Cedex, Paris  
Phone: +33 (0) 1 6447 2929  
Fax: +33 (0) 1 6447 9150  
paris@avnet-abacus.eu

8 chemin de la Terrasse  
Bat D ter étage  
31500 Toulouse  
Phone: +33 (0) 5 6247 4787  
Fax: +33 (0) 5 6247 4761  
toulouse@avnet-abacus.eu

35 avenue des Peupliers  
Les Peupliers2  
35510 Cesson  
Phone: +33 (0) 2 9983 7720  
Fax: +33 (0) 2 9983 4829  
rennes@avnet-abacus.eu

Parc Club du Moulin à Vent  
Bât 10, 33 rue du Dr. G Lévy  
F-69693 Vénissieux Cedex,  
Lyon  
Phone: +33 (0) 4 7877 1370  
Fax: +33 (0) 4 7877 1391  
lyon@avnet-abacus.eu

## GERMANY

Englische Str. 27  
D - 10587 Berlin  
Phone: +49 (0) 30 790 997 0  
Fax: +49 (0) 30 790 997 51  
berlin@avnet-abacus.eu

Industriestr. 26  
D-76297 Stutensee  
Phone: +49 (0)7249 910 149  
Fax: +49 (0)7249 910 177  
stutensee@avnet-abacus.eu

Wilhelmstr. 1, D-59439  
Holzwickede / Dortmund  
Phone: +49 (0) 2301 2959 27  
Fax: +49 (0) 2301 2959 29  
dortmund@avnet-abacus.eu

Oehleckerling 9a - 13  
22419 Hamburg  
Phone: +49 (0) 40 608 23 59 0  
Fax: +49 (0) 40 608 23 59 20  
hamburg@avnet-abacus.eu

Gruber Str. 60c-60d  
D-85586 Poing / Munich  
Phone: +49 (0) 8121 777 03  
Fax: +49 (0) 8121 777 531  
muenchen@avnet-abacus.eu

Lina-Ammon-Str. 19 b  
D-90471 Nürnberg  
Phone: +49 (0) 911 244 250  
Fax: +49 (0) 911 244 25 25  
nuernberg@avnet-abacus.eu

Gutenbergstr. 15  
D-70771 Leinfelden-  
Echterdingen / Stuttgart  
Phone: +49 (0) 711 78260 02  
Fax: +49 (0) 711 78260 333  
stuttgart@avnet-abacus.eu

Gaußstraße 10  
D-31275 Lehrte  
Phone: +49 (0) 5132 5099 0  
Fax: +49 (0) 5132 5099 76  
lehrte@avnet-abacus.eu

## GREECE

c/o Abacus Avnet Austria  
Schönbrunner Str. 297-307  
A-1120 Vienna  
Phone: +43 1 86642-0  
Fax: +43 1 86642 250  
greece@avnet-abacus.eu

## HUNGARY

c/o Avnet Abacus Austria  
Schönbrunner Str. 297-307  
A-1120 Vienna  
Phone: +43 1 86642-0  
Fax: +43 1 86642 250  
budapest@avnet-abacus.eu

## IRELAND

c/o Avnet Abacus Bolton  
Oceanic Building  
Waters Meeting Road  
Bolton BL1 8SW  
Phone: +44 (0)1204 547170  
Fax: +44 (0)1204 547171  
bolton@avnet.eu

## ISRAEL

Avnet Components Israel Ltd.  
P.O. Box 48 Tel-Mond, 4065001  
Phone: 972-9-7780280  
Fax: 972-3-760-1115  
avnet.israel@avnet.com

## ITALY

Via Manzoni 44  
I-20095 Cusano Milanino  
(Milano)  
Phone: +39 02 660 921  
Fax: +39 02 66092 332  
milano@avnet-abacus.eu

Viale dell'industria 23  
I-35129 Padova  
Phone: +39 049 7800 381  
Fax: +39 049 7730 36  
padova@avnet-abacus.eu

Via Zoe Fontana 220  
I-00131 Roma  
Phone: +39 06 4123 1952  
Fax: +39 06 4192 618  
roma@avnet-abacus.eu

Via Scaglia Est. 31/33  
41126 Modena  
Phone: +39 059 34891  
Fax: +39 059 344993  
modena@avnet-abacus.eu

Via Panciatichi 40/11  
I-50127 Firenze  
Phone: +39 055 436 1928  
Fax: +39 055 428 8810  
firenze@avnet-abacus.eu

## LATVIA

c/o Avnet Abacus Poland  
Plac Solny 16  
PL-50-062 Wroclaw  
Phone: +48 71 34 205 99  
Fax: +48 71 34 229 10  
latvia@avnet-abacus.eu

## LITHUANIA

c/o Avnet Abacus Poland  
Plac Solny 16  
PL-50-062 Wroclaw  
Phone: +48 71 34 205 99  
Fax: +48 71 34 229 10  
lithuania@avnet-abacus.eu

## NETHERLANDS

Stadionstraat 2, 6th fl.  
NL-4815 NG Breda  
Phone: +31 (0) 76 57 22 300  
Fax: +31 (0) 76 57 22 303  
breda@avnet-abacus.eu

## NORWAY

Ryensvingen 3 B  
N-0680 Oslo  
Phone: +47 (0) 22 70 76 60  
Fax: +47 (0) 22 70 76 61  
oslo@avnet-abacus.eu

## POLAND

Plac Solny 16  
PL-50-062 Wroclaw  
Phone: +48 71 34 205 99  
Fax: +48 71 34 229 10  
wroclaw@avnet-abacus.eu

## PORTUGAL

Tower Plaza, Rot. Eng. Edgar  
Cardoso, 23, Pl. 14, Sala E  
PT-4400-676 Vila Nova  
de Gaia  
Phone: +351 223 779502  
Fax: +351 223 779503  
portugal@avnet-abacus.eu

## ROMANIA

c/o Avnet Abacus Slovenia  
Dunajska Cesta 159  
1000 Ljubljana  
Phone: +386 (0)1 560 97 54  
Fax: +386 (0)1 560 98 78  
romania@avnet-abacus.eu

## RUSSIA

Office 31, Building 2  
10 Korovinskoye Shosse  
127486 Moscow  
Phone: +7 (495) 737 3689  
Fax: +7 (495) 737 3686  
Moscow@avnet-abacus.eu

## SERBIA

c/o Avnet Abacus Slovenia  
Dunajska Cesta 167  
1000 Ljubljana  
Phone: +386 (0)1 560 97 54  
Fax: +386 (0)1 560 98 78  
serbia@avnet-abacus.eu

## SLOVAKIA

c/o Avnet Abacus Austria  
Schönbrunner Str. 297-307  
A-1120 Vienna  
Phone: +43 1 86642-0  
Fax: +43 1 86642 250  
slovakia@avnet-abacus.eu

## SLOVENIA

Dunajska Cesta 167  
1000 Ljubljana  
Phone: +386 (0)1 560 97 54  
Fax: +386 (0)1 560 98 78  
ljubljana@avnet-abacus.eu

## SOUTH AFRICA

Ground Floor, Forrest House  
Belmont Office Park  
Belmont Road, Rondebosch  
7700, Cape Town  
Phone: +27 (0) 21 689 4141  
Fax: +27 (0) 21 686 4709  
sales@avnet.co.za

202 Chelmsford, 2nd Floor  
Nelson Road, Essex Gardens,  
Westville, 3629, Durban  
Phone: +27 (0) 31 266 8104  
Fax: +27 (0) 31 266 1891  
sales@avnet.co.za

Block 3, Pinewood Office Park  
33 Riley Road  
Woodmead, 2191  
Sandton, Johannesburg  
Phone: +27 (0) 11 319 8600  
Fax: +27 (0) 11 319 8650  
sales@avnet.co.za

## SPAIN

NyN Tower, C/ Tarragona,  
151-157, Floor 19  
ES-08014 Barcelona  
Phone: +34 (0) 93 327 85 50  
Fax: +34 (0) 93 425 05 44  
barcelona@avnet-abacus.eu

Plaza Zabalgane  
12 Bajo Izda,  
Galdakao / Vizcaya  
ES -48960 Bilbao  
Phone: +34 (0) 94 457 0044  
Fax: +34 (0) 94 456 8855  
bilbao@avnet-abacus.eu

C/Chile, 10 2ª Plta.  
Oficina 229  
ES -28290 Las Matas / Madrid  
Phone: +34 (0) 913 72 7200  
Fax: +34 (0) 916 36 9788  
madrid@avnet-abacus.eu

## SWEDEN

Löfströms Allé 5,  
Sundbyberg, Box 1830,  
SE-171 27 Solna  
Phone: +46 (0) 858 746200  
Fax: +46 (0) 858 746 001  
stockholm@avnet-abacus.eu

Smörhålevägen 3  
SE-43442 Kungsbacka  
Phone: +46 (0)8 58746 200  
Fax: +46 (0)300 140 15  
gothenburg@avnet-abacus.eu

## SWITZERLAND

Bernstrasse 392  
CH-8953 Dietikon  
Phone: +41 (0) 43 322 49 90  
Fax: +41 (0) 43 322 49 99  
zurich@avnet-abacus.eu

## TURKEY

Tatlisu Mahallesi,  
Pakdil Sokak  
No:5 B Blok Kat 2  
34774 Umraniye  
Istanbul Turbine  
Phone: +90 216 52 88 370  
Fax: +90 216 52 88 377  
istanbul@avnet-abacus.eu

## UK

First Floor, The Gatehouse  
Gatehouse Road  
Aylesbury, Bucks  
HP19 8DB  
Phone: +44 (0) 1296 678920  
Fax: +44 (0) 1296 678939  
Aylesbury@avnet.eu

Building 5  
Waltham Park  
White Waltham  
Maidenhead  
Berkshire SL6 3TN  
Phone: +44 (0)1628 512900  
Fax: +44 (0)1628 512999  
maidenhead@avnet.eu

Avnet House  
Rutherford Close  
Meadway,  
Stevenage  
Hertfordshire SG1 2EF  
Phone: +44 (0)1438 788 500  
Fax: +44 (0)1438 788 250  
stevenage@avnet.eu

Oceanic Building  
Waters Meeting Road  
Bolton  
BL1 8SW  
Phone: +44 (0)1204 547170  
Fax: +44 (0)1204 547171  
bolton@avnet.eu

## UKRAINE

c/o Avnet Abacus Poland  
Plac Solny 16  
PL-50-062 Wroclaw  
Phone: +48 71 34 205 99  
Fax: +48 71 34 229 10  
ukraine@avnet-abacus.eu

All trademarks and logos are the property of their respective owners. This document provides a brief overview only, no binding offers are intended. No guarantee as to the accuracy or completeness of any information. All information is subject to change, modifications and amendments without notice. Printed on FSC certified paper.