

LIGHTING SOLUTIONS

INNOVATIVE SOLUTIONS FOR LIGHTING APPLICATIONS

INDOOR, OUTDOOR AND SPECIALTY

TERMINALS



[FASTON Terminals](#)



[Ultra-Fast FASTON Terminals](#)



[Ring Terminals](#)

POWER



[Universal MATE-N-LOK Sealed Connectors](#)



[VAL-U-LOK Connectors](#)

SIGNAL



[Economy Power 2.5 Connectors](#)




[2.5mm Sealed Signal Double Lock Connectors](#)

RELAY



[OJT Relay](#)



[Mini Universal MATE-N-LOK Connectors](#)



[Universal MATE-N-LOK Connectors](#)



[Micro Universal MATE-N-LOK Connectors \(side locking version\)](#)

HEAT SHRINK TUBING



[Heat Shrink Tubing \(TFE, RT375, RW125\)](#)



[Heat Shrink Caps](#)

		Outdoor Lighting	Indoor Lighting	Specialty Lighting
Terminals	FASTON Terminals		x	x
	Ultra-Fast FASTON Terminals		x	x
	Ring Terminals		x	x
	Economy Power 2.5 Connectors		x	x
	2.5mm Sealed Signal Double Lock Connectors	x		x
Power	Micro Universal MATE-N-LOK Connectors (side locking version)		x	x
	Mini Universal MATE-N-LOK Connectors	x	x	x
	VAL-U-LOK Connectors		x	x
	Universal MATE-N-LOK Connectors	x	x	x
	Universal MATE-N-LOK Sealed Connectors	x		x
Relay	OJT Relay	x	x	
Heat Shrink Tubing	Heat Shrink Tubing (TFE, RT375, RW125)	x	x	x
	Heat Shrink Caps	x	x	

	Centerline (mm)	Current Rating	Voltage Rating	Wire Size (AWG)	Position Size	Configurations	Operating Temp. Range °C	Flammability	Approvals	Features
FASTON Terminals										
	N/A	N/A	N/A	14-12	N/A	Wire & Cable	-40°C to +110°C	N/A	CSA, UL	Straight and flag configurations, stress relieved receptacles
Ultra-Fast FASTON Terminals										
	N/A	N/A	600 VAC	22-18	N/A	Wire & Cable	-40°C to +110°C	UL 94V-2	CSA, UL	Tin plated copper alloy terminals
Ring Terminals										
	N/A	Varies	N/A	Various	N/A	Wire to Board	-40°C to +250°C	N/A	UL	Circular, flat sided, square tongue, ant rotational, stud retaining
Economy Power 2.5 Connectors										
	2.5	4.2A max	250 VAC	26-20	2-15	Wire to Board (Through Hole)	-55°C to +105°C	UL 94V-0	UL, VDE	Housing locking latch, polarization tabs
2.5mm Sealed Signal Double Lock Connectors										
	5	N/A	600 VAC	N/A	2	Wire to Wire	-30°C to +140°C	UL 94V-0	N/A	Plug housing, tab contact, TPA, seals
OJT Relay										
	N/A	10A	250 VAC	N/A	N/A	N/A	-40°C to +85°C max	N/A	UL, VDE, TUV, CQC	Operates in ambient temperatures of up to 85°C

	Centerline (mm)	Current Rating	Voltage Rating	Wire Size (AWG)	Position Size	Configurations	Operating Temp. Range °C	Flammability	Approvals	Features
Heat Shrink Tubing (TFE, RT375, RW125)										
	N/A	N/A	0.6	N/A	N/A	N/A	-55°C to 135°C	N/A	N/A	Chemical resistant, color differentiation, flexibility
Heatshrink Caps										
	N/A	N/A	N/A	N/A	N/A	N/A	-55°C to 135°C	N/A	N/A	Mechanical protection, abrasion resistance
Universal MATE-N-LOK Sealed Connectors										
	6.35	19A	600	30-10	1-15 W-W, 2-15 W-B	Wire to Wire Wire to Board Wire to Panel (Through Hole)	-55°C to +105°C (125° available)	UL 94V-0, V-2	N/A	N/A
VAL-U-LOK Connectors										
	4.2	9A	600 VAC	N/A	12	Wire to Board Wire to Wire (Through Hole)	-40°C to 105°C	CSA, UL	N/A	Contacts are offered in strip form or loose piece
Mini Universal MATE-N-LOK Connectors										
	4.14	9.5 (both) 10.5 (II)	600 VAC or VDC	30-16	1-4, 6, 9, 12, 15 2-24	Wire to Wire Wire to Board (Through Hole)	-55°C to +105°C	UL 94 V0&V2	UL, CSA, (250V Max. UL, CSA, VDE (II)	Sealed version

	Centerline (mm)	Current Rating	Voltage Rating	Wire Size (AWG)	Position Size	Configurations	Operating Temp. Range °C	Flammability	Approvals	Features
Universal MATE-N-LOK Connectors										
	6.35	19A	600 VAC or VDC	30-10	1-15 2-15 (II)	Wire to Wire Wire to Board (Through Hole)	-55°C to +105°C	UL 94 V0, V2 & GWEPT 750°C	UL, CSA, VDE	Sealed version
Micro Universal MATE-N-LOK Connectors (side locking version)										
	3.0	5A	250 VAC	30-18	2-24	Wire to Wire Wire to Board Wire to Panel (Surface mount & Through Hole)	-40°C to +105°C	UL 94 V0 & V2 GWEPT 750°C NF Version available for headers	UL, CSA, VDE	45% lower profile version available, surface-mount header configuration, dual beam contact design

te.com

MATE-N-LOK, POWER TRIPLE LOCK, TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2021 TE Connectivity Ltd. family of companies All Rights Reserved.

05/21 Original