




Data Sheet – CP 1254 A3 (CoinPower®)¹

	Type Designation	CP 1254 A3
	Type Number	63125
	Cell Code	ICR1254
	System	Graphite – layered metal oxide (LiNi _x Mn _y Co _z O ₂)
	UL Recognition	MH13654
	Nominal Voltage [V]	3.7 (average)
	Typical Capacity C [mAh]	63 (at 0.2C from 4.2 V to 3.0 V at 20 °C)
	Nominal Capacity C [mAh]	60 (at 0.2C from 4.2 V to 3.0 V at 20 °C)
	Dimensions [mm] (without Tags)	
	Diameter	12.1 +0.0/-0.3
	Height	5.4 +0.2/-0.1
	Weight. approx [g]	1.6 +0.2/-0.2
	Charging Method	Constant Current + Constant Voltage
	Charge Voltage [V]	4.20 ± 0.05
	Initial Charge Current [mA]	Standard Charge: 30 Fast Charge ² : 60 Rapid Charge ³ : 120
	Charging Cut-Off (a) or (b)	
	a) by time [h]	Standard Charge: 5 Fast/Rapid Charge: 3
	b) by min current [mA]	1.2
	Discharge Cut-Off Voltage [V]	3.0
	Max. Pulse Discharge Current [mA]	180 @ 2s
	Max. Continuous Discharge Current [mA]	120
	Operating Temperature [°C]	Charge: 0 to 45 Discharge: -20 to 60
	Storage Temperature	1 Year at -20 to 20 °C > 90
	Capacity Recovery Rate⁴ [%]	3 Month at -20 to 45 °C > 90 1 Month at -20 to 60 °C > 85
	Impedance Initial [Ω]	< 0.5 @ 1kHz
	Cycle Life 0.5C/0.5C, 20 °C⁵ [Cycles]	>500 (> 80% of C _{ini})
	Safety	UN 38.3 passed relevant tests acc. IEC 61233 passed
	Internal Approval	
	Overcharge Test (12V, 3C, 12h)	passed
	Overcharge Test (5V, 1A, 12h)	passed

¹ Recommendations regarding Charging/Discharging and Safety (cf. Handling Precautions/Advanced Product Information) have to be accepted. Cell must not be used without external safety electronics (PCM – Protection Circuit Module)! The CoinPower cell may exclusively be used for the intended purpose. For medical applications please contact VARTA Microbattery. This product is protected by at least one of the following patents: US 6265100 B1, US 6066184 A, US 9178251 B2, US 9231281 B2, US 8586232 B2, US 9153835 B2, CN 102318122 B, CN 102804473 B, EP 2628203 B1, EP 2443691 B1, EP 2415101 B1, EP 2394324 B1, JP 5767115 B2, DE 19647593 B4.

² "CoinPower A3-Version Charging Document" must be observed.

³ "CoinPower A3-Version Charging Document" must be observed. Max. charging voltage: 4.00V ± 0.05V; min. charging temperature: 15°C.

⁴ After storage at initial cell voltage of 3.6 to 3.7 V / cell

⁵ typical values