

# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series



### Highlights & Features

- Up to 700W in 3.5" x 8.5" x 1.63" Package
- Up to 14.5W/inch<sup>3</sup> Power Density
- Full Power up to 50°C Ambient
- 3 Slots Modules Configurable
- 2xMOPP Isolation for Medical Application
- Output selectable from 2V to 60V
- Current sharing for single slot modules
- Class B Conducted and Radiated EMI
- IEC 60601-1-2 4<sup>th</sup> edition immunity compliance
- Normal and Reversed Option for Global Remote On/Off
- Analog Voltage Trimming

### Safety Certifications

- IEC60601-1 2nd edition
- IEC60601-1 3rd edition + A1 CB report
- TUV EN60601-1:2006/A11/A12
- ANSI/AAMI ES 60601-1+CAN/CSA-C22.2 NO.60601-1: (Ed.3.2005)
- IEC60950-1 CB report
- IEC62368-1 CB report
- TUV EN62368-1
- UL62368-1 and CAN/CSA C22.2 No. 62368-1
- GB4943.1-2011, GB9254-2008, GB17625.1-2012

| <b>Input</b>            |  |             |             |
|-------------------------|--|-------------|-------------|
| Input Voltage           | 90VAC ~ 264VAC                             |             |             |
| Input Frequency         | 47Hz ~ 63Hz                                |             |             |
| Input Current           | <8.5A                                      |             |             |
| Inrush Current          | <40A                                       |             |             |
| Power Factor            | >0.95 @ rated load                         |             |             |
| Efficiency              | Up to 93% <sup>1)</sup>                    |             |             |
| Patient Leakage Current | <100uA normal, <500uA SFC                  |             |             |
| Earth Leakage Current   | <300uA normal, <1mA SFC                    |             |             |
| <b>Output Module</b>    |  |             |             |
| Output Number           | Single Output                              |             | Dual Output |
| Consuming Slots         | Single Slot                                | Triple Slot | Single Slot |
| Output Voltage          | 2V ~ 60V                                   | 8V ~ 60V    | 3.3V ~ 30V  |
| Output Power            | 300W Max                                   | 700W Max    | 180W Max    |
| Ripple & Noise          | <1% Vrated pk-pk or 100mV, which is larger |             |             |
| Standby Power           | 5V / 2A (No minimum load required)         |             |             |
| <b>Environmental</b>    |  |             |             |
| MTBF                    | 500KHrs                                    |             |             |
| Operation Temperature   | -20°C ~ 70°C <sup>2)</sup>                 |             |             |
| Operation Altitude      | 5000m or 50kPa                             |             |             |

1) Exclude fan power with module assembled, efficiency may vary for different configurations

2) Power de-rating with temperature above 50°C, refer to power de-rating curve for detail

# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

### Model Numbering

|  |   |   |                                |                                  |   |   |   |   |   |
|--|---|---|--------------------------------|----------------------------------|---|---|---|---|---|
| <b>MEG</b>   | - | <b>700</b>  | <b>A</b>                       | <b>3</b>                         | <b>X</b>  | - | <b>Y-Y-Y</b>                                  | - | <b>ZZZZZ</b>                              |
| <b>ME: Delta Medical Power Supply</b><br>G: Configurable |   | <b>Max Wattage in Product Series</b><br>700: 700W | <b>Family Code</b><br>A series | <b>Slot Number</b><br>3: 3 Slots | <b>Inlet Type</b><br>T: US Terminal<br>E: EU Terminal<br>C: C14 |   | <b>Output Configurations</b><br><br>See below |   | <b>PSU Configuration</b><br><br>See below |

### Output Configurations:

|                              |
|------------------------------|
| <b>Y-Y-Y</b>                 |
| <b>Output Configurations</b> |
| See below                    |

For single output **module**, output module code combined with a voltage code and a current code.

For dual output module, output module code is combined with two voltage code.

Please check Table 1 for all available combinations.

#### For example:

J1: 12V, 25A, single slot, single output module.

O2: 24V, 50A, triple slot, single output module.

OJ: Dual output module, one 24V/4A output, one 12V/5A output.

Split the modules with a "-".

If any slot to be left empty, use code "NU".

# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

Output Modules:

Table 1. Output Modules

| Voltage Code |         | Current Code       |             |                    |             |                                |                      |
|--------------|---------|--------------------|-------------|--------------------|-------------|--------------------------------|----------------------|
|              |         | Single Slot Module |             | Triple Slot Module |             | Single Slot Dual Output Module |                      |
|              |         | 1                  |             | 2                  |             |                                |                      |
| Code         | Voltage | Current            | Power (max) | Current            | Power (max) | V1 or V2 Current               | V1 or V2 Power (max) |
| A            | 2.0V    | 45.0A              | 90W         | -                  | -           | -                              | -                    |
| B            | 2.4V    | 45.0A              | 108W        | -                  | -           | -                              | -                    |
| C            | 3.0V    | 45.0A              | 135W        | -                  | -           | -                              | -                    |
| D            | 3.3V    | 45.0A              | 149W        | -                  | -           | 5.0A                           | 16.5W                |
| E            | 5.0V    | 45.0A              | 225W        | -                  | -           | 5.0A                           | 25W                  |
| F            | 5.5V    | 45.0A              | 248W        | -                  | -           | 5.0A                           | 27.5W                |
| G            | 6.0V    | 42.0A              | 252W        | -                  | -           | 5.0A                           | 30W                  |
| H            | 8.0V    | 25.0A              | 200W        | 78.7A              | 630W        | 5.0A                           | 40W                  |
| I            | 10.0V   | 25.0A              | 250W        | 70.0A              | 700W        | 5.0A                           | 50W                  |
| J            | 12.0V   | 25.0A              | 300W        | 58.3A              | 700W        | 5.0A                           | 60W                  |
| K            | 14.0V   | 21.4A              | 300W        | 50.0A              | 700W        | 5.0A                           | 70W                  |
| L            | 15.0V   | 20.0A              | 300W        | 46.7A              | 700W        | 5.0A                           | 75W                  |
| M            | 18.0V   | 16.7A              | 300W        | 38.9A              | 700W        | 5.0A                           | 90W                  |
| N            | 20.0V   | 15.0A              | 300W        | 35.0A              | 700W        | 4.5A                           | 90W                  |
| O            | 24.0V   | 12.5A              | 300W        | 29.2A              | 700W        | 3.7A                           | 90W                  |
| P            | 28.0V   | 10.7A              | 300W        | 25.0A              | 700W        | 3.2A                           | 90W                  |
| Q            | 30.0V   | 10.0A              | 300W        | 23.3A              | 700W        | 3.0A                           | 90W                  |
| R            | 32.0V   | 9.4A               | 300W        | 21.9A              | 700W        | -                              | -                    |
| S            | 36.0V   | 8.3A               | 300W        | 19.4A              | 700W        | -                              | -                    |
| T            | 42.0V   | 7.1A               | 300W        | 16.7A              | 700W        | -                              | -                    |
| U            | 48.0V   | 6.3A               | 300W        | 14.6A              | 700W        | -                              | -                    |
| V            | 54.0V   | 5.5A               | 300W        | 13.0A              | 700W        | -                              | -                    |
| W            | 60.0V   | 5.0A               | 300W        | 11.7A              | 700W        | -                              | -                    |

Note: for Triple slot module series, the module's max output power can be up to 1200W peak, constant operation power will be limited with 700W power by the frame.



# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

### PSU Configurations:

Use following definition for PSU configurations

|                      |  |                           |                    |
|----------------------|--|---------------------------|--------------------|
| <b>Z</b>             | <b>Z</b>   | <b>Z</b>                  | <b>ZZ</b>          |
| <b>Parallel Code</b> | <b>Control Code</b>  | <b>Communication Code</b> | <b>CC code</b>     |
| See Table 2          | 0: Normal Logic & Normal Fan Direction<br>1: Reversed Logic & Normal Fan Direction | 0: Default N/A            | Use AA for default |

### Parallel Code:

Parallel feature is available for the same output modules. Select parallel code, Delta will parallel the outputs before shipping to customer. Parallel feature is designed for single slot modules and only two modules can be paralleled. Triple slot modules and dual output module cannot support this option.

Table 2 Parallel Code

| Code | 1           | 2 | 3 |
|------|-------------|---|---|
| 0    | No Parallel |   |   |
| A    |             |   |   |
| B    |             |   |   |

### Examples:

**MEG-700A3T J1-J1-O1 A00AA**

3 Slots, US Terminal type input, two 12V modules in parallel, one 24V module

# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

### Specifications

#### Input Ratings / Characteristics

|                             |   |
|-----------------------------|---|
| Nominal Input Voltage       | 100-240Vac                              |
| Input Voltage Range         | 90-264Vac                               |
| Nominal Input Frequency     | 50-60Hz                                 |
| Input Frequency Range       | 47-63Hz                                 |
| Input Current (max)         | 8.5A                                    |
| Input Surge Voltage (max)   | 300Vac for 100ms                        |
| Full load Efficiency (typ.) | 91% @ 115Vac/60Hz<br>93% @ 230Vac/50Hz  |
| Inrush Current (max)        | 40A @ 230Vac, cold start                |
| Power Factor (min)          | >0.95 @ 115V/50Hz, 230V/50Hz, full load |

#### Output Ratings / Characteristics

|  |   |
|--|---|
| Total Regulation   | ±3%   |
| Output Power   | Up to 300W per single slot module, 700W per triple slot module  |
| Output Voltage Trimming range                            | ±10% of module rated output voltage   |
| Line Regulation (max)                                    | ±0.5%   |
| Load Regulation (max)                                    | ±1%   |
| Ripple & Noise (typ.)                                    | 1% pk-pk Vrated or 100mV, which is greater  |
| Start-up Time (max)                                      | 3000ms @ 115Vac   |
| Hold-up Time (min)                                       | 12ms @ rated load, with nominal input range<br>400W @200Vac/240Vac for SEMI F47   |
| Dynamic Response<br>(Overshoot & Undershoot O/P Voltage) | ±5% @ with 50-100% load change  |
| Capacitive load (max)                                    | Single Slot Single Output Module: 1500uF on each load<br>Triple Slot Single Output Module: 2800uF on each load<br>Single Slot Dual Output Module: 1000uF on each load |
| Rise time (max)  | 100ms   |
| Remote Sense   | Up to 500mV compensation for voltage drop across external wire connections to load.<br>Short and reverse connection protected.  |
| Inhibit  | Default ON, see detail in description   |
| Power Good   | Open collector signal when output is in regulation. See application note for detail   |

# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

### Global Control

|                |  |
|----------------|--|
| DC OK          | Open collector signal. Pulled high when all output is in regulation. |
| Global Inhibit | Default ON, see detail in description                                |

### Standby Ratings / Characteristics

|  |                             |
|--|-----------------------------|
| Nominal Output Voltage of standby output | 5V                          |
| Nominal Output Current of standby output | 2.0A                        |
| Total Regulation of standby output       | ±3%                         |
| Ripple & Noise of standby output         | 100mV max (Refer to Fig. 1) |




Figure 1. Ripple & Noise Measurement Circuit

### Mechanical

|                        |                                     |
|------------------------|-------------------------------------|
| Case Material          | SGCC                                |
| Dimensions (W x L x H) | 3.5"x8.5"x1.63" (88.9x215.9x41.5mm) |
| Unit Weight            | 0.8kg(1.76lb)                       |

### Environment

|                             |               |   |
|-----------------------------|---------------|---|
| Surrounding Air Temperature | Operating     | Absolute Maximum/Minimum Rating.<br>-20°C to +70°C. Power derating linearly to 50% power under 70°C |
|                             | Storage       | -40°C to +85°C  |
| Operating Humidity          |               | 5-95% RH (Non-Condensing)   |
| Operating Altitude          |               | Up to 5,000 meters (up to 16,400 feet or 106-54kPa)   |
| Non-Operating Altitude      |               | Up to 5,575 meters (up to 18,290 feet or 106-50kPa)   |
| Shock Test                  | Non-Operating | 50G, 11ms, 3 shocks for each direction  |
| Vibration                   | Non-Operating | 5-500Hz, 2Grms, 15 minutes for each three axis  |

# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

### Protections

|                              |   |
|------------------------------|---|
| Overvoltage (max)            | Latch off. Reset by recycling AC<br>In 110% to 130% rated module output voltage range |
| Overload / Overcurrent (Typ) | Hiccup Mode (Non-Latching, Auto-Recovery)<br>Up to 950W power for 5 seconds operation |
| Over Temperature             | Latch off   |
| Short Circuit                | Hiccup Mode (Non-Latching, Auto-Recovery)   |

### Reliability Data

|  |                                     |
|--|-------------------------------------|
| MTBF (Minimum) at 160Vac, 35°C           | >500kHrs based on Telecordia SR-332 |
| Operating life (Minimum) at 160Vac, 25°C | 3 Years                             |

### Safety Standards / Directives

|                    |  |
|--------------------|--|
| Medical Safety     | IEC60601-1 2 <sup>nd</sup> and 3 <sup>rd</sup> +A1 edition CB report<br>TUV EN60601-1:2006<br>ANSI/AAMI ES 60601-1+CAN/CSA-C22.2 No.60601-1: (Ed.3.2005) |
| ITE Safety         | IEC60950-1 CB report<br>IEC62368-1 CB report<br>TUV EN 62368-1<br>UL 62368-1 and CAN/CSA C22.2 No. 62368-1<br>GB4943.1-2011, GB9254-2008, GB17625.1-2012 |
| CE                 | MDD Directive 93/42/EEC  |
| Galvanic Isolation | Input to Output (2xMOPP) 4000Vac<br>Input to Ground (1xMOPP) 1768Vac<br>Output to Ground 500Vac (Type B application rated)                               |

# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

## EMC

|                                   |               |   |
|-----------------------------------|---------------|---|
| EMC / Emissions                   |               | EN55011/EN55032, FCC Title 47:Class B   |
| Harmonic Current Emissions        | IEC61000-3-2  | Meet Class A limit  |
| Immunity to                       |               |   |
| Voltage Flicker                   | IEC61000-3-3  |   |
| Electrostatic Discharge           | IEC61000-4-2  | Level 4 Criteria A <sup>1)5)</sup><br>Air Discharge: 15kV<br>Contact Discharge: 8kV   |
| Radiated Field                    | IEC61000-4-3  | Level 3 Criteria A <sup>1)</sup><br>80MHz-1000MHz, 10V/m AM modulation  |
|                                   | IEC60601-1-2  | Criteria A <sup>1)5)</sup><br>80MHz-2700MHz, 10V/m AM modulation<br>385MHz-5785MHz, 28V/m Pulse mode and other modulation   |
| Electrical Fast Transient / Burst | IEC61000-4-4  | Level 3 Criteria A <sup>1)</sup> :2kV   |
| Surge                             | IEC61000-4-5  | Level 3 Criteria A <sup>1)5)</sup><br>Common Mode <sup>3)</sup> : 2kV<br>Differential Mode <sup>4)</sup> : 1kV  |
| Conducted                         | IEC61000-4-6  | Level 2 Criteria A <sup>1)5)</sup><br>150kHz-80MHz, 3Vrms, 6Vrms at ISM bands and Amateur radio bands   |
| Power Frequency Magnetic Fields   | IEC61000-4-8  | Criteria A <sup>1)5)</sup><br>Magnetic field strength 30A/m   |
| Voltage Dips                      | IEC61000-4-11 | 30% 10ms Criteria A <sup>1)</sup><br>60% 100ms Criteria B <sup>2)</sup><br>100% 5000ms Criteria B <sup>2)</sup>   |
| Voltage Dips <sup>5)</sup>        |               | Criteria A <sup>1)</sup> @ rated full load<br>0% U <sub>T</sub> , 0.5 cycle(10ms)<br>(0°,45°,90°,135°,180°,225°,270°,315°,360°)<br>Criteria B <sup>2)</sup> , can meet Criteria A with 400W or lower load<br>0% U <sub>T</sub> ,1 cycle (20ms), 0°<br>Criteria B <sup>2)</sup><br>70% U <sub>T</sub> ,25 cycle (500ms), 0°<br>Criteria B <sup>2)</sup><br>0% U <sub>T</sub> ,250 cycle (5000ms), 0° |

1) Criteria A: Normal performance within the specification limits

2) Criteria B: Output out of regulation, or shuts down during test. Automatically restored to normal operation after test.

3) Asymmetrical: Common mode (Line to earth)

4) Symmetrical: Differential mode (Line to line)


5) Compliant with IEC-60601-1-2 4<sup>th</sup> edition requirements.



# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

### MEG Series Mechanical Outlines



- Note:**
1. Output Module Connectors: All single O/P modules are M4 x 8 mm screws, tighten between 7.0 to 10.0 kgf.cm (6.08 to 8.68 lbf.in); Dual O/P module is PUSH IN conductor connector; Wire Strip Length: 0.315" - 0.354" (8.0 - 9.0 mm).
  2. Case Material: SGCC (conductive).
  3. Customer Mounting: Screw M4-type mounting holes; Max. Penetration is 3.0 mm (0.118"); Max. Torque: 4.5 kgf.cm (3.91 lbf.in)
  4. Adjustable VR clockwise is to increase the output voltage.
  5. All dimensions are in millimeters and inches.

# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

### AC Inlet Type Option

“C” TYPE




Figure 4. IEC320-C14  
CONDUCTOR SIZE: 14 AWG Max.

“E” TYPE




Figure 5. European Terminal Block  
TIGHTENING TORQUE:2.4 Lbf.in

“T” TYPE






Figure 6. American Barrier Strip  
CONDUCTOR SIZE: 14 AWG Max.  
TIGHTENING TORQUE:8kgf.cm


### Connector Definitions – Frame



IEC Connector  
(IEC320-C14)



European  
Terminal Block



American  
Barrier Strip

Figure 8. AC Input Connector

| Pin   | Function              |
|-------|-----------------------|
| PIN 1 | AC Neutral            |
| PIN 2 | AC Line (Phase)       |
| PIN 3 | Chassis(Earth) Ground |

Table 3. AC Input Connector - pin assignment





Figure 9. Global Control Signals

# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

| Global control signals CN203 (Molex:87833-1031)<br>Mating With Molex:51110-1051 or equivalent Terminal: 0503948052 |                  |
|--|------------------|
| Pin  | Function         |
| 1  | Global DC_OK+    |
| 2  | Global DC_OK-    |
| 3  | 5V+              |
| 4  | 5V+              |
| 5  | GROUND           |
| 6  | GROUND           |
| 7  | Global Inhibit + |
| 8  | Global Inhibit - |
| 9  | No Connection    |
| 10   | No Connection    |

Table 4. Global Control Signals (CN203) – Pin assignment

# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

### Connector Definitions – Single Slot Single Output Module




Figure 10. -x1 Module Connector

| Pin | Function      |
|-----|---------------|
| V+  | Output        |
| V-  | Output Return |

Wire range: 8-20 AWG  
Screw torque: 7.0 to 10.0 kgf.cm (6.08 to 8.68 lbf.in)  
Screws are suitable for slotted and Phillips head screwdrivers.

Table 5. DC output port - pin assignment

| Control Connector CN102 (Molex: 87833-0851)<br>Mating With Molex: 51110-0851 or equivalent , Terminal: 0503948052 |                         |
|---|-------------------------|
| Pin   | Function                |
| 1   | Remote On_Off/Inhibit + |
| 2   | Remote On_Off/Inhibit - |
| 3   | Remote Sense +          |
| 4   | Remote Sense -          |
| 5   | Power Good- "Collector" |
| 6   | Power Good- "Emitter"   |
| 7   | Current Share           |
| 8   | Reserve/No Connection   |

Table 6. Control Signals Connector - pin assignment

### Connector Definitions – Triple Slot Single Output Module




Figure 11. -x2 Module Connector

| Pin | Function      |
|-----|---------------|
| V+  | Output        |
| V-  | Output Return |

Wire range: 2-16 AWG  
Screw torque: 15.0 to 20.0 kgf.cm (13.02 to 17.36 lbf.in)  
Screws are suitable for slotted and Phillips head screwdrivers.

Table 7. DC output port - pin assignment

| Control Connector CN104 (Molex: 87833-0851)<br>Mating With Molex: 51110-0851 or equivalent Terminal: 0503948052 |                         |
|---|-------------------------|
| Pin   | Function                |
| 1   | Remote On_Off/Inhibit + |
| 2   | Remote On_Off/Inhibit - |
| 3   | Remote Sense +          |
| 4   | Remote Sense -          |
| 5   | Power Good- "Collector" |
| 6   | Power Good- "Emitter"   |
| 7   | Current Share           |
| 8   | Reserve/No Connection   |

Table 8. Control Signals Connector - pin assignment

# Medical / Industrial AC-DC Configurable Power Supply Up to 700 Watt / MEG-700A Series

## Connector Definitions – Single Slot Dual Output Module




Figure 12. -x3 Module Connector

| Pin                   | Function         |
|-----------------------|------------------|
| V1+                   | V1 Output        |
| V1-                   | V1 Output Return |
| V2+                   | V2 Output        |
| V2-                   | V2 Output Return |
| Wire range: 28-16 AWG |                  |

Table 9. DC output port - pin assignment

| Control Connector CN200 (Molex: 87438-0563)<br>Mating With Molex: 87439-0500 Terminal: 874210102 |                    |
|--|--------------------|
| Pin  | Function           |
| 1  | Remote Inhibit 2 + |
| 2  | Remote Inhibit 2 - |
| 3  | NC                 |
| 4  | Remote Inhibit 1 + |
| 5  | Remote Inhibit 1 - |

Table 10. Control Signals Connector - pin assignment

## Functions

### Start-up Time

The time required for the output voltage to reach 90% of its final steady state value, after the input voltage is applied.

### Rise Time

The time required for the output voltage to change from 10% to 90% of its final steady state value.

### Hold-up Time

Time between the collapse of the AC input voltage, and the output falling to 90% of its steady state value.




Figure 13. Time Sequence

### Dynamic Response

The power supply output voltage will remain within  $\pm 5\%$  of its steady state value, when subjected to a dynamic load 50 to 100% of its rated current.




Figure 14. Dynamic from 50% load to 100% Load

# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

### Inrush Current

Inrush current is the input current that occurs when the input voltage is first applied. For AC input voltages, the maximum peak value of inrush current will occur during the first half cycle of the applied AC voltage. This peak value decreases exponentially during subsequent cycles of AC voltage.




Figure 15. Inrush Current

### Overvoltage Protection

The power supply's overvoltage circuit will be activated when its internal feedback circuit fails. The output voltage shall not exceed its specifications defined on Page 9 under "Protections". Power supply will latch off, and require removal/re-application of input AC voltage in order to restart.

### Overload & Overcurrent Protections

Each output will enter auto-recovery mode when the output current reaches over current protection set point. The output can hold to 950W typical for 5 second before tripping protection. The power supply will recover once the fault condition causing the OLP and OCP is removed and  $I_o$  is back within the specified limit. The time interval between each auto re-start during protection is 4s typical.




Figure 16. Auto-Recovery

### Short Circuit Protection

The power supply's output OLP/OCP function also provides protection against short circuits. When a short circuit is applied, the output current will operate in "Hiccup mode", as shown in the illustration in the OLP/OCP section on this page. The power supply will return to normal operation after the short circuit is removed.

### Over Temperature Protection

Each output module and PFC module sense each module operation temperature. Any output module temperature is higher than the over temperature protection set point, all the modules will be shut down latched.

An AC recycle is required to reset the power supply to normal operation.

### Remote Sense

Remote sense feature can be used to compensate for the extra voltage drop on output wires that are connected from the main output terminals, to the load. With wires connected from the remote sense pins, at the same locations as the wires from the main output, the remote sense function can compensate up to 500mV voltage drop. If the remote sense pins are shorted, or if a reverse/inverted polarity connection is made, the output module will be turned off.

### Remote On\_Off/Inhibit

The remote control signal can be used to enable or disable only the main output. When the main output is disabled, the +5V Standby output will continue to operate. Every module has its own remote on/on control signal pin, and can work independently from each other. Below is a suggested connection, system can use a switch to conduct through this diode (suggested pull up resistor to 5V standby with 1Kohm resistor) to disable the main out. The signal can be floated (no connection to the signal), in order to enable the main output.




Figure 17. Remote On\_Off connection

# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

### Global Remote On\_Off/Inhibit

The global inhibit function will turn on/off all the output modules. The control logic is selectable on demand. In normal logic, the module is default on with the control logic described in Figure 17. The module outputs will be turned off if the diode is conducted and modules will be on if diode is left floated or open.

### Power Good Signal

Power Good+/- pin on every module's control connector is an isolated open collector transistor (80V/50mA rating). A resistor (suggested value 10Kohm, 1/8W) can be added between Power Good- pin and DC RTN, Power Good+ pin can be connected to 5V standby (or, other available pull-up voltage that is no greater than the transistor rating). Value of resistor may have to be adjusted, depending on voltage used, and other end-use conditions of the Power Good+ pin connection to the product. When DC output is presented, Power Good Signal (Shown in below figure) generated will be high. When DC output is off, Power Good Signal generated will be low. There will be a minimum of 5 milliseconds between the time the Power Good Signal goes to low level, and the time when the output reaches 90% of its rated value.




Figure 19. Power good signal sequence




Figure 18. Power good signal connection


### Global DC\_OK

Global DC\_OK indicate the module output information. DC\_OK pin is an open collector type output (80V/50mA rating). DC\_OK signal connection can refer to power good signal. When all module outputs are on, DC\_OK pin will be high. When one of the outputs is off, DC\_OK pin will be pulled low .

# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series


### Power Derating – MEG-700A Series




### Power Derating – Triple Slot Modules

No air flow direction power derating unless specifically identified.


8V Module Max. Output Power Derating Curves




12V Module Max. Output Power Derating Curves



18V Module Max. Output Power Derating Curves



24V Module Max. Output Power Derating Curves







# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

36V Module Max. Output Power Derating Curves




48V Module Max. Output Power Derating Curves




### Power Derating – Single Slot Modules & Dual Output Modules

Max. Output Power Derating Curves



Max. Output Power Derating Curves



# Medical / Industrial AC-DC Configurable Power Supply

## Up to 700 Watt / MEG-700A Series

### Certificate



Delta has been certified as meeting the requirement of ISO 13485: 2003 and EN ISO 13485:2012 for the design and manufacture of switching power supply and adaptor for medical device.



In addition to a UL Total Certification Program (TCP) approved client laboratory for IEC 60950 and IEC 60065. Delta also has participated UL Client Test Data Program (CDTP) for IEC 60601

### Attention

Delta provides all information in the datasheets on an "AS IS" basis and does not offer any kind of warranty through the information for using the product. In the event of any discrepancy between the information in the catalog and datasheets, the datasheets shall prevail (please refer to [www.DeltaPSU.com](http://www.DeltaPSU.com) for the latest datasheets information). Delta shall have no liability of indemnification for any claim or action arising from any error for the provided information in the datasheets. Customer shall take its responsibility for evaluation of using the product before placing an order with Delta.

Delta reserves the right to make changes to the information described in the datasheets without notice.