

**Panasonic**

# SHORTFORM CATALOGUE

AUTOMOTIVE & INDUSTRIAL COMPONENTS · EUROPE



Sensors · Capacitors · Resistors · Inductors · Circuit Protection  
Switches · Encoders · Fuses · Wireless Modules · Semiconductors  
Thermal Heat Sink Solution · SD-Cards

# SHORTFORM CATALOGUE

AUTOMOTIVE & INDUSTRIAL COMPONENTS · EUROPE

<b>CHAPTER</b>	<b>PAGE</b>
AUTOMOTIVE SOLUTIONS . . . . .	4-5
HOME SOLUTIONS . . . . .	6-7
APPLICATIONS MATRIX . . . . .	8-9
SENSORS . . . . .	10-15
CAPACITORS . . . . .	16-24
RESISTORS . . . . .	25-36
INDUCTORS . . . . .	37-41
CIRCUIT PROTECTION . . . . .	42-46
FUSES . . . . .	47-48
THERMAL HEAT SINK SOLUTION . . . . .	49-53
SWITCHES . . . . .	54-58
ENCODERS . . . . .	59
WIRELESS CONNECTIVITY . . . . .	60-64
SEMICONDUCTORS . . . . .	65-70
SD-CARDS . . . . .	71-74
CAUTIONS AND GUIDELINES . . . . .	75

# AUTOMOTIVE SOLUTIONS

Panasonic offers a wide range of components and devices for various applications in the Automotive Market.

Starting from passive components, like capacitors, resistors and inductors, Panasonic delivers to all in car electrical applications such as airbags, brake systems, lighting systems and control panels. Our sensors are mainly used for monitoring and detecting, whilst semiconductors focus on power electronics and battery management solutions. Pyrolytic Graphite Sheets resolve heat issues experienced in displays or headlight applications. Panasonic's input devices are being used for radio, navigation, steering wheels and where a human-machine-interface is required.

## ELECTRIFICATION

- > Power Electronics
- > Battery Management

## CHASSIS & SAFETY SYSTEMS

- > Active & Passive Safety
- > ADAS (Advanced Driver Assistance Systems)
- > Headlight

## INTERIOR & HMI

- > Instrumentation & HMI
- > Infotainment & Connectivity
- > Body & Security

Details in the matrix on the pages 8/9

## Infotainment & Connectivity



## Antenna Modules



## Black Box



## ADAS



## Power Electronics & Battery Management



Airbag, Instrumentation & HMI




Energy Management



HUD & Driver Monitoring



Seat Comfort



Headlight



RKE, Access Control & Alarm


Brake Systems & TPMS



Watch the Panasonic Automotive Solutions Video



Wind & Solar Energy



Industry




M2M

Lighting



Power Tools



Charging Station



Garden Tools, eBike



Robot Cleaner

## Beauty Products & Men's Care



## Smart Home



## Toys



Dryer



Vacuum Cleaner



Refrigerator, Oven,  
Coffee Machine

# HOME SOLUTIONS

Looking into the Smart Home, Panasonic contributes to the fields of energy creation, storage and distribution.

Starting from solar and wind energy, we deliver passive components, semiconductors and thermal solutions from the source of creation to the energy storage within the house. Modern Smart Homes use our devices in areas such as home appliances, storage solutions, personal health care and kitchen appliances. Whilst in Power Tools, Electronic Toys and gadgets you can utilize our sensors, input devices and power supplies. Wireless connectivity solutions from Panasonic enables communication between various applications, giving life to the internet of things.

## RENEWABLE ENERGY

- > Wind, Solar

## MOBILITY

- > eBike
- > Charging Station

## APPLIANCE

- > Home Appliance
- > Personal, Healthcare and Toys
- > Power Tools

## LIGHTING

- > Lighting

## INTERNET OF THINGS

- > Industry 4.0
- > Smart Home

**Details in the matrix on the pages 8/9**


# APPLICATIONS MATRIX

			SENSORS							CAPACITORS						RESISTORS										
			Grid-EYE	MA Motion Proximity Switch	Pressure Sensors	Pressure Sensors w/ built-in amplifier	Ambient Light Sensors (NapIca)	Acceleration Sensors	1-axis Accelerometer	Aluminium Electrolytic	Electric Double Layer	Film	Polymer Aluminium SP-CAP	Conductive Polymer Hybrid	Polymer Aluminium OSCON	Polymer Aluminium POSCAP	Shunt Resistors	Thin Film Resistors	High Power & Pulse Proof Resistors	Thick Film Resistors	Anti-Sulfurated Resistors	Network & Array Resistors	Metal (Oxide) Film Resistors Radial	Trimmer Potentiometers SMD		
<b>AUTOMOTIVE</b>																										
<b>Electrification</b>	Power Electronics	Inverter DCDC Converter Charger (AC/DC, Bidirectional)								•		•		•			•	•	•		•	•				
	Battery Management	Battery Module								•	•		•				•	•	•		•	•				
<b>Chassis &amp; Safety Systems</b>	Active & Passive Safety	Brake Systems, ABS, ESP Airbags, Restraint Systems Remote Keyless Entry (RKE)								•			•				•	•	•		•	•				
	ADAS	Camera System Radar System	•							•		•		•	•		•	•	•		•	•				
	Headlight	LED Xenon Laser					•	•	•				•				•	•	•			•	•			
<b>Interior &amp; HMI</b>	Instrumentation & HMI	Displays Head-Up- Displays Steering Wheel HVAC ICP (Integrated Control Panel)								•		•		•	•		•	•	•			•	•			
		Infotainment & Connectivity	Radio Multimedia Connectivity, Telematics, eCall Electric Toll Collection (ETC)								•	•	•	•	•	•	•	•	•	•		•	•	•	•	
			Body & Security	Access & Door Control Seat Comfort Tire pressure monitoring systems (TPMS) Energy Management Antenna Modules Driver Monitoring with Camera Car Alarm Black Box								•	•	•	•	•	•	•	•	•	•		•	•	•	•
	<b>HOME</b>																									
<b>Renewable Energy</b>	Wind, Wind Turbine, Solar	Generation Storage Distribution Inverter									•		•				•	•	•		•	•	•	•		
												•	•	•	•		•	•	•		•	•	•	•		
<b>Mobility</b>	eBike	eBike															•	•	•		•	•	•	•		
	Charging Station	Charging Station										•	•	•	•		•	•	•		•	•	•	•		
<b>Appliance</b>	Home Appliance	Coffee Machine Fridge-Freezers Oven, Microwaves Vacuum & Robot Cleaner Dryer Laundry & Irons	•		•	•				•	•	•	•	•	•	•	•	•	•		•	•	•	•		
		Personal, Health Care & Toys	Men's Grooming Beauty Products Oral Care Toys	•	•	•	•				•	•	•	•	•	•	•	•	•	•		•	•	•	•	
			Power Tools	Drilling Screwdriver Jig saw Garden Tools Sealing gun								•	•	•	•	•	•	•	•	•	•		•	•	•	•
	<b>Lighting</b>	Lighting	Emergency Lighting	•	•					•	•						•	•	•		•	•	•	•		
	<b>Internet of Things</b>	Industry 4.0	M2M Communication								•	•		•	•	•	•	•	•			•	•	•		
Smart Home		Control of Lighting, Heating, Shutter								•	•		•	•	•	•	•	•			•	•	•			
<b>INFRASTRUCTURE</b>																										
<b>Mobility</b>	Train	Inverter		•								•			•	•	•	•			•	•	•			
<b>Information</b>	Data Server, Server	Power Supply										•	•	•	•		•	•	•		•	•	•			
<b>Communication</b>	BTS (Base Transceiver Station)	Power Supply										•	•	•	•		•	•	•		•	•	•			
<b>HEALTHCARE</b>																										
<b>Healthcare</b>	Wearables	Sleep Monitor Fitness Tracker										•			•	•	•	•		•	•	•	•			
		Home, Personal MHC Tracking	Scale Thermometer Blood Pressure Blood Sugar		•	•							•	•	•	•	•	•	•	•		•	•	•		
	Sports Activity		Fitness machines	•									•	•	•	•	•	•	•		•	•	•	•		





# WIDE RANGE OF MEMS AND OPTICAL SENSOR TECHNOLOGIES



## SENSORS

---

- > High Precision
- > High Reliability
- > Compact Size
- > Energy Saving
- > Environmental Friendly

### **Grid-Eye**

State-of-the-art IR temperature sensor featuring 64 thermopile elements in an 8 x 8 grid

### **MA Motion Proximity Switch**

Compact, easy to use proximity switch

### **Pressure Sensors**

High-precision, miniature sensors that cover low to high pressures

### **Pressure Sensors with built-in amplifier**

Contains built-in amplification and temperature compensation circuit

### **Ambient Light Sensors (NaPiCa)**

Visible light detection with proportional current output

### **Acceleration Sensor**

Capacitive MEMS acceleration sensors

# GRID-EYE

## 1ST SMD THERMOPILE ARRAY SENSOR

Grid-EYE features 64 thermopile elements in an 8x8 grid format that detect absolute temperatures by infrared radiation. Grid-EYE is able to measure actual temperature and temperature gradients, providing thermal images. It is easily possible to detect multiple persons, identify positions and direction of movement, almost independent of ambient light conditions without disturbing privacy as with conventional cameras.

Cost-effective and compact solutions for contactless temperature measurement across the entire specified area can be and with very accurate results. The built-in silicon lens provides a viewing angle of 60°.

The measurement values can be read out via I<sup>2</sup>C interface in 1 or 10 frames per second. The interrupt signal output delivers a quick response to time-critical events, offering a high degree of flexibility.



Compared to single element thermopile sensors and pyro-electric detectors, Grid-EYE sensors offers extended possibilities for detecting persons and objects, enabling advanced Applications.

### Grid-EYE – Infrared Array Sensor






Series / Type	Number of pixels	Operating voltage	P/N	Part. No.
Infrared Array Sensor Grid-EYE	64 (vertical 8 x horizontal 8)	3.3VDC	High gain	AMG8831
			Low gain	AMG8832
		5.0VDC	High gain	AMG8851
			Low gain	AMG8852

Type	Detection	Moving object	Motionless object	Moving direction	Temperature measuring	Thermal image
Pyroelectric		✓	✗	✗	✗	✗
Thermopile (single element)		✓	✓	✗	✓	✗
		↓	↓	↓	↓	↓
Grid-EYE		✓	✓	✓	✓	✓

## FEATURES

- > Dimensions: 11.6 x 4.3 x 8.0mm (L x H x W)
- > Operating voltage: 3.3V or 5.0V (depends on P/N)
- > Current consumption: Typ. 4.5mA (normal mode); 0.8mA (stand-by mode), 0.2mA (sleep mode)
- > Temperature range of measuring object: With amplification factor high gain: 0°C to 80°C, with low gain: -20°C to 100°C
- > Field of view: 60° (vertical and horizontal)
- > Number of pixels: 64 (vertical 8 x horizontal 8)
- > External interface: I<sup>2</sup>C (fast mode)
- > Frame rate: 1 or 10 frames/s
- > Typical absolute temperature accuracy: Typ. ±2.5°C (depends on P/N)

„MA Motion“ Proximity Switch

Series / Type	Available Detection Range *2	Operating Voltage	Mounting Holes	Output	Circuit for „Plug and Play“ or adjacent use *1	Part No. *2
 <p>Thin short type (Dimensions excl. mounting holes: W 11mm x H 20mm x D 12.7mm )</p>	5cm 10cm 15cm	4.5 to 5.5V	V-Type	NPN open collector output	Built-in oscillator – „Plug and Play“	AMA1459xx
					External triggering type	AMA1159xx
				PNP open collector output	Built-in oscillator – „Plug and Play“	AMA1469xx
					External triggering type	AMA1169xx
 <p>Short type (Dimensions excl. mounting holes: W 11mm x H 20mm x D 19.5mm)</p>	5-10cm (1cm steps)	4.5 to 5.5V	H-Type	NPN open collector output	Built-in oscillator – „Plug and Play“	AMBA1409xx
					External triggering type	AMBA1109xx
		5.5 to 27V		Built-in oscillator – „Plug and Play“	AMBA1402xx	
				External triggering type	AMBA1102xx	
 <p>Middle type (Dimensions excl. mounting holes: W 14mm x H 31.2mm x D 23.1mm)</p>	20-80cm (10cm steps)	4.5 to 5.5V	H-Type	NPN open collector output	Built-in oscillator – „Plug and Play“	AMBA2409xx
					External triggering type	AMBA2109xx
		5.5 to 27V		Built-in oscillator – „Plug and Play“	AMBA2402xx	
				External triggering type	AMBA2102xx	
 <p>Long type (Dimensions excl. mounting holes: W 20mm x H 46mm x D 29.7mm)</p> <p>H-Type</p>  <p>V-Type</p>	30-200cm (10cm steps)	4.5 to 5.5V	H-Type	NPN open collector output	Built-in oscillator – „Plug and Play“	AMBA3409xx
					External triggering type	AMBA3109xx
			V-Type		Built-in oscillator – „Plug and Play“	AMBA3549xx
					External triggering type	AMBA3159xx
		5.5 to 27V	H-Type	Built-in oscillator – „Plug and Play“	AMBA3402xx	
				External triggering type	AMBA3102xx	
			V-Type	Built-in oscillator – „Plug and Play“	AMBA3452xx	
				External triggering type	AMBA3152xx	


\*1: If you plan to use multiple sensors side-by-side, or you wish to keep the current consumption small, inquire for details about external trigger type, which is suitable for such applications.

\*2: Please see datasheet for part numbers depending on detection range

FEATURES

- > Thin design with only 1.2mm thickness available (AMA type)
- > „Plug and Play“ type with built-in oscillator – only connect DC power supply
- > „External trigger type“ for adjacent (side-by-side) use without interference or energy saving
- > Detection range available from 5cm to 200cm
- > Detection almost unaffected by object, color and material
- > Good performance even when detection surface is dirty

## PS/PF Gauge Pressure Sensors

Series / Type	Rated Pressure	Drive Current	Bridge Resistance	Temp. Compensation Range	Offset Voltage	Output Span Voltage	Linearity	Pressure Hysteresis	Offset Voltage-Temperature Characteristics <sup>2</sup>	Sensitivity-Temperature Characteristics <sup>2</sup>	Packaging Size	Part No.
 Gauge Pressure	4.9kPa	1.5mA	5kΩ	0-50°C	±20mV	40±20mV	±0.7%FS	±0.6%FS	±15%FS	±10%FS	PF/PS	ADPxx01x
	34.3kPa			0-50°C	±20mV	100±40mV	±0.3%FS	±0.2%FS	±5.0%FS	±2.5%FS	PF/PS	ADPxx21x
	49.0kPa			0-50°C	±20mV	100±40mV	±0.3%FS	±0.2%FS	±5.0%FS	±2.5%FS	PF/PS	ADPxx31x
	98.1kPa			0-50°C	±20mV	100±40mV	±0.3%FS	±0.2%FS	±5.0%FS	±2.5%FS	PF	ADP1x41
	196.1kPa			0-50°C	±20mV	100±40mV	±0.3%FS	±0.2%FS	±5.0%FS	±2.5%FS	PF/PS	ADPxx51x
	343.2kPa			0-50°C	±20mV	100±40mV	±0.3%FS	±0.2%FS	±5.0%FS	±2.5%FS	PF/PS	ADPxx61x
	490.3kPa			0-50°C	±20mV	100±40mV	±0.5%FS	±0.4%FS	±5.0%FS	±2.5%FS	PF/PS	ADPxx71x
	833.6kPa			0-50°C	±20mV	100±40mV	±0.6%FS	±0.4%FS	±5.0%FS	±2.5%FS	PF/PS	ADPxx71x
	980.7kPa			0-50°C	±20mV	100±40mV	±0.6%FS	±0.4%FS	±5.0%FS	±2.5%FS	PF	ADP1x91
	98.1kPa			1.0mA	5/3.3kΩ	0-60°C	±20mV	65±25mV	±1.0%FS	±1.0%FS	±3.5%FS	±2.5%FS
980.7kPa	1.0mA	5/3.3kΩ	0-60°C	±20mV	65±25mV	±1.0%FS	±1.0%FS	±3.5%FS	±2.5%FS	PS	ADP4x91x	
Gauge Pressure (economy type)	40.0kPa	1.5mA	3.3kΩ	5-45°C	±15mV	43.5±22.5mV	±0.3%FS	±0.7%FS	±10%FS	±1.3%FS	PF/PS	APDxxA23

Medium: Air<sup>1</sup>

DIP Terminal Type: Standard/Reversed

Unless otherwise specified, measurements were taken with a drive current of ±0.01mA and humidity ranging from 25% to 85%.

<sup>1</sup>Please consult us if a pressure medium other than air is to be used.<sup>2</sup>This is the regulation which applies within the compensation temperature range.

Please consult us if the intended use involves a negative pressure

Dimensions:

PF Type (W 10mm x L 8.6mm x H 9.9mm)



PS Type (W 7.2mm x L 7.2mm x H 8.5mm)

## FEATURES

## PS / PF SERIES – HIGH PRECISION GAUGE AIR PRESSURE SENSORS

- > High level of accuracy and linearity
- > Miniature “PS” package
- > Wide lineup
- > Pressure ranges from 4.9kPa to 980kPa
- > 5kΩ and 3.3kΩ bridge resistance available
- > Standard / reversed DIP packages
- > Economy type for consumer applications

**Gauge Pressure sensors with built-in amplifier**

Series / Type	Pressure Sensors with Amplifier	Pressure	Drive Voltage	Current Consumption	Offset Voltage *2,3	Span Voltage *2,3	Overall Accuracy *3,4	Temperature Compensation Range	Port Type*5	Part No. *5
 Gauge pressure	Standard Type	±100kPa	5V±0.25V	max. 10mA	2.5V ± 0.05V	4.0V (Typical)	±1.25%FS	0 to 50°C	S/M	ADP510x
		-100kPa			0.5V ± 0.05V					ADP511x
		25kPa			ADP512x					
		50kPa			ADP513x					
		100kPa			ADP514x					
		200kPa			ADP515x					
		500kPa			ADP516x					
		1,000kPa			ADP517x					
	Low Pressure Type	6kPa	5V±0.25V	max. 10mA	0.5V (Typical)	4.0V (Typical)	±2.5%FS	0 to 70°C	M/L/P	APD5B6x
	Economy Type	40kPa	3V±0.15V	max. 3mA	0.3V±0.09V *2,3,1	2.4±0.03V *2,3,1	±4.0%FS (Offset); 1,3% FS (Sensitivity)	5 to 45°C	M	ADP51A11

Medium: Air\*1  
Terminal Type: DIP

0: S Package  
length: 3mm, diameter: 3mm  
1: M Package  
length: 5mm, diameter: 3mm  
2: L Package (Only low pressure type)  
length: 13.5mm diameter: 5.45mm  
3: P Package (Only low pressure type)  
length: 15.6mm , diameter: 5.45mm


\*1. Please consult us for pressure media other than air.  
\*2. Indicates output when temperature is 25°C (77°F).  
\*3. Indicates output when drive voltage is 5V (3V for economy type).  
Although output fluctuates due to fluctuations in the drive voltage, this is not included.  
\*4. Overall accuracy indicates the accuracy of the offset voltage and rated output voltage at the specified temperature compensation range  
\*5 Port Types

**FEATURES**

**PS-A SERIES – GAUGE AIR PRESSURE SENSORS WITH INTEGRATED CIRCUIT**

- > Built in Amplifier and temperature compensation circuit
- > High accuracy and reliability
- > Overall accuracy up to 1.25% of FS (standard type)
- > Wide lineup
- > Pressure ranges from -100kPa to +1000kPa
- > Standard / reversed DIP packages
- > Economy type for consumer applications

**NaPiCa ambient light sensor**


Series / Type	Photo current *1	Reverse Voltage	Photocurrent	Power Dissipation	Operating Temperature	Dark Current	Packaging	Part No.
 NaPiCa	260µA	1.5 to 6V	5mA	40mW	-30 to +85°C	max 0.3µA	Baggage package	AMS302
							Tape and reel	AMS302T

\*1 Ev = 100 lx (Ev: Brightness, Fluorescent lamp is used as light source), V = 5V  
Tape and reel package Through-hole type: Carton: 2,000pcs.; Case: 2,000pcs.  
Baggage package Through-hole type: Carton: 500pcs.; Case: 1,000pcs.

**FEATURES**

- > Linear output: Photocurrent is proportional to illumination
- > Easy measurement of ambient light level similar to the human eye
- > Cadmium free and RoHS compliant – replacement of CdS cells
- > Integrated amplifier for schrieblisque high output current

### Acceleration Sensors GS1 / GS2 (High-precision MEMS 2-axis acceleration sensor)



Series / Type	Operation Power Supply Voltage	Current Consumption	Acceleration Detection Range	Detection Sensitivity	Temperature Sensitivity	Offset Voltage	Offset Voltage Temperature Characteristics	Non-Linearity	Shock	Part No.
 1-axis Acceleration sensor GS1	5V DC	5mA (typ.)	±2g	1V/g	±4%	2.5±0.1V	±70mg	±1%	max. 5000g	AGS11151
		5mA (typ.)	±1.5g	1.333V/g	±4%	2.5±0.1V	±70mg	±1%	max. 5000g	AGS11351
2-axis Acceleration sensor GS2	5V DC	2mA (typ.)	±2g	1V/g	±2%	2.5±0.06V	±55mg	±1%	max. 5000g	AGS21151
		2mA (typ.)	±1.5g	1.333V/g	±2%	2.5±0.08V	±55mg	±1%	max. 5000g	AGS21351
	3V DC	1.8mA (typ.)	±2g	0.6V/g	±2%	1.5±0.036V	±55mg	±1%	max. 5000g	AGS21631
		1.8mA (typ.)	±1.5g	0.8V/g	±2%	1.5±0.048V	±55mg	±1%	max. 5000g	AGS21831

Operating temperature: -40 to 85°C  
 Cross Axis sensitivity: ±5%

## FEATURES

- > High precision and high reliability:  
 Offset temperature characteristics ±47mg (GS1) and ±38mg (GS2) (Typical values)
- > High sensitivity: 1 to 1.333V/g (VDD=5V)

### 1-axis Accelerometer GF1 (Electrostatic capacitance detection sensor)

Series / Type	Operation Power Supply Voltage	Acceleration Detection Range	Detection Sensitivity	Current Consumption	Offset Voltage	Offset Voltage Temperature Characteristics	Non-Linearity	Shock	Installation Type	Part No.
 1-axis accelerometer GF1 Bracket	5V DC	±11.76m/s <sup>2</sup> (±1.2g)	1.333V/g	10mA	2.5±0.1V	±70mg	±1%	max. 5000g	Bracket	AGF11311
 1-axis accelerometer GF1 Direct Mount	5V DC	±4.9m/s <sup>2</sup> (±0.5g)	3.0V/g	10mA	2.5±0.1V	±70mg	±1%	max. 5000g	Direct mount	AGF10711
		±11.76m/s <sup>2</sup> (±1.2g)	1.333V/g	15mA	2.5±0.1V	±70mg	±1%	max. 5000g	Direct mount	AGF10321
	12V DC	±4.9m/s <sup>2</sup> (±0.5g)	3.0V/g	15mA	2.5±0.1V	±70mg	±1%	max. 5000g	Direct mount	AGF10721
		±11.76m/s <sup>2</sup> (±1.2g)	1.333V/g	15mA	2.5±0.1V	±70mg	±1%	max. 5000g	Direct mount	AGF10331
24V DC	±4.9m/s <sup>2</sup> (±0.5g)	3.0V/g	15mA	2.5±0.1V	±70mg	±1%	max. 5000g	Direct mount	AGF10731	
	±11.76m/s <sup>2</sup> (±1.2g)	1.333V/g	15mA	2.5±0.1V	±70mg	±1%	max. 5000g	Direct mount	AGF10331	

Operating temperature: -30 to 85°C  
 Temperature sensitivity: ±3%  
 Cross Axis sensitivity: ±5%

## FEATURES

- > IP67 Water and dust protected package
- > High reliability: Superior offset voltage temperature characteristics (33mg (typ.))
- > Fast response: 15ms (typ.)
- > Compact size: 58×36.5×33mm (without bracket)

# CAPACITORS FOR DEMANDING APPLICATIONS

## Aluminium Electrolytic Capacitor

Capacitors with a liquid electrolyte using an AL oxide film as dielectric – available in Surface Mount and Leaded Radial Technology.

## Electric Double Layer Capacitor (Gold Cap)

Unlike batteries, Gold Caps do not rely on a chemical reaction to produce electric current. Rather they are storage cells that utilize the absorption/release reaction of ions.

## Film Capacitor

Electrical capacitors using a thin insulating plastic film as dielectric.

## Polymer Capacitor (SP-CAP, POSCAP, OS-CON)

Using solid polymer electrolyte instead of liquid electrolyte achieving low ESR values and excellent performance over a wide frequency range.

## Conductive Polymer Hybrid

Using best of two worlds combining the low leakage of Aluminium Electrolytic and low ESR of the Polymer technology.

# CAPACITORS

---

- > Wide range of Capacitance Values
- > Very low ESR Types
- > High Ripple Currents
- > Up to 10,000h endurance
- > Temperatures up to +135°C
- > Compact Size
- > AEC-Q200 qualified Series
- > Alternatives to MLCC and Tantalum






## Aluminum Electrolytic Capacitors – Surface Mount Type

Series / Type	Temperature	Endurance	Rated W.V.	Capacity	Features	AEC-Q200	Part No.
 Type V - Series S High temp. reflow	-40 to +85°C	2,000h	6.3 to 50V	1 to 1,500µF	5.5mm height Dia. ≤ 6.3mm	qualified*	EEExAxxxxAx
			4 to 100V	1 to 1,500µF			EEExAxxxxNx EEExAxxxxSx EEExSxxxxSx
Type V - Series HA High temp. reflow	-40 to +105°C	1,000h	6.3 to 50V	1 to 1,500µF	5.5mm height	qualified*	EEEHxxxxxAx
Type V - Series HA			6.3 to 100V				EEEHxxxxxP EEEHxxxxxR
Type V - Series HB High temp. reflow		2,000h	6.3 to 50V	1 to 470µF	6.1mm height Dia. ≤ 6.3mm	qualified*	EEEBxxxxxAx
Type V - Series HB			4 to 50V				EEEBxxxxxP EEEBxxxxxR EEEBxxxxxSx
Type V - Series HC		3,000h	6.3 to 50V	1 to 1,000µF	Dia. 8-10 / 5,000h	qualified*	EEEHxxxxxxx
Type V - Series HD High temp. reflow		5,000h	6.3 to 100V	1 to 1,000µF	Long life	qualified*	EEEHxxxxxx EEEHxxxxxAx
Type V - Series HD High temp. reflow Medium-size	-55 to +105°C		6.3 to 35V	680 to 7,500µF			EEEHxxxxxAM EEEHxxxxxAQ
Type V - Series FC High temp. reflow	-40 to +105°C	1,000h	6.3 to 35V	1 to 1,500µF	Low impedance (50% less than HA series)	qualified*	EEEFxxxxxAx
Type V - Series FC			6.3 to 50V				EEEFxxxxxP EEEFxxxxxR
Type V - Series FK High temp. reflow	-55 to +105°C	2,000h	6.3 to 35V	4.7 to 1,500µF	Low impedance	qualified*	EEEFxxxxxAP EEEFxxxxxAR
Type V - Series FK High temp. reflow Medium-size		5,000h	6.3 to 100V	47 to 6,800µF			105°C / 5,000h
Type V - Series FK		2,000 to 5,000h		3.3 to 6,800µF	Low impedance (40% to 60% less than FC series)	qualified*	EEEFxxxxxR EEEFxxxxxP EEVFKxxxxxM EEVFKxxxxxQ
Type V - Series FP High temp. reflow		2,000h	6.3 to 50V	10 to 1,800µF	Low ESR (30% to 50% less than FK series)	qualified*	EEEFxxxxxxx
Type V - Series FT High temp. reflow	6.3 to 50V		10 to 2,200µF	Low impedance miniaturized	qualified*		EEEFxxxxxAP EEEFxxxxxAR
Type V - Series TG	-40 to +125°C	1,000h 2,000h	10 to 100V	10 to 4,700µF	40% smaller than TA series	qualified*	EEETGxxxxxxx EEVTGxxxxxxx
Type V - Series TK High temp. reflow Medium-size		2,000h			47 to 4,700µF		125°C / 2,000h
Type V - Series TK		3,000h	10 to 35V	47 to 470µF	Low ESR at -40°C (50% lower than TG series)	qualified*	EEETKxxxxxP EEETKxxxxxUP
Type V - Series TP High temp. reflow		3,000h (D8: 2,000h)			Low ESR	qualified*	EEETPxxxxxAx
Type V - Series TQ High temp. reflow		2,000h	35V	47 to 100µF	Low ESR, 1 size smaller than TK-series	qualified*	EEETQxxxxxxx
Type V - Series EB	-25 to +105°C	3,000 to 5,000h	160 to 450V	2.2 to 100µF	Dia, 10 to 18mm		EEVEBxxxxxxx

Vibration-proof product is available upon request ( $\geq \varnothing 8\text{mm}$  diameter).

\* The series qualify for AEC-Q200, but may have some deviations.


## Aluminum Electrolytic Capacitors – Radial Lead Type




Series / Type	Temperature	Endurance	Rated W.V.	Capacity	Features	AEC-Q200	Part No.
Type A - Series FC	-55 to +105°C	1,000 to 5,000h	6.3 to 100V	2.2 to 15,000µF	Low impedance	qualified*	EEAFCxxxxxxx EEUFCxxxxxxx
Type A - Series FK		3,000 to 5,000h	6.3 to 35V	180 to 12,000µF	Low impedance (10 to 30% less than FC series)	qualified*	EEUFKxxxxxxx
Type A - Series FM	-40 to +105°C	2,000 to 7,000h	6.3 to 50V	22 to 6,800µF	Low Impedance		EEUFMxxxxxxx
Type A - Series FR		5,000 to 10,000h	6.3 to 63V	4.7 to 8,200µF	Low ESR		EEUFRxxxxxxx
Type A - Series ED	-25 to +105°C	8,000 to 10,000h	160 to 450V	10 to 330µF	High ripple current (at high frequency)		EEUEDxxxxxxx
Type A - Series EB	-40 to +105°C	5,000 to 10,000h	10 to 63V	0.47 to 3,300µF	Long life Low profile		EEUEBxxxxxxx
Type A - Series EE	-25 to +105°C	8,000 to 10,000h	160 to 450V	10 to 330µF	High ripple		EEUEExxxxxxx
Type A - Series TA	-40 to +125°C	2,000h	10 to 63V	2.2 to 4,700µF	High ripple	qualified*	EEUTAxxxxxxx
Type A - Series TP	-40 to +135°C	1,000 to 5,000h	25 to 35V	100 to 5,100µF	High Ripple (20 to 40% higher than TA series)	qualified*	EEUTPxxxxxxx
Type A - Series NHG	-55 (-25) to +105°C	1,000 to 2,000h	6.3 to 450V	1 to 22,000µF	+105°C 1000h; 2000h	qualified*	ECAXxHGxxxxx
Type A - Series HD	-55 to +105°C	1,000 to 2,000h	10 to 50V	2.2 to 22,000µF	miniaturized (1 case smaller to NHG series)	qualified*	EEUHDxxxxxxx
Type A - Series GA	-55 to +105°C	1,000h	10 to 50V	1.5 to 220µF	7mm height		EEAGAxxxxxxx
Type A - Series GA Bi-polar	-40 to +105°C	1,000 to 2,000h	6.3 to 50V	1.5 to 330µF	Bi-polar		ECAXxENxxxxx
Type A - Series M	-40 (-25) to +85°C	2,000h	6.3 to 450V	1 to 22,000µF	Smaller than SU series		ECAXxMxxxxx
Type A - Series SU Bi-polar			6.3 to 50V	2.2 to 6,800µF	Bi-polar		ECAXxNxxxxx
Type A - Series KA	-40 to +85°C	1,000h	4 to 50V	2.2 to 470µF	7mm height		ECAXxKAxxxx
Type A - Series KA Bi-polar				2.2 to 100µF			ECAXxKNxxxx
Type A - Series KS				2.2 to 330µF	5mm height		ECAXxKSxxxx
Type A - Series KS Bi-polar				6.3 to 50V			2.2 to 47µF

\* The series qualify for AEC-Q200, but may have some deviations.


### Electric Double Layer Capacitors – Radial Lead Type

Series / Type	Temperature	Endurance	Rated W.V.	Capacity	Features	Part No.
 Series HZ	-25 to +70°C	1,000h	2.5V	3.3 to 10F	Miniaturized	EECHZxxxxxx
	-25 to +60 (+70)°C		2.1V 2.3V	22 to 70F	Large Capacitance	EECHWxxxxxx





### Electric Double Layer Capacitors – Stacked Coin Type

Series / Type	Temperature	Endurance	Rated W.V.	Capacity	Features	Part No.
 Series SD	-25 to +70°C	1,000h	5.5V	0.22 to 0.33F	Tabbed lead terminals	EECS0HDxxxxx
	-40 to +70°C					EECS0HDxxxxxN <a href="#">UPGRADE</a>
Series SG	-25 to +70°C	1,000h	5.5V	0.47 to 1.5F	Tabbed lead terminals	EECS5R5xxxx
	-40 to +70°C					EECS5R5xxxxN <a href="#">UPGRADE</a>
Series SE	-25 to +70°C	1,000h	5.5V	0.22F	5mm pitch lead taping	EECSE0Hxxxxx
	-40 to +70°C					EECSE0HxxxxxN <a href="#">UPGRADE</a>
Series NF	-25 to +70°C	1,000h	5.5V	0.22 to 1.5F	Flat type	EECF5R5Uxxxx
	-40 to +70°C					EECF5R5UxxxxN <a href="#">UPGRADE</a>
Series F	-25 to +85°C	1,000h	5.5V	0.1 to 1.5F	85°C Flat type	EECF5R5Hxxxx
	-40 to +85°C					EECF5R5HxxxxN <a href="#">UPGRADE</a>
Series RG	-25 to +85°C	2,000h	3.6V	0.22 to 1.0F	2,000h at 85°C	EECRGxxxxxx
	-40 to +85°C					EECRGxxxxxxN <a href="#">UPGRADE</a>
Series RF	-25 to +85°C	1,000h	5.5V	0.1 to 0.68F	85°C Flat type	EECRFxxxxxx
	-40 to +85°C					EECRFxxxxxxN <a href="#">UPGRADE</a>

### Film Capacitors – Surface Mount Type

Series / Type	Temperature	Rated W.V.	Capacity	Features	Dielectric material	Part No.
 Series ECHU(X)	-55 to +125°C	16VDC 50VDC	0.00010 to 0.22µF	Tight capacitance tolerance	PPS	ECHUxxxxxxX5
						Series ECHU(C)
Series ECWU(X)	-55 to +125°C	100VDC 250VDC 630VDC	0.0010 to 0.010µF	Small type	PEN	ECWUxxxxxxX5
Series ECWU(C)			0.0010 to 1.0µF	Wide rated voltage range		ECWUxxxxxxCx
Series ECWU(V16)			-55 to +85°C	250VDC	0.001 to 0.12µF	For xDSL DC-blocking
Series ECPU(A)	-40 to +85°C	16VDC	0.10 to 1.0µF	High volumetric efficiency	Plastic resin	ECPUxxxxxxMA5

## Film Capacitors – Radial Lead Type

Series / Type	Temperature	Rated W.V.	Capacity	Features	Dielectric material	Part No.
 Series EZPE <b>UPGRADE</b>	-40 to +85°C	500VDC 800VDC 1,100VDC 1,300VDC	10 to 110µF	High safety Self-healing Self-protecting	PP	EZPExxxxxTA
		450VDC 525VDC	66µF, 29µF	High safety Self-healing Self-protecting low profile		EZPExxxxxTx
 	-40 to +105°C 100 to 1250VDC -40 to +85°C 125, 250VAC	100 to 1,250VDC 125, 250VAC	0.0010 to 10µF	Wide rated voltage range	PET	ECQExxxxxF ECQExxxxxF
		250VDC 125VAC	0.010 to 4.7µF	Small type		ECQExxxxxB ECQExxxxxB
		250 to 630VDC 125VAC 250VAC	0.010 to 10µF	Wide rated voltage range		ECQExxxxxT ECQExxxxxT
Series ECWF(L)	-40 to +105°C	400VDC 450VDC 630VDC	0.010 to 2.4µF	High frequency	PP	ECWFxxxxL
Series ECWF(A)		250VDC 450VDC 630VDC	0.10 to 6.8µF	Miniaturization of ECWF(L)		ECWFxxxxxA
Series ECWFD		450VDC	0.47 to 2.2µF	Low Hum Sound Noise		ECWFD2Wxxxx
Series ECWFE <b>NEW SERIES</b>		450VDC	0.1 to 4.7µF	Low Hum Sound Noise box type		ECWFE2Wxxxx
Series ECWH(V)	-25 to +105°C	1000 to 2,000VDC	0.0010 to 0.10µF	Low-loss Inherent Temperature rise		ECWHxxxxxVx ECWHxxxxRxV
Series ECWH(A)	-40 to +105°C	800VDC 1,600VDC	0.010 to 0.047µF	High voltage and high frequency		ECWHxxxxHx ECWHxxxxRHA ECWHA3Cxxxx
Series ECWH(C)	-40 to +105°C General resonance circuit -40 to +85°C Air cooling	630VDC, 1,250VDC	0.10 to 0.33µF	Low-loss		ECWH6xxxHC ECWH6xxxHCx ECWH6xxxRHC ECWHC3BxxxJA
Series ECQUA	-40 to 110°C	275VAC	0.1 to 2.2µF	Safety standard Class X2		ECQUAAFxxx
Series ECQUL	-40 to +100°C	275VAC (250VAC)	0.0010 to 2.2µF	Safety standard Class Y2 / X2	PET	ECQUxxxxxL
Series ECQUG		300VAC (250VAC)	0.010 to 1.0µF	Safety standard Class X1		ECQUxxxxxG
 DC-Link Film Capacitor	-40 to 105°C	450VDC	581µF	Automotive, high safety, self healing, low ESR	PP	EZTVKCTYP1HA

# POLYMER CAPACITORS

## SPEED UP YOUR DESIGN – THE NEXT STAGE OF LOW ESR



### OS-CON™

OS-CON™ is an aluminium solid capacitor with high conductive polymer electrolyte material. OS-CON™ acquires high ripple currents, low ESR, excellent noise reduction capability and frequency characteristics. In addition, OS-CON™ has a long life span and its ESR has little change even at low temperatures since the electrolyte is solid.



### POSCAP™

POSCAP™ is a solid electrolytic chip capacitor. The anode is sintered tantalum and the cathode is a highly conductive polymer. POSCAP™ has a low ESR (Equivalent Series Resistance) level and excellent performance for high frequency while maintaining a low profile and high capacitance. In addition, it has high reliability and high heat resistance.



### SP-CAP – CONDUCTIVE POLYMER ALUMINIUM CAPACITORS

Based on common aluminium electrolytic capacitor technology SP cap uses solid polymer electrolyte instead of liquid electrolyte. It has been continuously developed since 1990 and offers very stable capacitance characteristics over the complete operating temperature and frequency range, especially compared to ceramic and low ESR tantalum capacitors. And in terms of safety SP Cap does not easily ignite or “smoke” at over-voltage conditions or in case of short circuit. If a defect occurs, the polymer will become self-insulating and shuts off the current flow.




### CONDUCTIVE POLYMER HYBRID ALUMINIUM ELECTROLYTIC CAPACITORS

Lytic meets Polymer. It brings together low ESR characteristics of specialty polymer capacitor and the low leakage current of aluminium electrolytic capacitor. The series shows a compact design, high reliability in high temperatures with the safety of the aluminum electrolytic capacitor.

## FEATURES

- > High Reliability, long lifetime
- > High Efficiency in Small Case Sizes
- > Low ESR – High Ripple Current
- > High Miniaturization Potential
- > The Smart Alternatives to Tantalum Capacitors


## POSCAP – Conductive Polymer Tantalum Solid Capacitors

Series / Type	Features	Temperature	Endurance*	Rated voltage [V. DC]	Capacitance range [μF]	ESR range [mΩ @ 100kHz+]	Case size range [LxWxH in mm (Code)]	Part No.	
	TCE <small>NEW</small>	High Temperature	-55 to 125°C	1,000h	2.5 to 10	100 to 1,000	12 to 25	7.3 x 4.3 x 1.8 (D2E) to 7.3 x 4.3 x 3.8 (D4)	xxTCExxxxx
	TCF <small>NEW</small>	High Temperature			2.5 to 10	150 to 1,000	5 to 15	7.3 x 4.3 x 2.8 (D3L) to 7.3 x 4.3 x 3.8 (D4)	xxTCFxxxxx
	TV **	High Reliability Guaranteed at 125°C			6.3 to 10	68 to 150	25	7.3 x 4.3 x 1.8 (D2E) to 7.3 x 4.3 x 2.8 (D3L)	xxTVxxxxx
	TH	Guaranteed at 125°C			2.5 to 10	68 to 470	15 to 40	7.3 x 4.3 x 1.8 (D2E) to 7.3 x 4.3 x 3.8 (D4)	xxTHxxxxx
	TA **	High Reliability	-55 to 105°C	2,000h	2.5 to 10	47 to 680	9 to 70	3.5 x 2.8 x 1.9 (B2) to 7.3 x 4.3 x 2.8 (D3L)	xxTAXxxxxx
	TPB	Standard			4 to 10	33 to 470	35 to 70	3.5 x 2.8 x 1.9 (B2) to 7.3 x 4.3 x 3.8 (D4)	xxTPBxxxxx
	TPC	Low Profile			6.3 to 12.5	10 to 330	40 to 80	3.5 x 2.8 x 1.1 (B1) to 7.3 x 4.3 x 1.9 (D2)	xxTPCxxxxx
	TQC <small>UPDATE</small>	High Voltage			16 to 35	2.7 to 150	40 to 300	3.5 x 2.8 x 1.4 (B15) to 7.3 x 4.3 x 2.8 (D3L)	xxTQCxxxxx
	TPE <small>UPDATE</small>	Low ESR			2 to 10	47 to 1,500	70 to 150	3.5 x 2.8 x 1.9 (B2) to 7.3 x 4.3 x 3.8 (D4)	xxTPExxxxx
	TPF <small>UPDATE</small>	Low ESR Large Capacitance			2 to 10	150 to 1,000	5 to 15	7.3 x 4.3 x 1.8 (D2E) to 7.3 x 4.3 x 3.8 (D4)	xxTPFxxxxx
	TPSF <small>UPDATE</small>	Low ESR Small Size Large Capacitance			2 to 2.5	200 to 270	6 to 9	3.5 x 2.8 x 1.1 (B1S) to 3.5 x 2.8 x 1.9 (B2S)	xxTPSFxxxxx
	TPG <small>UPDATE</small>	Small Size Large Capacitance			1,000h	2.5 to 12.5	33 to 220	35 to 70	3.5 x 2.8 x 1.1 (B1G) to 3.5 x 2.8 x 1.4 (B15G)
	TPH	Small Size Low Profile	2.5 to 10	33 to 220	7 to 35	3.2 x 1.6 x 0.9 (A09) to 3.2 x 1.6 x 1.4 (A14)	xxTPHxxxxx		
TPU	Small Size Low Profile	-55 to 85°C	1,000h	2.5 to 10	4.7 to 150	100 to 300	2.0 x 1.25 x 0.9 (S09) to 3.5 x 2.8 x 0.9 (B09)	xxTPUxxxxx	

\* Lifetime calculation: 10times x 20°C (eg. 125°C 1,000h => 105°C 10,000h => 85°C 100,000h)


\*\* Automotive grade

## Polymer Aluminum Capacitors

Series / Type	Features	Temperature	Endurance*	Rated voltage [V. DC]	Capacitance range [μF]	ESR range [mΩ @ 100kHz]	Case size range [LxWxH in mm]	Part No.
 HX <small>NEW</small>	High Temperature Low ESR High voltage	-55 to 125°C	1,000h	2 to 25	15 to 560	4.5 to 40	7.3 x 4.3 x 1.9	EEFHXXXXXXXX
CX <small>UPDATE</small>	High Capacitance Low Profile 1.9mm Height	-55 to 105°C	2,000h <small>UPDATE</small>	2 to 6.3	100 to 560	12 to 15	7.3 x 4.3 x 1.9	EEFCXXXXXXXX
	High Voltage Low Profile 1.9mm Height			10 to 35	15 to 100	40		
CT <small>UPDATE</small>	Low Profile 1.4mm Height			4 to 6.3	100 to 180	15	7.3 x 4.3 x 1.4	EEFCTXXXXXXXX
	High Voltage Low Profile 1.4mm Height			10 to 35	22 to 68	40		
CS <small>UPDATE</small>	Low Profile 1.1mm Height			4 to 6.3	68 to 120	15	7.3 x 4.3 x 1.1	EEFCSXXXXXXXX
	High Voltage Low Profile 1.1mm Height			10 to 35	10 to 47	40		
SX	Low ESR Low Profile 1.9mm Height			2 to 6.3	82 to 560	4.5 to 9	7.3 x 4.3 x 1.9	EEFSXXXXXXXX
ST	Low ESR Low Profile 1.4mm Height			2 to 2.5	270 to 330	6	7.3 x 4.3 x 1.4	EEFSTXXXXXXXX
SS	Low ESR Low Profile 1.1mm Height			2 to 2.5	180 to 220	6	7.3 x 4.3 x 1.1	EEFSSXXXXXXXX
SR	Low ESR Low Profile max. 1mm Height			2 to 6.3	68 to 220	4.5 to 9	7.3 x 4.3 x 1.0	EEFSRXXXXXXXX
GX	Low ESR Low Profile 1.9mm Height			2 to 2.5	330 to 560	3	7.3 x 4.3 x 1.9	EEFGXXXXXXXX
	Low ESL Low ESR Low Profile 1.9mm Height							EEFGXXXXXXXXL
LX	Low ESL Low ESR Low Profile 1.9mm Height			2 to 2.5	330 to 560	4.5 to 6	7.3 x 4.3 x 1.9	EEFLXXXXXXXX
LT	Low ESL Low ESR Low Profile 1.4mm Height			2 to 2.5	270 to 330	6	7.3 x 4.3 x 1.4	EEFLTXXXXXXXX
LS	Low ESL Low ESR Low Profile 1.1mm Height			2 to 2.5	180 to 220	6	7.3 x 4.3 x 1.1	EEFLSXXXXXXXX
LR	Low ESL Low ESR Low Profile max. 1mm Height			2 to 6.3	68 to 220	4.5 to 6	7.3 x 4.3 x 1.0	EEFLRXXXXXXXX

\* Lifetime calculation: 10times x 20°C (eg. 125°C 1,000h => 105°C 10,000h => 85°C 100,000h)


## OS-CON – Conductive Polymer Aluminum Solid Capacitors

Series / Type	Features	Temperature	Endurance*	Rated voltage [V. DC]	Capacitance range [μF]	Ripple Current [mArms @ 105°C]	Case size range [DxHmax (Code)]	Part No.	
	SVP	Standard	-55 to 105°C	2,000h	2.5 to 20	3.3 to 1,500	670 to 5,440	5.0 x 4.5 (B45) to 6.3 x 10.0 (C10)	xxSVPxxxx xxASVPxxx (**)
	SVPA	Low ESR High Ripple Current	-55 to 105°C	2,000h	2.5 to 20	10 to 820	1,700 to 4,240	5 x 6 (B6) to 10 x 8 (F8)	xxSVPAxxxx
	SVPB	Low Profile	-55 to 105°C	1,000h	2.5 to 20	15 to 120	1,670 to 2,000	6.3 x 5 (C5) to 6.3 x 5.5 (C55)	xxSVPBxxxx
	SVPC <small>UPDATE</small>	Large Capacitance Low ESR	-55 to 105°C	2,000h	2.5 to 16	39 to 2,700	1,820 to 5,150	5 x 6 (B6) to 10 x 12.7 (F12)	xxSVPCxxxx
	SVPF	Long Life High Voltage Large Capacitance	-55 to 105°C	5,000h	16 to 50	10 to 1,000	2,450 to 5,400	5 x 6 (B6) to 10 x 12.7 (F12)	xxSVPFxxxx
	SVPG <small>UPDATE</small>	Low ESR High Ripple Current	-55 to 105°C	5,000h	16 to 25	15 to 270	2,800 to 5,800	5.0 x 4.5 (B45) to 6.3 x 10.0 (C10)	xxSVPGxxxx
	SVPE	Super Low ESR Large Capacitance	-55 to 105°C	2,000h	2 to 16	150 to 1,200	2,700 to 6,100	5 x 6 (B6) to 10 x 12.7 (F12)	xxSVPExxxx
	SVPS	Long Life	-55 to 105°C	5,000h	4 to 25	10 to 680	700 to 4,130	4 x 5.5 (A5) to 10 x 8 (F8)	xxSVPSxxxx
	SVQP	Guaranteed @ 125°C	-55 to 125°C	1,000h	4 to 20	22 to 220	1,450 to 2,560	6.3 x 6 (C6) to 8 x 7 (E7)	xxSVQPxxxx xxASVQPxxx (**)
	SVPD	Guaranteed @ 125°C High Voltage	-55 to 125°C	2,000h	10 to 35	8.2 to 82	1,300 to 3,800	6.3 x 6 (C6) to 10 x 12.7 (F12)	xxSVPDxxxx xxASVPDxxx (**)
	SXV <small>NEW</small>	Super High Voltage Long Life	-55 to 105°C	5,000h	63 to 100	15 to 33	2,350 to 2,950	8 x 12 (E12)	xxSXVxxxx
SEPF <small>UPDATE</small>	Long Life High Voltage Large Capacitance	-55 to 105°C	5,000h	16 to 35	22 to 1,000	2,400 to 5,400	6.3 x 5.5 (C55) to 10 x 13 (F13)	xxSEPFxxxx	
SXE <small>NEW</small>	Super High Voltage Long life	-55 to 105°C	5,000h	63 to 100	15 to 33	2,350 to 2,950	8 x 12 (E12)	xxSXExxxx	

\* Lifetime calculation: 10 times x 20°C (eg. 105°C 5,000h => 85°C 50,000h)

\*\* Automotive grade available

## Conductive Polymer Hybrid Aluminum Electrolytic Capacitors

Series / Type	Features	Temperature	Endurance*	Rated voltage [V. DC]	Capacitance range [μF]	Ripple Current [mArms @ 105°C]	AEC-Q200	Part No.
	ZA	High Ripple Current Long Life	-55 to 105°C	10,000h	25 to 80	10 to 330	qualified**	EEHZAxxxxx
	ZC	High Ripple Current Long Life 125°C	-55 to 125°C	4,000h	25 to 63			EEHZCxxxxx


Vibration-proof product is available upon request (≥ Ø 8mm diameter).

\* Lifetime calculation: 2times x 10°C (eg. 105°C 10,000h => 85°C 40,000h)

\*\* The series qualify for AEC-Q200, but may have some deviations.



# FOR AUTOMOTIVE AND HIGH RELIABILITY APPLICATIONS



## **ERA Series – High Reliability Thin Film Resistors**

- > High reliability, high heat resistance and high moisture resistance make ERA-series perfectly suited to harsh environment applications, such as automotive, medical, transportation and any measurement industry

## **High power & Anti-Surge Resistors (ERJP and ERJT Series)**

- > Electronic surge can occur anywhere in a vehicle's electronic circuitry, industrial, measurement and telecom applications
- > Panasonic ERJP series have great Anti-Surge characteristics and excellent heat dissipation characteristics due to 'Serpentine Resistor Pattern Structure' which helps to decrease electric field strength per unit length
- > Combined with a variety of small case size Panasonic Anti-Surge Resistors are suitable to replace MELF in plenty of cases

## **SMD Current Sensing Shunt Resistors – Soft Termination**

- > Current Sensing Resistors are designed for low resistance so as to minimize power consumption
- > In order to meet the requirements of the market Panasonic offers a wide range of Current Sensing Resistors in many case sizes (0402 to 2526) and many resistance values in different technologies
- > Metal plate technology (ERJM-series) and special constructions makes them suitable for the harsh environment while maintaining their high reliability and high power
- > Double sided resistor element technology (ERJxBW-series) & wide terminal technology (ERJA, ERJB-series) for high power purpose

## RESISTORS

---

- > Corresponding to AEC-Q200
- > High power in small package
- > High performance and reliability
- > Stability over life time
- > Wide Resistance Value
- > Excellent TCR
- > Down Sizing
- > Cost Saving

# HIGH POWER SMD RESISTORS


## DOWNSIZING AND COMPONENT-SAVING PURPOSE

### ADDED VALUE

- > Downsizing & High Power Load
- > Components-Saving
- > Cost Saving


### STANDARD TYPE STRUCTURE

Resistance Element



Hot spot and power limitation, due to „L shaped“ laser trimming.


### ANTI-SURGE TYPE STRUCTURE




1	2	3	4	5	6	7	8	9	10	11	12	Digit	
E	R	J	P	0	6	D	1	0	0	2	V	Part Number	
<b>Product Code</b>			<b>Size, Power, Rating</b>			<b>Resistance Tolerance</b>		<b>Resistance Value</b>			<b>Packaging Methods</b>		
Thick Film Chip Resistors			Type	Inch	Power R.	Code	Tolerance	The first two or three digits are significant figures of resistance and the third or fourth one denotes number of zeros following. Three digit type (±5%) Four digit type (±1.0%, ±0.5%) Example: 222 -> 2.2kΩ, 1002 -> 10kΩ			Code	Packaging	Type
			P03	0603	0.20W	D	±0.5%				V	Punched Carrier Taping 4mm pitch, 5,000 pcs.	ERJP03 ERJPA3 ERJP06 ERJP08
			PA3	0603	0.25W	F	±1.0%				U	Embossed Carrier Taping 4mm pitch, 5,000 pcs.	ERJP14
			P06	0805	0.50W	J	±5.0%						
			P08	1206	0.66W								
			P14	1210	0.50W								

### WIDE TERMINAL TYPE STRUCTURE


> ERJB3 Series  
(Size 0508)



> ERJB2 Series  
(Size 0612)



> ERJB1 Series  
(Size 1020)

















1	2	3	4	5	6	7	8	9	10	11	Digit			
E	R	J	A	1	A	J	1	0	2	U	Part Number			
<b>Product Code</b>			<b>Size, Power, Rating</b>			<b>Resistance Value Region</b>		<b>Resistance Tolerance</b>		<b>Resistance Value</b>		<b>Packaging Methods</b>		
Thick Film Chip Resistors			Type	Inch	Power R.	A	10Ω ≤ R	F	±1.0%	Shown by three digits or letters. Only when it is possible, shown by four digits or letters. Ex.: 102: 1.0kΩ R01: 0.01 Ω = 10mΩ 4R7: 4.7Ω R015: 0.015Ω = 15mΩ		Code	Packaging	Type
			B1	2010	1W (2W; R≤10Ω)	B	0.22Ω ≤ R < 10Ω	G	±2.0%			V	Punched Carrier Taping 4mm pitch, 5,000 pcs.	ERJB2 ERJB3
			B2	1206	0.75W (1W; R≤10Ω)	C	0.01Ω ≤ R < 0.22Ω	J	±5.0%			U	Embossed Carrier Taping 4mm pitch, 5,000 pcs.	ERJB1
			B3	0805	0.33W (0.5W; R≤10Ω)	D	0.005Ω ≤ R < 0.01Ω					Embossed Carrier Taping 4mm pitch, 4,000 pcs.		ERJA1

# HIGH POWER SMD RESISTORS

## DOWNSIZING AND COMPONENT-SAVING PURPOSE

### DOWNSIZING & COMPONENT SAVING MATRIX

Power \ Size	0402 (1005mm)	0603 (1608mm)	0805 / 0508	1206/0612 (3216/1632mm)	1210 (3225mm)	2010/1020 (5025/2550mm)
2W						ERJB1 
1W				ERJB2 		
0.66W (2/3W)				ERJP08 		
0.5W (1/2W)			ERJB3  ERJP06 		ERJP14 	ERJ12 (0.75W) 
0.33W (1/3W)					ERJ14 	
0.25W (1/4W)		ERJPA3 			ERJ8ENF 	
0.2W (1/5W)	ERJPA2 					
0.125W (1/8W)				ERJ6ENF 		
0.1W (1/10W)		ERJ3EKF 				
0.063W (1/16W)	ERJ2RKF 					


Higher Power  
in Smaller Size

**DOWNSIZING SOLUTION**

- > Reducing PCB Area
- > Reducing Large Size Resistor (1206) by high power series

1W	0612 Wide-terminal (B2)
0.66W	1206 High Power (P08 up-grade enable)
0.5W	0508 Wide-terminal (B3) 0805 High Power (P06 up-grade enable)
0.25W	0603 High Power (PA3)
0.20W	0402 High Power (PA2)

**HIGH POWER TYPE**




(ERJP03, P06, P08, P14)

**NEW HIGH POWER TYPE**




(ERJPA2, PA3)

**WIDE TERMINAL TYPE**



(ERJB3, B2, B1, A1)

**STANDARD TYPE**



(ERJ2, 3, 6, 8, 14, 12, 1T)

# SELECTION GUIDE

## SURFACE MOUNT RESISTORS

Selection Guide Surface Mount Resistors								
Size mm (inch)	Tolerance (%)	Power Rating (79°C)(W)	Resistance Range (Ω)	Standard Resistance Value	Category Temp. Range (°C)	Series	Part. No.	
0402 (01005)	±1	0.031	10-1M	E24, E96	-55 to +125	Precision	ERJXGN	
	±5	0.031	4.7-1M	E24	-55 to +125	General	ERJXGN	
0603 (0201)	±0.5	0.05	100-1M	E24, E96	-55 to +125	Precision	ERJ1RH/1RK	
	±1	0.05	10-1M	E24, E96	-55 to +125	Precision	ERJ1GN	
		0.05	10-1M	E24, E96	-55 to +125	Anti-Sulfurated	ERJU01	
	±5	0.05	1-10M	E24	-55 to +125	General	ERJ1GN	
		0.05	1-10M	E24	-55 to +125	Anti-Sulfurated	ERJU01	
1005 (0402)	±0.1	0.063	10.5-100k	E24	-55 to +155	Metal Film, High Reliability	ERA2A	
	±0.5	0.063	10-1M	E24, E96	-55 to +125	Precision	ERJ2RH/2RK	
		0.063	10-100k	E24	-55 to +155	Metal Film, High Reliability	ERA2A	
	±1	0.125 (0.166)	0.3-1m	E24	-55 to +125	Low Resistance	ERJ2BQ	
		0.1	10-1M	E24, E96	-55 to +155	Precision	ERJ2RK	
		0.1	10-1M	E24, E96	-55 to +155	Anti-Sulfurated	ERJS02/U02	
	±2	0.125 (0.25)	0.03-0.1m	E24	-55 to +155	Low Resistance	ERJ2BW	
		0.125 (0.166)	0.1-1m	E24	-55 to +125	Low Resistance	ERJ2BS/2BQ	
	±5	0.125 (0.25)	0.03-0.1m	E24	-55 to +155	Low Resistance	ERJ2BW	
		0.125 (0.166)	0.1-1	E24	-55 to +125	Low Resistance	ERJ2BS/2BQ	
		0.1	1-1M	E24	-55 to +155	General	ERJ2GE	
		0.1	1-1.2M	E24	-55 to +155	Anti-Sulfurated	ERJS02/U01	
	1608 (0603)	±0.05	0.1	1-100k	E24	-55 to +155	Metal Film, High Reliability	ERA3A
		±0.1	0.1	10.5-105k	E24	-55 to +155	Metal Film, High Reliability	ERA3A
		±0.5	0.1	10-105k	E24	-55 to +155	Metal Film, High Reliability	ERA3A
0.063 (0.1)			10-1M	E24, E96	-55 to +125	Precision	ERJ3RB/3RE	
0.2			10-1M	E24, E96	-55 to +155	Anti-Surge	ERJP03	
±1		0.1 (0.2)	0.05-1m	Each 1mΩ	-55 to +125	Low Resistance	ERJL03	
		0.25	0.02-1m	E24	-55 to +155	Low Resistance	ERJ3BW	
		0.2 (0.25)	0.1-0.9m	E24	-55 to +125	Low Resistance	ERJ3BS/3BQ	
		0.1	0.1-0.9m	E24	-55 to +125	Low Resistance	ERJ3RS/3RQ	
		0.25	0.01-0.03	10mΩ	-55 to +155	Metal Plate	ERJM03	
		0.1	10-1M	E24, E96	-55 to +155	Precision	ERJ3EK	
		0.2	10-1M	E24, E96	-55 to +155	Anti-Surge	ERJP03	
		0.1	10-1M	E24, E96	-55 to +155	Anti-Sulfurated	ERJS03/U03	
±2		0.25	0.03-0.1m	E24	-55 to +155	Low Resistance	ERJ3BW	
		0.2 (0.25)	0.1-9.9m	E24	-55 to +125	Low Resistance	ERJ3BS/3BQ	
		0.1	0.1-9.9m	E24	-55 to +125	Low Resistance	ERJ3RS/3RQ	
±5		0.1 (0.2)	0.05-0.1m	Each 1mΩ	-55 to +125	Low Resistance	ERJL03	
		0.25	0.03-0.1m	E24	-55 to +155	Low Resistance	ERJ3BW	
		0.2 (0.25)	0.1-9.9m	E24	-55 to +125	Low Resistance	ERJ3BS/3BQ	
		0.1	0.1-9.9m	E24	-55 to +125	Low Resistance	ERJ3RS/3RQ	
		0.25	0.01-0.05	10mΩ	-55 to +155	Metal Plate	ERJM03	
	0.1	1-10M	E24	-55 to +155	General	ERJ3GE		
	0.2	1-1M	E24	-55 to +155	Anti-Surge	ERJP03		
	0.1	1-10M	E24	-55 to +155	Anti-Sulfurated	ERJS03/U03		

# SELECTION GUIDE

## SURFACE MOUNT RESISTORS

**Selection Guide Surface Mount Resistors**

Size mm (inch)	Tolerance (%)	Power Rating (79°C)(W)	Resistance Range (Ω)	Standard Resistane Value	Category Temp. Range (°C)	Series	Part. No.
2012 (0805)	±0.05	0.125	1k-100k	E24	-55 to +155	Metal Film, High Reliability	ERA6A
	±0.1	0.125	150-1M	E24	-55 to +155	Metal Film, High Reliability	ERA6A
	±0.5	0.125	10-1M	E24	-55 to +155	Metal Film, High Reliability	ERA6A
		0.1	10-1M	E24, E96	-55 to +125	Precision	ERJ6RB/6RE
		0.25	10-1M	E24, E96	-55 to +155	Anti-Surge	ERJP06
	±1	0.125 (0.25)	0.05-0.1m	Each 1mΩ	-55 to +125	Low Resistance	ERJL06
		0.33	0.01-0.1m	E24	-55 to +155	Low Resistance	ERJ6BW
		0.25 (0.33)	0.1-9m	E24	-55 to +125	Low Resistance	ERJ6BS/6BQ
		0.125	0.1-9m	E24	-55 to +125	Low Resistance	ERJ6RS/6RQ
		0.125	10-2.2M	E24, E96	-55 to +155	Precision	ERJ6EN
		0.25	10-1M	E24, E96	-55 to +155	Anti-Surge	ERJP06
		0.33 (0.5)	0.05-10m	E24	-55 to +155	High Power	ERJB3
		0.125	10-1M	E24, E96	-55 to +155	Anti-Sulfurated	ERJS06/U06
	±2	0.33	0.01-0.1m	E24	-55 to +155	Low Resistance	ERJ6BW
		0.25 (0.33)	0.1-8m	E24	-55 to +125	Low Resistance	ERJ6BS/6BQ
		0.125	0.1-8m	E24	-55 to +125	Low Resistance	ERJ6RS/6RQ
		0.33 (0.5)	0.02-1m	E24	-55 to +155	High Power	ERJB3
	±5	0.125 (0.25)	0.050-0.1m	E24	-55 to +125	Low Resistance	ERJL06
		0.33	0.01-0.1	Each 1mΩ	-55 to +155	Low Resistance	ERJ6BW
		0.25 (0.33)	0.1-9m	E24	-55 to +125	Low Resistance	ERJ6BS/6BQ
0.125		0.1-9m	E24	-55 to +125	Low Resistance	ERJ6RS/6RQ	
0.125		1-10M	E24	-55 to +155	General	ERJ6GE	
0.25		1-2.2M	E24	-55 to +155	Anti-Surge	ERJP06	
0.25		1-1M	E24	-55 to +155	Anti-Pulse	ERJT06	
0.33 (0.5)		0.05-1M	E24	-55 to +155	High Power	ERJB3	
3216 (1206)	±0.1	0.25	50-1M	E24	-55 to +155	Metal Film, High Reliability	ERA8A
	±0.5	0.25	10-1M	E24	-55 to +155	Metal Film, High Reliability	ERA8A
		0.33	10-1M	E24, E96	-55 to +155	Anti-Surge	ERJP08
	±1	0.25 (0.33)	0.050-0.1m	Each 1mΩ	-55 to +125	Low Resistance	ERJL08
		0.5 (1)	0.01-0.1m	E24	-55 to +155	Low Resistance	ERJ8BW
		0.33 (0.5)	0.1-9m	E24	-55 to +125	Low Resistance	ERJ8BS/8RS
		0.25	0.1-9m	E24	-55 to +125	Low Resistance	ERJ8RS/8RQ
		0.25	10-2.2M	E24, E96	-55 to +155	Precision	ERJ8EN
		0.33	10-1M	E24, E96	-55 to +155	Anti-Surge	ERJP08
		0.75 (1)	0.01-1M	E24	-55 to +155	High Power	ERJB2
		0.25	10-1M	E24, E96	-55 to +155	Anti-Sulfurated	ERJS08/U08
	±2	0.5 (1)	0.01-0.1m	E24	-55 to +155	Low Resistance	ERJB2
		0.33 (0.5)	0.1-9m	E24	-55 to +125	Low Resistance	ERJL08
		0.25	0.1-9m	E24	-55 to +125	Low Resistance	ERJ8BW
		0.75 (1)	0.01-1M	E24	-55 to +155	High Power	ERJ8BS/8BQ

# SELECTION GUIDE

## SURFACE MOUNT RESISTORS

**Selection Guide Surface Mount Resistors**

Size mm (inch)	Tolerance (%)	Power Rating (79°C)(W)	Resistance Range (Ω)	Standard Resistance Value	Category Temp. Range (°C)	Series	Part. No.	
3216 (1206)	±5	0.25 (0.33)	0.050-0.1m	Each 1mΩ	-55 to +125	Low Resistance	ERJ08	
		0.5 (1)	0.01-0.1	E24	-55 to +155	Low Resistance	ERJ8BW	
		0.33 (0.5)	0.1-9m	E24	-55 to +125	Low Resistance	ERJ8BS/8BQ	
		0.25	0.1-9m	E24	-55 to +125	Low Resistance	ERJ8RS/8RQ	
		0.25	1-10M	E24	-55 to +155	General	ERJ8GE	
		0.33	1-10M	E24	-55 to +155	Anti-Surge	ERJP08	
		0.33	1-1M	E24	-55 to +155	Anti-Pulse	ERJT08	
		0.75 (1)	5m-1M	1mΩ Step/E24	-55 to +155	High Power	ERJB2	
		0.25	1-10M	E24	-55 to +155	Anti-Sulfurated	ERJS08/U08	
3225 (1210)	±0.5	0.5	10-1M	E24, E96	-55 to +155	Anti-Surge	ERJP14	
		±1	0.33	0.05-0.1m	Each 1mΩ	-55 to +125	Low Resistance	ERJL14
	0.5		0.1-9m	E24	-55 to +125	Low Resistance	ERJ14BS/14BQ	
	0.25		0.1-9m	E24	-55 to +125	Low Resistance	ERJ14RS/14RQ	
	0.5		10-1M	E24, E96	-55 to +155	Precision	ERJ14N	
	0.5		10-1M	E24, E96	-55 to +155	Anti-Surge	ERJP14	
	0.5		10-1M	E24, E96	-55 to +155	Anti-Sulfurated	ERJS14/U14	
	±2	0.5	0.1-9m	E24	-55 to +125	Low Resistance	ERJ14BS/14BQ	
		0.25	0.1-9m	E24	-55 to +125	Low Resistance	ERJ14RS/14RQ	
	±5	0.33	0.05-0.1m	Each 1mΩ	-55 to +125	Low Resistance	ERJL14	
			0.1-9m	E24	-55 to +125	Low Resistance	ERJ14BS/14BQ	
			0.1-9m	E24	-55 to +125	Low Resistance	ERJ14RS/14RQ	
			1-10M	E24	-55 to +155	General	ERJ14Y	
			1-1M	E24	-55 to +155	Anti-Surge	ERJP14	
			1-1M	E24	-55 to +155	Anti-Pulse	ERJT14	
	4532 (1812)	±1	0.5	0.05-0.1m	Each 1mΩ	-55 to +125	Low Resistance	ERJL12
			0.5	0.1-9m	E24	-55 to +125	Low Resistance	ERJ12RS/12RQ
			0.75	10-1M	E24, E96	-55 to +155	Precision	ERJ12N
0.75			10-1M	E24, E96	-55 to +155	Anti-Sulfurated	ERJS12/U12	
±2		0.5	0.1-9m	E24	-55 to +125	Low Resistance	ERJ12RS/12RQ	
		±5	0.5	0.05-0.1m	Each 1mΩ	-55 to +125	Low Resistance	ERJL12
0.5			0.1-9m	E24	-55 to +125	Low Resistance	ERJ12RS/12RQ	
0.75			1-10M	E24	-55 to +155	General	ERJ12Y	
0.75			1-10M	E24	-55 to +155	Anti-Sulfurated	ERJS12/U12	
5025 (2010)		±1	0.5	0.050-0.1	Each 1mΩ	-55 to +125	Low Resistance	ERJL1D
			0.5	0.1-9m	E24	-55 to +125	Low Resistance	ERJ12ZS/12ZQ
			0.75	10-1M	E24, E96	-55 to +155	Precision	ERJ12S
	1 (2)		0.01-10k	E24	-55 to +155	High Power	ERJB1	
	0.75		10-1M	E24, E96	-55 to +155	Anti-Sulfurated	ERJS1D/U1D	
	±2	0.5	0.1-9m	E24	-55 to +125	Low Resistance	ERJ12ZS/12ZQ	
		1 (2)	0.01-10k	E24	-55 to +155	High Power	ERJB1	


# SELECTION GUIDE

## SURFACE MOUNT RESISTORS

**Selection Guide Surface Mount Resistors**

Size mm (inch)	Tolerance (%)	Power Rating (79°C)(W)	Resistance Range (Ω)	Standard Resistane Value	Category Temp. Range (°C)	Series	Part. No.	
5025 (2010)	±5	0.5	0.050-0.1	Each 1mΩ	-55 to +125	Low Resistance	ERJL1D	
		0.5	0.1-9m	E24	-55 to +125	Low Resistance	ERJ12ZS/12ZQ	
		0.75	1-10M	E24	-55 to +155	General	ERJ12ZY	
		1(2)	0.01-10k	E24	-55 to +155	High Power	ERJB1	
		0.75	1-10M	E24	-55 to +155	Anti-Sulfurated	ERJS1D/U1D	
6432 (2512)	±1	1	0.050-0.1m	Each 1mΩ	-55 to +125	Low Resistance	ERJL1W	
		1	0.1-9m	E24	-55 to +125	Low Resistance	ERJ1TRS/1TRQ	
		1	10-1M	E24, E96	-55 to +155	Precision	ERJ1TN	
		1	1m-20m	1, 1.5, 2, 3, 4, 5, 6, 10, 15, 20mΩ	-55 to +170	Metal Plate	ERJM1W	
		1.33	0.1-10k	E24	-55 to +155	High Power	ERJA1	
		1	10-1M	E24, E96	-55 to +155	Anti-Sulfurated	ERJS1T/U1T	
	±2	1	0.1-9m	E24	-55 to +125	Low Resistance	ERJ1TRS/1TRQ	
		1.33	0.01-10k	E24	-55 to +155	High Power	ERJA1	
	±5	±5	1	0.050-0.1m	Each 1mΩ	-55 to +125	Low Resistance	ERJL1W
			1	0.1-9m	E24	-55 to +125	Low Resistance	ERJ1TRS/1TRQ
			1	1-1M	E24	-55 to +155	General	ERJ1TY
			1	1m-20m	1, 1.5, 2, 3, 4, 5, 6, 10, 15, 20mΩ	-55 to +170	Metal Plate	ERJM1W
1.33			0.01-10k	E24	-55 to +155	High Power	ERJA1	
1			1-10M	E24	-55 to +155	Anti-Sulfurated	ERJS1T/U1T	


## Shunt Resistors (Low ohmic Current Sensing Resistor) – Surface Mount Type

Series / Type	Power Rating	Resistance	Tolerance	T.C.R	Features	Size	Part No.
 Metal Plate Type	1W (2W R <sub>≤</sub> 10mΩ)	≥ 0.3mΩ	±1% ±5%	≥ ±50ppm	Low resistance values and high precision	2512	ERJM1WSxxxxU
	1W (2W R <sub>≤</sub> 10mΩ)					2512	ERJM1WTxxxxU
	3W				Low resistance values and high power. Operation temperature Range -65°C to +170°C	2512	ERJMS4SxxxxU
	2W (3W R <sub>≤</sub> 5mΩ)					2512	ERJMS4HxxxxU
	5W					2526	ERJMS6SxxxxU
Metal Plate Wide Terminal Type	2W	1m to 5mΩ	±1% ±5%	≥ ±75ppm	Small size and high power	1020	ERJMB1xxxxU
High Power Wide Terminal Type	0.33W (0.5W R <sub>≤</sub> 1Ω)	≥ 5mΩ	±1% ±2% ±5%	≥ ±50ppm	Superior solder-joint reliability by wide terminal structure	0508	ERJB3xxxxV
	0.75W (1W R <sub>≤</sub> 10Ω)					0612	ERJB2xxxxV
	1W (2W R <sub>≤</sub> 10Ω)					1020	ERJB1xxxxU
	1.33W					1225	ERJA1xxxxU
	1W					0612	ERJD2xxxxxV*
	2W					1020	ERJD1xxxxxU*
Thick Film Low Resistance	0.1W	100m to 9.1Ω	±1% ±2% ±5%	≥ ±100ppm	Thick Film Low Resistance Type	0603	ERJ3RxxxxV
	0.125W					0805	ERJ6RxxxxV
	0.25W					1206	ERJ8RxxxxV
	0.25W					1210	ERJ14RxxxxU
	0.5W					1812	ERJ12RxxxxU
	0.5W					2010	ERJ12ZxxxxU
	1W					2512	ERJ1TRxxxxU
	0.166W					100m to 9.1Ω	±1% ±2% ±5%
	0.25W	0603	ERJ3BxxxxV				
	0.33W	0805	ERJ6BxxxxV				
	0.5W	1206	ERJ8BxxxxV				
	0.5W	1210	ERJ14BxxxxU				
	0.25W	10m to 100mΩ	±1% ±2% ±5%	≥ ±50ppm	Low Resistance Type High power Type Double-sided resistive elements structure	0402	ERJ2BWxxxxX
	0.33W					0603	ERJ3BWxxxxV
	0.5W					0805	ERJ6BWxxxxV
	1W					1206	ERJ8BWxxxxV
	1W					1206	ERJ8CWxxxxV
	0.2W	20m to 100mΩ	±1% ±5%	≥ ±100ppm	Low TCR Type	0603	ERJL03xxxxV
0.25W	0805					ERJL06xxxxV	
0.33W	1206					ERJL08xxxxV	
0.33W	1210					ERJL14xxxxU	
0.5W	1812					ERJL12xxxxU	
0.5W	2010					ERJL1DxxxxU	
1W	2512					ERJL1WxxxxU	




\* Under development




## Thin Film Resistors – Surface Mount Type

Series / Type	Power Rating	Resistance	Tolerance	T.C.R	Size	Part No.
 <p>Metal Film High Reliability Type</p> <p>Suitable at high temperature and humidity (85°C 85%RH rated load, Category temperature range: -55 to +155°C)</p>	0.05W	10 to 100K $\Omega$	$\pm 0.1\%$	$\pm 25\text{ppm}$	0201	ERA1AEB
			$\pm 0.25\%$	$\pm 25\text{ppm}$	0201	ERA1AEC
	0.063W	10 to 100K $\Omega$	$\pm 0.1\%$	$\pm 10\text{ppm}$	0402	ERA2ARB
			$\pm 0.25\%$	$\pm 10\text{ppm}$	0402	ERA2ARC
			$\pm 0.1\%$	$\pm 15\text{ppm}$	0402	ERA2APB
			$\pm 0.1\%$	$\pm 25\text{ppm}$	0402	ERA2AEB
			$\pm 0.25\%$	$\pm 25\text{ppm}$	0402	ERA2AEC
			$\pm 0.5\%$	$\pm 25\text{ppm}$	0402	ERA2AED
			$\pm 0.1\%$	$\pm 50\text{ppm}$	0402	ERA2AHB
			$\pm 0.5\%$	$\pm 100\text{ppm}$	0402	ERA2AKD
	0.1W	10 to 330K $\Omega$	$\pm 0.05\%$	$\pm 10\text{ppm}$	0603	ERA3ARW
			$\pm 0.1\%$	$\pm 10\text{ppm}$	0603	ERA3ARB
			$\pm 0.1\%$	$\pm 15\text{ppm}$	0603	ERA3APB
			$\pm 0.1\%$	$\pm 25\text{ppm}$	0603	ERA3AEB
			$\pm 0.25\%$	$\pm 25\text{ppm}$	0603	ERA3AEC
			$\pm 0.5\%$	$\pm 25\text{ppm}$	0603	ERA3AED
			$\pm 0.5\%$	$\pm 50\text{ppm}$	0603	ERA3AHD
	0.125W	10 to 1M $\Omega$	$\pm 0.05\%$	$\pm 10\text{ppm}$	0805	ERA6ARW
			$\pm 0.1\%$	$\pm 10\text{ppm}$	0805	ERA6ARB
			$\pm 0.1\%$	$\pm 15\text{ppm}$	0805	ERA6APB
			$\pm 0.1\%$	$\pm 25\text{ppm}$	0805	ERA6AEB
			$\pm 0.25\%$	$\pm 25\text{ppm}$	0805	ERA6AEC
			$\pm 0.5\%$	$\pm 25\text{ppm}$	0805	ERA6AED
			$\pm 0.5\%$	$\pm 50\text{ppm}$	0805	ERA6AHD
	0.25W	10 to 1M $\Omega$	$\pm 0.05\%$	$\pm 10\text{ppm}$	1206	ERA8ARW
			$\pm 0.1\%$	$\pm 10\text{ppm}$	1206	ERA8ARB
			$\pm 0.5\%$	$\pm 10\text{ppm}$	1206	ERA8ARD
			$\pm 0.1\%$	$\pm 15\text{ppm}$	1206	ERA8APB
$\pm 0.1\%$			$\pm 25\text{ppm}$	1206	ERA8AEB	
$\pm 0.25\%$			$\pm 25\text{ppm}$	1206	ERA8AEC	
$\pm 0.5\%$			$\pm 25\text{ppm}$	1206	ERA8AED	
$\pm 0.5\%$			$\pm 50\text{ppm}$	1206	ERA8AHD	


## High Power &amp; Pulse Proof Resistors – Surface Mount Type

Series / Type	Power Rating	Resistance	Tolerance	Features	Size	Part No.
 High Power Wide Terminal Type	0.33W (0.5W R $\leq$ 1 $\Omega$ )	5m to 1M $\Omega$	$\pm$ 1% $\pm$ 2% $\pm$ 5%	Superior solder-joint reliability by wide terminal structure	0508	ERJB3xxxxxV
	0.75W (1W R $\leq$ 10 $\Omega$ )				612	ERJB2xxxxxV
	1W (2W R $\leq$ 10 $\Omega$ )				1020	ERJB1xxxxxU
	1.33W				1225	ERJA1xxxxxU
 Anti-Surge Type	0.2W	1 to 3,3M $\Omega$	$\pm$ 0.5% $\pm$ 1% $\pm$ 5%	Anti-Surge & High voltage Characteristic	0603	ERJP03xxxxxV
	0.25W				0603	ERJPA3xxxxxV
	0.5W				0805	ERJP06xxxxxV
	0.66W				1206	ERJP08xxxxxV
	0.5W				1210	ERJP14xxxxxU
	0.5W	1 to 10M $\Omega$	$\pm$ 1% $\pm$ 5%	Double-sided resistive elements structure	0805	ERJP6WxxxxxV
 Anti-Pulse Type	0.25W	1 to 1M $\Omega$	$\pm$ 5%	Anti-Pulse Characteristic	0805	ERJT06xxxxxV
	0.33W				1206	ERJT08xxxxxV
	0.5W				1210	ERJT14xxxxxU


## Thick Film Resistors – Surface Mount Type

Series / Type	Power Rating	Resistance	Tolerance	Features	Size	Part No.
 Thick Film	0.031 to 1W	1 to 10M $\Omega$	$\pm$ 5% Jumper	Size: 01005 to 2512	01005	ERJXGNJxxxY
					0201	ERJ1GNJxxxC
					0402	ERJ2GEJxxxX
					0603	ERJ3GEYJxxxV
					0805	ERJ6GEYJxxxV
					1206	ERJ8GEYJxxxV
					1210	ERJ14YJxxxU
					1812	ERJ12YJxxxU
					2010	ERJ12ZYJxxxU
					2512	ERJ1TYJxxxU
Precision Thick Film	0.05 to 1W	10 to 2.2M $\Omega$	$\pm$ 0.5% $\pm$ 1%	Precision Type	01005	ERJXGNFxxxx(U/Y)
					0201	ERJ1GNFxxxxC
					0201	ERJ1RxDxxxxC
					0402	ERJ2RxxxxxxX
					0603	ERJ3EKFxxxxV
					0603	ERJ3RxDxxxxV
					0805	ERJ6ENFxxxxV
					0805	ERJ6RxDxxxxV
					1206	ERJ8ENFxxxxV
					1210	ERJ14NFxxxxU
					1812	ERJ12NFxxxxU
					2010	ERJ12SFxxxxU
					2512	ERJ1TNFxxxxU



## Anti-Sulfurated Resistors – Surface Mount Type

Series / Type	Power Rating	Resistance	Tolerance	Features	Size	Part No.
 Thick Film Anti-Sulfurated Au-based inner electrode	0.1 to 1W	1 to 1MΩ	±1% ±5%	Special construction to avoid open failure due to the presence of sulfur	0402	ERJS02xxxxX
					0603	ERJS03xxxxV
					0805	ERJS06xxxxV
					1206	ERJS08xxxxV
					1812	ERJS12xxxxU
					1210	ERJS14xxxxU
					2010	ERJS1DxxxxU
					2512	ERJS1TxxxxU
Thick Film Anti-Sulfurated Ag-Pd-based inner electrode	0.25W	0.1 to 0.2Ω	±1% ±2% ±5%	Special construction to avoid open failure due to the presence of sulfur. Low resistance type.	0805	ERJS6SxxxxV
		0.22 to 1Ω			ERJS6QxxxxV	
	0.05 to 1W	1 to 1MΩ	±1% ±5%	Special construction to avoid open failure due to the presence of sulfur	0201	ERJU01xxxxC
					0402	ERJU02xxxxX
					0603	ERJU03xxxxV
					0805	ERJU06xxxxV
					1206	ERJU08xxxxV
					1812	ERJU12xxxxU
					1210	ERJU14xxxxU
					2010	ERJU1DxxxxU
2512	ERJU1TxxxxU					
Thick Film Anti-Sulfurated Wide Terminal Type	2W	10m to 1Ω	±1% ±5%	High power and high solder-joint reliability by wide terminal construction	1020	ERJC1CxxxxU


## Anti-Sulfurated Network &amp; Array Resistors - Surface Mount Type

Series / Type	Power Rating	Resistance	Tolerance	Features	Size	Part No.
 Resistor Array Anti-Sulfurated	0.031 to 0.1W per element	10 to 1MΩ	±5%	High resistance to sulfurization achieved by adopting an Ag-Pb-based inner electrode.	0402 × 2R	EXBU24xxxxX
					0402 × 4R	EXBU28xxxxX
					0402 × 8R	EXBU2HxxxxV
					0603 × 2R	EXBU34xxxxV
					0603 × 4R	EXBU38xxxxV


## Network &amp; Array Resistors - Surface Mount Type

Series / Type	Power Rating	Resistance	Tolerance	Features	Size	Part No.
 Resistor Array	0.031 to 0.1W per element	10 to 1MΩ	±5%	Placement efficiency of chip resistor array is 2 / 4 / 8 times of the flat type chip resistor	0201 x 2R	EXB14VxxxJX
					0201 x 4R	EXB18VxxxJX
					0402 x 2R	EXB24VxxxJX
					0402 x 4R	EXB28VxxxJX
					0402 x 8R	EXB2HVxxxJV
					0603 x 2R	EXB34VxxxJV
					0603 x 4R	EXB38VxxxJV
					0402 x 4R	EXBN8VxxxJX
					0805 x 4R	EXBS8VxxxJ
					0603 x 2R	EXBV4VxxxJV
0603 x 4R	EXBV8VxxxJV					
 Resistor Networks	0.025 to 0.063W per element	47 to 1MΩ	±5%	High density placing for digital signal circuits	2512	EXBAXxxxxxx
					1206	EXBDxxxxxx
					1608	EXBExxxxxxx
					1506	EXBQxxxxxx


## Metal (Oxide) Film Resistors – Radial Lead Type

Series / Type	Power Rating	Resistance	Tolerance	Features	Size (mm)	Part No.				
 Small size	0.5 to 5W	0.1 to 9.1Ω	±2% ±5%	Non flammable coating Small size	6.35 x 2.3	ERX12Sxxxxxx				
					9 x 2.8	ERX1Sxxxxxx				
					12 x 4	ERX2Sxxxxxx				
					15 x 5.5	ERX3Sxxxxxx				
					24 x 8	ERX5Sxxxxxx				
		6.35 x 2.3			ERG12Sxxxxxx					
		9 x 2.8			ERG1Sxxxxxx					
		12 x 4			ERG2Sxxxxxx					
		15 x 5.5			ERG3Sxxxxxx					
		24 x 8			ERG5Sxxxxxx					
		Small size Anti-heat conducting Type (Fe lead wire)			1 to 5W	0.1 to 9.1Ω	±2% ±5%		9 x 2.8	ERX1Fxxxxxx
									12 x 4	ERX2Fxxxxxx
									15 x 5.5	ERX3Fxxxxxx
									24 x 8	ERX5Fxxxxxx
9 x 2.8	ERG1Fxxxxxx									
12 x 4	ERG2Fxxxxxx									
15 x 5.5	ERG3Fxxxxxx									
24 x 8	ERG5Fxxxxxx									
9.1 < R ≤ 100kΩ									9 x 2.8	ERG1Fxxxxxx
									12 x 4	ERG2Fxxxxxx
		15 x 5.5			ERG3Fxxxxxx					
		24 x 8			ERG5Fxxxxxx					
		9 x 2.8			ERG1Fxxxxxx					

## Trimmer Potentiometers - Surface Mount Type

Series / Type	Power Rating	Resistance	Tolerance	Features	Part No.				
 Cermet 2mm Square Open	0.15W	100 to 1MΩ	±25%	Low-profile 0.7mm (EVM2T) 0.81mm (EVM2N) 1.05mm (EVM2W)	EVM2GSX80Bxx				
					EVM2NSX80Bxx				
					EVM2WSX80Bxx				
				Cermet 3mm Square Open				Auto, Adjust (EVM3Y) Both Sides Adjust (EVM3S) Back Sides Adjust (EVM3R)	EVM3ESX50Bxx
									EVM3GSX50Bxx
									EVM3RSX50Bxx
									EVM3SSX50Bxx
				Cermet 3mm Square Open					EVM3YSX50Bxx
									EVM3WSX80Bxx
				Cermet 3mm Square Open				Rotation stopper Automatic adjustment type	EVM3VSX50Bxx
Cermet 4mm Square Open	0.2W			4mm square series for reflow soldering	EVM1DSX30Bxx				
					EVM1ESX30Bxx				
					EVM1USX30Bxx				
Cermet 4mm Square Dustproof	0.3 to 0.5W			Radial Taping	EVMAAGA00Bxx				
					EVMAASA0xBxx				
					EVMAEGA00Bxx				
					EVMAESA0xBxx				
					EVMAHGA00Bxx				
					EVMAJGA00Bxx				
					EVMASGA00Bxx				

# WINDING AND METAL COMPOSITE TECHNOLOGIES



Surface Mount high **Power Inductors (ETQ-series)** in Metal Composite technology have excellent „non-hard“-saturation characteristics and reduce power loss at high switching frequencies.

SMD **ferrite Choke Coils** with plenty of series make it easy for design engineers to select the most suitable surface-mount choke for various applications such as DC/DC converters in portable equipment.

**Chip Inductors** with very good electrical performance characteristics in laser-cut technology and a wide range of inductance values and case sizes from 0402 to 0603.


**THT Choke Coils** with inductance values up to 10mH for conventional mounting completes the inductor product portfolio.

## INDUCTORS


---

- > Wide range of inductive products in both SMD and THT
- > Automotive Type Metal Composite Power Choke Coil is applicable 150°C/2,000h, 30G
- > AEC-Q200 Qualified Series available

## Power Choke Coil – Automotive Type


Series / Type	Size (LxWxH mm)	Inductivity (µH)	Rated Current (A) +40°C High Heat Dissipation	Saturation Current (A) L=-30%	R dc (mOhms)	Part No.
 Power Choke Coil Automotive Type	5x5x3	2.20	5.80	10.90	22.60	ETQP3M2R2YFP
	5x5x3	3.30	4.90	8.60	32.30	ETQP3M3R3YFP
	5x5x4	22.00	2.30	3.10	163.00	ETQP4M220YFP
	5x5x4	4.70	4.80	7.70	36.00	ETQP4M4R7YFP
	5x5x4	10.00	3.10	6.00	84.60	PCC-M0540M-100Y*
	5x5x4	15.00	2.40	3.20	139.00	PCC-M0540M-150Y*
	5x5x4	6.80	3.80	7.40	58.00	PCC-M0540M-6R8Y*
	6x6x3	10.00	3.30	6.40	81.40	ETQP3M100YFN
	6x6x3	1.00	10.70	20.00	7.90	ETQP3M1R0YFN
	6x6x3	1.50	9.10	16.00	11.00	ETQP3M1R5YFN
	6x6x3	2.20	7.20	13.00	17.50	ETQP3M2R2YFN
	6x6x3	3.30	5.60	11.20	29.00	ETQP3M3R3YFN
	6x6x3	4.70	4.40	8.80	43.00	ETQP3M4R7YFN
	6x6x3	6.80	4.10	7.20	55.20	ETQP3M6R8YFN
	6x6x3	0.68	12.00	24.00	6.30	ETQP3MR68YFN
	6x6x4.5	10.00	4.40	8.30	54.20	ETQP4M100YFN
	6x6x4.5	15.00	3.20	6.20	105.00	ETQP4M150YFN
	6x6x4.5	22.00	3.00	6.00	124.00	ETQP4M220YFN
	6x6x4.5	2.20	10.20	14.40	10.40	ETQP4M2R5YFN
	6x6x4.5	33.00	2.50	4.10	172.00	ETQP4M330YFN
	6x6x4.5	3.30	8.40	13.20	15.40	ETQP4M3R3YFN
	6x6x4.5	47.00	2.20	3.70	210.00	ETQP4M470YFN
	6x6x4.5	4.70	7.00	11.70	21.80	ETQP4M4R7YFN
	6x6x4.5	6.80	5.30	10.00	39.30	ETQP4M6R8YJN
	7x7x5	93.00	1.80	3.10	348.00	ETQP5M101YGM
	7x7x5.4	10.00	5.60	8.70	40.80	ETQP5M100YFM
	7x7x5.4	15.00	4.20	8.40	74.00	ETQP5M150YFM
	7x7x5.4	22.00	3.70	5.80	92.00	ETQP5M220YFM
	7x7x5.4	2.20	11.80	17.20	9.20	ETQP5M2R2YFM
	7x7x5.4	33.00	3.30	4.80	120.00	ETQP5M330YFM
	7x7x5.4	3.30	10.40	13.70	11.90	ETQP5M3R3YFM
	7x7x5.4	47.00	2.90	4.10	156.00	ETQP5M470YFM
	7x7x5.4	4.70	8.00	13.10	20.00	ETQP5M4R7YFM
	7x7x5.4	6.80	6.90	11.10	26.70	ETQP5M6R8YFM
	8x8x4	1.00	15.60	29.30	4.58	ETQP4M1R0YVK
	8x8x5	100.00	2.10	3.00	302.00	ETQP5M101YGK
	8x8x5	68.00	2.60	4.40	200.00	ETQP5M680YGK
	8x8x5.4	10.00	6.70	13.00	33.70	ETQP5M100YFK
	8x8x5.4	15.00	5.30	7.60	48.20	ETQP5M150YFK
	8x8x5.4	22.00	4.80	6.90	63.00	ETQP5M220YFK
	8x8x5.4	2.50	14.00	20.10	7.60	ETQP5M2R5YFK
	8x8x5.4	33.00	3.80	5.70	100.00	ETQP5M330YFK
	8x8x5.4	3.30	13.20	17.80	8.50	ETQP5M3R3YFK
	8x8x5.4	48.00	3.40	5.40	125.00	ETQP5M470YFK
	8x8x5.4	4.70	9.40	16.20	16.80	ETQP5M4R7YFK
8x8x5.4	6.80	8.50	13.30	20.40	ETQP5M6R8YFK	
10x10x5	97.00	2.70	3.80	208.00	ETQP5M101YGC	
10x10x5	1.00	27.50	38.40	2.30	ETQP5M1R0YLC	
10x10x5	3.30	13.90	23.50	7.10	ETQP5M3R3YGC	

## Power Choke Coil – Automotive Type




Series / Type	Size (LxWxH mm)	Inductivity ( $\mu\text{H}$ )	Rated Current (A) +40°C High Heat Dissipation	Saturation Current (A) L=-30%	R dc (mOhms)	Part No.
 Power Choke Coil Automotive Type	10x10x5	0.33	39.80	59.40	1.10	ETQP5MR33YLC
	10x10x5	0.68	31.50	40.60	1.75	ETQP5MR68YLC
	10x10x5.4	10.00	8.50	12.00	23.80	ETQP5M100YFC
	10x10x5.4	15.00	6.90	10.60	36.50	ETQP5M150YFC
	10x10x5.4	1.50	21.40	36.20	3.80	ETQP5M1R5YFC
	10x10x5.4	22.00	6.20	7.20	45.00	ETQP5M220YFC
	10x10x5.4	2.50	18.10	27.20	5.30	ETQP5M2R5YFC
	10x10x5.4	33.00	5.00	7.00	68.50	ETQP5M330YFC
	10x10x5.4	3.30	15.70	22.70	7.10	ETQP5M3R3YFC
	10x10x5.4	47.00	4.30	6.80	96.20	ETQP5M470YFC
	10x10x5.4	4.70	13.10	20.00	10.20	ETQP5M4R7YFC
	10x10x5.4	68.00	3.50	5.20	140.00	ETQP5M680YFC
	10x10x5.4	6.80	9.60	16.00	18.80	ETQP5M6R8YFC
	10x10x6	1.50	23.40	31.90	3.20	ETQP5M1R5YLC
	10x10x6	2.50	19.70	28.00	4.50	ETQP6M2R5YLC
	10x10x6	3.30	17.00	27.80	6.00	ETQP6M3R3YLC
	10x10x6	4.70	14.10	26.00	8.70	ETQP6M4R7YLC
	12x12x7	0.33	-	-	0.70	PCC-M1270MF-R33Y*
	12x12x7	0.68	-	-	1.10	PCC-M1270MF-R68Y*
	12x12x8	1.00	-	-	1.36	PCC-M1270MF-1R0Y*
	12x12x8	1.50	-	-	1.60	PCC-M1270MF-1R5Y*
	12x12x8	2.50	-	-	2.60	PCC-M1270MF-2R5Y*
	12x12x8	3.30	-	-	3.50	PCC-M1270MF-3R3Y*
	12x12x8	4.70	-	-	4.63	PCC-M1270MF-4R7Y*
	13.2x14.7x13.1	24.00	-	-	25.80	ETQPDH240DTV

\*Under development


## Power Choke Coil – Consumer Type

Series / Type	Size (LxWxHmm)	Inductance	Rated Current	Product Part No.
 Power Choke Coil Consumer Type	5.15x5.4x1.2	0.47 to 4.7 $\mu\text{H}$	5.5 to 2.2A	ETQP1Wxxx
	7.5x6.5x 3	0.33 $\mu\text{H}$	17A	ETQP3Lxxx
	7x6.6x3	1 to 4.7 $\mu\text{H}$	8.1 to 3.8A	ETQP3Wxxx
	8.7x7.0x4 to 11.5x10x4	0.20 to 0.68 $\mu\text{H}$	17 to 21A	ETQP4Lxxxx
	10x11x4	1.5 $\mu\text{H}$	13 A	ETQP4Wxxx
	12.5x12.5x3 to 12.5x12.5x6	0.58 to 12.5 $\mu\text{H}$	25.2 to 12A	ETQP6Fxxx
	12.9x13x3.9	0.36 to 1.43 $\mu\text{H}$	32 to 17A	ETQP3Hxxx
	12.9x13x4.9	0.29 to 2.61 $\mu\text{H}$	36 to 12A	ETQP2Hxxx
	14.5x12.5x5	0.5 to 0.6 $\mu\text{H}$	30 to 27 A	ETQP5Lxxx

**Power Inductors (Multilayer Type, Wire Wound Type)**










Series	External Dimension (typ.)	Appearance	max. Height	Inductance [L]	Rated Current I dc (A)	Part No.
	2.0x1.25	Magnetic Shielded Type	1.0	0.47-4.7μH	0.80-1.20	ELGTEA
	3.0		1.0	0.68-22μH	0.33-1.80	ELLVEG
	3.8		1.2	1-33μH	0.28-1.50	ELLVFG-C
			1.5	1-47μH	0.27-1.80	ELLVGG
			1.5	1-100μH	0.18-1.40	ELVGG-C
	6.0		1.2	1-47μH	0.29-1.90	ELL4FG-A
			1.4	1.2-100μH	0.25-1.90	ELL4GG
			1.8	1-150μH	0.22-1.90	ELL4LG-A
			1.6	1-100μH	0.30-2.50	ELL6GG
			2.0	0.8-100μH	0.38-2.80	ELL6PG
6.0x6.4	2.8		1-220μH	0.20-3.00	ELL6RH	
	3.3		1-680μH	0.16-3.40	ELL6SH	
	5.0		10-1,000μH	0.18-1.80	ELL6UH	
	5.0		0.8-1,000μH	0.25-9.00	ELL8TP	
8.0	10.0		4.5	1-1,000μH	0.31-8.00	ELLATP
4.5			1.5-1,000μH	0.32-6.70	ELLATV	
4.5			1.2-1,000μH	0.40-7.00	ELLCTP	
12.0	12.0	4.5	1.2-1,000μH	0.41-6.50	ELLCTV	

**Chip Inductors – Surface Mount Type**

Series / Type	Inductance	DC current	Size	Part No.
 High Frequency use (Non Magnetic core type) RF/RE	1 to 100μH	400 to 90mA	0402 (1005)	ELJRFxxxxFB
	1 to 220μH	500 to 70mA	0603 (1608)	ELJRExxxxFA
High Frequency use High-Q (Non Magnetic core type) QF,QE	1 to 39μH	400 to 150mA	0402 (1005)	ELJQFxxxxF
	2.2 to 56μH	970 to 180mA	0603 (1608)	ELJQExxxxFA
High Power (High power type) PF/PE	1 to 39μH	400 to 150mA	0402 (1005)	ELJPFxxxxFB
	2.2 to 56μH	970 to 180mA	0603 (1608)	ELJPExxxxFA




## Choke Coils

Series / Type	External Dimensions DxH (mm)	Inductance	Current IDC (A)	Part No.
 Regular	Ø9.5x8.9 (with case)	2.2-10,000µF	0.08-3.5	ECL09D*
 Regular	Ø11.5x13.9 (with case)	2.2-10,000µF	0.16-5.3	ECL11D*
 Regular	Ø12.5x16.5	100-10,000µF	0.27-1.9	ECL12D
 Regular	Ø16.0x23.0	3.3-10,000µF	0.26-8.5	ECL16B
 Regular	Ø20.0x27.0	3.3-10,000µF	0.36-8.5	ECL18B
 Shield	Ø10.0x13.0	3.9-8,200µF	0.10-2.9	ECL10E-L
 Shield	Ø13.0x18.5	4.7-10,000µF	0.13-4.4	ECL12E-L
 Shield	Ø16.0x22.0 (3 pin terminal)	5.6-10,000µF	0.30-5.4	ECL15E-L
 Shield	Ø19.0x25.1 (4 pin terminal)	5.6-10,000µF	0.33-5.9	ECL18E-L

\*Taping available

## Voltage Step-up Coils – Surface Mount Type

Type / Series	Inductance	Saturation Rated Current	Magnetic Composition	Size (DxH)	Part No.
 3KN	0.33 to 7.5mH	60 to 10mA	Brass ring	3.3x1.1mm to 3.3x2.0mm	ELT3KNxxxx
	10 to 50mH	10 to 1.5mA	Permalloy ring		
	1.1mH	25mA	Ring less		

# OUR PROTECTION FOR YOUR CIRCUIT



## CIRCUIT PROTECTION

---

- > SMD and leaded Types
- > Compact sizes
- > Wide range of peak current/energy handling
- > UL certified Types

### **Multilayer Varistors**

Multilayer structure to achieve small case size.

### **Metal Oxide Varistors (MOV)**

Large withstanding surge current capability in compact sizes. Large Energy Handling Capability absorbing transient overvoltages in compact sizes. Wide range of varistor voltages.

### **SMT Multilayer NTC Thermistors**

Highly reliable multilayer monolithic structure and a wide range of operating temperature.

### **EMI Filters**

Highly effective in noise suppression, good signal integrity for high bit rate data transmission and a simple multi-layer structure.

### **ESD Suppressor**

Excellent electrostatic-noise suppression and ESD withstanding characteristics and ultra low capacitance.






### **Common Mode Noise Filters**

Used for signal integrity enhancement and in differential signal system.

### **Fuses – Thermal Cutoffs**

Featuring quick temperature response and are mountable in a small space without insulation or protection.

## Metal Oxide Varistors (MOV) / Transient Surge Absorbers

Series / Type	Varistor Voltage	Maximum Peak Current	Features	Part No.
 Varistor Type: D Series: E	200 to 1,100V	600 to 10,000	Large withstanding surge current capability in compact sizes Large Energy Handling Capability absorbing transient overvoltages in compact sizes Wide range of varistor voltages	ERZE05Axxx
				ERZE07Axxx
				ERZE08Axxx
				ERZE10Axxx
				ERZE11Axxx
				ERZE14Axxx
 Varistor Type: D Series: V	18 to 1,800V	125 to 10,000	Standard type with radial leads for general surge protect applications For Surge Pulse	ERZV05Dxxxxx
				ERZV07Dxxxxx
				ERZV09Dxxxxx
				ERZV10Dxxxxx
				ERZV14Dxxxxx
				ERZV20Dxxxxx
 Varistor SMD Type Series: VF	22 to 470V	125 to 600 (@8/20us)	Surface mount type with protective coating so as to high level; reliability For Surge Pulse	ERZVF1Mxxx
				ERZVF2Mxxx
Varistor Type: SC	200 to 950V	In 20kA I <sub>max</sub> . 40kA (@8/20us)	For incorporation in a surge protective device corresponding to the IEC61643-1	ERZVS34Cxxx
 Varistor Type: E	200 to 1,100V	5,000 to 20,000	Very large surge withstanding capability with a compact size Direct mounting on boards like a power distribution board available Fast response to steep impulse voltage	ERZC20EKxxx
				ERZC32EKxxx
 Varistor UL and CSA Recognized with Tab, Type:CK		20 to 25	UL and CSA recognized components High energy handling capability (210 to 750 joules), Large withstanding peak current (25 to 30kA) Common terminals for electrical connection and mounting	ERZC32CKxxxW
				ERZC40CKxxxW
 Varistor Type: J	560 to 1,250V		Stack-type for heavy surge energy application (High power induced load etc)	ERZA80JK112
				ERZA80JK122
				ERZA80JK561
 Varistor Type: P	250 to 1,000V	5,000 (@8/20us)	Plug-in type with deterioration indicator For application to industrial equipment	ERZA20PK102
				ERZA20PK251
				ERZA20PK501
 Varistor Type: G	5 to 17kV	21kA to 5,000	For protection to switching surge of high voltage (3.3, 6.6kV) equipment	ERZA20GS173H
				ERZA20GS852H
				ERZA48GK502
Varistor For Thyristor Protection	510 to 2,500V		Thristor protection against switching surge transformer	ERZC20EKxxxP
				ERZC32EKxxxP
				ERZUxxJPxxx
Varistor Unit	22 to 1,000V	5,000 to 50,000	Surge absorber with connected ZNRs and circuit breaker in box	ERZAxxxxxxx

**Multilayer NTC Thermistors – Surface Mount Type**

Series / Type	Zero-Power Resistance @25°Cel	B Value	Heat Dissipation Constant	Features	Size	Part No.
NTC Thermistor (Chip Type)	22Ω to 470Ω	3,375 to 4,700K	1 or 2 or 3mW/°C	Highly reliable multilayer/monolithic structure Wide ranges of operating temperature (-40 to 125cel)	0201	ERTJZxxxxxxxxx
					0402	ERTJ0xxxxxxxxxx
					0603	ERTJ1xxxxxxxxxx





**EMI Filters**

Series / Type	Operating temperature	Rated Voltage	Rated Current	Features	Part No.
Coil Type (Digital Noise Filter)	-40 to +85°C	DC 50V, 25V Applicable normal voltage for varistor (Type ELKEV)	DC 6A (Type ELKEA) DC 2A	3218 case size, 6A rated current. (Type ELKEA) 3218 case size, 2A rated current. (Type ELKE) High ESD suppression with varistor and included coils. (Type ELKEV) No variation in attenuation characteristics as current changes. The stable P/N marking using laser technology makes the part number check easier.	ELKExxxFA
					ELKEAxxxFA
					ELKEVxxxFx


**ESD Suppressor – Surface Mount Type**

Series / Type	Rated Voltage	Capacitance	Peak Voltage	Clamping Volt.	Size	Part No.
ESD Suppressor  ESD Suppressor, 15kV Type	30V	0.04pF	500V max. (350V typ.)	100V max.	0201	EZAEG1A50AC
		0.05pF			0402	EZAEG2A50AX
		0.10pF			0603	EZAEG3A50AV
		0.04pF			0201	EZAEG1N50AC
		0.05pF			0402	EZAEG2N50AX
ESD Suppressor Array	15V	0.25pF			0805	EZAEGCA50AV


## Common Mode Noise Filters – Surface Mount Type

Series / Type	Components	Impedance	Rated Current	DC Resistance	Part No.
 Noise Filters (0302 small size)	1 lines	43Ω ±25%	100mA	2.7Ω	EXC14CG430U
		65Ω ±20%	130mA	2.5Ω	EXC14CE650U
		90Ω ±20%	130mA	2.5Ω	EXC14CE900U
		50Ω ±25%	160mA	1.5Ω	EXC24CH500U
		90Ω ±20%	130mA	2.5Ω	EXC24CH900U
Noise Filters (for Gbps)		24Ω ±25%	160mA	1.5Ω	EXC24CG240U
Noise Filters (for Gbps)		90Ω ±25%	100mA	3.0Ω	EXC24CG900U
Noise Filters (for Mbps)		36Ω ±25%	200mA	1.00Ω	EXC24CE360UP
		90Ω ±25%	160mA	1.75Ω	EXC24CE900U
		120Ω ±25%	140mA	2.20Ω	EXC24CE121U
		200Ω ±25%	130mA	2.70Ω	EXC24CE201U
		90Ω ±25%	130mA	2.50Ω	EXC24CF900U
Noise Filters (0805 small size)		67Ω ±25%	250mA	0.8Ω	EXC34CE670P
		90Ω ±25%	250mA	0.8Ω	EXC34CE900U
		120Ω ±25%	200mA	1.0Ω	EXC34CE121U
		200Ω ±25%	200mA	1.0Ω	EXC34CE201U
		90Ω ±25%	100mA	3.0Ω	EXC34CG900U
 Noise Filter Array (0603 small size)	2 lines	43Ω ±20%	100mA	2.7Ω	EXC18CG430U
		65Ω ±20%	140mA	1.8Ω	EXC18CE650U
		90Ω ±20%	130mA	2.0Ω	EXC18CE900U
		200Ω ±20%	100mA	3.5Ω	EXC18CE201U
Noise Filter Array (for Gbps)		50Ω ±25%	160mA	1.5Ω	EXC28CH500U
Noise Filter Array (for Gbps)		90Ω ±20%	130mA	2.5Ω	EXC28CH900U
Noise Filter Array (for Gbps)		24Ω ±25%	160mA	1.5Ω	EXC28CG240U
Noise Filter Array (for Gbps)		90Ω ±25%	100mA	3.0Ω	EXC28CG900U
Noise Filter Array (for Mbps)		90Ω ±25%	160mA	1.5Ω	EXC28CE900U
		120Ω ±25%	140mA	2.0Ω	EXC28CE121U
		200Ω ±25%	130mA	2.5Ω	EXC28CE201U
		300Ω ±25%	80mA	5.0Ω	EXC28CE301U
 2 mode Noise Filters	1 lines	120Ω ±25%	500mA	0.3Ω	EXC24CP121U
		220Ω ±25%	350mA	0.4Ω	EXC24CP221U
		220Ω ±25%	100mA	0.7Ω	EXC24CB221U
		1.000Ω ±25%	50mA	1.5Ω	EXC24CB102U
		600Ω ±25%	200mA	0.9Ω	EXC24CN601X
 Chip Bead Array	4 lines	120Ω ±25%	100mA	0.5Ω	EXC28BA121U
		220Ω ±25%		0.7Ω	EXC28BA221U
		120Ω ±25%		0.5Ω	EXC28BB121U
		220Ω ±25%		0.7Ω	EXC28BB221U



**SMD Chip Varistor - Automotive Type**

Series / Type	Circuit Voltage DC(V)	Maximum Allowable Voltage DC(V)	Normal Varistor Voltage at 1mA (V)	Capacitance at 1MHz	Application	Features	Size	Part No.	
 Multilayer Chip Varistor Automotive Type	DC3~5V	11V	18V	150pF max.	Sensor I/O data Line (ECU-ECU) Communication Line (CAN/LIN)	Replacement of 0.5W Zener Diode (2.5x1.25mm)	0402	EZJZ0V180HM	
	DC3~12V	13V	22V	150pF max.				EZJZ0V220HM	
	DC3~12V	18V	27V	47pF max.				EZJZ0V270EM	
	DC3~12V	18V	27V	20pF max.				EZJZ0V270RM	
	DC3~24V	30V	42V	56pF max.				EZJZ0V420WM	
	DC3~24V	40V	65V	27pF max.				EZJZ0V650DM	
	DC3~12V	18V	27V	47pF max.			0504 (2 Array)	EZJZSV270EM	
	DC3~12V	18V	27V	20pF max.				EZJZSV270RM	
	DC3~24V	30V	42V	56pF max.				EZJZSV420WM	
	DC3~5V	11V	18V	220pF max.				0603	EZJZ1V180JM
	DC3~12V	13V	22V	220pF max.					EZJZ1V220JM
	DC3~12V	18V	27V	100pF max.					EZJZ1V270GM
	DC3~12V	18V	27V	47pF max.			EZJZ1V270EM		
	DC3~12V	18V	27V	20pF max.			EZJZ1V270RM		
	DC3~24V	30V	42V	68pF max.			EZJZ1V420FM		
	DC3~24V	40V	65V	27pF max.			EZJZ1V650DM		
High Energy Type	DC12V	16V	20 to 23.2V		LED Lamp Electronic shifter Car air con, Power window	Replacement of 5W Zener Diode (>15.5x10x5mm) Meet for Load Damp Surge Maximum Surge: JASO A-1 70V 1time	3225	ERZHF2M220D	
		16V	27V ± 20% (21.6 to 32.4V)				3225	ERZHF2M270	



**Multilayer Varistors – Surface Mount Type**

Series / Type	Varistor Voltage	Maximum Peak Current	Part No.
 Multilayer Chip Varistor [Voltage/Signal lines]	6.8 to 170V	1 to 20A Contact discharge: 8kV	EZJPxxxxxx
			EZJZxxxxxx
Multilayer Chip Varistor [2 Array Type for Signal lines]	12 to 170V	3 to 5A Contact discharge: 8kV	EZJZSxxxxx
Multilayer Chip Varistor for ESD pulse	12 to 50V	Contact discharge: 30kV	EZJSxxxxxx

**Thermal Cutoffs – Radial Lead Type**

Series / Type	Rated Temp.	Functioning Temp.	Electrical Rating			Maximum Operating Temp.	Holding Temp.	Maximum Temp. Limit : Tm	Part No.		
			AC/DC	Volt	Amp.						
 <p>Series N</p>	86°C	82°C	AC	250	2	60°C	60°C	200°C	EYP2BN082		
			AC	125	3	52°C				56°C	
			DC	50	4	45°C				50°C	
	102°C	98°C	AC	250	2	65°C	75°C	200°C	EYP2BN099		
			AC	125	3	60°C				70°C	
			DC	50	4	55°C				65°C	
	114°C	110°C	AC	250	2	80°C	90°C	200°C	EYP2BN109		
			AC	125	3	76°C				86°C	
			DC	50	5	65°C				74°C	
	115°C	110°C	AC	250	2	80°C	90°C	200°C	EYP2BN110		
			AC	125	3	76°C				86°C	
			DC	50	5	65°C				74°C	
	134°C	129°C	AC	250	2	90°C	100°C	200°C	EYP2BN127		
			AC	125	3	75°C				90°C	
			DC	50	4	65°C				80°C	
	139°C	135°C	AC	250	2	100°C	110°C	200°C	EYP2BN134		
			AC	125	3	85°C				100°C	
			DC	50	6	60°C				70°C	
	145°C	141°C	AC	250	2	110°C	120°C	200°C	EYP2BN143		
			AC	125	3	105°C				115°C	
			DC	50	6	80°C				90°C	
	 <p>Series F</p>	102°C	98°C	AC	250	1	65°C	75°C	200°C	EYP1BF101	
				AC	125	2	60°C				70°C
				DC	50	35	55°C				65°C
115°C		110°C	AC	250	1	80°C	90°C	200°C	EYP1BF115		
			AC	125	2	76°C				90°C	
			DC	50	4	70°C				80°C	
134°C		129°C	AC	250	1	90°C	105°C	200°C	EYP1BF134		
			AC	125	2	85°C				100°C	
			DC	50	4	65°C				80°C	
139°C		135°C	AC	250	1	100°C	110°C	200°C	EYP1BF138		
			AC	125	2	90°C				105°C	
			DC	50	5	65°C				70°C	
145°C		141°C	AC	250	1	110°C	125°C	200°C	EYP1BF145		
			AC	125	2	110°C				125°C	
			DC	50	5	80°C				95°C	

**Thermal Cutoffs – Radial Lead Type**


Series / Type	Rated Temp.	Functioning Temp.	Electrical Rating			Maximum Operating Temp.	Holding Temp.	Maximum Temp. Limit : Tm	Part No.
			AC/DC	Volt	Amp.				
 Series E	102°C	98°C	AC	250	05	65°C	75°C	200°C	EYP05BE101
			AC	125	15	60°C	70°C		
			DC	50	3	55°C	65°C		
	115°C	110°C	AC	250	05	80°C	95°C	200°C	EYP05BE115
			AC	125	15	76°C	93°C		
			DC	50	3	70°C	84°C		
	134°C	129°C	AC	250	05	90°C	105°C	200°C	EYP05BE134
			AC	125	15	85°C	100°C		
			DC	50	3	70°C	85°C		
	139°C	135°C	AC	250	05	100°C	115°C	200°C	EYP05BE138
			AC	125	15	95°C	110°C		
			DC	50	4	65°C	80°C		
	145°C	141°C	AC	250	05	110°C	125°C	200°C	EYP05BE145
			AC	125	15	105°C	125°C		
			DC	50	5	80°C	95°C		
 Series H	102°C	98°C	AC	250	2	65°C	75°C	200°C	EYP2BH101
			AC	125	3	60°C	70°C		
			DC	50	35	55°C	65°C		
	115°C	110°C	AC	250	2	80°C	90°C	200°C	EYP2BH115
			AC	125	3	76°C	86°C		
			DC	50	35	74°C	84°C		
	134°C	129°C	AC	250	2	90°C	95°C	200°C	EYP2BH134
			AC	125	3	70°C	85°C		
			DC	50	35	65°C	80°C		
	139°C	135°C	AC	250	2	100°C	105°C	200°C	EYP2BH138
			AC	125	3	80°C	95°C		
			DC	50	35	75°C	90°C		
	145°C	141°C	AC	250	2	110°C	125°C	200°C	EYP2BH145
			AC	125	3	100°C	115°C		
			DC	50	45	85°C	100°C		
Series MP	92°C	88°C	DC	32	2	55°C	60°C	135°C	EYP2MP092AFT
	98°C	94°C	DC	32	2	60°C	65°C	135°C	EYP2MP098AFT
	Series MU	92°C	89°C	DC	32	4	55°C	55°C	135°C

**Micro Chip Fuse – Surface Mount Type**

Series / Type	Rated Current	Rated Voltage	Size	Part No.
Micro Chip Fuse	0.315A - 3.0A	32VDC	0402	ERBRDxRxxX
	0.5A - 5.0A		0603	ERBRExRxxV
	0.5A - 4.0A	63VDC (0.5A to 2.0A) 32VDC (2.5A to 4.0A)	1206	ERBRGxRxxV



# THE FUTURE OF THERMAL MANAGEMENT



## THERMAL HEAT SINK SOLUTION

---

- > Thermal Conductivity:  
700 to 1950 W/(m-K)
- > Offers thermal conductivity five times greater than copper, ten times greater than aluminium
- > Density: 0.85 to 2.13g/cm
- > Flexible and easy to cut or trim
- > Withstands repeated bending
- > Low thermal resistance
- > RoHS directive compliant

Our products efficiently diffuse heat in today's world of compact electronic devices. Enter with us the next dimension of thermal management.

Pyrolytic Graphite Sheet (PGS) is an ultra-thin, lightweight, graphite film with a thermal conductivity high enough to release and diffuse the heat generated by heat sources such as CPUs, processors, power amplifiers, cameras and mobile phones.

This material is flexible and can be cut into customized shapes.

# PYROLYTIC GRAPHITE SHEET (PGS)

## HIGH THERMAL CONDUCTIVITY FOR HEAT PROBLEMS


### ADDED VALUE

- > High thermal conductivity
- > Flexible Material
- > Shielding (Electromagnetic wave)

### FLEXIBLE MATERIAL




### CRYSTALLIZED STRUCTURE



### HIGH THERMAL CONDUCTIVITY

- > Best thermal conductivity in the industry
- > 5 times higher, in a range from 700 to 1950W/mK






## FUNCTION OF PGS GRAPHITE SHEET

### 1.) Thermal Transfer

Carrying the heat





Diffusing the heat







### 2.) Thermal Interface

Decreasing the thermal resistance and diffusing heat



**“PGS” Graphite Sheets Standard Series**

Type	PGS only S Type	Adhesive Tape A-A Type	A-M Type	A-F Type	
Front Face	-	-	-	-	
Rear Face	-	Insulative adhesion type 30 μm	Insulative thin adhesion type 10μm	Insulative thin adhesion type 6μm	
Structure					
Features	<ul style="list-style-type: none"> <li>&gt; High Thermal Conductivity</li> <li>&gt; High Flexibility</li> <li>&gt; Low Thermal Resistance</li> <li>&gt; Available up to 400°C</li> <li>&gt; Conductive Material</li> </ul>	<ul style="list-style-type: none"> <li>&gt; With insulation material on one side</li> <li>&gt; With strong adhesive tape for putting chassis</li> <li>&gt; Withstanding voltage: 2kV</li> </ul>	<ul style="list-style-type: none"> <li>&gt; With insulation material on one side</li> <li>&gt; Low thermal resistance comparison with A-A type</li> <li>&gt; Withstanding voltage: 1kV</li> </ul>	<ul style="list-style-type: none"> <li>&gt; With insulation material on one side</li> <li>&gt; Low thermal resistance comparison with A-A type</li> </ul>	
Withstanding temperature	400°C	100°C	100°C	100°C	
Standard Size	115x180mm	90x115mm	90x115mm	90x115mm	
Maximum Size	180x230mm (25μm to)	115x180mm	115x180mm	115x180mm	
100μm	Part No.	EYGS121810	EYGA091210A	EYGA091210M	EYGA091210F
	Thickness	100μm	130μm	110μm	106μm
70μm	Part No.	EYGS121807	EYGA091207A	EYGA091207M	EYGA091207F
	Thickness	70μm	100μm	80μm	76μm
50μm	Part No.	EYGS121805	EYGA091205A	EYGA091205M	EYGA091205F
	Thickness	50μm	80μm	60μm	56μm
40μm	Part No.	EYGS121804	EYGA091204A	EYGA091204M	EYGA091204F
	Thickness	40μm	70μm	50μm	46μm
25μm	Part No.	EYGS121803	EYGA091203A	EYGA091203M	EYGA091203F
	Thickness	25μm	55μm	35μm	31μm
17μm	Part No.	-	EYGA091202A	EYGA091202M	EYGA091202F
	Thickness	-	47μm	27μm	23μm
10μm	Part No.	-	EYGA091201A	EYGA091201M	EYGA091201F
	Thickness	-	40μm	20μm	16μm




Please contact our engineering section or factory about special applications.  
Withstanding voltages are for reference, not guaranteed.

“PGS” Graphite Sheets Standard Series

Type	Laminated Type (Insulation & Adhesive)				
	A-PA Type	A-PM Type	A-DM Type	A-DF Type	
Front Face	Polyester tape standard type 30μm	Polyester tape standard type 30μm	Polyester tape thin type 10μm	Polyester tape thin type 10μm	
Rear Face	Insulative adhesion type 30μm	Insulative thin adhesion type 10μm	Insulative thin adhesion type 10μm	Insulative thin adhesion type 6μm	
Structure					
Features	<ul style="list-style-type: none"> <li>&gt; With insulation material on both side</li> <li>&gt; Withstanding voltage:                             <ul style="list-style-type: none"> <li>&gt; PET tape: 4kV</li> <li>&gt; Adhesive tape: 2kV</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>&gt; With insulation material on both side</li> <li>&gt; Withstanding voltage:                             <ul style="list-style-type: none"> <li>&gt; PET tape: 4kV</li> <li>&gt; Adhesive tape: 1kV</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>&gt; With insulation material on both side</li> <li>&gt; Withstanding voltage:                             <ul style="list-style-type: none"> <li>&gt; PET tape: 1kV</li> <li>&gt; Adhesive tape: 1kV</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>&gt; With insulation material on both side</li> <li>&gt; Withstanding voltage:                             <ul style="list-style-type: none"> <li>&gt; PET tape: 1kV</li> </ul> </li> </ul>	
Withstanding temperature	100°C	100°C	100°C	100°C	
Standard Size	90x115mm	90x115mm	90x115mm	90x115mm	
Maximum Size	115x180mm	115x180mm	115x180mm	115x180mm	
100μm	Part No.	EYGA091210PA	EYGA091210PM	EYGA091210DM	EYGA091210DF
	Thickness	160μm	140μm	120μm	116μm
70μm	Part No.	EYGA091207PA	EYGA091207PM	EYGA091207DM	EYGA091207DF
	Thickness	130μm	110μm	90μm	86μm
50μm	Part No.	EYGA091205PA	EYGA091205PM	EYGA091205DM	EYGA091205DF
	Thickness	110μm	90μm	70μm	66μm
40μm	Part No.	EYGA091204PA	EYGA091204PM	EYGA091204DM	EYGA091204DF
	Thickness	100μm	80μm	60μm	56μm
25μm	Part No.	EYGA091203PA	EYGA091203PM	EYGA091203DM	EYGA091203DF
	Thickness	85μm	65μm	45μm	41μm
17μm	Part No.	EYGA091202PA	EYGA091202PM	EYGA091202DM	EYGA091202DF
	Thickness	77μm	57μm	37μm	33μm
10μm	Part No.	EYGA091201PA	EYGA091201PM	EYGA091201DM	EYGA091201DF
	Thickness	70μm	50μm	30μm	26μm



Please contact our engineering section or factory about special applications.  
Withstanding voltages are for reference, not guaranteed.

**“PGS” Graphite Sheets High Heat Resistance Series**

Type	High Heat Resistance Type		
	A-V Type	A-RV Type	A-KV Type
Front Face	-	High heat resistance and insulation type 13μm	High heat resistance and insulation type 30μm
Rear Face	High heat resistance and insulation adhesion type 18μm	High heat resistance and insulation adhesion type 18μm	High heat resistance and insulation adhesion type 18μm
Structure			
Features	<ul style="list-style-type: none"> <li>&gt; With high heat resistance and insulation tape on one side</li> <li>&gt; Withstanding voltage adhesive tape: 2kV</li> </ul>	<ul style="list-style-type: none"> <li>&gt; With high heat resistance and insulation tape on both side</li> <li>&gt; Withstanding voltage:                             <ul style="list-style-type: none"> <li>&gt; PEEK tape: 2kV</li> <li>&gt; adhesive tape: 2kV</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>&gt; With high heat resistance and more insulated tape on both side</li> <li>&gt; Withstanding voltage:                             <ul style="list-style-type: none"> <li>&gt; PI tape: 5kV</li> <li>&gt; adhesive tape: 2kV</li> </ul> </li> </ul>
Withstanding temperature	150°C	150°C	150°C (Polyimide: 180°C)
Standard Size	90x115mm	90x115mm	90x115mm
Maximum Size	115x180mm	115x180mm	115x180mm
100μm	Part No. EYGA091210V	EYGA091210RV	EYGA091210KV
	Thickness 118μm	131μm	148μm
70μm	Part No. EYGA091207V	EYGA091207RV	EYGA091207KV
	Thickness 88μm	101μm	118μm
50μm	Part No. EYGA091205V	EYGA091205RV	EYGA091205KV
	Thickness 68μm	81μm	98μm
40μm	Part No. EYGA091204V	EYGA091204RV	EYGA091204KV
	Thickness 58μm	71μm	88μm
25μm	Part No. EYGA091203V	EYGA091203RV	EYGA091203KV
	Thickness 43μm	56μm	73μm
17μm	Part No. EYGA091202V	EYGA091202RV	EYGA091202KV
	Thickness 35μm	48μm	65μm
10μm	Part No. EYGA091201V	EYGA091201RV	EYGA091201KV
	Thickness 28μm	41μm	58μm

Please contact our engineering section or factory about special applications.  
Withstanding voltages are for reference, not guaranteed.

# TOUCH AND FEEL THE DIFFERENCE



## SWITCHES

---

- > Wide range of size and operating forces
- > Very low contact resistance
- > High contact reliability
- > Temperature range from -40 up to +85°C
- > Excellent tactile behaviour
- > Long life type up to 1Mio cycles
- > Variety of IP67 switches

**Light Touch Switches** provide a unique, sharp tactile feel, have low contact resistance, minimal bounce noise, high contact reliability and are available in a wide selection of operating forces.

**Detector Switches** are used to detect mechanical movement, such as the closing of a flip-phone or detecting end positions of rotaries. Detector Switches can also be used as an Encoder function enabling lower cost solutions.











**Encoders** convert the manual rotary operation of an actuator or knob into coded signal outputs and offer options such as excellent haptics with various detents, high torque, push-on switch, long life, and center space.

**Carbon-Type Potentiometers** are used for analog Input systems. These devices are available with or without detents as well as center space and high torque capability. Excellent output linearity combined with long life capability provides added value.

## Light Touch Switches – Surface Mount Type









Series / Type	Dimensions LxWxH (mm)	Operating Force	Operating Cycles	Travel	Part No.
 4mm Square	4.1x4.1x0.35 4.1x4.1x0.43 4.1x4.1x0.58	1.0N 1.6N 2.4N	200,000 500,000 1,000,000	0.25mm	EVQ6P6xxx EVQ7P6xxx EVQ9P6xxx EVQP6xxxx
 4.5mm Square	4.5x4.5x0.55	1.6N 2.4N	200,000	0.20mm	EVQPQxxxx
 4.9mm Square	4.9x4.9x0.8 4.9x4.9x1.5	1.0N 1.6N 2.6N	200,000 500,000	0.25mm	EVQPLxxxx
 6mm Square Thin Type	6.5x6.0x2.0 6.5x6.0x2.5 6.5x6.0x3.1	0.5N 0.6N 1.0N 1.3N 1.6N 2.6N 3.5N	100,000 200,000 1,000,000 2,000,000	0.25mm 0.35mm	EVQP0xxxx EVQQ2xxxx
 2.6x1.6mm IP67	2.6x1.6x0.53	1.6N	500,000	0.11mm	EVPPBxxxx <small>NEW</small>
 3.0x2.0mm IP67	3.0x2.0x0.6	1.6N 2.4N 3.3N	300,000	0.13mm 0.15mm	EVPAWxxxx <small>NEW</small>
 3.0x2.6mm	3.0x2.6x0.65	1.6N	100,000	0.15mm	EVPAFxxxx
 3.0x2.6mm Double-action	3.0x2.6x0.7	1st: 0.7N 2nd: 2.0N	100,000	1st: 0.07mm 2nd: 0.16mm	EVPAxxxxx <small>NEW</small>
 3.4x2.9mm IP67	3.4x2.9x1.7	1.6N	500,000	0.15mm	EVPAYxxxx <small>NEW</small>
 3.5x2.9mm	3.5x2.9x1.7	1.0N 1.6N 2.4N 3.5N 5.0N	200,000 1,000,000	0.15mm	EVPAAxxxxx
 4.7x3.5mm	4.7x3.5x2.1 4.7x3.5x2.5	1.0N 1.6N 2.4N 2.5N 3.5N 5.0N	200,000 500,000 1,000,000	0.25mm 0.70mm	EVQ3P2xxx EVQP2xxxx EVQP9xxxx
 3.5x2.9mm Side-operation Type	3.5x2.9x1.35	1.6N 2.2N	100,000	0.20mm	EVQ9P7xxx EVQP3xxxx EVQP7xxxx
 3.8x1.9mm Side-operation Type IP67	3.8x1.9x1.6	1.6N	200,000	0.12mm	EVPAKxxxx <small>NEW</small>
 4.7x3.5mm Side-operation Type	4.7x3.5x1.65			0.30mm	EVQPUxxxx
 2.8x2.3mm Side-operation Type Edge Mount	2.8x2.3x1.95	1.6N	300,000	0.13mm	EVPAVxxxx <small>NEW</small>
 4.5x2.2mm Side-operation Type Edge Mount	4.5x2.2x2.9	1.6N	200,000	0.15mm	EVPAExxxxx
 6.2x2.5mm Side-operation Type Edge Mount	6.2x2.55x3.5	1.0N 1.6N 2.4N 2.5N 3.5N 5.0N	200,000 500,000 1,000,000	0.25mm 0.70mm	EVQP4xxxx EVQP8xxxx

## Light Touch Switches – Surface Mount Type


Series / Type	Dimensions LxWxH (mm)	Operating Force	Operating Cycles	Travel	Part No.
 6.1x4.0mm Side-operation Type	6.1x4.0x1.8	1.6N 2.2N	100,000	0.30mm	EVQPSxxxx
 3.5x2.9mm Side-operation Type Half Dive	3.5x2.9x1.2			0.20mm	EVPANxxxx
 6.0x3.5mm	6.0x3.5x4.3 6.0x3.5x5.0	1.0N 1.6N 2.4N	30,000 50,000	0.25mm	EVQ5Pxxxx EVQPE1xxx EVQPNxxxx
 4mm Square Double-action	4.0x4.1x0.59	0.8N / 1.6N 0.9N / 2.0N 1.0N / 2.6N	30,000 100,000	0.15 / 0.3mm	EVPAHxxxx
 6mm Square Double-action Thin Type	6.0x6.0x0.9 6.0x6.0x0.95	0.7N / 2.6N 1.0N / 2.6N	30,000	0.4mm / 0.5mm	EVQ3PRxxx EVQPRxxxx EVQQ0xxxx
 7x3.5mm Double-action Side-operational	4.7x3.5x1.2	1.6N / 2.6N	100,000	0.15mm / 0.4mm	EVPAJxxxx
 6mm Square Long Travel	6.0x6.1x5.0	1.6N 2.0N 2.2N 2.5N 3.5N	30,000 100,000	1.0mm 1.3mm	EVQ9Pxxxx EVQP19xxx EVQP1Bxxx EVQP1Dxxx EVQP1Fxxx EVQP1Kxxx
 6mm Square Long Travel 2 terminal type	6.0x6.1x5.0	1.6N 2.0N 2.2N 2.5N 3.0N 3.5N	30,000 100,000	1.0mm 1.3mm	EVPASxxxx
 8mm Square Long Travel	8.5x8.5x6.5	4.0N 5.0N	100,000	1.0mm	EVQQ1xxxx
 10mm Square Center Space Long Travel	9.8x9.8x4.6	4.0N			EVPADxxxx





## Light Touch Switches – Radial Lead Type

Series / Type	Dimensions LxWxH (mm)	Operating Force	Operating Cycles	Travel	Part No.
 5N	6.0x6.0x4.3 6.0x6.0x5.0 6.0x6.0x7.0 6.0x6.0x9.5	1.0N 1.3N 1.6N 2.6N	50,000 100,000	0.25mm	EVQPAxxxx EVQPBxxxx
 5N Side-operation Type	7.5x7.1x7.15 7.5x7.1x7.85 7.5x7.1x9.85 7.5x7.1x12.35				EVQPFxxxx
 5N Type 2R	6.0x6.0x4.3 6.0x6.0x5.0 6.0x6.0x7.0 6.0x6.0x9.5				EVQ2xxxx
 5N Type 4R Side-operation Type	7.5x7.1x9.25				EVQPCxxxx
 Type 2R Round Type	6.0x6.0x4.3 6.0x6.0x5.0 6.0x6.0x7.0 6.0x6.0x9.5				EVQ11xxxx
 6.0x3.5mm	6.0x3.5x4.3 6.0x3.5x5.0	1.0N 1.6N 2.4N	30,000 50,000		EVQPExxxx
 Over Travel	6.2x6.2x7.45	0.74N 1.3N	1,000,000 5,000,000	0.2mm	EVQP0xxxx
 6mm Square 2R Long Travel	6.0x6.1x5.0	1.6N 2.0N 2.2N 2.5N 3.5N	30,000 100,000	1.0mm 1.3mm	EVQPVxxxx










## Push Switches – Surface Mount Type

Series / Type	Dimensions LxWxH (mm)	Lock Travel	Full Travel	Operating Force	Part No.
	8.9x10.0x20.5	1.5mm 2.5mm	2.5mm 3.5mm	2.0N 3.5N	ESB30xxxx


## Push Switches – Radial Lead Type

Series / Type	Dimensions LxWxH (mm)	Lock Travel	Full Travel	Operating Force	Part No.
	8.5x8.5x13.5	1.5mm	2.5mm	2.94N	ESB64xx
	10.0x7.75x12.5		2.3mm	3.0N	ESB33xxx
	8.9x10.0x20.5	1.5mm 2.5mm	2.5mm 3.5mm	2.0N 3.5N	ESB30xxxxx
	7.8x7.9x17.5	–	2.5mm	2.0N 4.0N	ESE20C4xx ESE20D4xx
	7.8x7.9x12.5				ESE20C3xx ESE20D3xx


## Detector Switches

Series / Type	Dimensions LxWxH (mm)	Travel	Operating Force	Rating	Part No.
 09HL	3.0x3.5x0.9	1.4mm 2.1mm	300mN	50µA 3VDC to 10µA 5VDC	ESE58xxxx
 1VR	2.2x3.35x1.5	1.5mm	250mN		ESE16xxxx
 1VL	4.2x3.6x1.2	2.15mm 3.05mm	300mN		ESE13xxxx
 1HL	4.0x4.4x1.2	1.4mm 2.1mm			ESE18xxxx
 2HL	5.4x5.75x1.7	3.2mm	390mN		ESE31xxxx
 2N	Wide Variation	0.6mm 1.2mm 1.45mm 2.20mm 4.25mm	300mN		ESE22xxxx
 5N		Wide Variation	350mN		ESE11xxxx
 1HW	5.0x4.4x1.5	1.0mm 2.2mm	300mN		ESE23xxxx
 2W	7.5x3.0x5.6 7.5x4.65x5.6	Wide Variation	350mN		ESE24xxxx


## Rotary Potentiometers – Vertical Type – Surface Mount Type

Series / Type	Pulse	Detents	Rotation Torque	Height of body	Endurance (Cycles)	Part No.
 10mm GS	333.3°	—	3mNm	2.0mm	100,000	EVWAE4001B14




## Encoders – Horizontal Type – Radial Lead Type

Series / Type	Pulse	Detents	Rotation Torque	Height from PCB to shaft	Endurance (Cycles)	Part No.
 10mm GS	12	24	5mNm	7.0mm	100,000	EVQVXM00112B
				9.0mm		EVQVXD00112B
				11.0mm		EVQVXC00112B



## Encoders – Surface Mount Type

Series / Type	Bushing	Pulse	Detents	Rotation Torque	Switch Push Force / Stroke	Height (mm)	Endurance (Cycles)	Part No.
 11mm Square GS serration-shaft Komuso Junior (shaft wobble reduced), with Switch Push Function	-	8	16	14mNm	6N / 0.4mm	17.5	30,000	EVEUPCAH508B
		16	32	14mNm				EVEUPCAH516B
		8	16	14mNm	4N / 1.5mm			EVEUBCAH508B
		16	32	14mNm				EVEUBCAH516B


## Encoders – Radial Lead Type

Series / Type	Bushing	Pulse	Detents	Rotation Torque	Switch Push Force / Stroke	Height (mm)	Endurance (Cycles)	Part No.
 11mm Square GS serration-shaft Komuso Junior (shaft wobble reduced), with Switch Push Funct.	-	8	16	14mNm	6N / 0.4mm	18.0	30,000	EVEYPCAJO08B
		16	32	14mNm				EVEYPCAJO16B
		8	16	14mNm	4N / 1.5mm			EVEYBCAJ008B
		16	32	14mNm				EVEYBCAJ016B
 12mm Square GS with Switch Push D-shaft	Die-cast (7 & 9mm)	20	20	3~20mNm	3N / 0.4mm	20	30,000	EVEJBBF2020B
		20	20					EVEJBBF2520B
 16mm Square GS Komuso Senior High torque with switch push func.	-	16	32	25mNm	6N / 0.5mm	21.5		EVEQDBRG516B
		8	16	25mNm				EVEPDBRG508B

## Center Space Encoders – Radial Lead Type

Series / Type	Pulse	Detents	Rotation Torque	Endurance	Part No.
 20/12mm	9	18	6mNm	30,000	EVQV6B00909B
	9	18	7mNm		EVQV6A00609B
	9	18	9mNm		EVQV5A00109B
 27/18mm	9	18	9mNm		EVQV5N00409B
	9	18	13.5mNm		EVQV5D00309B
	9	18	18mNm		EVQV5G00209B
	15	30	9mNm		EVQV5L00415B
	15	30	13.5mNm		EVQV5C00315B
	15	30	18mNm		EVQV5B00215B
	15	30	25mNm		EVQV5K00715B

# MODULES FOR A WIRELESS WORLD



## WIRELESS CONNECTIVITY

---

One major trend in the wireless connected world is the **Internet of Everything (IoE)** – connect the unconnected.

Application in the IoE are divided towards what shall be connected.

- > Person to Machine
- > Machine to Machine
- > Person to Person





In a connected world all these will interact together.

Panasonic is manufacturing modules in the field of **Wireless Personal Area Network** (WPAN: *Bluetooth*<sup>®</sup>, ISM and Mesh Networking), **Wireless Body Area Network** (WBAN) and expanding its portfolio to **Wireless Local Area Network** (WLAN: Wi-Fi). The modules are engineered in Germany and produced in Europe under the premise of TS16949.

All products are qualified according to CE, FCC, IC, and *Bluetooth*<sup>®</sup> QDID if applicable. Different software/profile options are available.

With short project deadlines, a module design enables you to be the first in the market, quickly. Panasonic evaluation kits provide an easy to use and low-cost platform for evaluating and prototyping your design.






Classic *Bluetooth*® Modules

Series	PAN13x0 Series	PAN1322 Series	PAN1555 Series	PAN13x5B Series
				
Status	Mass Production	Mass Production	Mass Production	Mass Production
Part Number*	ENW89814C2MF	ENW89841A3KF	ENW89815AxKF	ENW89829x3KF
RF Category	<b>Classic <i>Bluetooth</i>® v2.1 + EDR class 2</b>	<b>Classic <i>Bluetooth</i>® v2.1 + EDR class 2</b>	<b>Classic <i>Bluetooth</i>® v3.0 + EDR class 2</b>	<b>Classic <i>Bluetooth</i>® v2.1 + EDR class 1.5</b>
Software/Profile	HCI	SPP	SPP/HDP+SPP/HID/...	HCI
Used ICs	PMB8763	PMB8754	BC6 + STM32F103	CC2560B
Size [mm]	11.6x8.7x1.8	15.6x8.7x1.8	22.8x13.5x2.7	9.0x6.5x1.8 9.0x9.5x1.8
Rx Sensitivity [dBm]	-86 @ BER 10 <sup>-3</sup>	-86 @ BER 10 <sup>-3</sup>	-86 @ BER 10 <sup>-3</sup>	-93 @ BER 10 <sup>-3</sup>
Tx Power (max.) [dBm]	+4	+4	+4	+10
Power Supply [V]	2.9 to 4.1	2.9 to 4.1	2.7 to 3.6	1.8 to 4.8
Current Consumption	Tx, EDR: 40mA Sleep Mode: 80µA	Tx, EDR: 40mA Sleep Mode: 80µA	ACL, DH1: 47mA Sleep Mode: <100µA	Tx, EDR: 40mA Sleep Mode: 135µA
Interfaces	GPIO, PCM, UART, JTAG	GPIO, UART, JTAG	GPIO, UART, I <sup>2</sup> C, SPI, ADC	GPIO, PCM, UART
Footprint-compatible to	PAN13x0/PAN1322/PAN172x Series			All CC256x based <i>Bluetooth</i> ® modules are footprint- and pin-compatible
Operating Temp. [°C]	-40 to +85	-40 to +85	-40 to +85	-40 to +85
Evaluation Kit*	n/a	ENW89841AYKF (KIT)	n/a	EVAL_PAN1323 (EMK)

\* x is a parameter to be defined.

**Classic *Bluetooth*®** technology is best suited to high data rate applications (up to 3Mbits), where the network size is under eight nodes. This is a piconet of one master device and up to seven slaves. Role switching is supported. Larger networks can be formed with Scatternets. Connections are robust, even in noisy environments, by using 79 channels, each 1MHz wide, adaptive frequency hopping, and multiple modulation schemes. Range can be adjusted using hardware and software from under a meter to over two hundred meters. There are several types of profiles which describe a variety of use cases. For example, SPP or Serial Port Profile is a standard profile for wirelessly connecting devices in place of a serial cable.

**Bluetooth® Smart Ready and Bluetooth® Smart Modules**




Series	PAN13x6B Series	PAN1026 Series	PAN1760 Series	PAN172x Series	PAN1740 Series
					
Status	Mass Production	Mass Production	Engineering Sample	Mass Production	Mass Production
Part Number*	ENW89823x3KF	ENW89837A3KF	ENW89847A1KF	ENW898xxxKF	ENW89846A1KF
RF Category	<b>Bluetooth® Smart Ready Bluetooth® v4.0 class 1.5</b>	<b>Bluetooth® Smart Ready Bluetooth® v4.0 class 2</b>	<b>Bluetooth® Smart Bluetooth® v4.1</b>	<b>Bluetooth® Smart Bluetooth® v4.0</b>	<b>Bluetooth® Smart Bluetooth® v4.1</b>
Software/Profile	HCI	SPP + GATT	Embedded Profiles	nBlue™ by BlueRadios Inc./ TI SW stack	Embedded Profiles
Used ICs	CC2564B	TC35661-501	TC35667	CC2540/CC2541	DA14580
Size [mm] w/o antenna w/ antenna	9.0x 6.5x1.8 9.0x9.5x1.8	15.6x8.7x1.8	15.6x8.7x1.8	11.6x8.7x1.8 15.6x8.7x1.8	9.0x9.5x1.8
Rx Sensitivity [dBm]	-93 @ BER 10 <sup>-3</sup>	-88 @ BER 10 <sup>-3</sup>	-91	-94 @ BER 1%	-93 @ BER 1%
Tx Power (max.) [dBm]	+10	+4	+0	+4/0	+0
Power Supply [V]	1.8 to 4.8	1.8 or 3.3	1.8 to 3.6	2.0 to 3.6	2.35 to 3.3
Current Consumption	Tx, EDR: 40mA Sleep Mode: 135µA	ACL, DH1: 46mA Sleep Mode: <100µA	Tx: 8.7mA Rx: 8.4mA LPM: 0.7/5/8/10µA	Tx: 23mA @ -6dBm Rx: 18mA Sleep Mode: <1µA	Tx: 4.9mA Rx: 4.9mA Sleep Mode: <1µA
Interfaces	GPIO, PCM, UART	GPIO, UART	GPIO, UART, SPI, I <sup>2</sup> C, ADC	GPIO, UART, USB only PAN17x0 Series	GPIO, UART, SPI, I <sup>2</sup> C, 3-axis QD, ADC
Memory			32kB on chip RAM 512kB EEPROM	256kb	32kb OTP
Specialty		Same <b>Bluetooth®</b> Low Energy Software Platform		2 internal crystal	2 internal crystal
Footprint-compatible to	All CC256x based <b>Bluetooth®</b> modules are footprint- and pin- compatible	PAN1760 Series	PAN1026 Series	PAN13x0/PAN1322/ PAN172x Series	
Operating Temp. [°C]	-40 to +85	-40 to +85	-40 to +85	-40 to +85	-40 to +85
Evaluation Kit*	EVAL_PAN1323 (EMK)	ENW89837AYKF (KIT)	ENW89847AYKF (KIT)	ENW898xxAY2F (BR KIT) ENW898xxAY1F (TI KIT)	ENW89846AYKF (KIT) ENW89846AVKF (EMK)

\* x is a parameter to be defined.

**Bluetooth® Smart Ready** technology builds the centre of the **Bluetooth®** ecosystem in combining Classic **Bluetooth®** technology and **Bluetooth®** Smart technology in one device. These so called dual-mode modules combine both communication stacks and permit a shared antenna. It can communicate with other devices implementing both technologies as well as devices implementing either technology and therefore can easily be added to 'hub' devices, e.g. for industrial, automation, medical and fitness products. Single-mode and dual-mode devices are respectively designated as **Bluetooth®** Smart and **Bluetooth®** Smart Ready. Some profiles and use cases will be supported by only one of the technologies. Therefore, devices implementing both technologies have the ability to support the most use cases.

**Bluetooth® Smart** technology achieves its low power consumption primarily by keeping its radio turned off most of the time. It scans only three advertising channels, and its radio awakens only to send or receive short bursts of data, with small packet sizes from 8 to 27 octets. **Bluetooth®** Smart technology can transmit authenticated data in as little as 3ms, versus the 1000ms typical for Classic **Bluetooth®** technology. All this relates in a maximum practical data rate well under 100kbps typically. In **Bluetooth®** Smart technology each use case is allocated to one **Bluetooth®** Smart profile. For transmitting temperature the temperature profile and service are used. Profile and services are using the GATT-based architecture.

## Wi-Fi and Wi-Fi Combo Modules

Series	PAN90x0** Series	PAN93x0 Series	PAN90x5** Series
			
Status	Engineering Sample	ES Q2/2015	Under Development
Part Number*	ENW49801x1JF (USB) ENW49802x1JF (SDIO)	ENW49A01x3EF	ENWF9101x1JF (commercial grade) ENWF9101x1EF (extended grade)
RF Category	<b>Wi-Fi Radio 802.11 b/g/n</b>	<b>Wi-Fi Embedded 802.11 b/g/n</b>	<b>Combo Radio Wi-Fi 802.11 b/g/n (MIMO 2x2) + Bluetooth® Smart Ready Bluetooth® v4.0 class 1.5</b>
Software/Profile	Linux / Android Driver	Full Embedded	Linux / Android Driver
Used ICs	88W8782	88MC200 + 88W8782	88W8797
Size [mm]	22.75x13.5x2.42	29.0x13.5x2.66	26.0x13.5x2.40
Antenna Options	w/ antenna / w/ 50Ω bottom pad	w/ antenna / w/ 50Ω bottom pad	w/o antenna / w/ 2 antenna
Rx Sensitivity [dBm]	-98 @ 1M-DSSS -88 @ 11M-CCK -93 @ 6M-BPSK -76 @ 54M-OFDM -74 @ 65M-MCS7	-98 @ 1M-DSSS -88 @ 11M-CCK -93 @ 6M-BPSK -76 @ 54M-OFDM -74 @ 65M-MCS7	-98 @ 1M-DSSS -88 @ 11M-CCK -93 @ 6M-BPSK -76 @ 54M-OFDM -74 @ 65M-MCS7
Tx Power (max.) [dBm]	+18 @ 11b	+18 @ 11b	+18 @ 11b
Power Supply [V]	3.0 to 3.6	3.0 to 3.6	3.0 to 3.6
Current Consumption	430mA @ 11Mbps	~450mA	tbd
Centre Frequency [GHz]	2.4	2.4	2.4
Interfaces	USB2.0 or SDIO	GPIO, QSPI, I <sup>2</sup> C, UART, JTAG	USB2.0, SDIO3.0, HS UART
Specialty	Coexistence Interface for external co-located 2.4GHz radios		Coexistence with cellular and other 2.4GHz on-chip radios
Operating Temp. [°C]	0 to +70	-30 to +70	0 to +70 (commercial grade) -30 to +85 (extended grade)
Evaluation Kit*	ENW49802AYJF (KIT)	tbd	ENWF9101AYEF (KIT)





\* x is a parameter to be defined.

\*\* Annual Volume Requirement of 100k. Please engage with Panasonic sales team and wireless team to determine if this module is suitable for your applications. Panasonic reserves the right to support or to not support requests based on corporate policy that includes export control and application restrictions or other requirements.

Based on the IEEE 802.11 standard, **Wi-Fi** is part of the Wireless Local Area Network (WLAN). Wi-Fi enables devices to exchange data or connect to the internet using 2.4GHz and 5GHz. Therefore Wi-Fi is the technology working anywhere in the world. The range of Wi-Fi technology varies by Wi-Fi standard (a/b/g/n/ac etc.) and frequency band. The 802.11n standard uses high throughput data rates, double the radio spectrum/bandwidth (40MHz) compared to 802.11a or 802.11g (20MHz) and introduces MIMO technology for RF multipath data propagation.

The latest 802.11ac standard, which uses the 5GHz band, uses radio spectrum/bandwidth of up to 160MHz and enhanced MIMO technology. The term “Wi-Fi” is used in general English as a synonym for “WLAN”. Radio modules offer easy hardware integration with flexible software part whereas embedded modules cover the full package on hardware and software side. **Combo modules** of Wi-Fi and other wireless technology allow interaction of those technologies. NFC for example can act as enabling technology for Bluetooth and Wi-Fi connection set-up.

## ISM and Mesh Networking Modules

Series	PAN235x Series	PAN237x Series	PAN4561H Series	PAN4580x Series
				
Status	Mass Production	Engineering Sample	Mass Production	Mass Production
Part Number*	ENW5961xN3xx	ENW59637C1xF	ENWC9A22xxEF	ENWC9A31xxEF
RF Category	<b>ISM Transceiver</b>	<b>ISM Transceiver</b>	<b>Mesh Networking (ZigBee® ready)</b>	<b>Mesh Networking (ZigBee® ready)</b>
Software/Profile	n/a	n/a	SNAP® by Synapse Wireless Inc.	SNAP® by Synapse Wireless Inc.
Used ICs	CC1101	CC1200	MC13213 + CC2591	ATmega128RFA1
Size [mm]	8.0x8.2x1.9	13.8x11.8x1.9	35.0x15.0x3.8	29.8x19.0x2.6
Antenna Options	w/o antenna	w/o antenna	w/ ceramic antenna / U.FL connector / bottom pad	
Rx Sensitivity [dBm]	-112 @ 1.2k GFSK -104 @ 38.4k GFSK -95 @ 250k GFSK -89 @ 500k 4FSK	-123 @ 1.2k-2FSK -110 @ 50k-2GFSK -97 @ 500k-2GFSK -97 @ 1M-4GFSK	-98 @ 250 kbps	-100 @ 250kbps -96 @ 500kbps -94 @ 1Mbps -86 @ 2Mbps
Tx Power (max.) [dBm]	+10	+15	+18.5	+3.5
Power Supply [V]	1.8 to 3.6	2.0 to 3.6	2.7 to 3.4	1.9 to 3.6
Current Consumption	Tx: 36mA Rx: 18mA Sleep Mode: <1µA	Tx: 54mA Rx: 2mA to 23mA Sleep Mode: <1µA	Tx: 210mA Rx: 48mA Off Mode: 2µA	Tx: 20mA Rx: 17mA Sleep Mode: 1.5µA
Centre Frequency [MHz]	433/868/915	169/433/868/915/955	2,400	2,400
Interfaces	GPIO, SPI	GPIO, SPI	GPIO, UART, I²C	GPIO, 2x UART, SPI, ADC, I²C
Operating Temp. [°C]	-40 to +85	-40 to +85	-40 to +85	-40 to +85
Evaluation Kit*	n/a	n/a	ENWC9A30x4EF + RF Module USB Adapter	ENWC9A33xxEF + RF Module USB Adapter

\* x is a parameter to be defined.

**Industrial, Scientific and Medical (ISM radio band)** solutions benefits of reduced cost, proprietary network, low power and various speeds of data transmission. Many ISM Modules work outside of the crowded 2.4GHz spectrum to provide high RF performance and data integrity. These modules allow the highest flexibility for realising your wireless connection. If a system does not need to be open, this might be an economical way to transmit/receive data.

Based on the IEEE 802.15.4 standard, **Mesh Networking** was developed for the purpose of sending small amounts of data short distances, using very little power. The key feature of this technology is the ability to create a self-healing mesh network where nodes “talk” to each other in a way that gets a message to a desired end point using the best path. When not in use, nodes will “sleep” using extremely little power. The ecosystem of IEEE 802.15.4 comprises different standards like ZigBee, KNX, Wireless HART, 6LoWPAN/IPv6 and many more. If a system does not need to be open, SNAP® (Synapse Network Application Protocol) might be an efficient and easy way to realise a Mesh Network.



# ORIGINAL SOLUTIONS FOR POWER, LIGHTING AND COMMUNICATION



## SEMI- CONDUCTORS

---

- > The quick and easy way to improve and differentiate your green electronic designs
- > Original design solutions
- > Advanced materials, beyond silicon
- > Reduce power waste
- > Integration and miniaturization

### POWER

- > High efficiency, fast transient response DCDC converters and modules for point of load. Reduce development time, bill of material and power waste.
- > Fast switching, low on-resistance, normally off GaN power transistors.

### NFC

- > Easily add cloud connectivity to your products with Panasonic NFC modules and interface ICs. Worldwide standards supported.


### DISCRETES

- > Thin-wafer trench MOSFETs and diodes in innovative chip-scale packages exhibit superior efficiency and heat extraction characteristics while reducing the PCB footprint. For load switching and switched power supplies.

### LEDs

- > Wide range of mono- dual- and tri-colour top-firing LEDs in SMT, including 0.2mm ultra thin 0402/0603 packaging.
- > High brightness white GaN on GaN LED for automotive front lighting.

# COMPETITIVE EDGE AND FOCUS MARKETS



**LEVERAGING PANASONIC EXPERTISE IN SEMICONDUCTOR MATERIALS AND MANUFACTURING METHODS TO DELIVER ADVANCED SOLUTIONS AND PRODUCTS TO THE AUTOMOTIVE, INDUSTRIAL AND ICT MARKETS.**

# ADVANCED AUTOMOTIVE SOLUTIONS

## SOLUTION FOR LIGHTING AND BATTERY MONITORING

### 1 LIGHTING SOLUTIONS\*

- > GaN on GaN high brightness white LED
- > For DRL, high beam, low beam
- > Integrated driver ICs
- > Multi-string digital control



### 2 MOSFETS

- > Battery protection
- > Thin trench technology
- > Flip-chip packages
- > Superior heat extraction
- > High efficiency

### 3 BATTERY MONITORING SYSTEMS\*

- > Chipset BMS IC / CAN MCU / SBC
- > Silicon On Insulator technology
- > High precision
- > Wide temperature range
- > High robustness

\*Advanced product, please contact your nearest Panasonic sales representative for more information

# ADVANCED POWER SOLUTIONS

## EFFICIENT POWER DEVICES AND POWERFUL DIGITAL CONTROL

### 1 INVERTER MCU\*


- > Dual motor control
- > Sub-nanosecond resolution PWM
- > HW acceleration for Field Oriented Control
- > Control software

### 2 PSIP

- > Embedded power / POL
- > Fast and easy design
- > Simplified procurement
- > High power density


### 3 GaN / SiC\*

- > High power converters
- > AC-DC / DC-DC
- > Fast switching
- > Low losses




\*Advanced product, please contact your nearest Panasonic sales representative for more information

**Non-isolated DCDC step down power modules - „Power Supply in Package“ (PSiP)**

Series / Type	V <sub>in</sub> min/max (V)	V <sub>out</sub> min / max (V)	I <sub>out</sub> max (A)	Package (mm <sup>3</sup> )	Part number
 PSiP <small>NEW</small>	4.5 / 28	0.6 / 5.5	10	QFN (8.5x7.5x4.7)	NN31000A
	4.5 / 28	0.6 / 5.5	7		NN31001A
	4.5 / 28	0.6 / 5.5	4		NN31002A


Built-in safety: under voltage lock out, over voltage detection, under voltage detection, over current protection, short circuit protection, thermal shut down

**Step down DCDC converter with built in MOSFET - „MCP DCDC“**

Series / Type	V <sub>in</sub> min/max (V)	V <sub>out</sub> min / max (V)	I <sub>out</sub> max (A)	Package (mm <sup>2</sup> )	Part number
 5V V <sub>in</sub> (*I2C interface)	4.5 / 5.6	0.6 / 3.5	6	HQFN24 (4x4)	NN30195A
	4.5 / 5.6	0.6 / 3.5	9	HQFN40 (6x6)	NN30196A
	4.5 / 5.6	0.6 / 3.5	6	HQFN24 (4x4)	NN30295A(*)
	4.0 / 5.6	0.6 / 3.5	6	HQFN24 (4x4)	NN30297A(*)
Extended V <sub>in</sub> / V <sub>out</sub> range	4.5 / 28	0.75 / 5.5	3	HQFN24 (4x4)	NN30320A
	4.5 / 28	0.75 / 5.5	6	HQFN24 (4x4)	NN30321A
	4.5 / 30	0.75 / 5.5	10	HQFN40 (6x6)	NN30312A
Extended V <sub>in</sub> range, for secondary power rail (external 5V supply required)	4.75 / 24	0.75 / 3.6	8	HQFN24 (4x4)	NN30421A
	4.5 / 24	0.75 / 3.6	8	HQFN24 (4x4)	NN30331A
	4.5 / 24	0.75 / 3.6	10	HQFN24 (4x4)	NN30332A


Built-in safety: under voltage lock out, over voltage detection, under voltage detection, over current protection, short circuit protection, thermal shut down

**Integrated multi-channel synchronous step down DCDC and LDO**

Series / Type	Channels (buck /LDO)	V <sub>in</sub> min/max (V)	V <sub>out</sub> min / max (V)	I <sub>out</sub> max (A)	Package (mm <sup>2</sup> )	Part number
 Step down DCDC	(1 / -)	2.5/5.5	1.15/1.3/1.8/2.8	1.2	WLCSP (1.5x1.5)	AN30180A
	(1 / -)	2.5/5.5	1.2/1.35/1.85/3.3	1.2	WLCSP (1.5x1.5)	AN30180AA
	(2 / -)	2.9/5.5	1.2/1.8	0.8	HQFN24 (4x4)	AN30181A
	(2 / -)	2.9/5.5	1.0/1.8	0.8	HQFN24 (4x4)	AN30185A
Multi-channel DCDC/LDO	(1 / 4)	2.5/5.5	(DCDC) 0.8 to 2.4 (LDO) 1 to 3.3	(DCDC) 0.6 (LDO) 0.3	WLCSP (1.6x2.1)	AN30183A
	(2 / 6)	2.5/5.5			WLCSP (2.2x2.2)	AN30182A



Built-in safety: under voltage lock out, over current protection, short circuit protection, thermal shut down

**Step down DCDC converter for USB and car radio**

Series / Type	Output	V <sub>in</sub> min/max (V)	V <sub>out</sub> min / max (V)	I <sub>out</sub> max (A)	Package	Part number
 Baseline (* USB current sense)	2	5 / 25	1.2 / 0.88*V <sub>cc</sub>	Ext. FET	SSOP24	AN33012UA
	1	5 / 25	1.2 / 0.88*V <sub>cc</sub>	1.5	SSOP24	AN33013UA
	1	5 / 25	1.2 / 9	1.5	SSOP24	AN33014UA(*)
Extended V <sub>in</sub> range (* USB current sense)	1	5 / 39	1.2 / 0.88*V <sub>cc</sub>	1.5	SSOP24	AN33016UA
	1	5 / 39	1.2 / 9	2.1	HQFP48	AN33017UA(*)






Built-in safety: under voltage lock out, over voltage protection, over current protection, short circuit protection, thermal shut down

## Near field communication ICs and modules - Built-in FeRAM


Series / Type	V <sub>in</sub> min/max (V)	FeRAM	NFC forum	Safety	Digital I/Fs	Dimensions (mm)	Part number
 NFC ICs	1.8 / 3.6 or 4.5 / 5.5	4Kbit	Type 3	-	UART/sync serial	SSOP16 (5x6.4x1.3)	MN63Y1210A
	1.7 / 3.6	4Kbit	Type 3/4B	AES128	I2C (100kbps)	QFN16 (3.2x4.2x0.77)	MN63Y1208
	-	4Kbit	Type 3/4B	AES128	IRQ	SON8 (2x2x0.45)	MN63Y1212
	1.7 / 3.6	4Kbit	Type 3/4B	AES128	I2C (100kbps)		MN63Y1213
	1.7 / 3.6	8Kbit	Type 3/4A/4B	Password	I2C (400kbps)		MN63Y1214
1.7 / 3.6	8Kbit	Type 4A/4B	Password	I2C (400kbps)	MN63Y1217		
 NFC modules (including antenna)	3.3 ±5%	4Kbit	Type 3/4B	AES128	I2C (100kbps)	40x30	MN63Y3208N1
	-	4Kbit	Type 3/4B	AES128	IRQ	11.5x25	MN63Y3212N1
	-	4Kbit	Type 3/4B	AES128	-	Ø30 (round)	MN63Y3212N4
	1.7 / 3.6	4Kbit	Type 3/4B	AES128	I2C (100kbps)	9x30	MN63Y3213N1

Power supply (V<sub>in</sub>) is optional for use as NFC tag - energy is harvested from the magnetic coupling






## (Chip Size Package) Discrete semiconductors

Series / Type	V <sub>SS</sub> (V)	I <sub>S</sub> (A)	R <sub>SSON</sub> (mΩ)	Package	Part number
 MOS FET Dual N channel	12	11	3	CSP (1.77x3.54mm)	FCAB2126
	12	1.5	95	CSP (0.6x0.6mm)	FC4B2130
Series / Type	V <sub>DSS</sub> (V)	I <sub>D</sub> (A)	R <sub>DSON</sub> (mΩ)	Package	Part number
 MOS FET N channel	60	3.3	62	CSP (1.2x1.2mm)	FK4B0613
	40	4.6	32	CSP (1.2x1.2mm)	FK4B0416
	12	3.1	17	CSP (1.0x1.0mm)	FK4B0112
 MOS FET P channel	-60	-1.8	197	CSP (1.2x1.2mm)	FJ4B0618
	-40	-3	74	CSP (1.2x1.2mm)	FJ4B0421
	-12	-2	40	CSP (1.0x1.0mm)	FJ4B0112
Series / Type	V <sub>R</sub> (V)	I <sub>F</sub> (A)	V <sub>F</sub> (V)	Package	Part number
 Schottky Barrier Diode	40	1	0.37	CSP (1.0x0.6mm)	DB4G429
	30	0.5	0.4	CSP (0.6x0.3mm)	DB2L324
	30	0.1	0.35	CSP (0.6x0.3mm)	DB2L335
Series / Type	V <sub>RWM</sub> (V)	ESD (V)	C <sub>t</sub> (pF)	Package	Part number
 Bi-directional TVS diode	5	+/-15kV	6	CSP (0.6x0.3mm)	DY2L5A0C

## (Power Mount Chip Size Package) Discrete semiconductors

Series / Type	V <sub>DSS</sub> (V)	I <sub>D</sub> (A)	R <sub>DSON</sub> (mΩ)	Package	Part number
 MOS FET N channel	24	6	20	PMCP (1.8x1.6mm)	FK3P0211
	-20	-7.5	16.5	PMCP (2.0x2.0mm)	FJ3P0210
	-12	-7.5	13.5	PMCP (2.0x2.0mm)	FJ3P0113

SMT LEDs in low profile packaging

Series / Type	Colour	Forward Voltage Vf(V) Typ.	Dominant Colour $\lambda_d$ (nm) / (Typ)	Io (mcd) Typ.	IF (mA)	Part number
 0603 1.6x0.8mm 0.2mm height	White	2.9	x 0.2635 / y 0.2645	60	5	LNJ037X8ARA
	RED	1.95	630	16	5	LNJ237W82RA
	YG	1.95	572	7.5	5	LNJ337W83RA
	Amber	1.95	590	25	5	LNJ437W84RA
	Orange	1.95	620	17.5	5	LNJ837W83RA
	Soft Orange	1.95	605	27.5	5	LNJ837W86RA
	Blue	2.9	472	17	5	LNJ937W8CRA
 0603 1.6x0.8mm 0.35mm height	White	2.9	x 0.2655 / y 0.2630	40	5	LNJ026X8ARA1
	White	2.95	x 0.2900 / y 0.3005	150	5	LNJ026X8BRA4
	YG	2.05	572	18	10	LNJ326W83RA1
	Amber	2.05	589	35	10	LNJ426W83RA1
	Pure Green	2.9	527	40	5	LNJ626W8CRA
	Orange	1.9	620	19	5	LNJ826W83RA
	Soft Orange	1.92	605	16.9	10	LNJ826W86RA
	Blue	2.9	470	11.5	5	LNJ926W8CRA
 0402 1.0x0.5mm 0.2mm height	White	2.9	x 0.247 / y 0.234	50	5	LNJ047X8ARA
	RED	1.95	630	16	5	LNJ247W82RA
	YG	1.95	572	13	5	LNJ347W83RA
	Amber	1.95	590	30	5	LNJ447W84RA1
	Pure Green	3.1	527	90	5	LNJ647W8CRA
	Orange	1.95	620	30	5	LNJ847W83RA
	Soft Orange	1.95	605	30	5	LNJ847W86RA
	Blue	2.9	472	18	5	LNJ947W8CRA
 Dual-colour LED 1.3x1.05mm 0.25mm height	Green	1.95	572	7.5	5	LNJ167W8RRA
	RED	1.95	628	15	5	LNJ167W87RA
	Pure Green	3.00	525	90	5	
	RED	1.95	628	15	5	LNJ167W85RA
	Blue	2.95	470	15	5	
	RED	1.95	628	15	5	
 Tri-colour LED 1.3x1.05mm 0.25mm height	Pure Green	3.00	525	90	5	LNJ757W86RA
	Blue	2.95	470	15	5	
	RED	1.90	628	30	5	

# INDUSTRIAL GRADE SD MEMORY CARD

---

- > Flexible customisation and technical support
- > Industrial Grade NAND Flash Memory
- > Power Failure Recovery minimises data damage
- > Double Bit Error Correction improves data retention
- > Static Wear Levelling to maximise the lifetime

As equipment and devices become increasingly advanced in performance and functions, SD Memory Cards require larger capacity and higher speed performance.

Since the release of its first SD Card in 2000, Panasonic has been a leader in its development. Today's Industrial SD Cards have achieved new levels of performance and reliability.

We also offer customisation services to meet specific user needs, and a technical support system including failure analysis, thus delivering flexible SD card solutions to all.



CUSTOMISATION, TECHNICAL SUPPORT  
AND HIGH RELIABILITY FOR INDUSTRIAL USE

## SLC FX Series – High grade series with superb rewriting durability suitable for long-term data storage

MADE IN JAPAN



Model	RP-SDFC51	RP-SDF02G	RP-SDF04G	RP-SDF08G	RP-SDF16G
Capacity*1	512MB	2GB	4GB	8GB	16GB
Flash Memory/Type	Single-Level Cell (SLC) NAND Flash Memory				
SD Physical Specification	Ver. 3.01 (No UHS-I Compliant)		Ver. 3.01 (UHS-I Compliant)		
Speed Class	Speed Class 6		Speed Class10, UHS Speed Class 1		
Operating Temperature	-40 to +85°C				
Controller	Designed by Panasonic				
Functions	Double Power Failure Recovery, Error Correction Code, Refresh Function, Static Wear Levelling, Intelligent Data Writing				
Write/Read Tests for All Memory Areas	Completed				
Size (HxWxD)	32.0x24.0x2.1mm				

\*1: SD Card utilises a portion of the memory for copy protection and other purposes. Therefore the usable capacity will be less.

## MLC JD Series – Industry's first\*1 bit-error-free SD card\*2 with RAID technology

MADE IN JAPAN



Model	RP-SDJD32	RP-SDJD64
Capacity*3	32GB	64GB
Flash Memory/Type	Multi-Level Cell (MLC) NAND Flash Memory	
SD Physical Specification	Ver. 4.10 (UHS-II Compliant)	
Speed Class	UHS Speed Class 1	Speed Class 10, UHS Speed Class 1
Operating Temperature	-25 to +85°C	
Controller	Designed by Panasonic	
Functions	RAID Technology, Power Failure Recovery, Error Correction Code, Refresh Function, Static Wear Levelling, Intelligent Data Writing	
Write/Read Tests for All Memory Areas	Completed	
Size (HxWxD)	32.0x24.0x2.1mm	

\*1 For Industrial SD Cards. As of April 1st, 2014.

\*2 All bit error correction cannot be guaranteed.

\*3 SD Card utilises a portion of the memory for copy protection and other purposes. Therefore the usable capacity will be less.



## MLC GD Series – Ideal for recording large-volume image data

MADE IN JAPAN



Model	RP-SDGD04	RP-SDGD08	RP-SDGD16	RP-SDGD32	RP-SDGD64
Capacity*1	4GB	8GB	16GB	32GB	64GB
Flash Memory/Type	Multi-Level Cell (MLC) NAND Flash Memory				
SD Physical Specification	Ver. 3.01 (UHS-I Compliant)				
Speed Class	Speed Class 10, UHS Speed Class 1				
Operating Temperature	-25 to +85°C				
Controller	Designed by Panasonic				
Functions	Power Failure Recovery, Error Correction Code, Refresh Function, Static Wear Levelling, Intelligent Data Writing				
Write/Read Tests for All Memory Areas	Completed				
Size (HxWxD)	32.0x24.0x2.1mm				

\*1: SD Card utilises a portion of the memory for copy protection and other purposes. Therefore the usable capacity will be less.

## MLC P Series – Basic series suitable for various industrial equipment

MADE IN JAPAN



Model	RP-SDPC04	RP-SDPC08	RP-SDPC16
Capacity*1	4GB	8GB	16GB
Flash Memory/Type	Multi-Level Cell (MLC) NAND Flash Memory		
SD Physical Specification	Ver. 3.01 (No UHS-I Compliant)		
Speed Class	Speed Class 4		
Operating Temperature	-40 to +85°C		
Controller	Designed by Panasonic		
Functions	Power Failure Recovery*2, Error Correction Code, Refresh Function, Static Wear Levelling, Intelligent Data Writing		
Write/Read Tests for All Memory Areas	Completed		
Size (HxWxD)	32.0x24.0x2.1mm		

\*1: SD Card utilises a portion of the memory for copy protection and other purposes. Therefore the usable capacity will be less.

\*2: Customisable.

## MLC KC Series – microSD series with power failure recovery suitable for embedded use

MADE IN JAPAN



Model	RP-SMKC04	RP-SMKC08	RP-SMKC16
Capacity*1	4GB	8GB	16GB
Flash Memory/Type	Multi-Level Cell (MLC) NAND Flash Memory		
SD Physical Specification	Ver. 3.01 (UHS-I Compliant)		
Speed Class	Speed Class 2 (No UHS Speed Class Compliant)		
Operating Temperature	-40 to +85°C		
Controller	Designed by Panasonic		
Functions	Double Power Failure Recovery, Error Correction Code, Refresh Function, Static Wear Levelling, Intelligent Data Writing		
Write/Read Tests for All Memory Areas	Completed		
Size (HxWxD)	15.0x11.0x1.1mm		

\*1: SD Card utilises a portion of the memory for copy protection and other purposes. Therefore the usable capacity will be less.

## FEATURES

### > Temperature Resistance

Operation is assured even under harsh temperature conditions

### > Electrostatic Resistance

IEC 61000-4-2 compliance: Clears Electrostatic Discharge Immunity Tests of 150pF energy storage capacitance, 15kV aerial discharge and 330Ω discharge resistance

### > Impact Resistance

Bending load resistance: 20N (Newton) min., (SD standard: 10N)

Twisting torque resistance: 0.3N~m (Newton meter) min.

(SD standard: 0.15N~m) – for a full size SD card only

### > Magnetic Resistance

Operable after being set onto a 1,000-gauss DC magnetic field for approx. 1 minute

### > X-Ray Resistance

ISO 7816-1 compliance: Operable after 0.1Gy (gray) of X-ray irradiation

### > Water Resistance

JIS IPX7 compliance: Operable after submerging the product in water (tap water, 1m depth) for 30 minutes – microSD only

### > Durability against Insertion / Removal

Tested for 10,000 cycles of card insertion/removal using a card reader

### > Built-in Fuse

The internal card fuse protects against excess current and abnormal heating

## GUIDELINES AND CAUTIONS FOR USING THE PRODUCT TECHNICAL INFORMATION AND THE PRODUCTS DISPLAYED ON THIS MATERIAL

- > The products described on this material were designed and manufactured for standard applications such as general electronics devices, office equipment, data and communications equipment, measuring instruments, household appliances and audio-video equipment. For special applications in which quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or cause threat of personal injury (such as for aircraft and aerospace equipment, traffic and transport equipment, combustion equipment, medical equipment, accident prevention and anti-theft devices, and safety equipment), please use only after your company has sufficiently tested the suitability of our products for that application.
- > When using our products in equipment that requires a high degree of reliability, regardless of the application, it is recommend that you use protection circuits and redundancy circuits for equipment safety and test for safety.
- > The products and product specifications described on this material are subjected to change for improvement without prior notice. Therefore, be sure to request and confirm in advance the most current specifications, which explain the specifications in details, before the final stage of your design, purchasing or use for any application.
- > The technical information on this material provides examples of the typical operations and application circuits. It is not intended to guarantee the non-infringement of or grant license for intellectual property rights of this company or any third parts.
- > Permissions must be obtained from the Japanese government if products, product specifications and technical information on this material that are subject to the „Foreign Exchange and Foreign Trade Law“ are to be exported or taken out of Japan.
- > The information contained on this material may not be reprinted or reproduced whether wholly or in part, without the prior written permission of Panasonic Automotive & Industrial Systems Europe GmbH.

Design and specifications are each subject to change without notice. Ask the factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## ABOUT PAISEU

Panasonic Automotive & Industrial Systems Europe (PAISEU) is a company that provides unparalleled expertise to leading car manufacturers, industrial customers and OEMs. It researches, develops, manufactures and supplies key electronic components, devices and modules up to complete solutions across a broad range of industries; and provides production equipment which builds the manufacturing lines of global corporations. Globally, Panasonic's Automotive and Industrial Systems company is responsible for over one third of Panasonic's overall revenue.

## CONTACTS

### Headquarter Europe

Panasonic Automotive & Industrial Systems  
Europe GmbH  
Robert-Bosch-Str. 27-29  
63225 Langen  
Germany

### United Kingdom/Ireland

Panasonic Automotive & Industrial Systems  
Europe GmbH  
Willoughby Road, Bracknell  
Berkshire RG12 8FP  
United Kingdom  
Phone: +44-1344-862-444  
Fax: +44-1344-476-575

### Italy

Panasonic Italia Branch of Panasonic Marketing  
Europe GmbH  
Viale Dell'Innovazione 3  
20126 Milan  
Italy  
Phone: +39-02-67881  
Fax: +39-02-6788-207

### Spain

Panasonic Automotive & Industrial Systems  
Europe GmbH  
Sucursal en Espana  
Parque Empresarial @ Sant Cugat  
Via Augusta 15\_25 Edificio B2 Planta 4 Oficina 17  
08174 Sant Cugat del Vales, Barcelona  
Spain  
Phone: +34-93-504-3010  
Fax: +34-93-675-5892

### Finland

Panasonic Automotive & Industrial Systems  
Europe GmbH  
Urho Kekkosen Katu 7B  
00100 Helsinki  
Finland  
Phone: +358-9-6898-4150  
Fax: +358-9-6898-4151

### France

Panasonic Automotive & Industrial Systems  
Europe GmbH  
8/10 Rue des petits Ruisseaux  
91370 Verrieres-Le-Buisson  
France  
Phone: +33-1-60-13-57-00  
Fax: +33-1-60-13-57-72

### Germany

(for all other European Countries)

Panasonic Automotive & Industrial Systems  
Europe GmbH  
Hans-Pinsel-Str. 2  
85540 Haar  
Germany  
Phone: +49-89-46-159-0

Panasonic Automotive & Industrial Systems  
Europe GmbH  
Winsbergring 15  
22525 Hamburg  
Germany  
Phone: +49-40-85386-370  
Fax: +49-40-85386-101

### Email and Website for all European countries:

info.ais@eu.panasonic.com  
<http://eu.industrial.panasonic.com>



For more details please contact:

# Panasonic®

Panasonic is a registered trademark  
of Panasonic Corporation.  
Printed in Germany, February 2015  
© Panasonic Corporation